



[Click Here to Request a Large Quantity Quote](#)

[AC-to-DC Regulated & Unregulated Table-Top Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2289159	Globtek	GT21089-1005-T3	5	2	10	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$7.95
196218	Globtek	TR9CA2000C12CP-Y(R)	5	2	10	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$16.95
2179577	Delta Electronics	ADP-12GB-2.5	5	2.5	12	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL	\$4.49
196270	Jameco Reliapro	PSU25A-13-R	5	2.5	25	INCLUDED	100 to 240	47 to 63	DIN Male	4-pin mini DIN	N/A	UL/CUL/CE	\$27.95
2230740	Jameco Reliapro	GPSN25A-13	5	2.5	30	INCLUDED	100 to 240	50 to 60	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CE	\$34.95
2235760	Globtek	GT-21089-1305	5	2.6	13	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CCC/CE	\$7.95
2227815	Globtek	TR9CA2000LLP-Y-D	5	2.6	13	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CCC/CE	\$7.95
2256982	MEAN WELL	GST18A05-P1J	5	3	15	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
1940387	MEAN WELL	GS18A05-P1J	5	3	15	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$11.95
2270887	Arndt	SQ15W5P-10	5	3	15	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL	\$6.95
2292423	Globtek	GT-41062-1805-T3	5	3.4	17	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CE/CCC	\$8.49
2202870	Arndt	EADP-20NB	5	4	20	INCLUDED	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CEC	\$6.95
2203848	Arndt	G32DD-050400-A	5	4	20	INCLUDED	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive		\$6.95
2203821	Arndt	AD6550LF	5	4	20	INCLUDED	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CECV	\$6.49
2257168	MEAN WELL	GST25A05-P1J	5	4	20	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
1940571	MEAN WELL	GS25A05-P1J	5	4	20	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2203830	Arndt	HK-AD-050U400-DH	5	4	20	NOT INCLUDED, RECOMMEND 2271583	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/FCC	\$4.95
2229511	Ault	SC200	5	4	32	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	DIN Male	5-pin DIN	N/A	UL/CSA/TUV/CE	\$15.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2250951	MEAN WELL	GP50A13D-R1B	5	4	50	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	DIN Male	5-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$41.80
2227807	Sceptre Power	PS-5050APL05	5	5	25	INCLUDED	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$12.95
2224278	MEAN WELL	GST40A05-P1J	5	5	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40
2224059	Sparkle Power	AD025DGAA1-J25	5	5	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$10.95
2234249	Arndt	FY0506000	5	6	30	INCLUDED	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC	\$8.49
2224358	MEAN WELL	GST60A05-P1J	5	6	30	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
2179606	Globtek	TR9CB2500LCP-Y-MED	6	2.5	15	NOT INCLUDED, RECOMMEND 2271759	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$14.95
2144956	Jameco Reliapro	GQ65-060330-E1	6	3.3	19.8	NOT INCLUDED, RECOMMEND 1951123	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/TUV/CE	\$9.49
2257176	MEAN WELL	GST25A07-P1J	7.5	2.93	22	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2231435	Arndt	094-0224-000	9	1.1	10	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm right angle	Center Positive	UL/CUL/TUV/CE/CCC	\$5.49

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2257002	MEAN WELL	GST18A09-P1J	9	2	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2257184	MEAN WELL	GST25A09-P1J	9	2.55	23	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
2257272	MEAN WELL	GST25B09-P1J	9	2.55	23	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
2224294	MEAN WELL	GST40A09-P1J	9	4.45	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2224374	MEAN WELL	GST60A09-P1J	9	6	54	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$14.95
2227823	Globtek	TR9CE1250LCP-Y	12	1.25	15	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CCC/CE	\$12.95
1954244	MEAN WELL	GS15A-3P1J	12	1.25	15	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm right angle	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$15.00
230683	Globtek	TR9CE1250LCP-Y-MED(R)	12	1.25	15	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$29.95
2289471	Jameco Reliapro	SA06-15S12R-U	12	1.25	15	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC	\$7.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2229491	Dee Van Enterprise Usa	DSA-0151D-12-2.1	12	1.5	18	NOT INCLUDED, RECOMMEND 2271575	100 to 125	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$7.49
2229482	Dee Van Enterprise Usa	DSA-0151D-12-2.5	12	1.5	18	NOT INCLUDED, RECOMMEND 2271575	100 to 125	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$8.95
2257011	MEAN WELL	GST18A12-P1J	12	1.5	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2270895	Phihong	PSA18U-120	12	1.5	18	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	DIN Male	4-Pin	N/A	UL/CUL/TUV/CE	\$8.95
2227381	Delta Electronics	EADP-24MB	12	2	24	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/CCC/CE	\$7.95
2188570	Arndt	MPGS-U0241202000D2	12	2	24	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/FCC	\$7.95
2257192	MEAN WELL	GST25A12-P1J	12	2.08	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2257281	MEAN WELL	GST25B12-P1J	12	2.08	25	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$9.90
2236754	Arndt	PS-2.1-12-3-DC-S1	12	3	36	INCLUDED	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/FCC	\$5.49

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2167445	Jameco Reliapro	K36V120300E2	12	3	36	NOT INCLUDED, RECOMMEND 2271583	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CSA/EN	\$12.95
2227401	Arndt	ADA017	12	3	36	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL	\$7.95
2230168	Arndt	EADP-36FB	12	3	36	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL	\$5.95
2257361	MEAN WELL	GST36B12-P1J	12	3	36	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$14.10
2224307	MEAN WELL	GST40A12-P1J	12	3.34	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40
2271239	Jameco Reliapro	G99-KPL060F-L253	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC/CCC	\$14.95
2208956	Jameco Reliapro	KPL-060F-VI	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$13.95
2236543	Lite-On Electronics	PA-1600-2A-LF	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$11.95
2272991	EDAC	EA1050A-120	12	5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CE/FCC/CCC	\$12.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2224382	MEAN WELL	GST60A12-P1J	12	5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
1952370	MEAN WELL	GS60A12-P1J	12	5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$14.95
2214230	MEAN WELL	GSM60B12-P1J	12	5	60	NOT INCLUDED, RECOMMEND 2271583	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$19.95
2223460	MEAN WELL	GST90A12-P1M	12	6.67	80	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2223582	MEAN WELL	GST120A12-R7B	12	8.5	102	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2226425	MEAN WELL	GST160A12-R7B	12	11.5	138	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
2226476	MEAN WELL	GST220A12-R7B	12	15	180	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
2226521	MEAN WELL	GST280A12-C6P	12	21	252	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
2257029	MEAN WELL	GST18A15-P1J	15	1.2	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2257117	MEAN WELL	GST18B15-P1J	15	1.2	18	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2257205	MEAN WELL	GST25A15-P1J	15	1.66	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
1940619	MEAN WELL	GS25A15-P1J	15	1.66	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2257299	MEAN WELL	GST25B15-P1J	15	1.66	25	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
2224315	MEAN WELL	GST40A15-P1J	15	2.67	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40
2271223	Jameco Reliapro	G99-KPL060H-L035	15	4	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC/CCC	\$13.95
2224391	MEAN WELL	GST60A15-P1J	15	4	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
1954295	MEAN WELL	GS60A15-P1J	15	4	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$14.95
2223478	MEAN WELL	GST90A15-P1M	15	6	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2223591	MEAN WELL	GST120A15-R7B	15	7	105	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2226433	MEAN WELL	GST160A15-R7B	15	9.6	144	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
2226484	MEAN WELL	GST220A15-R7B	15	13.4	201	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
2226530	MEAN WELL	GST280A15-C6P	15	15	255	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
2257037	MEAN WELL	GST18A18-P1J	18	1	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$9.49
2257213	MEAN WELL	GST25A18-P1J	18	1.38	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.49
2257301	MEAN WELL	GST25B18-P1J	18	1.38	25	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2292327	Arndt	PA1030-180T1A	18	1.67	30.06	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Stripped & Tinned	18 AWG SPT-1	N/A	UL/CUL/CE/FCC	\$8.95
2224323	MEAN WELL	GST40A18-P1J	18	2.22	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2224403	MEAN WELL	GST60A18-P1J	18	3.33	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
2223486	MEAN WELL	GST90A19-P1M	19	4.74	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2226548	MEAN WELL	GST280A20-C6P	20	20	260	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
2257045	MEAN WELL	GST18A24-P1J	24	0.75	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
1940635	MEAN WELL	GS25A24-P1JU	24	1.04	25	INCLUDED	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2257221	MEAN WELL	GST25A24-P1J	24	1.04	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2190346	MEAN WELL	GS25A24-P1J	24	1.04	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
1940547	MEAN WELL	GS25B24-P1J	24	1.04	25	NOT INCLUDED, RECOMMEND 2271583	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$9.49
2257379	MEAN WELL	GST36B24-P1J	24	1.5	36	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$14.10

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2224331	MEAN WELL	GST40A24-P1J	24	1.67	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40
230798	Globtek	TR9CI2100LCP-Y-MED-R	24	2.1	50.4	NOT INCLUDED, RECOMMEND 2271759	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$49.95
2229984	Jameco Reliapro	KPL-060M-2.1-VI	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$13.95
2229992	Jameco Reliapro	KPL-060M-2.5-VI	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$12.95
2224411	MEAN WELL	GST60A24-P1J	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
1952214	MEAN WELL	GS60A24-P1J	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$16.25
2271311	Jameco Reliapro	GM95-240375-F	24	3.75	90	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/CCC	\$20.95
2223494	MEAN WELL	GST90A24-P1M	24	3.75	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2271231	Jameco Reliapro	G99-ABU120M-N039	24	5	120	NOT INCLUDED, RECOMMEND 2271575	100 to 240	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC/CCC	\$31.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2223646	MEAN WELL	GST120A24-P1M	24	5	120	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2223611	MEAN WELL	GST120A24-R7B	24	5	120	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2226450	MEAN WELL	GST160A24-R7B	24	6.67	160	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
2099286	MEAN WELL	GS220A24-R7B	24	9.2	220	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CE/PFC	\$57.95
2226505	MEAN WELL	GST220A24-R7B	24	9.2	221	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
2226556	MEAN WELL	GST280A24-C6P	24	24	280.08	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
2257061	MEAN WELL	GST18A48-P1J	48	0.375	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2202562	Phihong	PSA18U-480	48	0.38	18	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/CE/CCC	\$3.95
2230820	Condor Power Supplies Inc.	CENB1050A4803F01	48	1.1	52.8	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Locking Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL	\$10.39

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2224420	MEAN WELL	GST60A48-P1J	48	1.25	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
2223507	MEAN WELL	GST90A48-P1M	48	1.87	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2271319	Jameco Reliapro	GM95-480200-F	48	2	96	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/CCC	\$19.95
2223620	MEAN WELL	GST120A48-R7B	48	2.5	120	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2226468	MEAN WELL	GST160A48-R7B	48	3.34	160	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
2226513	MEAN WELL	GST220A48-R7B	48	4.6	221	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
2226564	MEAN WELL	GST280A48-C6P	48	48	280.32	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
2273007	Li Tone Electronics (LTE)	65E-S7-1	56	1.16	65	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC	\$11.95