



[Click Here to Request a Large Quantity Quote](#)

[Switching Regulators](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage Range (VDC)	Price 1
2275911	MEAN WELL	DDR-15G-3.3	11.6W DIN Rail Type DC-DC Converter 9 to 36VDC Input 3v3 3500mA Output	3.3	3.5	11.6	DDR-15	13 to 36	\$17.95
2275871	MEAN WELL	DDR-15G-5	15W DIN Rail Type DC-DC Converter 9 to 36VDC Input 5V 3A Output	5	3	15	DDR-15	9 to 36	\$16.20
2276079	MEAN WELL	DDR-30L-5	30W DIN Rail Type DC-DC Converter 18-75VDC Input L-Series 5V@6A Output	5	6	30	DDR-30	18 to 75	\$21.60
2276047	MEAN WELL	DDR-30G-5	30W DIN Rail Type DC-DC Converter 9 to 36VDC Input 5V 6A Output	5	6	30	DDR-30	9 to 36	\$21.60
2276111	MEAN WELL	DDR-60G-5	54W DIN Rail Type DC-DC Converter 9-36VDC Input G-Series 5V@10.8A Output	5	10.8	54	DDR-60	9 to 36	\$29.95
2276143	MEAN WELL	DDR-60L-5	60W DIN Rail Type DC-DC Converter 18-75VDC Input L-Series 5V@12A Output	5	10.8	60	DDR-60	18 to 75	\$29.95
2275879	MEAN WELL	DDR-15G-12	15W DIN Rail Type DC-DC Converter 9 to 36VDC Input 12V 1250mA Output	12	1.25	15	DDR-15	10 to 36	\$16.20
2275927	MEAN WELL	DDR-15L-12	15W DIN Rail Type DC-DC Converter 18 to 75VDC Input 12V 1250mA Output	12	1.25	15	DDR-15	18 to 75	\$16.20
2276087	MEAN WELL	DDR-30L-12	30W DIN Rail Type DC-DC Converter 18-75VDC Input L-Series 12V @2.5A Output	12	2.5	30	DDR-30	18 to 75	\$21.60
2276055	MEAN WELL	DDR-30G-12	30W DIN Rail Type DC-DC Converter 9 to 36VDC Input 12V 2500mA Output	12	2.5	30	DDR-30	9 to 36	\$21.60
2276119	MEAN WELL	DDR-60G-12	60W DIN Rail Type DC-DC Converter 9-36VDC Input G-Series 12V@5A Output	12	5	60	DDR-60	9 to 36	\$29.95
2279367	MEAN WELL	DDR-120A-12	99W DIN Rail Type DC-DC Converter 9-18VDC Input 12V 8300mA Output	12	8.3	99.6	DDR-120	9 to 18	\$54.00
2279391	MEAN WELL	DDR-120B-12	120W DIN Rail Type DC-DC Converter 16.8 to 33.6VDC Input 12V 10A Output	12	10	120	DDR-120	16.8 to 33.6	\$59.49
2279423	MEAN WELL	DDR-120C-12	120W DIN Rail Type DC-DC Converter 33.6 to 67.2VDC Input 12V 10A Output	12	10	120	DDR-120	33.6 to 67.2	\$54.00
2276151	MEAN WELL	DDR-60L-12	60W DIN Rail Type DC-DC Converter 18-75VDC Input L-Series 12V@5A Output	12	10.8	60	DDR-60	18 to 75	\$27.00

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage Range (VDC)	Price 1
2309607	MEAN WELL	DDR-480B-12	DC-DC Converter DIN-Rail Type 12V 33.4A 400W 16.8 to 33.6Vin	12	33.4	400.8	DDR-480	16.8 to 33.6	\$181.00
2309631	MEAN WELL	DDR-480C-12	DC-DC Converter DIN-Rail Type 12V 33.4A 400W 33.6V to 67.2Vin	12	33.4	400.8	DDR-480	33.6 to 67.2	\$181.00
2309655	MEAN WELL	DDR-480D-12	DC-DC Converter DIN-Rail Type 12V 33.4A 400W 67.2V to 154Vin	12	33.4	400.8	DDR-480	67.2 to 154	\$181.00
2275887	MEAN WELL	DDR-15G-15	15W DIN Rail Type DC-DC Converter 9 to 36VDC Input 15V 1A Output	15	1	15	DDR-15	11 to 36	\$17.95
2276063	MEAN WELL	DDR-30G-15	30W DIN Rail Type DC-DC Converter 9-36VDC Input G-Series 15V@2A Output	15	2	30	DDR-30	9 to 36	\$23.95
2276127	MEAN WELL	DDR-60G-15	60W DIN Rail Type DC-DC Converter 9-36VDC Input G-Series 15V @4A Output	15	4	60	DDR-60	9 to 36	\$29.95
2275895	MEAN WELL	DDR-15G-24	15W DIN Rail Type DC-DC Converter 9 to 36VDC Input 24V 630mA Output	24	0.63	15	DDR-15	12 to 36	\$16.20
2275951	MEAN WELL	DDR-15L-24	15W DIN Rail Type DC-DC Converter 18 to 75VDC Input 24V 630mA Output	24	0.63	15	DDR-15	18 to 75	\$16.20
2276103	MEAN WELL	DDR-30L-24	30W DIN Rail Type DC-DC Converter 18-75VDC Input L-Series 24V@1.25A Output	24	1.25	30	DDR-30	18 to 75	\$21.60
2276071	MEAN WELL	DDR-30G-24	30W DIN Rail Type DC-DC Converter 9-36VDC Input G-Series 24V@1.25A Output	24	1.25	30	DDR-30	9 to 36	\$21.60
2276279	MEAN WELL	DDR-60L-24	60W DIN Rail Type DC-DC Converter 18-75VDC Input L-Series 24V@2.5A Output	24	2.5	60	DDR-60	18 to 75	\$27.00
2276135	MEAN WELL	DDR-60G-24	60W DIN Rail Type DC-DC Converter 9-36VDC Input G-Series 24V@2.5A Output	24	2.5	60	DDR-60	9 to 36	\$29.95
2279375	MEAN WELL	DDR-120A-24	100W DIN Rail Type DC-DC Converter 9-18VDC Input 24V 4200mA Output	24	4.2	100.8	DDR-120	9 to 18	\$54.49
2279399	MEAN WELL	DDR-120B-24	120W DIN Rail Type DC-DC Converter 16.8 to 33.6VDC Input 24V 5A Output	24	5	120	DDR-120	16.8 to 33.6	\$59.49
2279431	MEAN WELL	DDR-120C-24	120W DIN Rail Type DC-DC Converter 33.6 to 67.2VDC Input 24V 5A Output	24	5	120	DDR-120	33.6 to 67.2	\$54.00
2279471	MEAN WELL	DDR-240B-24	240W DIN Rail Type DC-DC Converter 16.8 to 33.6VDC Input 24V 10A Output	24	10	240	DDR-240	16.8 to 33.6	\$81.00
2279487	MEAN WELL	DDR-240C-24	240W DIN Rail Type DC-DC Converter 33.6 to 67.2VDC Input 24V 10A Output	24	10	240	DDR-240	33.6 to 67.2	\$89.95
2279503	MEAN WELL	DDR-240D-24	240W DIN Rail Type DC-DC Converter 67.2 to 154VDC Input 24V 10A Output	24	10	240	DDR-240	67.2 to 154	\$81.00

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage Range (VDC)	Price 1
2309615	MEAN WELL	DDR-480B-24	DC-DC Converter DIN-Rail Type 24V 20A 480W 16.8 to 33.6Vin	24	20	480	DDR-480	16.8 to 33.6	\$181.00
2309639	MEAN WELL	DDR-480C-24	DC-DC Converter DIN-Rail Type 24V 20A 480W 33.6V to 67.2Vin	24	20	480	DDR-480	33.6 to 67.2	\$181.00
2309663	MEAN WELL	DDR-480D-24	DC-DC Converter DIN-Rail Type 24V 20A 480W 67.2V to 154Vin	24	20	480	DDR-480	67.2 to 154	\$181.00
2279383	MEAN WELL	DDR-120A-48	100W DIN Rail Type DC-DC Converter 9-18VDC Input 48V 2100mA Output	48	2.1	100.8	DDR-120	9 to 18	\$59.49
2279407	MEAN WELL	DDR-120B-48	120W DIN Rail Type DC-DC Converter 16.8 to 33.6VDC Input 48V 2500mA Output	48	2.5	120	DDR-120	16.8 to 33.6	\$54.00
2279439	MEAN WELL	DDR-120C-48	120W DIN Rail Type DC-DC Converter 33.6 to 67.2VDC Input 48V 2500mA Output	48	2.5	120	DDR-120	33.6 to 67.2	\$54.00
2279463	MEAN WELL	DDR-120D-48	120W DIN Rail Type DC-DC Converter 67.2 to 154VDC Input 48V 2500mA Output	48	2.5	120	DDR-120	67.2 to 154	\$44.95
2279479	MEAN WELL	DDR-240B-48	240W DIN Rail Type DC-DC Converter 16.8 to 33.6VDC Input 48V 5A Output	48	5	240	DDR-240	16.8 to 33.6	\$81.00
2279495	MEAN WELL	DDR-240C-48	240W DIN Rail Type DC-DC Converter 33.6 to 67.2VDC Input 48V 5A Output	48	5	240	DDR-240	33.6 to 67.2	\$89.95
2279511	MEAN WELL	DDR-240D-48	240W DIN Rail Type DC-DC Converter 67.2 to 154VDC Input 48V 5A Output	48	5	240	DDR-240	67.2 to 154	\$81.00
2309623	MEAN WELL	DDR-480B-48	DC-DC Converter DIN-Rail Type 48V 10A 480W 16.8 to 33.6Vin	48	10	480	DDR-480	16.8 to 33.6	\$181.00
2309647	MEAN WELL	DDR-480C-48	DC-DC Converter DIN-Rail Type 48V 10A 480W 33.6V to 67.2Vin	48	10	480	DDR-480	33.6 to 67.2	\$181.00
2309671	MEAN WELL	DDR-480D-48	DC-DC Converter DIN-Rail Type 48V 10A 480W 67.2V to 154Vin	48	10	480	DDR-480	67.2 to 154	\$181.00