



[Click Here to Request a Large Quantity Quote](#)

[27.6 to 48 Volt DIN Rail Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Frequency	Size (W" x H" x D")	Input Voltage Range (VDC)	Input Voltage (VDC)	Low Power Source (LPS)	Maximum Input Current (A)	Price 1
2216770	MEAN WELL	DRC-60B	27.6	1.4	60	90 to 264	47 to 63	3.54 x 3.94 x 1.57				1.3	\$28.95
2220859	MEAN WELL	DRC-100B	27.6	3.5	96.6	90 to 264	47 to 63	3.54 x 3.94 x 2.17			No	1.8	\$41.95
2251233	MEAN WELL	HDR-15-48	48	0.32	15.4	85 to 264	47 to 63	3.54 x 2.15 x 0.69			Yes	0.5	\$11.60
2251284	MEAN WELL	HDR-30-48	48	0.75	36	85 to 264	47 to 63	3.54 x 2.15 x 1.38			Yes	0.88	\$14.30
1943431	MEAN WELL	MDR-40-48	48	0.83	39.8	85 to 264	47 to 63	3.54 x 3.94 x 1.57			No	1.1	\$18.10
2251330	MEAN WELL	HDR-60-48	48	1.25	60	85 to 264	47 to 63	3.54 x 2.15 x 2.07			Yes	1.2	\$19.40
1943473	MEAN WELL	MDR-60-48	48	1.25	60	85 to 264	47 to 63	3.54 x 3.94 x 1.57			No	1.8	\$19.40
221866	MEAN WELL	DR-75-48	48	1.6	76.8	85 to 264	47 to 63	4.93 x 3.94 x 2.19				1.6	\$34.95
2190338	MEAN WELL	SDR-75-48	48	1.6	76.8	88 to 264	47 to 63	4.93 x 4.02 x 1.26			No	1.4	\$33.40
2216665	MEAN WELL	EDR-75-48	48	1.6	76.8	90 to 264	47 to 63	4.93 x 4.02 x 1.26			No	1.45	\$22.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Frequency	Size (W" x H" x D")	Input Voltage Range (VDC)	Input Voltage (VDC)	Low Power Source (LPS)	Maximum Input Current (A)	Price 1
1943502	MEAN WELL	MDR-100-48	48	2	96	85 to 264	47 to 63	3.54 x 3.94 x 2.17			No	1.3	\$33.60
2264383	MEAN WELL	HDR-100-48N	48	2.1	100.8	85 to 264	47 to 63	2.76 x 3.54 x 2.15			No	3	\$27.70
2279383	MEAN WELL	DDR-120A-48	48	2.1	100.8				9 to 18	12		11.2	\$54.00
221904	MEAN WELL	DR-120-48	48	2.5	120	88 to 132 , 176 to 264	47 to 63	4.93 x 3.94 x 8.94			No	2.6	\$41.49
2107338	MEAN WELL	SDR-120-48	48	2.5	120	88 to 264	47 to 63	4.93 x 4.47 x 1.57			No	1.4	\$54.00
2218599	MEAN WELL	NDR-120-48	48	2.5	120	90 to 264	47 to 63	4.93 x 4.47 x 1.57			No	2.25	\$28.30
2218556	MEAN WELL	EDR-120-48	48	2.5	120	90 to 264	47 to 63	4.93 x 4.47 x 1.57			No	2.25	\$25.70
2279439	MEAN WELL	DDR-120C-48	48	2.5	120				33.6 to 67.2	48		2.8	\$54.00
2279407	MEAN WELL	DDR-120B-48	48	2.5	120				16.8 to 33.6	24		5.6	\$54.00
2284551	MEAN WELL	HDR-150-48	48	2.72	130.6	85 to 264	47 to 63	3.54 x 2.15 x 4.13				3	\$35.20
2145182	MEAN WELL	WDR-240-48	48	5	240	180 to 550	47 to 63	4.93 x 4.47 x 2.48				2	\$117.00
2282855	MEAN WELL	TDR-240-48	48	5	240	340 to 550	47 to 63	2.48 x 4.93 x 4.47				0.69	\$80.80
221883	MEAN WELL	DRP-240-48	48	5	240	85 to 264	47 to 63	4.93 x 3.94 x 4.94				2.8	\$66.95
2094936	MEAN WELL	SDR-240-48	48	5	240	88 to 264	47 to 63	4.93 x 4.47 x 2.48				2.6	\$90.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Frequency	Size (W" x H" x D")	Input Voltage Range (VDC)	Input Voltage (VDC)	Low Power Source (LPS)	Maximum Input Current (A)	Price 1
2225078	MEAN WELL	NDR-240-48	48	5	240	90 to 264	47 to 63	4.93 x 4.47 x 2.48				2.5	\$52.10
2279511	MEAN WELL	DDR-240D-48	48	5	240				67.2 to 154	110		2.5	\$81.00
2279479	MEAN WELL	DDR-240B-48	48	5	240				16.8 to 33.6	24		11.2	\$81.00
2253052	MEAN WELL	TDR-480-48	48	10	480	340 to 550	47 to 63	4.93 x 5.06 x 3.37				0.85	\$124.00
301306	MEAN WELL	DRP-480S-48	48	10	480	90 to 132 , 180 to 264	47 to 63	4.93 x 3.94 x 8.94				8	\$124.95
2107346	MEAN WELL	SDR-480-48	48	10	480	90 to 264	47 to 63	4.93 x 5.06 x 3.37				5	\$145.00
2225094	MEAN WELL	NDR-480-48	48	10	480	90 to 264	47 to 63	4.93 x 5.06 x 3.37				4.8	\$102.00
2108955	MEAN WELL	SDR-480P-48	48	10	480	90 to 264	47 to 63	4.93 x 5.06 x 3.37				5	\$137.00
2172164	MEAN WELL	SDR-960-48	48	20	960	180 to 264	47 to 63	4.93 x 5.91 x 4.33				6	\$243.00