



[Click Here to Request a Large Quantity Quote](#)

[Hardware - Washers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Thread Size	Outer Diameter (in.)	Price 1
<a href="#">2094725</a>	Jameco Valuepro	33062	Flat	#2	0.188	\$0.05
<a href="#">2288119</a>	Jameco Valuepro	149228	Flat	#4	0.276	\$0.25
<a href="#">106826</a>	Jameco Valuepro	0149228	Flat	#4	0.281	\$0.05
<a href="#">2290607</a>	Jameco Valuepro	#4FWZ	Flat	#4	0.284	\$0.11
<a href="#">106833</a>	Jameco Valuepro	960-6	Flat	#6	0.373	\$0.06
<a href="#">106842</a>	Jameco Valuepro	960-8-3	Flat	#8	0.375	\$0.06
<a href="#">2183381</a>	Switchcraft	P-2061	Flat	1/4-32	0.406	\$0.29
<a href="#">2159963</a>	Jameco Valuepro	P-1476-1	Flat	15/32"	0.468	\$0.39
<a href="#">2282543</a>	Jameco Valuepro	90183A206	Flat	3/32"	0.312	\$0.25
<a href="#">2183293</a>	Jameco Valuepro	3/8-32FW	Flat	3/8"	0.616	\$0.19
<a href="#">2182522</a>	Switchcraft	S1022-1	Flat	3/8"	0.625	\$0.29
<a href="#">2159971</a>	Arndt	AN960-616L	Flat	3/8"	0.625	\$0.19
<a href="#">2288671</a>	Jameco Valuepro	5/16FW	Flat	5/16"	0.334	\$0.25
<a href="#">2182792</a>	Jameco Valuepro	5/16-32FW	Flat	5/16-32	0.416	\$0.15
<a href="#">2186187</a>	Arndt	P3031	Flat	7/16-32	0.65	\$0.19
<a href="#">2183251</a>	Jameco Valuepro	M10FW	Flat	M10	0.586	\$0.15
<a href="#">2183306</a>	Jameco Valuepro	M12FW	Flat	M12	0.705	\$0.15
<a href="#">2183234</a>	Jameco Valuepro	M6FW	Flat	M6	0.393	\$0.15
<a href="#">2182637</a>	Jameco Valuepro	M7FW	Flat	M7	0.473	\$0.15
<a href="#">2182565</a>	Jameco Valuepro	M8FW	Flat	M8	0.316	\$0.15
<a href="#">2182717</a>	Jameco Valuepro	M9FW	Flat	M9	0.551	\$0.15
<a href="#">2094733</a>	Jameco Valuepro	2ITLW-R	Internal Tooth Lock	#2	0.2	\$0.10
<a href="#">106850</a>	Jameco Valuepro	4ITLW	Internal Tooth Lock	#4	0.258	\$0.03
<a href="#">106868</a>	Jameco Valuepro	33707	Internal Tooth Lock	#6	0.277	\$0.04
<a href="#">106877</a>	Jameco Valuepro	#81TLW	Internal Tooth Lock	#8	0.323	\$0.04
<a href="#">2203240</a>	Dialight	8101-0000-03201	Internal Tooth Lock	1.01"	1.39	\$0.39
<a href="#">2089803</a>	Amphenol	31-5653	Internal Tooth Lock	1/2"	0.625	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Thread Size	Outer Diameter (in.)	Price 1
527646	TE Connectivity	1-329632-2	Internal Tooth Lock	1/2"	0.625	\$0.35
578339	C&K	700303202	Internal Tooth Lock	1/4-40	0.402	\$0.19
2182531	C&K	465200202	Internal Tooth Lock	10/32	0.31	\$0.25
2230918	Dialight	8101-000-002201	Internal Tooth Lock	11/16"	0.955	\$0.39
2182557	C&K	700302202	Internal Tooth Lock	15/32"	0.593	\$0.29
2235102	Dialight	17/32ITW	Internal Tooth Lock	17/32"	0.7	\$0.29
2276847	Amphenol	3/4-ITLW	Internal Tooth Lock	3/4"	1.05	\$0.49
2159980	Jameco Valuepro	3/8-32HN	Internal Tooth Lock	3/8"	0.675	\$0.25
2185791	Jameco Valuepro	3/8"ITW	Internal Tooth Lock	3/8"	0.5	\$0.25
101531	Amphenol	000-5579-NA	Internal Tooth Lock	3/8"	0.5	\$0.19
2201527	Jameco Valuepro	LW-11001-R	Internal Tooth Lock	5/16"	0.428	\$0.25
2182741	Jameco Valuepro	M12ITW	Internal Tooth Lock	M12	0.629	\$0.25
2227161	Jameco Valuepro	M7ITW	Internal Tooth Lock	M7	0.47	\$0.17
2182493	C&K	757200201	Keyway "D"-Style	1/4-40 UNS	0.468	\$0.15
578347	C&K	700701201	Keyway "O"-Style	1/4-40 UNS	0.468	\$0.15
2182590	C&K	465101201	Keyway "O"-Style	10-48 UNS	0.468	\$0.25
578380	C&K	707200201-VP	Keyway "O"-Style	15/32-32 NS	0.718	\$0.35
2233861	Jameco Valuepro	M10KLCK	Keyway "O"-Style	3/8-32 NEF	0.56	\$0.25
2182750	Jameco Valuepro	M12KLW	Keyway "O"-Style	M12 x .75	0.724	\$0.29
1581572	Keystone Electronics	904	Lockwasher Terminal Lug	#6	0.312	\$0.19
2297207	Eaton	09010002H	Neoprene	1/2"	0.5	\$0.25
2297183	Eaton	9732	Neoprene	1/2"	0.5	\$0.69
106789	Jameco Valuepro	33602	Split Lock	#2	0.172	\$0.07
40977	Jameco Valuepro	#S4LW	Split Lock	#4	0.21	\$0.08
42463	Jameco Valuepro	#6LW	Split Lock	#6	0.24	\$0.08
51609	Jameco Valuepro	#8LW2	Split Lock	#8	0.29	\$0.09
2183411	Jameco Valuepro	M7LW	Split Lock	M7	0.408	\$0.19
2099745	Jameco Valuepro	TL#4	Terminal Lug	#4	0.23	\$0.19
2100208	Jameco Valuepro	TL-STUD4	Terminal Lug	#4	0.26	\$0.19