



[Click Here to Request a Large Quantity Quote](#)

[DIN Rail Power Supplies \(15V to 24V\)](#)

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | Input Voltage (VAC) | Input Frequency | Output Connector Type | Size (W" x H" x D") | Agency Approvals | Low Power Source (LPS) | PFC Function | Price 1 |
|-------------------------|--------------|---------------------|------------------------------|--------------------|--------------------------|---------------------|-----------------|-----------------------|---------------------|-------------------------|------------------------|--------------|---------|
| 2251217 | MEAN WELL | HDR-15-15 | 15 | 1 | 15 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 2.15 x 0.69 | UL/CUL/TUV/CB/CE/EN/EAC | Yes | No | \$11.60 |
| 1943342 | MEAN WELL | MDR-20-15 | 15 | 1.34 | 20 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 3.94 x 0.89 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$13.50 |
| 2251313 | MEAN WELL | HDR-60-15 | 15 | 4 | 60 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 2.15 x 2.07 | UL/CUL/TUV/CB/CE/EN/EAC | Yes | No | \$19.40 |
| 373238 | MEAN WELL | DR-60-15 | 15 | 4 | 60 | 88 to 264 | 47 to 63 | Screw Terminal | 3.66 x 2.2 x 3.07 | UL/CUL/TUV/CB/CE/EN | No | No | \$19.95 |
| 2264343 | MEAN WELL | HDR-100-15 | 15 | 6.13 | 92 | 85 to 264 | 47 to 63 | Screw Terminal | 2.76 x 3.54 x 2.15 | UL/CUL/TUV/CB/CE/EN/EAC | Yes | No | \$27.70 |
| 2264351 | MEAN WELL | HDR-100-15N | 15 | 6.5 | 97.5 | 85 to 264 | 47 to 63 | Screw Terminal | 2.76 x 3.54 x 2.15 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$27.70 |
| 2284535 | MEAN WELL | HDR-150-15 | 15 | 8.55 | 128.3 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 2.15 x 4.13 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$35.20 |
| 1952986 | MEAN WELL | MDR-10-24 | 24 | 0.42 | 10 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 3.94 x 0.89 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$11.60 |
| 2251225 | MEAN WELL | HDR-15-24 | 24 | 0.63 | 15.2 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 2.15 x 0.69 | UL/CUL/TUV/CB/CE/EN/EAC | Yes | No | \$11.60 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | Input Voltage (VAC) | Input Frequency | Output Connector Type | Size (W" x H" x D") | Agency Approvals | Low Power Source (LPS) | PFC Function | Price 1 |
|-------------------------|--------------|---------------------|------------------------------|--------------------|--------------------------|---------------------|-----------------|-----------------------|---------------------|------------------------------|------------------------|--------------|---------|
| 1943385 | MEAN WELL | MDR-20-24 | 24 | 1 | 24 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 3.94 x 0.89 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$13.50 |
| 2251276 | MEAN WELL | HDR-30-24 | 24 | 1.5 | 36 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 2.15 x 1.38 | UL/CUL/TUV/CB/CE/EN/EAC | Yes | No | \$14.30 |
| 373203 | MEAN WELL | DR-30-24 | 24 | 1.5 | 36 | 85 to 264 | 47 to 63 | Screw Terminal | 3.66 x 2.2 x 3.07 | UL/CUL/TUV/CB/CE/EN | No | No | \$17.49 |
| 1943422 | MEAN WELL | MDR-40-24 | 24 | 1.7 | 40.8 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 3.94 x 1.57 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$18.10 |
| 192681 | MEAN WELL | DR-4524 | 24 | 2 | 48 | 85 to 264 | 47 to 63 | Screw Terminal | 3.07 x 2.64 x 3.66 | UL/CUL/TUV/CB/CE/EN | No | No | \$21.95 |
| 2251321 | MEAN WELL | HDR-60-24 | 24 | 2.5 | 60 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 2.15 x 2.07 | UL/CUL/TUV/CB/CE/EN/EAC | Yes | No | \$19.40 |
| 1943465 | MEAN WELL | MDR-60-24 | 24 | 2.5 | 60 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 3.94 x 1.57 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$19.40 |
| 2216817 | MEAN WELL | DRA-60-24 | 24 | 2.5 | 60 | 90 to 264 | 47 to 63 | Screw Terminal | 3.54 x 3.94 x 1.57 | UL/CUL/TUV/CB/CE/EN | No | No | \$23.60 |
| 212282 | MEAN WELL | DR-75-24 | 24 | 3.2 | 75 | 85 to 264 | 47 to 63 | Screw Terminal | 4.93 x 3.94 x 2.19 | UL/CUL/TUV/CB/CE/EN | No | No | \$34.95 |
| 2190320 | MEAN WELL | SDR-75-24 | 24 | 3.2 | 76.8 | 88 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.02 x 1.26 | UL/CUL/TUV/CB/CE/EN/EAC/SEMI | No | No | \$33.40 |
| 2216657 | MEAN WELL | EDR-75-24 | 24 | 3.2 | 76.8 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.02 x 1.26 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$22.20 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | Input Voltage (VAC) | Input Frequency | Output Connector Type | Size (W" x H" x D") | Agency Approvals | Low Power Source (LPS) | PFC Function | Price 1 |
|-------------------------|-----------------|---------------------|------------------------------|--------------------|--------------------------|------------------------|-----------------|-----------------------|---------------------|------------------------------|------------------------|--------------|----------|
| 2271375 | Phoenix Contact | 2904371 | 24 | 3.75 | 90 | 264 to 575 | 50 to 60 | Screw Terminal | 2.17 x 3.54 x 3.31 | UL/CUL/CE | Yes | Yes | \$22.95 |
| 2264359 | MEAN WELL | HDR-100-24 | 24 | 3.83 | 92 | 85 to 264 | 47 to 63 | Screw Terminal | 2.76 x 3.54 x 2.15 | UL/CUL/TUV/CB/CE/EN/EAC | Yes | No | \$27.70 |
| 1943490 | MEAN WELL | MDR-100-24 | 24 | 4 | 90 | 85 to 264 | 47 to 63 | Screw Terminal | 3.54 x 3.94 x 2.17 | UL/CUL/TUV/CE/EN/EAC | No | Yes | \$33.60 |
| 2123055 | MEAN WELL | WDR-120-24 | 24 | 5 | 120 | 180 to 550 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 1.57 | UL/CUL/CB/CE/EN/EAC | No | No | \$60.80 |
| 212266 | MEAN WELL | DR-120-24 | 24 | 5 | 120 | 88 to 132 , 176 to 264 | 47 to 63 | Screw Terminal | 4.93 x 3.94 x 2.58 | UL/CUL/TUV/CB/CE/EN | No | No | \$42.95 |
| 2099374 | MEAN WELL | SDR-120-24 | 24 | 5 | 120 | 88 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 1.57 | UL/CUL/TUV/CB/CE/EN/EAC/SEMI | No | Yes | \$54.00 |
| 2218548 | MEAN WELL | EDR-120-24 | 24 | 5 | 120 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 1.57 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$25.70 |
| 2218581 | MEAN WELL | NDR-120-24 | 24 | 5 | 120 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 1.57 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$28.30 |
| 2218564 | MEAN WELL | EDR-150-24 | 24 | 5.2 | 150 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 1.57 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$26.80 |
| 2150096 | MEAN WELL | WDR-240-24 | 24 | 10 | 240 | 180 to 550 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 2.48 | UL/CB/CE/EN/EAC | No | Yes | \$117.00 |
| 2282847 | MEAN WELL | TDR-240-24 | 24 | 10 | 240 | 340 to 550 | 47 to 63 | Screw Terminal | 2.48 x 4.93 x 4.47 | UL/CUL/TUV/CE/EN/EAC | No | Yes | \$80.80 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | Input Voltage (VAC) | Input Frequency | Output Connector Type | Size (W" x H" x D") | Agency Approvals | Low Power Source (LPS) | PFC Function | Price 1 |
|-------------------------|--------------|---------------------|------------------------------|--------------------|--------------------------|---------------------------|-----------------|-----------------------|---------------------|------------------------------|------------------------|--------------|----------|
| 373123 | MEAN WELL | DRT-240-24 | 24 | 10 | 240 | 340 to 550 | 47 to 63 | Screw Terminal | 4.93 x 3.94 x 8.94 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$79.95 |
| 2081086 | MEAN WELL | SDR-240-24 | 24 | 10 | 240 | 88 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 2.48 | UL/CUL/TUV/CB/CE/EN/EAC/SEMI | No | Yes | \$90.80 |
| 2225060 | MEAN WELL | NDR-240-24 | 24 | 10 | 240 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 4.47 x 2.48 | UL/CUL/TUV/CB/CE/EN/EAC | No | Yes | \$52.10 |
| 252663 | MEAN WELL | DRP-480-24 | 24 | 20 | 480 | 180 to 264 | 47 to 63 | Screw Terminal | 4.93 x 3.94 x 8.94 | UL/CUL/TUV/CB/CE/EN/EAC | No | Yes | \$99.95 |
| 2127806 | MEAN WELL | WDR-480-24 | 24 | 20 | 480 | 180 to 550 | 47 to 63 | Screw Terminal | 4.93 x 5.06 x 3.37 | UL/CB/CE/EN/EAC | No | Yes | \$169.00 |
| 372577 | MEAN WELL | DRT-480-24 | 24 | 20 | 480 | 340 to 550 | 47 to 63 | Screw Terminal | 4.93 x 3.94 x 8.94 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$109.95 |
| 2253044 | MEAN WELL | TDR-480-24 | 24 | 20 | 480 | 340 to 550 | 47 to 63 | Screw Terminal | 4.93 x 5.06 x 3.37 | UL/CB/CE/EN/EAC | No | Yes | \$114.95 |
| 295938 | MEAN WELL | DRP-480S-24 | 24 | 20 | 480 | 90 to 132 , 180 to 264 | 47 to 63 | Screw Terminal | 4.93 x 3.94 x 8.94 | UL/CUL/TUV/CB/CE/EN/EAC | No | Yes | \$124.95 |
| 2225086 | MEAN WELL | NDR-480-24 | 24 | 20 | 480 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 5.06 x 3.37 | UL/CUL/TUV/CB/CE/EN/EAC | No | Yes | \$102.00 |
| 2094944 | MEAN WELL | SDR-480-24 | 24 | 20 | 480 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 5.06 x 3.37 | UL/CUL/TUV/CB/CE/EN/EAC/SEMI | No | Yes | \$145.00 |
| 2108947 | MEAN WELL | SDR-480P-24 | 24 | 20 | 480 | 90 to 264 | 47 to 63 | Screw Terminal | 4.93 x 5.06 x 3.37 | UL/CUL/TUV/CB/CE/EN/EAC/SEMI | No | Yes | \$145.00 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | Input Voltage (VAC) | Input Frequency | Output Connector Type | Size (W" x H" x D") | Agency Approvals | Low Power Source (LPS) | PFC Function | Price 1 |
|-------------------------|--------------|---------------------|------------------------------|--------------------|--------------------------|---------------------|-----------------|-----------------------|---------------------|-------------------------|------------------------|--------------|----------|
| 2172156 | MEAN WELL | SDR-960-24 | 24 | 40 | 960 | 180 to 264 | 47 to 63 | Screw Terminal | 4.93 x 5.91 x 4.33 | UL/CUL/TUV/CB/CE/EN/EAC | No | Yes | \$243.00 |
| 373131 | MEAN WELL | DRT-960-24 | 24 | 40 | 960 | 340 to 550 | 47 to 63 | Screw Terminal | 4.93 x 3.94 x 10.97 | UL/CUL/TUV/CB/CE/EN/EAC | No | No | \$227.00 |