



[Click Here to Request a Large Quantity Quote](#)

[5 to 13.8 Volt DIN Rail Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Frequency	Size (W" x H" x D")	Input Voltage Range (VDC)	Input Voltage (VDC)	Low Power Source (LPS)	Maximum Input Current (A)	Price 1
2103978	MEAN WELL	MDR-10-5	5	2	10	85 to 264	47 to 63	3.54 x 3.94 x 0.89			No	0.33	\$11.60
2251196	MEAN WELL	HDR-15-5	5	2.4	12	85 to 264	47 to 63	3.54 x 2.15 x 0.69			Yes	0.5	\$11.60
2101243	MEAN WELL	DR-15-5	5	2.4	12	85 to 264	47 to 63	3.66 x 2.2 x 0.98			No	0.88	\$11.95
2251241	MEAN WELL	HDR-30-5	5	3	15	85 to 264	47 to 63	3.54 x 2.15 x 1.38			Yes	0.88	\$14.30
1943300	MEAN WELL	MDR-20-5	5	3	15	85 to 264	47 to 63	3.54 x 3.94 x 0.89			No	0.55	\$13.50
2275871	MEAN WELL	DDR-15G-5	5	3	15				9 to 36	9 to 36		2.4	\$16.20
2275919	MEAN WELL	DDR-15L-5	5	3	15				18 to 75	18 to 75		2.4	\$16.20
212303	MEAN WELL	DR-4505	5	5	25	85 to 264	47 to 63	3.07 x 2.64 x 3.66			No	1.5	\$14.95
1943393	MEAN WELL	MDR-40-5	5	6	30	85 to 264	47 to 63	3.54 x 3.94 x 1.57			No	1.1	\$18.10
2276047	MEAN WELL	DDR-30G-5	5	6	30				9 to 36	9 to 36		4.8	\$21.60
2276079	MEAN WELL	DDR-30L-5	5	6	30				18 to 75	18 to 75		4.8	\$21.60
2251292	MEAN WELL	HDR-60-5	5	6.5	32.5	85 to 264	47 to 63	3.54 x 2.15 x 2.07			Yes	1.2	\$19.40

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Frequency	Size (W" x H" x D")	Input Voltage Range (VDC)	Input Voltage (VDC)	Low Power Source (LPS)	Maximum Input Current (A)	Price 1
1943449	MEAN WELL	MDR-60-5	5	10	50	85 to 264	47 to 63	3.54 x 3.94 x 1.57			No	1.8	\$19.40
1952978	MEAN WELL	MDR-10-12	12	0.84	10	85 to 264	47 to 63	3.54 x 3.94 x 0.89			No	0.33	\$11.60
2251209	MEAN WELL	HDR-15-12	12	1.25	15	85 to 264	47 to 63	3.54 x 2.15 x 0.69			Yes	0.5	\$11.60
2094952	MEAN WELL	DR-15-12	12	1.25	15	85 to 264	47 to 63	3.66 x 2.2 x .98			No	0.88	\$13.49
2275879	MEAN WELL	DDR-15G-12	12	1.25	15				10 to 36	9 to 36		1	\$16.20
2275927	MEAN WELL	DDR-15L-12	12	1.25	15				18 to 75	18 to 75		1	\$16.20
1943334	MEAN WELL	MDR-20-12	12	1.67	20	85 to 264	47 to 63	3.54 x 3.94 x 0.89			No	0.55	\$13.50
2251250	MEAN WELL	HDR-30-12	12	2	24	85 to 264	47 to 63	3.54 x 2.15 x 1.38			Yes	0.88	\$14.30
2276055	MEAN WELL	DDR-30G-12	12	2.5	30				9 to 36	9 to 36		2	\$21.60
2276087	MEAN WELL	DDR-30L-12	12	2.5	30				18 to 75	18 to 75		2	\$21.60
1943406	MEAN WELL	MDR-40-12	12	3.33	40	85 to 264	47 to 63	3.54 x 3.94 x 1.57			No	1.1	\$18.10
2216788	MEAN WELL	DRA-40-12	12	3.34	40	90 to 264	47 to 63	3.54 x 3.94 x 1.57			Yes	0.8	\$21.30
192699	MEAN WELL	DR-4512	12	3.5	42	85 to 264	47 to 63	3.07 x 2.64 x 3.66			No	1.5	\$21.95
2251305	MEAN WELL	HDR-60-12	12	4.5	54	85 to 264	47 to 63	3.54 x 2.15 x 2.07			Yes	1.2	\$19.40

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Frequency	Size (W" x H" x D")	Input Voltage Range (VDC)	Input Voltage (VDC)	Low Power Source (LPS)	Maximum Input Current (A)	Price 1
1943457	MEAN WELL	MDR-60-12	12	5	60	85 to 264	47 to 63	3.54 x 3.94 x 1.57			No	1.8	\$19.40
2216809	MEAN WELL	DRA-60-12	12	5	60	90 to 264	47 to 63	3.54 x 3.94 x 1.57			No	1.3	\$23.60
2276119	MEAN WELL	DDR-60G-12	12	5	60				9 to 36	9 to 36		4	\$27.00
2190311	MEAN WELL	SDR-75-12	12	6.3	75.6	88 to 264	47 to 63	4.93 x 4.02 x 1.26			No	1.4	\$33.40
2216649	MEAN WELL	EDR-75-12	12	6.3	75.6	90 to 264	47 to 63	4.93 x 4.02 x 1.26			No	1.45	\$22.20
212291	MEAN WELL	DR-75-12	12	6.3	76	85 to 264	47 to 63	4.93 x 3.94 x 2.19			No	1.6	\$34.95
2264327	MEAN WELL	HDR-100-12	12	7.1	85.2	85 to 264	47 to 63	2.76 x 3.54 x 2.15			Yes	3	\$27.70
2264335	MEAN WELL	HDR-100-12N	12	7.5	90	85 to 264	47 to 63	2.76 x 3.54 x 2.15			No	3	\$27.70
1943481	MEAN WELL	MDR-100-12	12	7.5	90	85 to 264	47 to 63	3.54 x 3.94 x 2.17			No	1.3	\$33.60
2279367	MEAN WELL	DDR-120A-12	12	8.3	99.6				9 to 18	12		11.2	\$54.00
2123047	MEAN WELL	WDR-120-12	12	10	120	180 to 550	47 to 63	4.93 x 4.47 x 1.57			No	1.2	\$60.80
212274	MEAN WELL	DR-120-12	12	10	120	88 to 132 , 176 to 264	47 to 63	4.93 x 3.94 x 2.58			No	2.6	\$41.49
2099366	MEAN WELL	SDR-120-12	12	10	120	88 to 264	47 to 63	4.93 x 4.47 x 1.57			No	1.4	\$54.00

