



[Click Here to Request a Large Quantity Quote](#)

[Alnico Round, Square and Rectangular Speakers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Impedance	Nominal Input Power (W)	Input Power (max) (W)	Output	Frequency Range	Magnet Size (Diameter x H) (inches)	Termination Method	Magnet Material	Price 1
2303015	Arndt Electronics	P-200	16 Ohm	0.5	0.5	90 dB	300 Hz to 5000 Hz	0.87 x 0.45	Solderable Lug	AlNiCo	\$1.95
2217828	Jameco Valuepro	HKS-16-0.5	16 Ohm	0.5	1	89 dB	500 Hz to 5000 Hz	1.25 x 0.24	Solderable Lug	AlNiCo	\$0.59
2236674	Jameco Valuepro	FEB30045	45 Ohm	0.5	1	90 dB	260 Hz to 5000 Hz	3 x 3 x 1	Solderable Lug	AlNiCo	\$1.35
88411	Jameco Valuepro	A0200C	8 Ohm	0.2	0.4	82 dB	430 Hz to 4500 Hz	0.5 x 0.4	Solderable Lug	AlNiCo	\$2.25
2146388	Jameco Valuepro	TR-057A-R	8 Ohm	0.25	0.5	84 dB	300 Hz to 14000 Hz	0.5 x 0.4	Solderable Lug	AlNiCo	\$2.75
2258793	Jameco Valuepro	S03O7F390	8 Ohm	0.5	1	80 dB	100 Hz to 1000 Hz	1.2 x 0.8	Solderable Lug	AlNiCo	\$1.25
2270943	Jameco Valuepro	A0202C	8 Ohm	0.5	1	88 dB	320 Hz to 5000 Hz	0.8 x 0.4	Wires with Conn.	AlNiCo	\$1.25
2224032	Zenith Electronics	49-1334-02	8 Ohm	7	7	85 dB	100 Hz to 18000 Hz	2.1 x 1.0	Solderable Lug	AlNiCo	\$2.95
2258806	Samsung Electronics	15294900	8 Ohm	10	10	82 dB	100 Hz to 10000 Hz	2.5 x 1.1	Solderable Lug	AlNiCo	\$2.95