



[Click Here to Request a Large Quantity Quote](#)

[Frequency Control-Crystals](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Package / Case	Frequency	Load Capacitance	Frequency Tolerance	Frequency Stability	Price 1
14584	Jameco Valuepro	CY32.76	AT39 Tunning Fork	32.768 KHz	10.5 pF	±50ppm	±50ppm	\$0.19
325244	Jameco Valuepro	JVP-325243-R	AT39 Tunning Fork	32.768 KHz	12.5 pF	±50ppm	±50ppm	\$0.19
2298551	Citizen Watch	CA-301 11.0592MHZ	Cylindrical Can	11.0592 MHz	18 pF	±30ppm	±30ppm	\$0.75
2299127	Jameco Valuepro	NB10-6044	Cylindrical Can	149.475 KHz	n/a	n/a	n/a	\$0.75
2298559	Citizen Watch	CA-301 9.600MHZ	Cylindrical Can	9.6 MHz	18 pF	±30ppm	±30ppm	\$0.75
2299071	Jameco Valuepro	SG51KT2172A	DIP-14	32 MHz	n/a	±100ppm	±100ppm	\$0.99
2299135	Jameco Valuepro	CX1VS-03-32.768K-30	DIP-2	32.768 KHz	2 pF	±30ppm	±30ppm	\$0.75
14349	Major Brands	CY3.6864	HC33/U	3.6864 MHz	13 pF	±50ppm	±50ppm	\$2.95
137875	Jameco Valuepro	CY11.05LP	HC49/S Low Profile	11.0592 MHz	Series	±50ppm	±50ppm	\$0.29
137891	Jameco Valuepro	CY16LP	HC49/S Low Profile	16 MHz	Series	±50ppm	±50ppm	\$0.29
2299119	Jameco Valuepro	M-TRON-80	HC49/S Low Profile	24 MHz	n/a	n/a	n/a	\$0.49
537799	Jameco Valuepro	XTAL-14.31818MHZ-HC49U	HC49/U	14.31818 MHz	Series	±50ppm	±50ppm	\$0.49
102613	Jameco Valuepro	CY1.8432	HC49/U (HC18/U)	1.8432 MHz	18 pF	±50ppm	±50ppm	\$0.65
14381	Jameco Valuepro	CY10	HC49/U (HC18/U)	10 MHz	Series	±50ppm	±50ppm	\$0.49
324110	Jameco Valuepro	TQR49U11M0592A3210	HC49/U (HC18/U)	11.0592 MHz	32 pF	±50ppm	±50ppm	\$0.39
2159630	Jameco Valuepro	12MOOHC49U	HC49/U (HC18/U)	12 MHz	20 pF	±50ppm	±50ppm	\$0.19
2299111	Jameco Valuepro	MP49-14.459	HC49/U (HC18/U)	14.459 MHz	7 pF	±30ppm	n/a	\$0.49
14453	Jameco Valuepro	CY16	HC49/U (HC18/U)	16 MHz	Series	±50ppm	±50ppm	\$0.29
2299087	Jameco Valuepro	MP49	HC49/U (HC18/U)	17.570 MHz	7 pF	±50ppm	±50ppm	\$0.49
14517	Jameco Valuepro	CY20	HC49/U (HC18/U)	20 MHz	Series	±50ppm	±50ppm	\$0.29
2299103	Jameco Valuepro	MTRON-28.63	HC49/U (HC18/U)	28.63636 MHz	n/a	n/a	n/a	\$0.49
14533	Jameco Valuepro	CY3.57	HC49/U (HC18/U)	3.579545 MHz	18 pF	±50ppm	±50ppm	\$0.49
14592	Jameco Valuepro	MP040/4000.000	HC49/U (HC18/U)	4 MHz	20 pF	±50ppm	±50ppm	\$0.49
2299095	Jameco Valuepro	SRX2065	HC49/U (HC18/U)	5.676 MHz	n/a	n/a	n/a	\$0.49
14681	FOX ELECTRONICS	1988	HC49/U (HC18/U)	6 MHz	18 pF	±50ppm	±50ppm	\$0.49
14728	Jameco Valuepro	CY8	HC49/U (HC18/U)	8 MHz	Series	±50ppm	±50ppm	\$0.49
324187	Jameco Valuepro	TQR49U14M7456A2010	HC49/UA	14.7456 MHz	20 pF	±50ppm	±50ppm	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Package / Case	Frequency	Load Capacitance	Frequency Tolerance	Frequency Stability	Price 1
324233	Jameco Valuepro	CY18.432	HC49/UA	18.432 MHz	20 pF	±50ppm	±50ppm	\$0.39
325198	Jameco Valuepro	TQR49S12M0000A2040	HC49/US Low Profile	12 MHz	20 pF	±50ppm	±50ppm	\$0.19
325139	Jameco Valuepro	TQR49S16M0000A2010	HC49/US Low Profile	16 MHz	20 pF	±50ppm	±50ppm	\$0.49
325068	Jameco Valuepro	TQR49S20M0000A2010-R	HC49/US Low Profile	20 MHz	20 pF	±50ppm	±50ppm	\$0.49
325024	Jameco Valuepro	TQR49S24M0000A2010	HC49/US Low Profile	24 MHz	20 pF	±50ppm	±50ppm	\$0.39
2281063	Jameco Valuepro	1L.5561.001.04	HC49/US Low Profile	3.579545 MHz	16 pF	±5ppm	±5ppm	\$0.39
324962	Jameco Valuepro	TQR49S4M00000A2010-R	HC49/US Low Profile	4 MHz	20 pF	±50ppm	±50ppm	\$0.49
324929	Jameco Valuepro	TQR49S5M0000A2010	HC49/US Low Profile	5 MHz	20 pF	±50ppm	±50ppm	\$0.49
2298511	FOX ELECTRONICS	FPX143	SMD	14.31818 MHz	n/a	±50ppm	±50ppm	\$1.49
2298535	Citizen Watch	SX1555 32.768KHZ	SMD	32.768 KHz	12.5 pF	±20ppm	±20ppm	\$0.25
2298527	Citizen Watch	ATSM-49	SMD	8 MHz	18 pF	±30ppm	±50ppm	\$0.25
2299159	Epson	MA506-10.MHZ	SOJ-4	10 MHz	18 pF	±30ppm	n/a	\$0.75
2298543	Citizen Watch	MC-206 32.7680KA	SOP-4	32.768 KHz	12.5 pF	±20ppm	±20ppm	\$0.49