



[Click Here to Request a Large Quantity Quote](#)

[24 to 30 Volt Enclosed Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
1919078	MEAN WELL	RS-15-24	24	0.625	85 to 264	47 to 63	Screw Terminal Block	2.5	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$7.80
323311	MEAN WELL	RS-25-24	24	1.1	88 to 264	47 to 63	Screw Terminal Block	3	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$9.70
2257491	MEAN WELL	LRS-35-24	24	1.5	85 to 264	47 to 63	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$10.50
323353	MEAN WELL	RS-35-24	24	1.5	88 to 264	47 to 63	Screw Terminal Block	3.9	3.2	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.70
123319	MEAN WELL	S-40-24	24	1.8	85 to 264	47 to 63	Screw Terminal Block	5.1	3.9	1.5	No	UL/CUL/TUV/CB/CE	\$16.95
2257563	MEAN WELL	LRS-50-24	24	2.2	85 to 264	47 to 63	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$11.20
323417	MEAN WELL	RS-50-24	24	2.2	88 to 264	47 to 63	Screw Terminal Block	5.1	3.8	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$14.30
2164771	MEAN WELL	EPS-65-24-C	24	2.71	90 to 264	47 to 63	JST B4P-VH	4.07	2.44	1.46	No	UL/CUL/TUV/CB/CE/EN/EAC	\$16.20
2257627	MEAN WELL	LRS-75-24	24	3.2	85 to 264	47 to 63	Screw Terminal Block	3.9	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$13.50
2101008	MEAN WELL	HRP-75-24	24	3.2	85 to 264	47 to 63	Screw Terminal Block	5.1	3.9	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$37.40
2196166	MEAN WELL	RSP-75-24	24	3.2	85 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
323620	MEAN WELL	RS-75-24	24	3.2	88 to 264	47 to 63	Screw Terminal Block	5.1	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	\$17.10
2249221	MEAN WELL	RPS-120-24-C	24	3.5	80 to 264	47 to 63	JST B4P-PH	4.07	2.44	1.57	No	UL/CUL/TUV/CB/CE/EN/EAC	\$23.90
2204517	MEAN WELL	RSP-100-24	24	4.2	85 to 264	47 to 63	Screw Terminal Block	7.05	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$34.80
2257694	MEAN WELL	LRS-100-24	24	4.5	85 to 264	47 to 63	Screw Terminal Block	5.08	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$15.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2122845	MEAN WELL	HRP-100-24	24	4.5	85 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$43.10
323732	MEAN WELL	RS-100-24	24	4.5	88 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	\$23.00
173404	MEAN WELL	SP-150-24	24	6.25	85 to 264	47 to 63	Screw Terminal Block	7	3.9	2	Yes	UL/CUL/TUV/CB/CE/EN	\$51.49
2189142	MEAN WELL	RSP-150-24	24	6.3	85 to 264	47 to 63	Screw Terminal Block	7.84	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$37.10
2226185	MEAN WELL	HEP-150-24A	24	6.3	90 to 305	47 to 63	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/CB/CE/EN/EAC	\$77.00
2257740	MEAN WELL	LRS-150-24	24	6.5	85 to 132, 170 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$18.60
2257803	MEAN WELL	LRS-150F-24	24	6.5	85 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$20.90
2101868	MEAN WELL	HRP-150-24	24	6.5	85 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$52.40
2094864	MEAN WELL	HRPG-150-24	24	6.5	85 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$60.20
323855	MEAN WELL	RS-150-24	24	6.5	88 to 132, 176 to 264	47 to 63	Screw Terminal Block	7.8	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$24.70
2226249	MEAN WELL	HEP-185-24A	24	7.8	90 to 305	47 to 63	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/CB/CE/EN/EAC	\$79.40
2122255	MEAN WELL	HRP-200-24	24	8.4	85 to 264	47 to 63	Screw Terminal Block	7.8	3.9	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$67.80
2204630	MEAN WELL	RSP-200-24	24	8.4	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
2266375	MEAN WELL	UHP-200-24	24	8.4	90 to 264	47 to 63	Screw Terminal Block	7.64	2.17	1.02	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$47.50
2219743	MEAN WELL	LRS-200-24	24	8.8	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$24.70
2101518	MEAN WELL	SP-240-24	24	10	88 to 264	47 to 63	Screw Terminal Block	7.5	3.7	2	Yes	UL/CUL/TUV/CB/CE/EN	\$58.95
2253247	MEAN WELL	RPS-400-24-C	24	10.5	80 to 264	47 to 63	Screw Terminal Block	5.12	3.41	1.69	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$73.59

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2122714	MEAN WELL	SPV-300-24	24	12.5	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	2	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$78.30
244752	MEAN WELL	SP-320-24	24	13	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	2	Yes	UL/CUL/TUV/CB/CE/EN	\$69.95
2204699	MEAN WELL	RSP-320-24	24	13.4	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$51.10
2102220	MEAN WELL	HRP-300-24	24	14	85 to 264	47 to 63	Screw Terminal Block	7.7	4.1	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$79.80
2219823	MEAN WELL	LRS-350-24	24	14.6	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$31.50
2146564	MEAN WELL	SE-350-24	24	14.6	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	2	No	UL/CUL	\$48.95
2266247	MEAN WELL	UHP-350-24	24	14.6	90 to 264	47 to 63	Screw Terminal Block	8.66	2.44	1.22	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$66.50
2122335	MEAN WELL	HRP-450-24	24	18.8	85 to 264	47 to 63	Screw Terminal Block	8.6	4.1	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$128.00
2101606	MEAN WELL	SE-450-24	24	18.8	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.9	4.9	2	No	UL/CUL/CB/CE/EAC/BSMI	\$58.50
2197994	MEAN WELL	RSP-500-24	24	21	85 to 264	47 to 63	Screw Terminal Block	9.06	5	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$92.95
374231	MEAN WELL	PSP-600-24	24	25	88 to 264	47 to 63	Screw Terminal Block	6.7	5	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$129.00
295902	MEAN WELL	SE-600-24	24	25	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	9.7	5	2.5	No	UL/CUL/CE/EAC	\$72.20
2100961	MEAN WELL	HRP-600-24	24	27	85 to 264	47 to 63	Screw Terminal Block	8.6	4.1	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$134.00
2284503	MEAN WELL	UHP-750-24	24	31.3	90 to 264	47 to 63	Screw Terminal Block	9.33	3.94	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$186.00
2172121	MEAN WELL	RSP-750-24	24	31.3	90 to 264	47 to 63	Screw Terminal Block	9.8	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$179.00
1585717	MEAN WELL	RSP-1000-24	24	40	90 to 264	47 to 63	Screw Terminal Block	11.6	5	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$230.00
2101569	MEAN WELL	SE-1000-24	24	41.7	90 to 132, 180 to 264	47 to 63	Lug Terminal Female	10.9	5	2.5	No	UL/CUL/EAC/BSMI	\$157.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2278367	MEAN WELL	PSPA-1000-24	24	42	90 to 264	47 to 63	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$186.00
2284471	MEAN WELL	UHP-1000-24	24	42	90 to 264	47 to 63	Screw Terminal Block	9.45	4.53	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$247.00
2299415	MEAN WELL	UHP-1500-24	24	62.5	90 to 264	47 to 63	Screw Terminal Block	11.4	5.51	1.61	Yes	UL/CUL/CB/CE/EN/EAC/DEKRA	\$380.00
694938	MEAN WELL	RSP-1500-24	24	63	90 to 264	47 to 63	Lug Terminal Female	10.9	5	3.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$359.00
2251399	MEAN WELL	RSP-1600-24	24	67	90 to 264	47 to 63	Lug Terminal Female	11.81	3.35	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$380.00
2152999	MEAN WELL	RSP-2000-24	24	80	90 to 264	47 to 63	Screw Terminal Block	11.6	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$409.00
2106714	MEAN WELL	RSP-2400-24	24	100	180 to 264	47 to 63	Lug Terminal Female	10.9	7	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$414.00
2299391	MEAN WELL	UHP-2500-24	24	104.2	90 to 264	47 to 63	Screw Terminal Block	12.2	5.51	2.36	Yes	UL/CUL/CB/CE/EN/EAC/DEKRA	\$561.00
2106749	MEAN WELL	RSP-3000-24	24	125	180 to 264	47 to 63	Lug Terminal Female	10.9	7	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$471.00
2196174	MEAN WELL	RSP-75-27	27	2.8	85 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
2189151	MEAN WELL	RSP-150-27	27	5.6	85 to 264	47 to 63	Screw Terminal Block	7.84	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$37.10
2204648	MEAN WELL	RSP-200-27	27	7.5	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
2204701	MEAN WELL	RSP-320-27	27	11.9	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$51.10
2198006	MEAN WELL	RSP-500-27	27	18.6	85 to 264	47 to 63	Screw Terminal Block	9.06	5	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$91.20
374257	MEAN WELL	PSP-600-27	27	22.2	88 to 264	47 to 63	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$129.00
295911	MEAN WELL	SE-600-27	27	22.2	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	9.7	5	2.5	No	UL/CUL/CE/EAC	\$66.95
2172130	MEAN WELL	RSP-750-27	27	27.8	90 to 264	47 to 63	Screw Terminal Block	9.8	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$179.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
1585709	MEAN WELL	RSP-1000-27	27	37	90 to 264	47 to 63	Screw Terminal Block	11.6	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$230.00
694946	MEAN WELL	RSP-1500-27	27	56	90 to 264	47 to 63	Lug Terminal Female	10.9	5	3.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$359.00
2102473	MEAN WELL	SP-240-30	30	8	88 to 264	47 to 63	Screw Terminal Block	7.5	3.7	2	Yes	UL/CUL/TUV/CB/CE/EN	\$59.95