



[Click Here to Request a Large Quantity Quote](#)

[5 to 9 Volt Enclosed Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
1919043	MEAN WELL	RS-15-5	5	3	85 to 264	47 to 63	Screw Terminal Block	2.5	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$7.80
2251081	MEAN WELL	MPM-20-5	5	4	80 to 264	47 to 440	PCB Pin	2.06	1.07	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
323282	MEAN WELL	RS-25-5	5	5	88 to 264	47 to 63	Screw Terminal Block	3.1	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$9.70
2257467	MEAN WELL	LRS-35-5	5	7	85 to 264	47 to 63	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$11.00
323329	MEAN WELL	RS-35-5	5	7	88 to 264	47 to 63	Screw Terminal Block	3.9	3.2	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.70
2202984	Fortron/Source	S53P10A	5	10	100 to 120, 200 to 240	47 to 63	DB Connector Female						\$6.49
2257539	MEAN WELL	LRS-50-5	5	10	85 to 264	47 to 63	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$12.40
323388	MEAN WELL	RS-50-5	5	10	88 to 264	47 to 63	Screw Terminal Block	3.9	3.8	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$14.30
323581	MEAN WELL	RS-75-5	5	12	88 to 264	47 to 63	Screw Terminal Block	5.1	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	\$17.10
2257598	MEAN WELL	LRS-75-5	5	14	85 to 264	47 to 63	Screw Terminal Block	3.9	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$15.20
2101278	MEAN WELL	HRP-75-5	5	15	85 to 264	47 to 63	Screw Terminal Block	5.1	3.9	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$37.40
2196115	MEAN WELL	RSP-75-5	5	15	85 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
323708	MEAN WELL	RS-100-5	5	16	88 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	\$23.00
2257660	MEAN WELL	LRS-100-5	5	18	85 to 264	47 to 63	Screw Terminal Block	5.08	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$17.10
2204461	MEAN WELL	RSP-100-5	5	20	85 to 264	47 to 63	Screw Terminal Block	7.05	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$34.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
194791	MEAN WELL	SP-100-5	5	20	88 to 264	47 to 63	Screw Terminal Block	7	3.9	1.8	Yes	UL/CUL/TUV/CB/CE	\$44.95
2257774	MEAN WELL	LRS-150F-5	5	22	85 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$23.20
323821	MEAN WELL	RS-150-5	5	26	88 to 132, 176 to 264	47 to 63	Screw Terminal Block	7.8	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$24.70
201912	MEAN WELL	SP-150-5	5	30	85 to 264	47 to 63	Screw Terminal Block	7	3.9	2	Yes	UL/CUL/TUV/CB/CE/EN	\$51.49
2189097	MEAN WELL	RSP-150-5	5	30	85 to 264	47 to 63	Screw Terminal Block	7.84	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$37.10
2173933	MEAN WELL	RSP-200-5	5	40	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
2219719	MEAN WELL	LRS-200-5	5	40	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$27.60
2266351	MEAN WELL	UHP-200-5	5	40	90 to 264	47 to 63	Screw Terminal Block	7.64	2.17	1.02	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$47.50
244735	MEAN WELL	SP-320-5	5	55	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	2	Yes	UL/CUL/TUV/CB/CE/EN	\$69.95
2172068	MEAN WELL	RSP-320-5	5	60	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$51.10
2219794	MEAN WELL	LRS-350-5	5	60	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$34.80
2197960	MEAN WELL	RSP-500-5	5	90	85 to 264	47 to 63	Screw Terminal Block	9.06	5	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$91.20
374002	MEAN WELL	SE-600-5	5	100	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	9.7	5	2.5	No	UL/CUL/CE/EAC	\$67.49
694903	MEAN WELL	RSP-1500-5	5	240	90 to 264	47 to 63	Lug Terminal Female	10.9	5	3.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$359.00
2104452	MEAN WELL	SE-1500-5	5	300	180 to 264	47 to 63	Lug Terminal Female	10.9	7	2.5	No	UL/CUL/CB/CE/EAC/BSMI	\$219.95
2173941	MEAN WELL	RSP-200-7.5	7.5	26.7	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
2172076	MEAN WELL	RSP-320-7.5	7.5	40	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$51.10

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
394215	MEAN WELL	SP-320-7.5	7.5	40	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	2	Yes	UL/CUL/TUV/CB/CE/EN	\$69.95