



[Click Here to Request a Large Quantity Quote](#)

[36 to 54 Volt Enclosed Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2257504	MEAN WELL	LRS-35-36	36	1	85 to 264	47 to 63	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$11.00
2257707	MEAN WELL	LRS-100-36	36	2.8	85 to 264	47 to 63	Screw Terminal Block	5.08	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$16.00
2204710	MEAN WELL	RSP-320-36	36	8.9	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$51.10
2102318	MEAN WELL	HRP-300-36	36	9	85 to 264	47 to 63	Screw Terminal Block	7.8	4.1	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$79.80
2219831	MEAN WELL	LRS-350-36	36	9.7	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$32.90
2122351	MEAN WELL	HRP-450-36	36	12.5	85 to 264	47 to 63	Screw Terminal Block	8.6	4.1	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$128.00
2104524	MEAN WELL	SE-600-36	36	16.6	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	9.7	5	2.5	No	UL/CUL/CE/EAC	\$67.49
2284511	MEAN WELL	UHP-750-36	36	20.9	90 to 264	47 to 63	Screw Terminal Block	9.33	3.94	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$186.00
2284479	MEAN WELL	UHP-1000-36	36	28	90 to 264	47 to 63	Screw Terminal Block	9.45	4.53	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$247.00
2251410	MEAN WELL	RSP-1600-36	36	44.5	90 to 264	47 to 63	Lug Terminal Female	11.81	3.35	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$380.00
2106693	MEAN WELL	RS-15-48	48	0.313	85 to 264	47 to 63	Screw Terminal Block	2.5	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$7.80
693206	MEAN WELL	RS-25-48	48	0.57	88 to 264	47 to 63	Screw Terminal Block	3.1	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$9.70
2257580	MEAN WELL	LRS-50-48	48	1.1	85 to 264	47 to 63	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$11.80
2257643	MEAN WELL	LRS-75-48	48	1.6	85 to 264	47 to 63	Screw Terminal Block	3.9	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$14.30

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
693265	MEAN WELL	RS-75-48	48	1.7	88 to 264	47 to 63	Screw Terminal Block	5.1	3.8	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	\$17.10
2204533	MEAN WELL	RSP-100-48	48	2.1	85 to 264	47 to 63	Screw Terminal Block	7.05	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$34.80
2122870	MEAN WELL	HRP-100-48	48	2.2	85 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$43.10
2257715	MEAN WELL	LRS-100-48	48	2.3	85 to 264	47 to 63	Screw Terminal Block	5.08	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$16.00
2189169	MEAN WELL	RSP-150-48	48	3.2	85 to 264	47 to 63	Screw Terminal Block	7.84	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$37.10
2226206	MEAN WELL	HEP-150-48A	48	3.2	90 to 305	47 to 63	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/CB/CE/EN/EAC	\$77.00
2257766	MEAN WELL	LRS-150-48	48	3.3	85 to 132, 170 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$19.80
2257820	MEAN WELL	LRS-150F-48	48	3.3	85 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$22.00
323863	MEAN WELL	RS-150-48	48	3.3	88 to 132, 176 to 264	47 to 63	Screw Terminal Block	7.8	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$24.70
2204664	MEAN WELL	RSP-200-48	48	4.2	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
2266391	MEAN WELL	UHP-200-48	48	4.2	90 to 264	47 to 63	Screw Terminal Block	7.64	2.17	1.02	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$47.50
2219760	MEAN WELL	LRS-200-48	48	4.4	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$26.20
2102481	MEAN WELL	SP-240-48	48	5	88 to 264	47 to 63	Screw Terminal Block	7.5	3.7	2	Yes	UL/CUL/TUV/CB/CE/EN	\$47.95
2204728	MEAN WELL	RSP-320-48	48	6.7	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$51.10
2102326	MEAN WELL	HRP-300-48	48	7	85 to 264	47 to 63	Screw Terminal Block	7.8	4.1	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$79.80
2219840	MEAN WELL	LRS-350-48	48	7.3	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$32.90
2105164	MEAN WELL	SE-450-48	48	9.4	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.9	4.9	2	No	UL/CUL/CB/CE/EAC/BSMI	\$58.50

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2198014	MEAN WELL	RSP-500-48	48	10.5	85 to 264	47 to 63	Screw Terminal Block	9.06	5	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$91.20
374249	MEAN WELL	PSP-600-48	48	12.5	88 to 264	47 to 63	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$129.00
295929	MEAN WELL	SE-600-48	48	12.5	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	9.7	5	2.5	No	UL/CUL/CE/EAC	\$72.20
2100970	MEAN WELL	HRP-600-48	48	13	85 to 264	47 to 63	Screw Terminal Block	8.6	4.1	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$134.00
2284519	MEAN WELL	UHP-750-48	48	15.7	90 to 264	47 to 63	Screw Terminal Block	9.33	3.94	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$186.00
2172148	MEAN WELL	RSP-750-48	48	15.7	90 to 264	47 to 63	Screw Terminal Block	9.8	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$179.00
2101577	MEAN WELL	SE-1000-48	48	20.8	90 to 132, 180 to 264	47 to 63	Lug Terminal Female	10.9	5	2.5	No	UL/CUL/EAC/BSMI	\$157.00
2278375	MEAN WELL	PSPA-1000-48	48	21	90 to 264	47 to 63	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$186.00
2284487	MEAN WELL	UHP-1000-48	48	21	90 to 264	47 to 63	Screw Terminal Block	9.45	4.53	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$247.00
1585725	MEAN WELL	RSP-1000-48	48	21	90 to 264	47 to 63	Screw Terminal Block	11.6	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$230.00
2103370	MEAN WELL	SE-1500-48	48	31.3	180 to 264	47 to 63	Lug Terminal Female	10.9	7	2.5	No	UL/CUL/CB/CE/EAC/BSMI	\$241.00
2299423	MEAN WELL	UHP-1500-48	48	31.5	90 to 264	47 to 63	Screw Terminal Block	11.4	5.51	1.61	Yes	UL/CUL/CB/CE/EN/EAC/DEKRA	\$380.00
694954	MEAN WELL	RSP-1500-48	48	32	90 to 264	47 to 63	Lug Terminal Female	10.9	5	3.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$359.00
2251428	MEAN WELL	RSP-1600-48	48	33.5	90 to 264	47 to 63	Lug Terminal Female	11.81	3.35	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$380.00
2153001	MEAN WELL	RSP-2000-48	48	42	90 to 264	47 to 63	Screw Terminal Block	11.6	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$409.00
2106722	MEAN WELL	RSP-2400-48	48	50	180 to 264	47 to 63	Lug Terminal Female	10.9	7	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$414.00
2299407	MEAN WELL	UHP-2500-48	48	52.1	90 to 264	47 to 63	Screw Terminal Block	12.2	5.51	2.36	Yes	UL/CUL/CB/CE/EN/EAC/DEKRA	\$561.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2108921	MEAN WELL	RSP-3000-48	48	62.5	180 to 264	47 to 63	Lug Terminal Female	10.9	7	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$471.00
2216737	MEAN WELL	RST-5000-48	48	105	196 to 305, 340 to 530	47 to 63	Lug Terminal Female	18.1	8.3	3.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$1,096.00