



[Click Here to Request a Large Quantity Quote](#)

[Enclosed Single Output Power Supplies \(15V to 20V\)](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
323302	MEAN WELL	RS-25-15	15	1.7	88 to 264	47 to 63	Screw Terminal Block	3	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$9.70
323345	MEAN WELL	RS-35-15	15	2.4	88 to 264	47 to 63	Screw Terminal Block	3.9	3.2	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.70
2257555	MEAN WELL	LRS-50-15	15	3.4	85 to 264	47 to 63	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$11.80
323409	MEAN WELL	RS-50-15	15	3.4	88 to 264	47 to 63	Screw Terminal Block	3.9	3.8	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$14.30
2257619	MEAN WELL	LRS-75-15	15	5	85 to 264	47 to 63	Screw Terminal Block	3.9	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$14.30
323602	MEAN WELL	RS-75-15	15	5	88 to 264	47 to 63	Screw Terminal Block	5.1	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	\$17.10
2257686	MEAN WELL	LRS-100-15	15	7	85 to 264	47 to 63	Screw Terminal Block	5.08	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$16.00
323724	MEAN WELL	RS-100-15	15	7	88 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	\$23.00
2257731	MEAN WELL	LRS-150-15	15	10	85 to 132, 170 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$19.80
2257791	MEAN WELL	LRS-150F-15	15	10	85 to 264	47 to 63	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$22.00
2102191	MEAN WELL	HRP-150-15	15	10	85 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$52.40
323847	MEAN WELL	RS-150-15	15	10	88 to 132, 176 to 264	47 to 63	Screw Terminal Block	7.8	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$24.70
2204681	MEAN WELL	RSP-320-15	15	21.4	88 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$51.10
2219815	MEAN WELL	LRS-350-15	15	22.2	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	\$32.90

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
374222	MEAN WELL	PSP-600-15	15	40	88 to 264	47 to 63	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$129.00
291522	MEAN WELL	SE-600-15	15	40	90 to 132, 180 to 264	47 to 63	Screw Terminal Block	9.7	5	2.5	No	UL/CUL/CE/EAC	\$72.95
2100953	MEAN WELL	HRP-600-15	15	43	85 to 264	47 to 63	Screw Terminal Block	8.6	4.1	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$134.00
2104073	MEAN WELL	SE-1500-15	15	100	180 to 264	47 to 63	Lug Terminal Female	10.9	7	2.5	No	UL/CUL/CB/CE/EAC/BSMI	\$255.00
694920	MEAN WELL	RSP-1500-15	15	100	90 to 264	47 to 63	Lug Terminal Female	10.9	5	3.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$359.00