



[Click Here to Request a Large Quantity Quote](#)

[12 to 13.8 Volt Enclosed Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
<a href="#">1919051</a>	MEAN WELL	RS-15-12	12	1.3	85 to 264	Screw Terminal Block	2.5	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.35	\$7.80
<a href="#">323300</a>	MEAN WELL	RS-25-12	12	2.1	88 to 264	Screw Terminal Block	3	2	1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.7	\$9.70
<a href="#">2257475</a>	MEAN WELL	LRS-35-12	12	3	85 to 264	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.7	\$11.00
<a href="#">323337</a>	MEAN WELL	RS-35-12	12	3	88 to 264	Screw Terminal Block	3.9	3.2	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC	0.8	\$12.70
<a href="#">2220998</a>	MEAN WELL	NPF-40-12	12	3.34	90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.6	\$23.90
<a href="#">2257547</a>	MEAN WELL	LRS-50-12	12	4.2	85 to 264	Screw Terminal Block	3.9	3.23	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.95	\$11.80
<a href="#">323396</a>	MEAN WELL	RS-50-12	12	4.2	88 to 264	Screw Terminal Block	3.9	3.8	1.4	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.3	\$14.30
<a href="#">2164754</a>	MEAN WELL	EPS-65-12-C	12	5.42	90 to 264	JST B4P-VH	4.07	2.44	1.46	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$15.99
<a href="#">2257601</a>	MEAN WELL	LRS-75-12	12	6	85 to 264	Screw Terminal Block	3.9	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.4	\$14.30
<a href="#">323599</a>	MEAN WELL	RS-75-12	12	6	88 to 264	Screw Terminal Block	5.1	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	2	\$17.10
<a href="#">2257678</a>	MEAN WELL	LRS-100-12	12	8.5	85 to 264	Screw Terminal Block	5.08	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.9	\$16.00
<a href="#">2204488</a>	MEAN WELL	RSP-100-12	12	8.5	85 to 264	Screw Terminal Block	7.05	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.1	\$34.80
<a href="#">323716</a>	MEAN WELL	RS-100-12	12	8.5	88 to 264	Screw Terminal Block	6.3	3.8	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC	2.5	\$23.00
<a href="#">2257723</a>	MEAN WELL	LRS-150-12	12	12.5	85 to 132, 170 to 264	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	2.8	\$19.80
<a href="#">2257782</a>	MEAN WELL	LRS-150F-12	12	12.5	85 to 264	Screw Terminal Block	6.26	3.82	1.18	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	2.8	\$22.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
<a href="#">173421</a>	MEAN WELL	SP-150-12	12	12.5	85 to 264	Screw Terminal Block	7	3.9	2	Yes	UL/CUL/TUV/CB/CE/EN	2.5	\$44.95
<a href="#">2189118</a>	MEAN WELL	RSP-150-12	12	12.5	85 to 264	Screw Terminal Block	7.84	3.9	1.18	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.6	\$38.95
<a href="#">323839</a>	MEAN WELL	RS-150-12	12	12.5	88 to 132, 176 to 264	Screw Terminal Block	7.8	3.9	1.5	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	3	\$24.70
<a href="#">2102182</a>	MEAN WELL	HRP-150-12	12	13	85 to 264	Screw Terminal Block	6.3	3.8	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	2.3	\$52.40
<a href="#">194774</a>	MEAN WELL	SP-200-12	12	16.7	85 to 264	Screw Terminal Block	7	3.9	2	Yes	UL/CUL/TUV/CB/CE/EN/CCC	3.5	\$58.95
<a href="#">2122239</a>	MEAN WELL	HRP-200-12	12	16.7	85 to 264	Screw Terminal Block	7.8	3.9	1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	2.2	\$67.80
<a href="#">2173950</a>	MEAN WELL	RSP-200-12	12	16.7	88 to 264	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	3.5	\$42.20
<a href="#">2266359</a>	MEAN WELL	UHP-200-12	12	16.7	90 to 264	Screw Terminal Block	7.64	2.17	1.02	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	2.2	\$47.50
<a href="#">2219727</a>	MEAN WELL	LRS-200-12	12	17	90 to 132, 180 to 264	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	4	\$26.20
<a href="#">2101497</a>	MEAN WELL	SP-240-12	12	20	88 to 264	Screw Terminal Block	7.5	3.7	2	Yes	UL/CUL/TUV/CB/CE/EN	3.6	\$44.95
<a href="#">244743</a>	MEAN WELL	SP-320-12	12	25	88 to 264	Screw Terminal Block	8.5	4.5	2	Yes	UL/CUL/TUV/CB/CE/EN	5	\$69.95
<a href="#">2172084</a>	MEAN WELL	RSP-320-12	12	26.7	88 to 264	Screw Terminal Block	8.5	4.5	1.2	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	2.7	\$51.10
<a href="#">2102203</a>	MEAN WELL	HRP-300-12	12	27	85 to 264	Screw Terminal Block	7.8	4.1	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	5	\$79.80
<a href="#">2219807</a>	MEAN WELL	LRS-350-12	12	29	90 to 132, 180 to 264	Screw Terminal Block	8.5	4.5	1.2	No	UL/CUL/CB/CE/EAC/BSMI	6.8	\$32.90
<a href="#">2149503</a>	MEAN WELL	SE-350-12	12	29	90 to 132, 180 to 264	Screw Terminal Block	8.5	4.5	2	No	UL/CUL	7	\$41.95
<a href="#">2266231</a>	MEAN WELL	UHP-350-12	12	29.2	90 to 264	Screw Terminal Block	8.66	2.44	1.22	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4	\$66.50
<a href="#">2122319</a>	MEAN WELL	HRP-450-12	12	37.5	85 to 264	Screw Terminal Block	8.6	4.1	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	5	\$128.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
<a href="#">2094928</a>	MEAN WELL	SE-450-12	12	37.5	90 to 132, 180 to 264	Screw Terminal Block	8.9	4.9	2	No	UL/CUL/CB/CE/EAC/BSMI	10	\$58.50
<a href="#">2218741</a>	MEAN WELL	HEP-600-12	12	40	90 to 264	Screw Terminal Block	11	5.7	1.9	Yes	UL/CUL/TUV/CB/CE/EN/EAC	7	\$228.00
<a href="#">2197978</a>	MEAN WELL	RSP-500-12	12	41.7	85 to 264	Screw Terminal Block	9.06	5	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	5.3	\$92.95
<a href="#">374214</a>	MEAN WELL	PSP-600-12	12	50	88 to 264	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC	6.8	\$129.00
<a href="#">374011</a>	MEAN WELL	SE-600-12	12	50	90 to 132, 180 to 264	Screw Terminal Block	9.7	5	2.5	No	UL/CUL/CE/EAC	12	\$72.20
<a href="#">2096755</a>	MEAN WELL	HRP-600-12	12	53	85 to 264	Screw Terminal Block	8.6	4.1	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	8.5	\$134.00
<a href="#">2284495</a>	MEAN WELL	UHP-750-12	12	60	90 to 264	Screw Terminal Block	9.33	3.94	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	7.5	\$186.00
<a href="#">1585670</a>	MEAN WELL	RSP-1000-12	12	60	90 to 264	Screw Terminal Block	11.6	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	12	\$230.00
<a href="#">2172105</a>	MEAN WELL	RSP-750-12	12	62.5	90 to 264	Screw Terminal Block	9.8	5	1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	8.2	\$179.00
<a href="#">2278351</a>	MEAN WELL	PSPA-1000-12	12	80	90 to 264	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC	8.5	\$186.00
<a href="#">2284191</a>	MEAN WELL	UHP-1000-12	12	80	90 to 264	Screw Terminal Block	9.45	4.53	1.61	Yes	UL/CUL/TUV/CB/CE/EN/EAC	10.1	\$247.00
<a href="#">2101542</a>	MEAN WELL	SE-1000-12	12	83.3	90 to 132, 180 to 264	Lug Terminal Female	10.9	5	2.5	No	UL/CUL/EAC/BSMI	17.5	\$157.00
<a href="#">2104065</a>	MEAN WELL	SE-1500-12	12	125	180 to 264	Lug Terminal Female	10.9	7	2.5	No	UL/CUL/CB/CE/EAC/BSMI	17.5	\$209.95
<a href="#">694911</a>	MEAN WELL	RSP-1500-12	12	125	90 to 264	Lug Terminal Female	10.9	5	3.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	17	\$359.00
<a href="#">2106731</a>	MEAN WELL	RSP-3000-12	12	200	180 to 264	Lug Terminal Female	10.9	7	2.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	20	\$471.00
<a href="#">2106079</a>	MEAN WELL	PSP-600-13.5	13.5	44.5	88 to 264	Screw Terminal Block	6.7	4.7	3.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC	6.8	\$129.00