



[Click Here to Request a Large Quantity Quote](#)

[Encapsulated Single Output Power Supplies \(Medical Rated\)](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2251081	MEAN WELL	MPM-20-5	5	4	80 to 264	47 to 440	PCB Pin	2.06	1.07	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
2266479	MEAN WELL	MPM-05-12	12	0.42	80 to 264	47 to 440	PCB Pin	1.8	1	0.85	No	UL/CUL/TUV/CB/CE/EN/EAC	\$8.20
2251090	MEAN WELL	MPM-20-12	12	1.8	80 to 264	47 to 440	PCB Pin	2.06	1.07	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
2250863	MEAN WELL	MPM-30-12	12	2.5	80 to 264	47 to 63	PCB Pin	2.73	1.53	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$17.50
2250994	MEAN WELL	MPM-30-15ST	15	2	80 to 264	47 to 63	Screw Terminal Block	2.73	1.53	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$19.40
2266495	MEAN WELL	MPM-05-24	24	0.23	80 to 264	47 to 440	PCB Pin	1.8	1	0.85	No	UL/CUL/TUV/CB/CE/EN/EAC	\$8.20
2251111	MEAN WELL	MPM-20-24	24	0.9	80 to 264	47 to 440	PCB Pin	2.06	1.07	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30