



[Click Here to Request a Large Quantity Quote](#)

Standard Output 3mm LEDs

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Brightness (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Mounting	Price 1	Price 10
333383	Jameco Valuepro	UT63B1-41-URC3	3mm, T-1	Blue	50	Diffused	54	3.8	30 mA	466 nm	5.3	0.1"	\$0.49	\$0.39
253631	Hewlett Packard	HLMP-1585	3mm, T-1	Green	8.5	Diffused	75	2.2	10 mA	565 nm	6.3	0.1"	\$0.25	\$0.15
333201	Jameco Valuepro	LG12340	3mm, T-1	Green	9.6	Diffused	112	2.6	30 mA	565 nm	4.1	0.1"	\$0.25	\$0.12
697629	Lite-On Electronics	LTL-4231	3mm, T-1	Green	12.6	Diffused	40	2.6	30 mA	569 nm	5.25	0.1"	\$0.25	\$0.09
2194152	Lite-On Electronics	LTL-4231NLDLR1	3mm, T-1	Green	12.6	Diffused	60	2.1	30 mA	565 nm	4.45	0.1"	\$0.25	\$0.10
211086	Lite-On Electronics	LTL-4231N-022	3mm, T-1	Green	12.6	Diffused	60	2.1	30 mA	565 nm	5.25	0.1"	\$0.25	\$0.15
697637	Lite-On Electronics	LTL-4231N	3mm, T-1	Green	12.6	Diffused	60	2.1	30 mA	572 nm	4.45	0.1"	\$0.25	\$0.079
34606	Jameco Valuepro	LSG2040	3mm, T-1	Green	15	Diffused	36	2.6	30 mA	560 nm	5.2	0.1"	\$0.25	\$0.15
2155233	Arndt	BVL-360G1D	3mm, T-1	Green	18	Diffused	55	2.3	30 mA	573 nm	4.5	0.1"	\$0.25	\$0.049
156930	Jameco Valuepro	UT0321-41-HE-R	3mm, T-1	Green	30	Diffused	60	2.6	30 mA	572 nm	5.1	0.1"	\$0.25	\$0.15
697645	Lite-On Electronics	LTL-4232N	3mm, T-1	Green	40	Non Diffused	45	2.6	30 mA	569 nm	5.2	0.1"	\$0.25	\$0.12
152785	Jameco Valuepro	UT0341R-41-R	3mm, T-1	Orange Red	15.5	Diffused	56	2.1	30 mA	635 nm	5.1	0.1"	\$0.25	\$0.12
2081932	Jameco Valuepro	BVL-300E5D	3mm, T-1	Orange Red	18	Diffused	45	2.1	20 mA	622 nm	5.3	0.1"	\$0.25	\$0.15
697590	Lite-On Electronics	LTL-4221N	3mm, T-1	Red	3.8	Diffused	60	2.6	30 mA	635 nm	5.1	4mm	\$0.25	\$0.07
2276823	Major Brands	MV57642	3mm, T-1	Red	4	Diffused	90	2	10 mA	635 nm	4.5	0.1"	\$0.25	\$0.19

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Brightness (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Mounting	Price 1	Price 10
94529	Jameco Valuepro	LH2040	3mm, T-1	Red	4.5	Diffused	36	2.6	15 mA	697 nm	5.2	0.1"	\$0.25	\$0.19
202471	Unity Opto Technology	MCDL-314ED	3mm, T-1	Red	9	Diffused	40	2.8	30 mA	640 nm	5.25	0.1"	\$0.25	\$0.12
2006713	Lite-On Electronics	LTL-16KE	3mm, T-1	Red	12.6	Diffused	60	2.1	20 mA	621 nm	5.2	0.1"	\$0.25	\$0.08
2186435	Lite-On Electronics	LTL-16KEE-002	3mm, T-1	Red	19	Non Diffused	45	2	30 mA	635 nm	5.2	0.1"	\$0.25	\$0.12
333851	Jameco Valuepro	UT6371-41-M1-R	3mm, T-1	Red	65	Diffused	60	2.2	30 mA	643 nm	4.3	0.1"	\$0.25	\$0.12
2197732	Ligitek	LSR2643-1	3mm, T-1	Red	120	Water Clear	40	2.1	30 mA	660 nm	4.3	0.1"	\$0.25	\$0.12
2194144	Lite-On Electronics	LTL-4231NLDLLC	3mm, T-1	Yellow	1.1	Diffused	60	1.9	20 mA	565 nm	4.3	0.1"	\$0.25	\$0.06
2298455	Stanley Electric	AY3932S	3mm, T-1	Yellow	12	Diffused	50	2.2	10 mA	588 nm	5.5	0.1"	\$0.49	\$0.39
2155241	Arndt	BVL-360Y1D	3mm, T-1	Yellow	14	Diffused	55	2.2	30 mA	590 nm	4.5	0.1"	\$0.25	\$0.12
2006705	Lite-On Electronics	LTL-1CHYE	3mm, T-1	Yellow	40	Diffused	45	2.1	10 mA	585 nm	5.2	0.1"	\$0.25	\$0.07
2133632	Arndt	LT0333N-41-UR91	3mm, T-1	Yellow	700	Water Clear	35	1.9	20 mA	591 nm	5.2	0.1"	\$0.25	\$0.05