



[Click Here to Request a Large Quantity Quote](#)

[Terminal Blocks-Barrier Terminal Blocks](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Description	No. of Positions	Maximum Current Rating (A)	Rated Voltage (V)	Wire Size	Top Termination	Bottom Termination	Mounting	Body Orientation	Price 1
2172682	Adam Technologies	TDA-02-V2	Dual Row Barrier Strip	2	10	300	18-12	Screw, M3.5	Open Bottom	Chassis, Panel	Straight	\$1.75
2272863	Jameco Valuepro	GGE-10-2P	Dual Row Barrier Strip	2	10	600	22-12	Screw, M3.5	Open Bottom w/ Flange	Chassis, Panel	Straight	\$0.59
230973	Cinch Connectors	2-140	Dual Row Barrier Strip	2	15	250	16	Screw, 6-32	Open Bottom w/ Flange	Panel Mount	Straight	\$2.25
231351	Cinch Connectors	2-141	Dual Row Barrier Strip	2	20	250	14	Screw, 6-32	Closed Bottom w/ Flange	Panel Mount	Straight	\$1.95
2272879	Jameco Valuepro	GGE-20-2P	Dual Row Barrier Strip	2	20	600	22-12	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$0.885
237083	On Shore Technology	41296.2	Dual Row Barrier Strip	2	20	600	22-14	DIN Rail	DIN Rail	Cable Mount	Straight	\$0.99
2293327	Molex	38760-0103	Dual Row Barrier Strip	3	20	300	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$2.25
208857	Jameco Valuepro	GGE-10-4P-R	Dual Row Barrier Strip	4	10	600	22-14	Screw, M3.5	Open Bottom	Chassis, Panel	Straight	\$1.39
230990	Cinch Connectors	4-140	Dual Row Barrier Strip	4	15	250	16	Screw, 6-32	Open Bottom w/ Flange	Panel Mount	Straight	\$2.49
659411	Molex	38770-0104	Dual Row Barrier Strip	4	15	250	22-12	Screw, 6-32	Closed Bottom w/ Flange	Panel Mount	Straight	\$2.75
2272887	Jameco Valuepro	GGE-20-4P	Dual Row Barrier Strip	4	20	600	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$1.25
2273047	Molex	5-140	Dual Row Barrier Strip	5	15	250	16	Screw, 6-32	Open Bottom w/ Flange	Chassis, Panel	Straight	\$2.49
208865	Jameco Valuepro	GGE-10-6P-R	Dual Row Barrier Strip	6	10	600	22-12	Screw, M3.5	Open Bottom	Chassis, Panel	Straight	\$1.75
2288543	Cinch Connectors	6-140-YNF	Dual Row Barrier Strip	6	15	250	16	Screw, 5-40	None	Through Hole	Straight	\$6.95
231010	Cinch Connectors	6-140	Dual Row Barrier Strip	6	15	250	16	Screw, 6-32	Open Bottom w/ Flange	Panel Mount	Straight	\$3.39

Jameco Part #	Manufacturer	Manufacturer Part #	Description	No. of Positions	Maximum Current Rating (A)	Rated Voltage (V)	Wire Size	Top Termination	Bottom Termination	Mounting	Body Orientation	Price 1
231394	Cinch Connectors	6-141	Dual Row Barrier Strip	6	20	250	14	Screw, 6-32	Closed Bottom w/ Flange	Panel Mount	Straight	\$3.75
207547	Jameco Valuepro	GGE-20-6P-R	Dual Row Barrier Strip	6	20	600	22-12	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$1.59
2272871	Jameco Valuepro	GGE-10-8P	Dual Row Barrier Strip	8	10	600	22-12	Screw, M3.5	Open Bottom w/ Flange	Chassis, Panel	Straight	\$1.95
231036	Cinch Connectors	8-140	Dual Row Barrier Strip	8	15	250	16	Screw, 6-32	Open Bottom w/ Flange	Panel Mount	Straight	\$4.25
659454	Molex	38770-0108	Dual Row Barrier Strip	8	15	250	22-12	Screw, 6-32	Closed Bottom w/ Flange	Panel Mount	Straight	\$3.49
2272903	Jameco Valuepro	GGE-20-8P	Dual Row Barrier Strip	8	20	600	22-12	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$2.29
440891	Cinch Connectors	8-142	Dual Row Barrier Strip	8	30	250	10	Screw, 6-32	Open Bottom w/ Flange	Chassis, Panel	Straight	\$8.49
208900	Jameco Valuepro	GGE-10-10P-R	Dual Row Barrier Strip	10	10	600	22-12	Screw, M3.5	Open Bottom	Chassis, Panel	Straight	\$2.75
231052	Cinch Connectors	10-140	Dual Row Barrier Strip	10	15	250	16	Screw, 6-32	Open Bottom w/ Flange	Panel Mount	Straight	\$4.95
2272847	Molex	38770-0110	Dual Row Barrier Strip	10	15	300	22-14	Screw, 6-32	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$3.95
231431	Cinch Connectors	10-141	Dual Row Barrier Strip	10	20	250	14	Screw, 6-32	Closed Bottom w/ Flange	Panel Mount	Straight	\$5.95
2272911	Jameco Valuepro	GGE-20-10P	Dual Row Barrier Strip	10	20	600	22-12	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$2.49
208882	Jameco Valuepro	GGE-10-12P-R	Dual Row Barrier Strip	12	10	600	22-12	Screw, M3.5	Open Bottom	Chassis, Panel	Straight	\$2.95
2272855	Molex	38770-0112	Dual Row Barrier Strip	12	15	300	22-14	Screw, 6-32	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$5.29
207572	Jameco Valuepro	GGE-20-12P-R	Dual Row Barrier Strip	12	20	600	22-12	Screw, M3.5	Open Bottom w/ Flange	Chassis, Panel	Straight	\$2.95
2281103	Jameco Valuepro	672RZ18CRES	Dual Row Barrier Strip	18	30	600	14-12	Screw, 8-32	Closed Bottom w/ Flange	Panel Mount	Straight	\$12.95
441228	Cinch Connectors	20-141	Dual Row Barrier Strip	20	20	250	14	Screw, 6-32	Open Bottom w/ Flange	Panel Mount	Straight	\$8.95
2278167	On Shore Technology	DB-95MNW-25	Dual Row Barrier Strip	25	20	300	22-12	Screw, 6-32	Open Bottom w/ Flange	Chassis, Panel	Straight	\$4.95

Jameco Part #	Manufacturer	Manufacturer Part #	Description	No. of Positions	Maximum Current Rating (A)	Rated Voltage (V)	Wire Size	Top Termination	Bottom Termination	Mounting	Body Orientation	Price 1
2259260	On Shore Technology	ES0800/12DSFB	Dual Row Eurostyle Barrier Strip	12	15	300	22-14	Screw, M2.5	None	Chassis, Panel	Straight	\$1.49
215011	Jameco Valuepro	PA7DS	Dual Row Eurostyle Barrier Strip	12	17.5	450	22-12	Screw, M2.6	None	Chassis, Panel	Straight	\$1.75
2120170	On Shore Technology	ES1000/12DS	Dual Row Eurostyle Barrier Strip	12	20	300	20-12	Screw, M3	None	Chassis, Panel	Straight	\$2.95
215029	Jameco Valuepro	PA9DS	Dual Row Eurostyle Barrier Strip	12	24	450	22-12	Screw, M3	None	Chassis, Panel	Straight	\$2.25
215037	Jameco Valuepro	PA12HDS	Dual Row Eurostyle Barrier Strip	12	35	450	22-12	Screw, M3.5	None	Chassis, Panel	Straight	\$2.95
2275335	Jameco Valuepro	HI-202-02PH-S-D40	Single Row Barrier Strip	2	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$0.89
2275231	Jameco Valuepro	HI-201-02PH-S-D40	Single Row Barrier Strip	2	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Through Hole	Straight	\$1.29
2275439	Jameco Valuepro	HI-201-02P	Single Row Barrier Strip	2	10	250	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	Straight	\$1.09
2272959	Eaton	A303102	Single Row Barrier Strip	2	30	600	22-12	Screw, 6-32	Closed Bottom w/ Flange	Through Hole	Straight	\$0.99
2275175	Jameco Valuepro	HI-200-03PH-S-D40	Single Row Barrier Strip	3	10	250	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$1.49
2275343	Jameco Valuepro	HI-202-03PH-S-D40	Single Row Barrier Strip	3	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$1.25
2275239	Jameco Valuepro	HI-201-03PH-S-D40	Single Row Barrier Strip	3	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Through Hole	Straight	\$1.39
2275287	Jameco Valuepro	HI-201-03P	Single Row Barrier Strip	3	10	250	22-14	Screw, M3.5	PC Pin, w/o Flange	Through Hole	Straight	\$1.29
2288535	Cinch Connectors	3-140	Single Row Barrier Strip	3	15	250	16	Screw, 5-40	PC Pin, Offset w/ Flange	Through Hole	Straight	\$2.25
2277015	Molex	38720-6303	Single Row Barrier Strip	3	15	300	22-14	Screw, 6-32	PC Pin, w/o Flange	Through Hole	Straight	\$1.95
2272927	Eaton	A102203	Single Row Barrier Strip	3	20	250	22-14	Screw, 6-32	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$0.89
2275183	Jameco Valuepro	HI-200-04PH-S-D40	Single Row Barrier Strip	4	10	250	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$1.59
2275351	Jameco Valuepro	HI-202-04PH-S-D40	Single Row Barrier Strip	4	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$1.79

Jameco Part #	Manufacturer	Manufacturer Part #	Description	No. of Positions	Maximum Current Rating (A)	Rated Voltage (V)	Wire Size	Top Termination	Bottom Termination	Mounting	Body Orientation	Price 1
2275247	Jameco Valuepro	HI-201-04PH-S-D40	Single Row Barrier Strip	4	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Through Hole	Straight	\$1.49
2275295	Jameco Valuepro	HI-201-04P	Single Row Barrier Strip	4	10	250	22-14	Screw, M3.5	PC Pin,w/o Flange	Through Hole	Straight	\$1.39
2272983	Eaton	A102204	Single Row Barrier Strip	4	20	250	22-14	Screw, 6-32	PC Pin, Offset, w/o Flange	Chassis, Panel	Straight	\$1.49
2272975	Eaton	A104204R26	Single Row Barrier Strip	4	20	250	22-14	Screw, 6-32	PC Pin, Offset,R/A, w/o Flange	Through Hole	Right Angle	\$1.95
2275191	Jameco Valuepro	HI-200-05PH-S-D40	Single Row Barrier Strip	5	10	250	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$1.79
2275359	Jameco Valuepro	HI-202-05PH-S-D40	Single Row Barrier Strip	5	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$1.99
2275255	Jameco Valuepro	HI-201-05PH-S-D40	Single Row Barrier Strip	5	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Through Hole	Straight	\$1.59
2275303	Jameco Valuepro	HI-201-05P	Single Row Barrier Strip	5	10	250	22-14	Screw, M3.5	PC Pin, w/o Flange	Through Hole	Straight	\$1.49
797849	Molex	38720-6305	Single Row Barrier Strip	5	15	300	14-22	Screw, 6-32	PC Pin, w/o Flange	Through Hole	Straight	\$2.49
2275199	Jameco Valuepro	HI-200-06PH-S-D40	Single Row Barrier Strip	6	10	250	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$1.95
2275367	Jameco Valuepro	HI-202-06PH-S-D40	Single Row Barrier Strip	6	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$2.09
2275263	Jameco Valuepro	HI-201-06PH-S-D40	Single Row Barrier Strip	6	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Through Hole	Straight	\$1.79
2275311	Jameco Valuepro	HI-201-06P	Single Row Barrier Strip	6	10	250	22-14	Screw, M3.5	PC Pin, w/o Flange	Through Hole	Straight	\$1.59
2288551	Cinch Connectors	6-142-YCNF	Single Row Barrier Strip	6	15	250	10	Screw, 8-32	PC Pin, Offset w/o Flange	Through Hole	Straight	\$5.95
2273055	Magnum	A20220604	Single Row Barrier Strip	6	30	300	22-12	Screw, 6-32	PC Pin, w/o Flange	Through Hole	Straight	\$2.49
2272967	Eaton	A382207	Single Row Barrier Strip	7	30	600	22-12	Screw, 6-32	PC Pin, w/o Flange	Through Hole	Straight	\$2.95
2275207	Jameco Valuepro	HI-200-08PH-S-D40	Single Row Barrier Strip	8	10	250	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$2.09
2275383	Jameco Valuepro	HI-202-08PH-S-D40	Single Row Barrier Strip	8	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$2.25

Jameco Part #	Manufacturer	Manufacturer Part #	Description	No. of Positions	Maximum Current Rating (A)	Rated Voltage (V)	Wire Size	Top Termination	Bottom Termination	Mounting	Body Orientation	Price 1
2275271	Jameco Valuepro	HI-201-08PH-S-D40	Single Row Barrier Strip	8	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Through Hole	Straight	\$1.99
2275447	Jameco Valuepro	HI-201-08P	Single Row Barrier Strip	8	10	250	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	Straight	\$1.79
2288559	Cinch Connectors	38720-6208NF	Single Row Barrier Strip	8	15	300	22-14	Screw, 6-32	PC Pin, Offset w/o Flange	Through Hole	Straight	\$2.95
2272943	Eaton	A207108R42	Single Row Barrier Strip	8	30	300	22-12	Screw, 6-32	PC Pin Right Angle w/ Flange	Through Hole	Right Angle	\$2.95
2275215	Jameco Valuepro	HI-200-10PH-S-D40	Single Row Barrier Strip	10	10	250	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$4.49
2275399	Jameco Valuepro	HI-202-10PH-S-D40	Single Row Barrier Strip	10	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$2.49
2275279	Jameco Valuepro	HI-201-10PH-S-D40	Single Row Barrier Strip	10	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Through Hole	Straight	\$2.25
2275455	Jameco Valuepro	HI-201-10P	Single Row Barrier Strip	10	10	250	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	Straight	\$1.99
2281111	TYCO Power Systems	SSB7TM100102	Single Row Barrier Strip	10	30	600	10	Screw, 6-32	Open Bottom w/ Flange	Through Hole	Straight	\$4.95
2275223	Jameco Valuepro	HI-200-12PH-S-D40	Single Row Barrier Strip	12	10	250	22-14	Screw, M3.5	Closed Bottom w/ Flange	Chassis, Panel	Straight	\$4.95
2275407	Jameco Valuepro	HI-202-12PH-S-D40	Single Row Barrier Strip	12	10	250	22-14	Screw, M3.5	Insulated Solder Turret w/ Flange	Chassis, Panel	Straight	\$2.75
2275423	Jameco Valuepro	HI-201-12PH-S-D40	Single Row Barrier Strip	12	10	250	22-14	Screw, M3.5	PC Pin w/ Flange	Chassis, Panel	Straight	\$2.49
2275415	Jameco Valuepro	HI-201-12P	Single Row Barrier Strip	12	10	250	22-14	Screw, M3.5	PC Pin, w/o Flange	Chassis, Panel	Straight	\$2.25
2277911	Dinkle	DT35-B01W-02	Single Row Tri-Barrier Strip	2	20	300	22-12	Screw, M3.5	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$1.09
2272951	TE Connectivity	6PCR-03	Single Row Tri-Barrier Strip	3	25	300	22-12	Screw, 6-32	PC Pin Right Angle w/o Flange	Through Hole	Right Angle	\$0.99
2277071	Molex	386608803	Single Row Tri-Barrier Strip	3	45	600	18-8	Screw, 6-32	PC Pin, Zig Zag, w/o Flange	Through Hole	Straight	\$3.29
2277087	TE Connectivity	6PCV-04	Single Row Tri-Barrier Strip	4	25	300	22-12	Screw, 6-32	PC Pin Right Angle w/o Flange	Through Hole	Straight	\$1.49
2273031	TE Connectivity	4PCV-05-006	Single Row Tri-Barrier Strip	5	20	150	22-12	Screw, 6-32	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$1.25

Jameco Part #	Manufacturer	Manufacturer Part #	Description	No. of Positions	Maximum Current Rating (A)	Rated Voltage (V)	Wire Size	Top Termination	Bottom Termination	Mounting	Body Orientation	Price 1
2277895	TE Connectivity	4PCV-06-006	Single Row Tri-Barrier Strip	6	20	150	22-12	Screw, 6-32	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$1.49
2133616	Dinkle	DT39-B01W-06	Single Row Tri-Barrier Strip	6	20	300	22-12	Screw, M3.5	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$1.25
2277079	TE Connectivity	6PCV-06	Single Row Tri-Barrier Strip	6	25	300	22-12	Screw, 6-32	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$1.95
2162628	Arndt	HB951-08P	Single Row Tri-Barrier Strip	8	10	250	22-14	Screw, M3.5	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$2.95
2277903	TE Connectivity	4PCV-08-006	Single Row Tri-Barrier Strip	8	20	150	22-14	Screw, 6-32	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$1.95
2133624	Dinkle	DT39-B01W-08	Single Row Tri-Barrier Strip	8	20	300	22-12	Screw, M3.5	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$1.95
2277919	Dinkle	DT35-B01W-09	Single Row Tri-Barrier Strip	9	20	300	22-12	Screw, M3.5	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$2.49
2276559	Cooper Industries	CB10111S1968	Single Row Tri-Barrier Strip	10	15	300	22-14	Screw, 6-32	Insulated Solder Turret w/ Flange	Through Hole	Straight	\$3.95
2277927	Dinkle	DT35-B01W-10	Single Row Tri-Barrier Strip	10	20	300	22-12	Screw, M3.5	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$2.95
2273039	Eaton	CB20221107	Single Row Tri-Barrier Strip	11	30	300	22-12	Screw, 6-32	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$2.95
2272919	Eaton	CB20221207	Single Row Tri-Barrier Strip	12	30	300	22-12	Screw, 6-32	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$3.95
2277935	Dinkle	DT35-B01W-14	Single Row Tri-Barrier Strip	14	20	300	22-12	Screw, M3.5	PC Pin, Offset, w/o Flange	Through Hole	Straight	\$3.49