



[Click Here to Request a Large Quantity Quote](#)

[Motors-DC Direct Drive](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Nominal Voltage (VDC)	Voltage Range (VDC)	Current @ Max. Efficiency (A)	Speed @ Max. Efficiency (RPM)	Torque @ Max. Efficiency (g-cm)	Efficiency	Terminal Type	Shaft Diameter (inch)	Shaft Length (inch)	Size (Diameter x Depth) (inch)	Price 1
<a href="#">2209094</a>	Mabuchi Motor Company	MABUCHI-55	1.5	1.5 - 12	0.32	1350	6	50	5" Wires	0.09	0.35	1.3 x 1.4	\$1.95
<a href="#">231917</a>	Jameco Valuepro	FE-260-2670	1.5	1.5 - 3	0.66	3700	10.5	42	0.12/Solderable	0.078	0.314	.93 x 1.1	\$2.95
<a href="#">2235049</a>	Mabuchi Motor Company	RE140RA-2270	1.5	1.5 - 3.0	0.66	6150	6.7	50	4" Wires	0.078	0.31	.82 x .98	\$2.75
<a href="#">238465</a>	Jameco Valuepro	RF-310TA-11400	2.5	1 - 6	0.06	2190	3.3	75	0.05/Solderable	0.078	0.7	.96 x .78	\$2.65
<a href="#">238458</a>	Jameco Valuepro	RF-300CA-11400-R	3	1 - 6	0.065	2400	4.3	56	3" Wires	0.078	0.19	.96 x .52	\$3.25
<a href="#">2158442</a>	Nichibo Taiwan	RF-500TB-18280-R	3	1.0 - 3.0	0.17	2104	13.4	60	0.07/Solderable	0.078	0.34	1.2 x .75	\$2.95
<a href="#">2237765</a>	Nichibo Taiwan	FE-260B-20110-LR/46	3	1.0 - 3.0	0.756	5126	14.35	35	4" Wires	0.078	0.527	.93 x 1.0	\$1.95
<a href="#">1939589</a>	Jameco Valuepro	FF-130RH-15210	3	1.0 - 4.0	0.17	4280	5.8	50	0.08/Solderable	0.08	0.24	.79 x .98	\$2.75
<a href="#">154915</a>	Jency Motor Industrial Limited	ST130-12240-38	3	1.5 - 3.0	0.17	3588	7.4	55	0.09/Solderable	0.08	0.37	.79 x 1.1	\$2.25
<a href="#">2192755</a>	Jameco Valuepro	DCM-3V-4600	3	1.5 - 3.0	0.2	4600	6	42	2mm/solder	0.078	0.303	.78 x 1.0	\$1.95
<a href="#">2249256</a>	Velleman	MOT1N	3	1.5 - 3.0	0.35	11780	15.7	60	.05/Solderable	0.08	0.27	.90 x 1.0	\$3.95
<a href="#">154923</a>	Jency Motor Industrial Limited	ST130-22770-38	3	1.5 - 3.0	0.95	13200	10.3	40	0.09/Solderable	0.08	0.37	.79 x 1.1	\$2.25
<a href="#">1951449</a>	Jameco Valuepro	QJT-260-18130	3	1.5 - 4.5	0.46	4780	10	40	0.12/Solderable	0.078	0.314	.94 x 1.1	\$2.49
<a href="#">231925</a>	Jameco Valuepro	FE-260-2295	3	1.5 - 4.5	0.63	6850	14	53	0.12/Solderable	0.078	0.314	.93 x 1.1	\$2.49
<a href="#">2258507</a>	Mabuchi Motor Company	RE-260RA-2295	3	1.5 - 4.5	0.636	7600	13.4	54	2mm/solder	0.078	0.271	0.9 x 1.0	\$1.49
<a href="#">2233932</a>	Mabuchi Motor Company	RE-260RA/2295	3	1.5 - 4.5	0.636	7600	13.4	54	6" Wires	0.078	0.271	.93 x 1.1	\$1.95
<a href="#">211246</a>	Jameco Valuepro	RC-260RA-2670	4.5	3.0 - 4.5	1.43	15290	21.8	53	0.11/Solderable	0.08	0.28	.93 x 1.0	\$2.75
<a href="#">2230037</a>	Nichibo Taiwan	RF-500TB-14415-R-J/32	6	1.0 - 6.0	0.164	2755	83	55	1.9mm/solder	0.078	0.35	1.2 x .67	\$3.95

Jameco Part #	Manufacturer	Manufacturer Part #	Nominal Voltage (VDC)	Voltage Range (VDC)	Current @ Max. Efficiency (A)	Speed @ Max. Efficiency (RPM)	Torque @ Max. Efficiency (g-cm)	Efficiency	Terminal Type	Shaft Diameter (inch)	Shaft Length (inch)	Size (Diameter x Depth) (inch)	Price 1
<a href="#">2158434</a>	Nichibo Taiwan	RF370CH-22170-R	6	1.0 - 6.0	0.45	4787	34.28	63	0.15/Solderable	0.078	0.19	.96 x 1.2	\$1.75
<a href="#">2229976</a>	Nichibo Taiwan	FE-280SB-2295-NR/45	6	1.0 - 6.0	0.802	7949	225	62	3mm/solder	0.078	0.409	.95 x 1.7	\$2.25
<a href="#">231781</a>	Jameco Valuepro	PC-130F-12240	6	3 - 9	0.25	6800	7	33	0.08/Solderable	0.078	0.377	.80 x .98	\$3.49
<a href="#">2173044</a>	Nichibo Taiwan	RF-500TB-12560-R	6	6.0 - 12	0.08	2100	11	58	Solderable	0.078	0.342	1.2 x .76	\$3.95
<a href="#">232144</a>	Jameco Valuepro	FF-050S-11170-R	7	1.5 - 9	0.17	8500	7	51	0.08/Solderable	0.059	0.433	.61 x 1.1	\$2.95
<a href="#">177498</a>	Jameco Valuepro	RC280RA2485 (F-7089C460)	7.2	3.0 - 14	1.18	14260	33.3	57	0.11/Solderable	0.08	0.43	.95 x 1.2	\$2.49
<a href="#">2229968</a>	Nichibo Taiwan	PC-280S-2490-N/45	7.2	3.6 - 9.0	0.982	9823	304	65	2mm/solder	0.078	0.37	.95 x 1.7	\$2.49
<a href="#">2229909</a>	Mabuchi Motor Company	RS-540PH-7021	7.2	6.0 - 8.0	7.75	17317	227.5	60	3.8mm/solder	0.125	0.495	1.4 x 1.3	\$3.95
<a href="#">2258574</a>	Nichibo Taiwan	HP5FN-5515S-R	10.8	1.2 - 12	7.696	11017	305	71	3.8mm/solder	0.124	0.531	1.4 x 1.9	\$1.95
<a href="#">2258540</a>	Nichibo Taiwan	KC3SFN-8021F/75	12	1 - 12.75	16.09	19455	648	68	3.8mm/solder	0.124	0.334	1.5 x 2.2	\$4.95
<a href="#">2210845</a>	Nichibo Taiwan	775-7013F-R	12	1.0 - 12	3.2	15500	5640	76	4.8mm/solder	0.196	0.578	1.7 x 2.6	\$5.95
<a href="#">2217810</a>	Nichibo Taiwan	JD5B-2655W-R	12	1.0 - 18	0.19	6468	928	74	2.8mm/solder	0.09	0.326	.09 x .33	\$2.49
<a href="#">2224024</a>	Nichibo Taiwan	KP5FN-3255AS-RC-80	12	1.0 - 20	0.7	5010	1662	71	3.8mm/solder	0.124	0.503	1.4 x 2.2	\$4.25
<a href="#">2258531</a>	Nichibo Taiwan	DC-280ST-19155PAS/50	12	1.5 - 15	0.653	10235	49.38	67	wire socket	0.078	0.582	.95 x 1.2	\$1.25
<a href="#">2217781</a>	Nichibo Taiwan	PC-260SB-14280-NR	12	12.0 - 18	0.82	9000	151	61	2mm/solder	0.078	0.232	.96 x 1.1	\$2.49
<a href="#">2209203</a>	Nichibo Taiwan	MD5BN-12200	12	2.0 - 20	0.7	4200	168	50	5 " Wires	0.09	0.885	1.1 x 1.3	\$2.25
<a href="#">2258523</a>	Nichibo Taiwan	FK-180SH-18130-R	12	2.0 - 20	0.762	11806	44.24	61	2mm/solder	0.078	0.22	.61 x 1.3	\$1.95
<a href="#">238473</a>	Mabuchi Motor Company	RF370CA-15370	12	3 - 12	0.17	4840	25.3	75	0.08/Solderable	0.078	0.346	.96 x 1.2	\$3.25
<a href="#">231896</a>	Jameco Valuepro	FE-260-08450	12	6 - 12	0.11	5560	10.3	46	0.12/Solderable	0.078	0.314	.93 x 1.0	\$2.65
<a href="#">232040</a>	Jameco Valuepro	MD5-2070-R	12	6 - 12	1.3	12586	52	62	0.12/Solderable	0.091	0.48	1.1 x 1.3	\$2.95
<a href="#">232047</a>	Jameco Valuepro	MD5-2445	12	6 - 12	2.05	19850	79.7	66	0.12/Solderable	0.091	0.622	1.1 x 1.3	\$4.49
<a href="#">232022</a>	Jameco Valuepro	MS5N-1885-R	12	6 - 18	0.74	9820	53.5	60	0.11/Solderable	0.091	0.622	1.1 x 1.3	\$3.49

Jameco Part #	Manufacturer	Manufacturer Part #	Nominal Voltage (VDC)	Voltage Range (VDC)	Current @ Max. Efficiency (A)	Speed @ Max. Efficiency (RPM)	Torque @ Max. Efficiency (g-cm)	Efficiency	Terminal Type	Shaft Diameter (inch)	Shaft Length (inch)	Size (Diameter x Depth) (inch)	Price 1
<a href="#">231732</a>	Jameco Valuepro	PC-130SF-09480-R	12	6 - 24	0.11	4800	12.3	49	0.08/Solderable	0.078	0.377	.80 x .98	\$1.95
<a href="#">2167681</a>	Nichibo Taiwan	DC-130SB-10410	12	6.0 - 12	0.2	5624	71.2	47	Plug-in	0.079	0.52	.78 x 1.0	\$1.25
<a href="#">2234812</a>	Nichibo Taiwan	PC-260SB-14280-LNR/38	12	6.0 - 12	0.25	7524	23.25	61	2 wires	0.078	0.232	.95 x 1.1	\$2.25
<a href="#">2208841</a>	Nichibo Taiwan	UC-130S-19133PW	12	6.0 - 12	0.26	18587	196	56	2mm/solder	0.078	0.322	.78 x 1.0	\$2.39
<a href="#">2208850</a>	Nichibo Taiwan	UC-130S-22103PW	12	6.0 - 12	1.48	25253	192	50	2mm/solder	0.078	0.322	.78 x 1.0	\$1.95
<a href="#">2155250</a>	Nichibo Taiwan	MD3BN-14280-R/51	12	6.0 - 18	0.268	5260	36.2	63	0.11/Solderable	0.09	0.45	1.0 x 1.3	\$1.49
<a href="#">2167592</a>	Nichibo Taiwan	LS5BFN-2465-R/58	12	6.0 - 18	0.75	7205	83.3	72	0.11"/Solder	0.09	0.54	1.1 x 1.4	\$2.55
<a href="#">2295535</a>	Mabuchi Motor Company	RS-555PC-3550	12	9 - 30	1.3	4240	261		0.187 quick connect	0.125	0.35	1.50 x 2.62	\$3.95
<a href="#">174693</a>	Jameco Valuepro	RF-370CH-10670-19.5	12	9.0 - 14	0.015	3000	85.06	80	0.11/Solderable	0.08	0.71	.97 x 1.2	\$3.49
<a href="#">206949</a>	Jameco Valuepro	QJT-360S-14280	12	9.0 - 30	0.35	4930	44.5	52	0.11/Solderable	0.09	0.45	1.1 x 1.3	\$3.49
<a href="#">2258785</a>	Nichibo Taiwan	736-8017F-R-CE-IE/76	18	1 - 18	18.5	17794	134	74	2 wires	0.197	0.55	1.7 x 2.1	\$6.95
<a href="#">2217801</a>	Nichibo Taiwan	MS5BN-1980-R	18	1.0 - 18	0.35	19500	427	68	2.8mm/solder	0.09	0.511	1.1 x 1.3	\$0.99
<a href="#">2218011</a>	Mabuchi Motor Company	RS385PH-29505	24	12.0 - 30	0.41	7420	84	55	0.11"/Solder	0.09	0.96	1.1 x 1.5	\$1.49
<a href="#">2258558</a>	Nichibo Taiwan	DC-130S-06840-NR	24	3 - 30	0.069	5615	13.56	50	wire socket	0.078	0.44	.80 x 1.0	\$1.25