



[Click Here to Request a Large Quantity Quote](#)

General Purpose Transistors

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
26446	Major Brands	MPQ2222	Transistor MPQ2222 NPN GP Small Signal Quad	DIP-14	NPN	30V	60V	300@500mA	\$3.95
26454	Major Brands	MPQ2907	40V 600mA PNP Bipolar Transistor 14-Pin DIP	DIP-14	PNP	40V	60V	100 @ .15A	\$3.95
2289055	Major Brands	CA3146E	High Voltage 5-Transistor Array 14-Pin	PDIP-14	NPN	30V	40V	100 @ 1mA	\$4.95
1421165	STMicroelectronics	ULN2069B	Transistor Darlington NPN 80 Volt 1.75 Amp 16-Pin Power PDIP	PowerDIP-16	NPN	80 V	N/A	N/A	\$2.69
2290735	Major Brands	STA401A	Bipolar (BJT) Transistor Array 4 NPN Darlington (Quad) 60V 4A 4W Through Hole SIP-10	SIP 10	NPN	60V	60V	1000 @ 3A @ 4V	\$3.39
2295719	On Semiconductor	MMBT2484LT1G	Transistor Bipolar (BJT) NPN 60V 100mA 225mW Surface Mount SOT-23-3	SOT-23-3	NPN	60V	60V	250 @ 0.001A	\$0.25
2290727	Major Brands	BC807-25-TP	Bipolar (BJT) Transistor PNP 45V 500mA 100MHz 300mW Surface Mount SOT-23	SOT-23-3	PNP	45V	50V	160 @ .1A @ 1V	\$0.25
2132293	Motorola	BD158	Transistor BD158 Low Power Fast Switching NPN 500ma 300 Volt TO-126	TO-126-3	NPN	300V	325V	30 @ .05A	\$0.49
209277	Major Brands	2N5657	2N5657 Transistor 350V 500mA	TO-126-3	NPN	350V	375V	30 @ .1A	\$0.49
211490	Major Brands	2N4923	General Purpose NPN BJT Transistor 80V 1A TO-126	TO-126-3	NPN	80V	80V	80 @ 1A	\$1.39
2245685	New Jersey Semiconductor	2N2369	Transistor 2N2369 Bipolar NPN TO-18	TO-18-3	NPN	15V	40V	40 @ .01A	\$1.49
38236	Major Brands	2N2222A	2N2222A NPN Switching Transistor 40V 800mA TO-18	TO-18-3	NPN	40V	75V	100 @ .15A	\$1.29
2245773	New Jersey Semiconductor	2N2221	30V 0.8A Bipolar NPN Transistor TO-18	TO-18-3	NPN	50V	75V	35 @ .01A	\$1.95
2245714	New Jersey Semiconductor	2N3700	Transistor 2N3700 NPN General Purpose Amplifier 80V 1A TO-18	TO-18-3	NPN	80V	140V	50 @ .5A	\$1.49
2245731	New Jersey Semiconductor	2N3250	40V 0.2A Bipolar PNP Transistor TO-18	TO-18-3	PNP	40V	50V	50 @ .01A	\$1.75
2245722	New Jersey Semiconductor	2N3251	Transistor 2N3251 Bipolar PNP -40V -200mA TO-18	TO-18-3	PNP	40V	50V	80 @ .001A	\$1.75

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
38279	Major Brands	2N2907A	Transistor 2N2907A PNP General Purpose	TO-18-3	PNP	60V	60V	100 @ .15A	\$1.09
2245790	New Jersey Semiconductor	2N3496	Transistor 2N3496 Bipolar PNP 80V 0.01A TO-18	TO-18-3	PNP	80V	80V	40 @ .01A	\$1.95
2280127	STMicroelectronics	BUV48Q	Bipolar Transistor NPN BJT 450V 15A 125W TO-218	TO-218-3	NPN	450V	850V	8 @8A	\$3.95
2290583	Major Brands	TIP3055	Transistor Bipolar (BJT) NPN 60V 15A 2.5MHz 90W Through Hole TO-218	TO-218-3	NPN	60V	100V	20 @ 4A @ 4V	\$1.65
2285063	Major Brands	2N4914	General Purpose BJT NPN Transistor 60V 5A TO-220	TO-220	NPN	60V	60V	100 @2.5A	\$3.95
179354	Fairchild Semiconductor	TIP31C	Transistor TIP31C General Purpose BJT NPN 100 Volt 3 Amp TO-220	TO-220-3	NPN	100V	100V	10 @ 3A	\$0.59
179371	Major Brands	TIP41C	TIP41C NPN Bipolar Power Transistor 100 Vceo TO-220	TO-220-3	NPN	100V	100V	15 @ 3A	\$0.59
297781	Fairchild Semiconductor	TIP29C	Transistor TIP29C TO-220 NPN Epitax 100 Volt 1 Amp	TO-220-3	NPN	100V	100V	75@1A	\$0.59
288631	Major Brands	TIP48	Bipolar (BJT) Transistor NPN 300V 1A 10MHz 2W Through Hole TO-220-3	TO-220-3	NPN	300V	400V	30 @ .3A	\$0.69
1098206	Fairchild Semiconductor	TIP50	3 LEAD PLASTIC W/EXPOSED HEATSNK	TO-220-3	NPN	400V	500V	30 @300mA	\$0.69
787991	National Semiconductor	TIP41	Transistor BJT NPN 40V 6A TO-220AB	TO-220-3	NPN	40V	40V	15 @ 3A	\$0.99
2281295	Major Brands	BD437	TO-220 NPN Epitaxial Silicon Transistor 45V 4A	TO-220-3	NPN	45V	45V	30 @ 10mA	\$0.49
33048	Major Brands	TIP31A	Transistor TIP31A General Purpose 60 Volt 3 Amp TO-220	TO-220-3	NPN	60V	60V	10 @ 3A	\$0.59
1097220	Major Brands	TIP29A	<p>NPN General Purpose BJT Transistor 60V 1A TO-220</p>	TO-220-3	NPN	60V	60V	15 @1A	\$0.69
25857	Major Brands	MJE3055T	Transistor MJE3055T General Purpose NPN 60 Volt 10 Amp TO-220	TO-220-3	NPN	60V	70V	20 @ 4A	\$0.79
2281319	Motorola	MJE8502	TO-220 NPN Power Transistor 700V 5A	TO-220-3	NPN	700V	700V	750 @1.5A	\$1.95
297772	Motorola	TIP101	Bipolar BJT Transistor NPN Darlington 80V 8A 2W Through Hole TO-220AB	TO-220-3	NPN	80V	80V	1000 @ 3A	\$0.69
2287847	Bourns	BD543B-S	Bipolar Junction Transistor NPN 80V 8A TO-220	TO-220-3	NPN	80V	80V	20 @ 500mA	\$0.69
2288375	Bourns	BD242	Bipolar Junction Transistor PNP 45V 3A TO-220	TO-220-3	PNP	-45V	-45V	20 @ 500mA	\$0.49
2288383	Bourns	BD242A	Bipolar Junction Transistor PNP 60V 3A TO-220	TO-220-3	PNP	-60V	-70V	20 @ 500mA	\$0.49

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
181841	Major Brands	TIP32C	TIP32C PNP Bipolar Power Transistor 100 Vceo TO-220	TO-220-3	PNP	100V	100V	10 @ 3A	\$0.55
179346	STMicroelectronics	TIP30C	Transistor TIP30C General Purpose PNP 100 Volt 1 Amp TO-220AB	TO-220-3	PNP	100V	100V	15 @ 1A @ 4V	\$0.59
139580	Major Brands	TIP42C	TIP42C PNP Bipolar Power Transistor 100 Vceo TO-220	TO-220-3	PNP	100V	100V	15 @ 3A	\$0.79
2285111	Motorola	MJE15301	General Purpose BJT PNP Transistor 150V 8A TO-220	TO-220-3	PNP	150V	150V	40@8A	\$1.49
2285007	Motorola	MJE1123	General Purpose BJT PNP Transistor 40V 4A TO-220	TO-220-3	PNP	40V	50V	225@4A	\$0.49
2286727	SGS Thomson	2N6489	BJT PNP Transistor 40V 15A TO-220	TO-220-3	PNP	40V	50V	25 @ 1A	\$1.75
33064	Major Brands	TIP32A	Transistor TIP32A General Purpose PNP 60 Volt 3 Amp TO-220	TO-220-3	PNP	60V	60V	10 @ 3A	\$0.49
33030	Major Brands	TIP30A	Bipolar (BJT) Transistor PNP 60V 1A 3MHz 30W TO-220-3	TO-220-3	PNP	60V	60V	15 @ 1A	\$0.99
25831	Major Brands	MJE2955T	Transistor MJE2955T General Purpose PNP 60 Volt 10 Amp TO-220AB	TO-220-3	PNP	60V	70V	20 @ 4A	\$0.79
880976	NXP Semiconductors	TIP32B	TRANSISTOR,BIP,T0-220 PKG,PNP,3A,80V,TIP32B	TO-220-3	PNP	80V	80V	10 @ 3A	\$0.99
2287703	On Semiconductor	MJE170	Transistor BJT PNP 40V 3A TO-225	TO-225-3	PNP	60V	40V	250@3A	\$0.49
2284111	Major Brands	TIP35CG(TO-247)	Bipolar (BJT) Transistor NPN 100V 25A 3MHz 125W THM TO-247	TO-247-3	NPN	100V	100V	15 @ 15A @ 4V	\$1.59
890568	Major Brands	TIP35CG(TO-218)	Transistor TIP35C General Purpose NPN 100 Volt 25 Amp TO-247	TO-247-3	NPN	100V	100V	25 @ 1.5A	\$2.25
211385	Major Brands	TIP3055G	Transistor TIP3055 NPN 60 Volt 15 Amp Case 340D-02	TO-247-3	NPN	60V	100V	5 @ .001A	\$1.49
890592	STMicroelectronics	TIP36C	Transistor TIP36C General Purpose PNP 100 Volt 25 Amp TO-247	TO-247-3	PNP	100V	100V	25 @ 1.5A	\$1.95
903710	Fairchild Semiconductor	FJA4313OTU	Transistor BJT NPN 250V 17A TO-3P	TO-3	NPN	250V	250V	35 @ 7A	\$1.49
194618	Major Brands	2N6547	Transistor 2N6547 NPN Power Switching 15 Amp 400V TO-3	TO-3	NPN	400V	850	12 @ 5A	\$4.95
209242	Major Brands	2N3771	Transistor 2N3771 TO-3NPN 40 Volt 30 Amp	TO-3	NPN	40V	50V	15 @ 15A	\$2.25
38308	Major Brands	2N3055	Transistor 2N3055 NPN Power Bi Polar Expitaxial	TO-3	NPN	60V	100V	15 @ 10A	\$1.48

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
			Base						
2285671	Major Brands	RCS258	60V NPN General Purpose BJT Transistor TO-3	TO-3	NPN	60V	100V	15 @ 20A	\$4.95
211406	Major Brands	2N3055A	IC 2N3055A High Power Bipolar Transistor 100 volt 15 amp TO-3	TO-3	NPN	60V	100V	20 @ 4A	\$2.49
2285327	Major Brands	2N5302	High-Power BJT NPN Silicon Transistor 60V 30A TO-3	TO-3	NPN	60V	60V	15 @ 15A	\$2.95
2286039	Major Brands	2N2833	Germanium Power Transistor BJT PNP 75V 20A TO-3	TO-3	PNP	-75V	-120	25 @ 10mA	\$4.95
2280119	Motorola	2N6287	Bipolar Darlington Transistor PNP BJT 100V 20A 160W TO-3	TO-3	PNP	100V	100V	750 @ 10A @ 3V	\$4.95
211502	Major Brands	MJ2955	Transistor MJ2955 TO-3 PNP Silicon Power 60 Volt	TO-3	PNP	60V	100V	20 @ 4A	\$1.95
38295	Major Brands	2N3053	Transistor 2N3053 General Purpose NPN Small Signal TO-39	TO-39-3	NPN	40V	60V	25 @ .15A	\$1.09
38228	Major Brands	2N2219A	Transistor 2N2219A General Purpose NPN 40 Volt 0.8 Amp TO-39	TO-39-3	NPN	40V	75V	100 @ .15A	\$0.99
2245765	New Jersey Semiconductor	2N2218	Transistor 2N2218 Bipolar NPN 40V 0.8A TO-39	TO-39-3	NPN	40V	75V	40 @ .15A	\$1.49
2245781	New Jersey Semiconductor	2N2218A	Transistor 2N2218 Bipolar NPN 40V 0.8A TO-39	TO-39-3	NPN	40V	75V	40 @ .15A	\$1.95
2245706	New Jersey Semiconductor	2N1893	Transistor 2N1893 Bipolar NPN General Purpose 80V 0.5A TO-39	TO-39-3	NPN	80V	140V	40 @ .15A	\$1.49
2245693	New Jersey Semiconductor	2N4037	Transistor 2N4037 40V 1A Bipolar PNP TO-39	TO-39-3	PNP	40V	60V	50 @ .15A	\$1.95
194378	Major Brands	2N2905A	Transistor 2N2905A General Purpose PNP 60 Volt 0.6 Amp TO-39	TO-39-3	PNP	60V	60V	100 @ .15A	\$1.09
2245677	New Jersey Semiconductor	2N2904A	Transistor 2N2094 PNP Switching Bipolar -60V - 0.6A TO-39	TO-39-3	PNP	60V	60V	120 @ .15A	\$1.09
2245757	New Jersey Semiconductor	2N4036	Transistor 2N4036 Bipolar PNP 65 Volt 1 Amp TO-39	TO-39-3	PNP	65V	90V	40 @ .15A	\$2.49
140373	Major Brands	2N5179	Transistor 2N5179 General Purpose NPN 12 Volt 0.05 Amp TO-72	TO-72-4	NPN	12V	20V	25 @ 0.003A	\$3.95
2291207	Fairchild Semiconductor	SS8050DTA	Bipolar Transistor BJT NPN Epitaxial Silicon 25V 1500mA 100MHz 1W TO-92-3	TO-92	NPN	25V	40V	160 @ 0.1A	\$0.29
253411	Major Brands	2N4400	Transistor 2N4400 NPN Small Signal 600Ma 40V	TO-92	NPN	40V	60V	150 @ 600mA	\$0.35

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
			TO 92						
2291215	Fairchild Semiconductor	SS8550DTA	Bipolar Transistor BJT PNP Epitaxial Silicon 25V 1500mA 200MHz 1W TO-92-3	TO-92	PNP	-25V	-40V	45 @ -0.005A	\$0.29
2277615	Micro Electronics	BC173C	NPN Transistor Silicon Planar Epitaxial High Gain Low Noise 25V 100mA TO-92	TO-92 3	NPN	25V	25V	420@2mA, 5V	\$0.65
2277351	On Semiconductor	PN5130	NPN Small Signal Transistor 30V 50mA TO-92	TO-92-3	NPN	12V	30V	250@ 80mA	\$0.25
2277287	On Semiconductor	2N5831	NPN Silicon Planar Transistor 140V 600mA	TO-92-3	NPN	140V	160V	80 @ 10mA	\$1.49
2280615	National Semiconductor	2N5772	TO-92 General Purpose NPN Transistor 15V 300mA	TO-92-3	NPN	15V	40V	30 @ 30mA	\$0.25
800690	NXP Semiconductors	MPSA12	SS T092 DL XSTR NPN 20V, MPSA12, NXP Semiconduct	TO-92-3	NPN	20V	20V	20000 @ 10mA	\$0.25
2277159	Fairchild Semiconductor	TN3440A	NPN General Purpose Amplifier 250V 100mA TO-92	TO-92-3	NPN	250V	300V	40 @20 mA	\$0.25
2277255	On Semiconductor	MPS2924	NPN Small Signal General Purpose Amplifier 25V 100mA TO-92	TO-92-3	NPN	25V	25V	150@ 2mA	\$0.25
787608	Major Brands	PN3565	PN3565 - NPN General Purpose Amplifier TO-92 25V 0.5A	TO-92-3	NPN	25V	30V	150 @ .001A	\$0.89
2277383	On Semiconductor	MPS6520	NPN General Purpose Amplifier 25V 100mA TO-92	TO-92-3	NPN	25V	40V	100 @100mA	\$0.45
1945031	Fairchild Semiconductor	MPS6515	Transistor MPS6515 General Purpose NPN 25 Volt 0.2 Amp TO-92	TO-92-3	NPN	25V	40V	250 @ .002A	\$0.25
178546	Major Brands	MPSA42	Transistor MPSA42 NPN 300 Volt TO-92	TO-92-3	NPN	300V	300v	25 @ 300mA	\$0.29
2277215	On Semiconductor	BC238A	NPN Epitaxial Silicon Transistor TO-92 with DC Current Gain 120-220	TO-92-3	NPN	30V	1.05V	120 @2mA	\$0.25
254781	Major Brands	BC548B	Transistor BC548B TO-92 Transistor NPN Switch	TO-92-3	NPN	30V	30V	110 @ .002A	\$0.25
62316	Major Brands	2N5088	2N5088 - BJT NPN Silicon Amplifier Transistor 30V 0.05A TO-92	TO-92-3	NPN	30V	35V	300 @ .05A	\$0.39
2277375	On Semiconductor	MPS6513	NPN General Purpose Amplifier 30V 200mA TO-92	TO-92-3	NPN	30V	40V	90 @ 2mA	\$0.25
2277551	Motorola	BC184BP	NPN Silicon Small Signal Transistor 45V 200mA	TO-92-3	NPN	30V	45V	240 @2mA	\$0.69
2277183	On Semiconductor	2SC1854	NPN BJT 30V 500mA TO-92	TO-92-3	NPN	30V	50V	300 @ 50mA	\$1.49
783412	Major Brands	2N3704	Transistor 2N3704 General Purpose NPN 30 Volt 0.5 Amp TO-92	TO-92-3	NPN	30V	50V	30@.800mA	\$0.59
2277231	On Semiconductor	BC239B	NPN Epitaxial Silicon Transistor TO-92 with DC Current Gain 180-460	TO-92-3	NPN	30V	5V	180 @2mA	\$0.25
28628	Major Brands	PN2222	Transistor PN2222 General Purpose NPN 30 Volt	TO-92-3	NPN	30V	60V	100 @ .15A	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
			0.6 Amp						
2277655	Micro Electronics	BC223A	General Purpose Audio Amplifier NPN TO-92 40V 50mA	TO-92-3	NPN	40V	40V	100 @50mA	\$0.25
2277663	Micro Electronics	BF240	NPN RF Transistor TO-92 40V 50mA	TO-92-3	NPN	40V	40V	65 @1 mA	\$0.25
38359	Major Brands	2N3904BU	Transistor 2N3904 NPN General Purpose (bulk)	TO-92-3	NPN	40V	60V	100 @ .01A	\$0.25
178597	Fairchild Semiconductor	2N3904RLRP	Transistor General Purpose BJT NPN 40V 200mA TO-92-3 (Tape/Reel/Ammo)	TO-92-3	NPN	40V	60V	100 @ .01A	\$0.25
38421	Major Brands	2N4401T/R	Transistor 2N4401 NPN General Purpose	TO-92-3	NPN	40V	60V	100 @ .15A	\$0.25
783498	Fairchild Semiconductor	2N4401TA	Transistor 2N4401 General Purpose Amplifier 40 Volt 0.6 Amp TO-92	TO-92-3	NPN	40V	60V	100 @ 150mA	\$0.10
260558	NTE Electronics	NTE123AP	Transistor NTE123AP General Purpose Audio Amplifier NPN TO-92	TO-92-3	NPN	40V	60V	500 @ 600mA	\$0.89
178511	Major Brands	PN2222ABU	Transistor PN2222A NPN Silicon General Purpose TO-92	TO-92-3	NPN	40V	75V	100 @ .15A	\$0.39
787536	Fairchild Semiconductor	PN2222ATRA	Transistor PN2222A General Purpose NPN 40 Volt 1 Amp TO-92	TO-92-3	NPN	40V	75V	300 @ .15A	\$0.39
210673	Major Brands	MPS2222A	Transistor MPS2222A General Purpose NPN TO-92	TO-92-3	NPN	40V	75V	40 @ .50A	\$0.25
277413	Major Brands	PN3567	Transistor PN3567 NPN General Purpose 40V 600Ma TO-92	TO-92-3	NPN	40V	80V	120@600mA	\$0.89
210681	Major Brands	MPSA18	Transistor MPSA18 TO-92 NPN General Purpose BIPO Low Noise 45 Volt	TO-92-3	NPN	45V	45V	500 @ .001A	\$0.49
2277639	Micro Electronics	BC207	General Purpose Audio Amplifier NPN TO-92 50V 100mA	TO-92-3	NPN	45V	50V	110 @ 2mA	\$0.99
2277359	On Semiconductor	BC547A	NPN Epitaxial Silicon Transistor 50V 100mA TO-92	TO-92-3	NPN	45V	50V	110 @2mA	\$0.25
2277647	Micro Electronics	BC207B	General Purpose Audio Amplifier NPN TO-92 50V 100mA	TO-92-3	NPN	45V	50V	150 @2mA	\$0.89
254810	Major Brands	BC337	Transistor BC337 TO-92 NPN 800ma 45 Volt	TO-92-3	NPN	45V	50V	250 @ 800mA	\$0.25
254801	Major Brands	BC547B	Transistor BC547B TO-92 Transistor NPN Switch	TO-92-3	NPN	45V	50V	330 @ .002A	\$0.22
254799	Major Brands	BC547C	Transistor BC547C TO-92 Transistor NPN Switch	TO-92-3	NPN	45V	50V	600 @ .002A	\$0.25
2277583	Diodes Incorporated	ZTX450	Bipolar Transistor (BJT) NPN 45V 1A 150MHz 1W E-Line TO-92	TO-92-3	NPN	45V	60V	100 @150mA	\$0.29
2277391	On Semiconductor	MPS6565	NPN General Purpose Amplifier 45V 200mA TO-92	TO-92-3	NPN	45V	60V	160@ 10mA	\$0.19
2277199	On Semiconductor	BC237A	NPN Epitaxial Silicon Transistor TO-92 with DC	TO-92-3	NPN	50V	.83V	120 @ 2mA	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
			Current Gain 120-220						
2277207	On Semiconductor	BC237C	NPN Epitaxial Silicon Transistor TO-92 with DC Current Gain 380-800	TO-92-3	NPN	50V	.83V	380 @2mA	\$0.25
2277543	Motorola	BC182AP	NPN Epitaxial Silicon Amplifier Transistor 60V 100mA TO-92	TO-92-3	NPN	50V	60V	120 @ 3mA	\$0.25
2277263	On Semiconductor	2N3859A	NPN General Purpose Amplifier 60V 500mA TO-92	TO-92-3	NPN	60V	60V	100 @ 1mA	\$0.25
787616	Major Brands	PN3568	Transistor PN3568 General Purpose NPN 60 Volt 1 Amp TO-92	TO-92-3	NPN	60V	80V	40 @ .03A	\$0.99
2277503	On Semiconductor	BC546B	BC546B NPN Epitaxial Silicon Transistor 80V 100mA TO-92	TO-92-3	NPN	65V	80V	110 @ 2mA	\$0.25
2277623	Micro Electronics	BC174	NPN Silicon Planar Transistor 65Vceo 80 Vcbo TO-92	TO-92-3	NPN	65V	80V	120 @ 2mA	\$0.79
2290207	Major Brands	PN2243A	NPN Transistor 80V 120hFE 150mA TO-92	TO-92-3	NPN	80V	120V	120 @ 15mA	\$0.89
26462	Major Brands	MPSA06	Transistor MPSA06 General Purpose NPN 80 Volt 0.5 Amp TO-92	TO-92-3	NPN	80V	80V	100,000 @ .01A	\$0.29
2277567	Motorola	2N4870	PNP Unijunction Transistor 30V 1500mA	TO-92-3	PN	-	-		\$1.95
261121	NTE Electronics	NTE6410	Transistor NTE6410 UJT 30 Volt 300mw TO-92	TO-92-3	PN	2.5V	35V		\$4.95
2277151	Fairchild Semiconductor	KSA1013OBU	PNP Expitaxial Silicon Transistor TO-92	TO-92-3	PNP	-160V	-160V	60 @ -200mA	\$0.35
2286047	Toshiba	2SA1302-0	Silicon PNP Epitaxial BJT Bipolar Transistor 200V 15A	TO-92-3	PNP	-200V	-200V	55 @ 1mA	\$3.95
2169521	On Semiconductor	BC557C	BC557C BJT PNP Transistor	TO-92-3	PNP	-45V	-50V	800 @ -2A	\$0.25
2277343	On Semiconductor	MPSL51	PNP General Purpose Amplifier 100V 200mA TO-92	TO-92-3	PNP	100V	100V	40 @50mA	\$0.25
2277279	On Semiconductor	2N5830	PNP Silicon High Current Transistor 100V 200mA TO-92	TO-92-3	PNP	100V	120V	80 @10mA	\$0.25
2277167	Fairchild Semiconductor	PN4258	PNP Switching BJT 12V 200mA TO-92	TO-92-3	PNP	12V	12V	30 @ 10mA	\$0.99
210649	Major Brands	2N5401	Transistor 2N5401 TO-92 PNP 150 Volt 300ma	TO-92-3	PNP	150V	160V	60 @ .01A	\$0.25
214623	Major Brands	2N4126	2N4126 PNP General Purpose Amplifier TO-92 25V 200mA	TO-92-3	PNP	25V	25V	360 @ .20A	\$0.39
2277335	On Semiconductor	MPS3393	PNP General Purpose Amplifier 25V 100mA TO-92	TO-92-3	PNP	25V	25V	90 @ 2mA	\$0.39
2277319	On Semiconductor	BC309A	PNP Epitaxial Silicon Transistor 25V 100mA TO-92 with Current Gain 120-220	TO-92-3	PNP	25V	30V	120 @ 2mA	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Supplier Package	Transistor Polarity	Maximum Collector Emitter Voltage	Maximum Collector Base Voltage	Minimum DC Current Gain	Price 1
2277303	On Semiconductor	BC308B	PNP Epitaxial Silicon Transistor 25V 100mA TO-92 with Current Gain 180-460	TO-92-3	PNP	25V	30V	180 @ 2mA	\$0.25
2277311	On Semiconductor	BC308C	PNP Epitaxial Silicon Transistor 25V 100mA TO-92 with Current Gain 380-800	TO-92-3	PNP	25V	30V	380 @ 2mA	\$0.25
2277295	On Semiconductor	2SA950	PNP General Amplifier Transistor 25V 800mA TO-92	TO-92-3	PNP	25V	35V	100 @ 100mA	\$0.69
38375	Major Brands	2N3906RLRP	<p>Transistor 2N3906 PNP General Purpose (Tape/Reel/Ammo)</p>	TO-92-3	PNP	40V	40V	100 @ .01A	\$0.25
178618	Major Brands	2N3906BU	Transistor 2N3906 PNP SIL General Purpose TO-92 (bulk)	TO-92-3	PNP	40V	40V	100 @ .01A	\$0.25
38447	Major Brands	2N4403	Transistor 2N4403 General Purpose PNP 40 Volt 0.6 Amp TO-92	TO-92-3	PNP	40V	40V	100 @ .15A	\$0.25
62287	Major Brands	2N3905	Transistor General Purpose BJT PNP 40 Volt 0.2 Amp 3-Pin TO-92	TO-92-3	PNP	40V	40V	50 @ 10mA	\$0.55
28644	Major Brands	PN2907BU	Transistor PN2907 General Purpose PNP 40 Volt 0.6 Amp TO-92	TO-92-3	PNP	40V	60V	100 @ .15A	\$0.25
1215986	Fairchild Semiconductor	BC327	Transistor BC327 General Purpose PNP 45 Volt 0.8 Amp	TO-92-3	PNP	45V	50V	100 @ .10A	\$0.25
2277191	On Semiconductor	BC212A	PNP Silicon BJT 50V 200mA TO-92 with DC Current Gain 100-300	TO-92-3	PNP	50V	60V	100 @ 2mA	\$0.49
178520	Major Brands	PN2907ABU	Transistor PN2907A PNP SIL General Purpose BJT TO-92	TO-92-3	PNP	60V	60V	100 @ .15A	\$0.25
211342	Major Brands	MPS2907A	MPS2907A - General Purpose PNP Silicon Transistor TO-92	TO-92-3	PNP	60V	60V	100 @ .15A	\$0.25
2290591	Major Brands	PN2907ATA	PN2907A Transistor PNP SIL General Purpose Amplifier TO-92	TO-92-3	PNP	60V	60V	100 @ .15A @ 10V	\$0.25
1944951	Micro Electronics	PN4355	Transistor PN4355 General Purpose PNP 60 Volt 0.8 Amp TO-92	TO-92-3	PNP	60V	60V	5 @ .05A	\$0.39
2277367	On Semiconductor	BC640-016	Transistor BC640-016G PNP Silicon High Current - 80V 500mA TO-92	TO-92-3	PNP	80V	80V	100 @ 150mA	\$0.29
2130634	Velleman	K/TRANS1	Set of 100 Transistors						\$13.95
2095411	Major Brands	EPX-002P	Transistor Mounting Pads TO-92 : TO-98 : TO-18 : TO-72 Polypropolene White						\$0.25