



[Click Here to Request a Large Quantity Quote](#)

[NiCd & NiMH Rechargeable Batteries](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Cell Size	Volts (VDC)	Nominal Capacity (mAh)	Chemistry	Size	Termination	Features	Battery Type	Price 1
244620	Tenergy Corporation	10005	9V	8.4	200	Nickel Metal Hydride	1.04"L x 0.62"W x 1.91"H	Snaps	Rechargeable	Secondary	\$7.95
261657	Jameco Reliapro	N700AA/BTN	AA	1.2	700	Nickel Cadmium	0.55"Dia. x 1.90"L	Button Top	Rechargeable	Primary	\$1.95
244515	Jameco Reliapro	20104	AA	1.2	1000	Nickel Cadmium	0.55"Dia. x 1.90"L	Button Top	Rechargeable	Primary	\$1.89
2197492	Jameco Reliapro	AA2300-2PKG	AA	1.2	2300	Nickel Metal Hydride	0.55"Dia. x 1.90"L	Button Top	Rechargeable	Primary	\$2.95
2127777	Tenergy Corporation	10320	AA	1.2	2500	Nickel Metal Hydride	0.57"Dia. x 1.99"L	Button Top	Rechargeable	Primary	\$3.95
231095	Tenergy Corporation	10405	AAA	1.2	1000	Nickel Metal Hydride	0.40"Dia x 1.79"L	Button Top	Rechargeable	Primary	\$2.75
2129342	Dantona Industries	COMP-16-3NMH	Cylinder	3.6	80	Nickel Metal Hydride	0.61"Dia. x 0.72"L	PC mount, 3-pin	Rechargeable	Secondary	\$7.95
2137473	Evergreen	NHB60H3A2H	Cylinder	3.6	80	Nickel Metal Hydride	0.63"Dia. x 0.75"L	PC mount, 2-pin	Rechargeable	Secondary	\$4.95
2286351	Evergreen	GP60BNK	Cylinder	3.6	60	Nickel Cadmium	0.64"Dia. x 0.74"L	PC mount, 3-pin	Rechargeable	Secondary	\$1.95
2285815	Tysonic	GP50NH	N	1.2	520	Nickel Metal Hydride	0.46"Dia. x 1.16"L	Button Top	Rechargeable	Primary	\$1.95
244574	Jameco Reliapro	SC-1500	Sub-C	1.2	1500	Nickel Cadmium	0.87"Dia x 1.65"L	Flat Top	Rechargeable	Primary	\$3.29