



[Click Here to Request a Large Quantity Quote](#)

Ceramic Disc Capacitors

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 2301399 | Jameco Valuepro | DC.5-NP0 | 0.0000005 | 0.5 | 0.5 pF | 50 | +/-0.25 | 5 | 26 | 3 | \$2.95 | \$2.75 |
| 2301519 | Jameco Valuepro | DC1/1200 | 0.000001 | 1 | 1 pF | 1200 | 10 | 9 | 39 | 7 | \$0.65 | \$0.55 |
| 2301407 | Jameco Valuepro | DC1-NP0 | 0.000001 | 1 | 1 pF | 50 | +/-0.50 | 5 | 38 | 3 | \$0.25 | \$0.15 |
| 2301415 | Jameco Valuepro | DC1.2-NP0 | 0.0000012 | 1.2 | 1.2 pF | 50 | +/-0.25 | 5 | 24 | 5 | \$0.25 | \$0.15 |
| 2301423 | Jameco Valuepro | DC2-NP0 | 0.000002 | 2 | 2 pF | 50 | +/-0.25 | 7 | 42 | 6 | \$0.25 | \$0.15 |
| 2301431 | Jameco Valuepro | DC2.2-N080 | 0.0000022 | 2.2 | 2.2 pF | 50 | +/-0.50 | 4 | 34 | 3 | \$0.25 | \$0.15 |
| 2300615 | Jameco Valuepro | DC10/4000-X5F | 0.00001 | 10 | 10 pF | 3000 | 20 | 9 | 40 | 7 | \$0.59 | \$0.49 |
| 15333 | Jameco Valuepro | DC10/50 | 0.00001 | 10 | 10 pF | 50 | 20 | 5 | 28 | 6 | \$0.25 | \$0.15 |
| 2301439 | Jameco Valuepro | DC11-NP0 | 0.000011 | 11 | 11 pF | 50 | 5 | 4 | 32 | 3 | \$0.25 | \$0.15 |
| 2301527 | Jameco Valuepro | DC12/4000-NP0 | 0.000012 | 12 | 12 pF | 4000 | 5 | 8 | 37 | 8 | \$0.89 | \$0.79 |
| 2301447 | Jameco Valuepro | DC12-NP0 | 0.000012 | 12 | 12 pF | 50 | 5 | 5 | 26 | 5 | \$0.25 | \$0.15 |
| 2301535 | Jameco Valuepro | DC13/1000-NP0 | 0.000013 | 13 | 13 pF | 1000 | 5 | 7 | 40 | 6 | \$0.65 | \$0.55 |
| 2301455 | Jameco Valuepro | DC13-NP0 | 0.000013 | 13 | 13 pF | 50 | 10 | 5 | 26 | 7 | \$0.25 | \$0.15 |
| 2301463 | Jameco Valuepro | DC14-N150 | 0.000014 | 14 | 14 pF | 50 | 5 | 5 | 28 | 6 | \$0.25 | \$0.15 |
| 2301471 | Jameco Valuepro | DC15/1000-N1500 | 0.000015 | 15 | 15 pF | 1000 | 5 | 7 | 40 | 7 | \$0.65 | \$0.55 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 2301543 | Jameco Valuepro | DC15/4000-NP0 | 0.000015 | 15 | 15 pF | 4000 | 5 | 8 | 40 | 8 | \$0.89 | \$0.79 |
| 2301159 | Jameco Valuepro | DC15/50-NP0 | 0.000015 | 15 | 15 pF | 50 | 10 | 6 | 26 | 6 | \$0.25 | \$0.15 |
| 2280727 | Jameco Valuepro | DC15 | 0.000015 | 15 | 15 pF | 500 | 5 | 4 | 30 | 5 | \$0.25 | \$0.12 |
| 2301551 | Jameco Valuepro | DC18/3000-N330 | 0.000018 | 18 | 18 pF | 3000 | 5 | 12 | 38 | 10 | \$0.69 | \$0.59 |
| 2301167 | Jameco Valuepro | DC18 | 0.000018 | 18 | 18 pF | 50 | 10 | 4 | 30 | 5 | \$0.25 | \$0.12 |
| 2301511 | Jameco Valuepro | DC18/50-5 | 0.000018 | 18 | 18 pF | 50 | 5 | 4 | 32 | 3 | \$0.25 | \$0.15 |
| 2301287 | Jameco Valuepro | DC20/2000-NP0 | 0.00002 | 20 | 20 pF | 2000 | 5 | 8 | 38 | 6 | \$0.55 | \$0.45 |
| 2301599 | Jameco Valuepro | DC285/2500-N1500 | 0.00002 | 20 | 20 pF | 4000 | 5 | 10 | 36 | 8 | \$0.69 | \$0.59 |
| 2301479 | Jameco Valuepro | DC20 | 0.00002 | 20 | 20 pF | 50 | 20 | 5 | 26 | 5 | \$0.25 | \$0.15 |
| 2301143 | Jameco Valuepro | DC22/1K-Z5F | 0.000022 | 22 | 22 pF | 1000 | 10 | 6 | 26 | 7 | \$0.65 | \$0.55 |
| 2301295 | Jameco Valuepro | DC22/3000-NP0 | 0.000022 | 22 | 22 pF | 3000 | 5 | 8 | 40 | 8 | \$0.69 | \$0.59 |
| 15405 | Jameco Valuepro | DC22 | 0.000022 | 22 | 22 pF | 50 | 20 | 5 | 32 | 6 | \$0.25 | \$0.15 |
| 2301567 | Jameco Valuepro | DC22/6000-N1500 | 0.000022 | 22 | 22 pF | 6000 | 10 | 16 | 35 | 13 | \$1.19 | \$1.09 |
| 2301175 | Jameco Valuepro | DC24 | 0.000024 | 24 | 24 pF | 50 | 20 | 5 | 26 | 5 | \$0.25 | \$0.15 |
| 2301943 | Jameco Valuepro | DC25 | 0.000025 | 25 | 25 pF | 50 | 10 | 6 | 26 | 4 | \$0.25 | \$0.15 |
| 2280735 | Jameco Valuepro | DC27 | 0.000027 | 27 | 27 pF | 500 | 5 | 5 | 28 | 6 | \$0.25 | \$0.15 |
| 2301671 | Jameco Valuepro | DC33/50-NP0 | 0.00003 | 30 | 30 pF | 50 | 10 | 6 | 26 | 5 | \$0.25 | \$0.15 |
| 332217 | Jameco Valuepro | DC33/50 | 0.000033 | 33 | 33 pF | 50 | 20 | 5 | 28 | 6 | \$0.25 | \$0.15 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 1947028 | Jameco Valuepro | DC33TR | 0.000033 | 33 | 33 pF | 500 | 5 | 5 | 15 | 5 | \$0.25 | \$0.12 |
| 2301775 | Jameco Valuepro | DC36/2000-NP0 | 0.000036 | 36 | 36 pF | 2000 | 5 | 12 | 38 | 10 | \$0.59 | \$0.49 |
| 2301679 | Jameco Valuepro | DC36/50-NP0 | 0.000036 | 36 | 36 pF | 50 | 10 | 8 | 36 | 6 | \$0.25 | \$0.15 |
| 2301783 | Jameco Valuepro | DC39/2000-NP0 | 0.000039 | 39 | 39 pF | 2000 | 10 | 10 | 9 | 6 | \$0.55 | \$0.45 |
| 2301687 | Jameco Valuepro | DC39/50-NP0 | 0.000039 | 39 | 39 pF | 50 | 10 | 7 | 28 | 6 | \$0.25 | \$0.15 |
| 2301791 | Jameco Valuepro | DC39/6000-N1500 | 0.000039 | 39 | 39 pF | 6000 | 10 | 16 | 38 | 14 | \$1.09 | \$0.99 |
| 2301695 | Jameco Valuepro | DC40/50 | 0.00004 | 40 | 40 pF | 50 | 5 | 5 | 23 | 3 | \$0.25 | \$0.15 |
| 2301703 | Jameco Valuepro | DC43/50-N750 | 0.000043 | 43 | 43 pF | 50 | 10 | 5 | 25 | 5 | \$0.25 | \$0.15 |
| 2301039 | Jameco Valuepro | DC47/1000 | 0.000047 | 47 | 47 pF | 1000 | 10 | 7 | 17 | 6 | \$0.65 | \$0.55 |
| 2299263 | Jameco Valuepro | DC47/2000 | 0.000047 | 47 | 47 pF | 2000 | 10 | 9 | 32 | 8 | \$0.55 | \$0.45 |
| 2299279 | Jameco Valuepro | DC47/2000-N2200 | 0.000047 | 47 | 47 pF | 2000 | 10 | 13 | 40 | 10 | \$0.55 | \$0.45 |
| 2299271 | Jameco Valuepro | DC47/2000-N750 | 0.000047 | 47 | 47 pF | 2000 | 10 | 15 | 44 | 14 | \$0.69 | \$0.59 |
| 2299255 | Jameco Valuepro | DC47/2000-5 | 0.000047 | 47 | 47 pF | 2000 | 5 | 5 | 28 | 6 | \$0.65 | \$0.55 |
| 2299287 | Jameco Valuepro | DC47/3000 | 0.000047 | 47 | 47 pF | 3000 | 10 | 8 | 40 | 8 | \$0.69 | \$0.59 |
| 2299295 | Jameco Valuepro | DC47/4000 | 0.000047 | 47 | 47 pF | 4000 | 10 | 15 | 40 | 13 | \$0.79 | \$0.69 |
| 2301079 | Jameco Valuepro | DC47/10 | 0.000047 | 47 | 47 pF | 50 | 10 | 5 | 28 | 6 | \$0.25 | \$0.15 |
| 15512 | Jameco Valuepro | DC47 | 0.000047 | 47 | 47 pF | 50 | 20 | 5 | 26 | 6 | \$0.25 | \$0.15 |
| 2300831 | Jameco Valuepro | DC47/50-NP0 | 0.000047 | 47 | 47 pF | 50 | 5 | 5 | 26 | 3 | \$0.25 | \$0.17 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 1947036 | Jameco Valuepro | DC47TR | 0.000047 | 47 | 47 pF | 500 | 5 | 6 | 28 | 6 | \$0.25 | \$0.12 |
| 2299303 | Jameco Valuepro | DC47/5000-N1500 | 0.000047 | 47 | 47 pF | 5000 | 10 | 15 | 12 | 14 | \$1.09 | \$0.99 |
| 2300535 | Jameco Valuepro | DC47/6000-N1500 | 0.000047 | 47 | 47 pF | 6000 | 10 | 15 | 39 | 10 | \$1.19 | \$1.09 |
| 2300839 | Jameco Valuepro | DC47/63 | 0.000047 | 47 | 47 pF | 63 | 5 | 8 | 32 | 6 | \$0.29 | \$0.18 |
| 2301047 | Jameco Valuepro | DC50/1000 | 0.00005 | 50 | 50 pF | 1000 | 10 | 7 | 7 | 6 | \$0.25 | \$0.15 |
| 2300847 | Jameco Valuepro | DC50/50 | 0.00005 | 50 | 50 pF | 50 | 10 | 4 | 32 | 3 | \$0.25 | \$0.15 |
| 2301711 | Jameco Valuepro | DC51/1K-N470 | 0.000051 | 51 | 51 pF | 1000 | 5 | 9 | 42 | 6 | \$0.89 | \$0.79 |
| 2301375 | Jameco Valuepro | DC56/1000 | 0.000056 | 56 | 56 pF | 1000 | 10 | 7 | 18 | 7 | \$0.65 | \$0.55 |
| 2300543 | Jameco Valuepro | DC56/3000-N750 | 0.000056 | 56 | 56 pF | 3000 | 10 | 14 | 40 | 10 | \$0.39 | \$0.29 |
| 2300567 | Jameco Valuepro | DC56/3000/10-N750 | 0.000056 | 56 | 56 pF | 3000 | 10 | 17 | 40 | 10 | \$0.69 | \$0.59 |
| 2300575 | Jameco Valuepro | DC56/4000-N1500 | 0.000056 | 56 | 56 pF | 4000 | 10 | 18 | 35 | 13 | \$0.89 | \$0.79 |
| 2301719 | Jameco Valuepro | DC56/50/10 | 0.000056 | 56 | 56 pF | 50 | 10 | 6 | 28 | 6 | \$0.25 | \$0.15 |
| 2300815 | Jameco Valuepro | DC56/50 | 0.000056 | 56 | 56 pF | 50 | 5 | 6 | 28 | 5 | \$0.25 | \$0.15 |
| 2300583 | Jameco Valuepro | DC56/5000 | 0.000056 | 56 | 56 pF | 5000 | 10 | 12 | 44 | 10 | \$0.89 | \$0.79 |
| 2300591 | Jameco Valuepro | DC56/6000 | 0.000056 | 56 | 56 pF | 6000 | 10 | 10 | 35 | 10 | \$1.09 | \$0.99 |
| 2301727 | Jameco Valuepro | DC62/50-N750 | 0.000062 | 62 | 62 pF | 50 | 5 | 6 | 32 | 6 | \$0.25 | \$0.15 |
| 2301111 | Jameco Valuepro | DC68/1K | 0.000068 | 68 | 68 pF | 1000 | 10 | 6 | 40 | 5 | \$0.65 | \$0.55 |
| 2301807 | Jameco Valuepro | DC68/3000-NP0 | 0.000068 | 68 | 68 pF | 3000 | 5 | 13 | 40 | 8 | \$0.69 | \$0.59 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 15552 | Arndt | DC68 | 0.000068 | 68 | 68 pF | 50 | 5 | 8 | 30 | 5 | \$0.25 | \$0.15 |
| 2300607 | Jameco Valuepro | DC90/5000 | 0.00009 | 90 | 90 pF | 5000 | 10 | 14 | 46 | 12 | \$0.89 | \$0.79 |
| 2300599 | Jameco Valuepro | DC91/3000 | 0.000091 | 91 | 91 pF | 3000 | 10 | 18 | 38 | 10 | \$0.59 | \$0.49 |
| 2300823 | Jameco Valuepro | DC91/50 | 0.000091 | 91 | 91 pF | 50 | 5 | 10 | 26 | 5 | \$0.25 | \$0.15 |
| 1947044 | Jameco Valuepro | DC100TR | 0.0001 | 100 | 100 pF | 100 | 10 | 7 | 26 | 5 | \$0.25 | \$0.19 |
| 2301055 | Jameco Valuepro | DC100/1000 | 0.0001 | 100 | 100 pF | 1000 | 10 | 6 | 22 | 5 | \$0.69 | \$0.59 |
| 2280783 | Jameco Valuepro | DC100/12K | 0.0001 | 100 | 100 pF | 12000 | 20 | 8 | 40 | 9 | \$1.95 | \$1.75 |
| 2300623 | Jameco Valuepro | DC100/1400 | 0.0001 | 100 | 100 pF | 1400 | 20 | 10 | 11 | 10 | \$0.69 | \$0.59 |
| 2300631 | Jameco Valuepro | DC100/1500 | 0.0001 | 100 | 100 pF | 1500 | 10 | 7 | 32 | 6 | \$0.69 | \$0.59 |
| 2300775 | Jameco Valuepro | DC100/15000-X5F | 0.0001 | 100 | 100 pF | 15000 | 10 | 24 | 46 | 14 | \$2.29 | \$2.19 |
| 2300783 | Jameco Valuepro | DC100/15000-Z5U | 0.0001 | 100 | 100 pF | 15000 | 2 | 17 | 52 | 20 | \$3.95 | \$3.59 |
| 2300639 | Jameco Valuepro | DC100/2000 | 0.0001 | 100 | 100 pF | 2000 | 10 | 5 | 18 | 6 | \$0.65 | \$0.55 |
| 2300655 | Jameco Valuepro | DC100/2000-N750 | 0.0001 | 100 | 100 pF | 2000 | 10 | 19 | 6 | 8 | \$0.69 | \$0.59 |
| 2300647 | Jameco Valuepro | DC100/2000-20 | 0.0001 | 100 | 100 pF | 2000 | 20 | 4 | 13 | 6 | \$0.55 | \$0.45 |
| 2300679 | Jameco Valuepro | DC100/3000-10 | 0.0001 | 100 | 100 pF | 3000 | 10 | 8 | 18 | 8 | \$0.69 | \$0.59 |
| 2300695 | Jameco Valuepro | DC100/3000-N1500-22 | 0.0001 | 100 | 100 pF | 3000 | 10 | 22 | 36 | 10 | \$0.65 | \$0.55 |
| 2300687 | Jameco Valuepro | DC100/3000-N1500 | 0.0001 | 100 | 100 pF | 3000 | 20 | 15 | 36 | 10 | \$0.59 | \$0.49 |
| 2300711 | Jameco Valuepro | DC100/3000-5 | 0.0001 | 100 | 100 pF | 3000 | 5 | 10 | 50 | 9 | \$0.69 | \$0.59 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 2300671 | Jameco Valuepro | DC100/3000-N1500-13 | 0.0001 | 100 | 100 pF | 3000 | 5 | 13 | 44 | 10 | \$0.69 | \$0.59 |
| 2300663 | Jameco Valuepro | DC100/3000 | 0.0001 | 100 | 100 pF | 3000 | 5 | 15 | 38 | 8 | \$0.69 | \$0.59 |
| 2300727 | Jameco Valuepro | DC100/3000-N1500-16 | 0.0001 | 100 | 100 pF | 3000 | 5 | 16 | 40 | 10 | \$0.69 | \$0.59 |
| 2300703 | Jameco Valuepro | DC100/3000-N750 | 0.0001 | 100 | 100 pF | 3000 | 5 | 17 | 40 | 15 | \$0.79 | \$0.69 |
| 2300719 | Jameco Valuepro | DC100/3000-N1500-20 | 0.0001 | 100 | 100 pF | 3000 | 5 | 20 | 44 | 10 | \$0.69 | \$0.59 |
| 2300751 | Jameco Valuepro | DC100/4000-N2200 | 0.0001 | 100 | 100 pF | 4000 | 10 | 15 | 38 | 13 | \$0.89 | \$0.79 |
| 2300735 | Jameco Valuepro | DC100/4000-Z5U | 0.0001 | 100 | 100 pF | 4000 | 10 | 20 | 7 | 10 | \$0.69 | \$0.59 |
| 2300743 | Jameco Valuepro | DC100/4000-N1500 | 0.0001 | 100 | 100 pF | 4000 | 10 | 20 | 36 | 12 | \$0.79 | \$0.69 |
| 15341 | Jameco Valuepro | DC100 | 0.0001 | 100 | 100 pF | 50 | 20 | 5 | 26 | 6 | \$0.25 | \$0.15 |
| 2300879 | Jameco Valuepro | DC100/50-4 | 0.0001 | 100 | 100 pF | 50 | 5 | 4 | 8 | 5 | \$0.25 | \$0.13 |
| 2300855 | Jameco Valuepro | DC100/50 | 0.0001 | 100 | 100 pF | 50 | 5 | 5 | 28 | 3 | \$0.25 | \$0.15 |
| 2300759 | Jameco Valuepro | DC100/6000-N1500 | 0.0001 | 100 | 100 pF | 6000 | 10 | 18 | 36 | 13 | \$1.19 | \$1.09 |
| 2300767 | Jameco Valuepro | DC100/6000-Z5U | 0.0001 | 100 | 100 pF | 6000 | 20 | 16 | 36 | 13 | \$1.19 | \$1.09 |
| 2300863 | Jameco Valuepro | DC110/50 | 0.00011 | 110 | 110 pF | 50 | 5 | 5 | 26 | 4 | \$0.25 | \$0.16 |
| 2301735 | Jameco Valuepro | DC130/50-NP0 | 0.00013 | 130 | 130 pF | 50 | 5 | 7 | 32 | 6 | \$0.25 | \$0.16 |
| 2301799 | Jameco Valuepro | DC130/6000-N1500 | 0.00013 | 130 | 130 pF | 6000 | 5 | 20 | 34 | 14 | \$1.19 | \$1.09 |
| 2301815 | Jameco Valuepro | DC140/4000-N2200 | 0.00014 | 140 | 140 pF | 4000 | 10 | 19 | 8 | 11 | \$0.79 | \$0.69 |
| 1947087 | Jameco Valuepro | DC150TR | 0.00015 | 150 | 150 pF | 100 | +80/-20 | 5 | 19 | 6 | \$0.29 | \$0.22 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 1947052 | Jameco Valuepro | DC150/10TR | 0.00015 | 150 | 150 pF | 100 | 10 | 8 | 28 | 5 | \$0.25 | \$0.19 |
| 2301951 | Jameco Valuepro | DC150/1000-Z5R | 0.00015 | 150 | 150 pF | 1000 | 10 | 7 | 23 | 7 | \$0.69 | \$0.59 |
| 2301303 | Jameco Valuepro | DC150/2000 | 0.00015 | 150 | 150 pF | 2000 | 10 | 5 | 38 | 9 | \$0.55 | \$0.45 |
| 2301823 | Jameco Valuepro | DC150/2000-N750 | 0.00015 | 150 | 150 pF | 2000 | 5 | 17 | 37 | 10 | \$0.65 | \$0.55 |
| 2301311 | Jameco Valuepro | DC150/3000-N750 | 0.00015 | 150 | 150 pF | 3000 | 10 | 22 | 35 | 12 | \$0.89 | \$0.79 |
| 2301743 | Jameco Valuepro | DC150/50-Y5P | 0.00015 | 150 | 150 pF | 50 | 10 | 6 | 28 | 5 | \$0.25 | \$0.16 |
| 2301191 | Jameco Valuepro | DC150/50 | 0.00015 | 150 | 150 pF | 50 | 10 | 8 | 28 | 6 | \$0.25 | \$0.16 |
| 2301575 | Jameco Valuepro | DC150/5000-N1500 | 0.00015 | 150 | 150 pF | 5000 | 10 | 24 | 40 | 10 | \$1.09 | \$0.99 |
| 2301327 | Jameco Valuepro | DC160/4000 | 0.00016 | 160 | 160 pF | 4000 | 10 | 23 | 36 | 14 | \$0.79 | \$0.69 |
| 2301751 | Jameco Valuepro | DC160/50-NP0 | 0.00016 | 160 | 160 pF | 50 | 5 | 12 | 28 | 6 | \$0.25 | \$0.16 |
| 2301759 | Jameco Valuepro | DC180/50 | 0.00018 | 180 | 180 pF | 50 | 10 | 6 | 28 | 5 | \$0.25 | \$0.16 |
| 2301831 | Jameco Valuepro | DC180/5000-Y5F | 0.00018 | 180 | 180 pF | 5000 | 10 | 14 | 35 | 13 | \$1.09 | \$0.99 |
| 2301767 | Jameco Valuepro | DC200/50-Y5P | 0.0002 | 200 | 200 pF | 50 | 20 | 6 | 28 | 6 | \$0.25 | \$0.16 |
| 2302143 | Jameco Valuepro | DC200/4000 | 0.00022 | 220 | 200 pF | 4000 | 5 | 10 | 40 | 9 | \$0.79 | \$0.69 |
| 2301151 | Jameco Valuepro | DC220/1K-Z5F | 0.00022 | 220 | 220 pF | 1000 | 10 | 6 | 32 | 7 | \$0.69 | \$0.59 |
| 2302087 | Jameco Valuepro | DC220/2000-N1500 | 0.00022 | 220 | 220 pF | 2000 | 10 | 14 | 40 | 10 | \$0.55 | \$0.45 |
| 1947132 | Jameco Valuepro | DC220 | 0.00022 | 220 | 220 pF | 50 | 10 | 4 | 5 | 6 | \$0.25 | \$0.14 |
| 2281031 | Jameco Valuepro | DC220-10 | 0.00022 | 220 | 220 pF | 50 | 10 | 5 | 28 | 6 | \$0.25 | \$0.16 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 15413 | Jameco Valuepro | DC220-20 | 0.00022 | 220 | 220 pF | 50 | 20 | 5 | 26 | 7 | \$0.25 | \$0.15 |
| 2301959 | Jameco Valuepro | DC240/1000 | 0.00024 | 240 | 240 pF | 1000 | 10 | 7 | 32 | 7 | \$0.69 | \$0.59 |
| 2301967 | Jameco Valuepro | DC250-NPO | 0.00025 | 250 | 250 pF | 50 | 10 | 9 | 26 | 7 | \$0.25 | \$0.19 |
| 2302119 | Jameco Valuepro | DC250/6000-N2200 | 0.00025 | 250 | 250 pF | 6000 | 5 | 25 | 40 | 13 | \$1.29 | \$1.19 |
| 2302111 | Jameco Valuepro | DC260/2000-N3300 | 0.00026 | 260 | 260 pF | 2000 | 10 | 15 | 36 | 10 | \$0.55 | \$0.45 |
| 2301583 | Jameco Valuepro | DC270/2000-Z5F | 0.00027 | 270 | 270 pF | 2000 | 20 | 13 | 40 | 7 | \$0.55 | \$0.45 |
| 2301975 | Jameco Valuepro | DC270 | 0.00027 | 270 | 270 pF | 50 | 10 | 4 | 30 | 4 | \$0.25 | \$0.16 |
| 2301983 | Jameco Valuepro | DC270/50 | 0.00027 | 270 | 270 pF | 50 | 5 | 6 | 28 | 5 | \$0.25 | \$0.19 |
| 2301591 | Jameco Valuepro | DC280/4000-N1500 | 0.00028 | 280 | 280 pF | 4000 | 10 | 26 | 40 | 7 | \$0.89 | \$0.79 |
| 1947301 | Jameco Valuepro | DC330TR | 0.00033 | 330 | 330 pF | 100 | +80/-20 | 5 | 16 | 5 | \$0.29 | \$0.22 |
| 2301495 | Jameco Valuepro | DC330/1000-Y5P | 0.00033 | 330 | 330 pF | 1000 | 10 | 7 | 26 | 6 | \$0.69 | \$0.59 |
| 2301487 | Jameco Valuepro | DC330/50-Y5V | 0.00033 | 330 | 330 pF | 50 | 10 | 4 | 26 | 5 | \$0.25 | \$0.16 |
| 1947319 | Jameco Valuepro | DC470TR | 0.00047 | 470 | 470 pF | 100 | +80/-20 | 5 | 16 | 5 | \$0.29 | \$0.22 |
| 2301127 | Jameco Valuepro | DC470/1K-Z5F | 0.00047 | 470 | 470 pF | 1000 | 10 | 7 | 6 | 6 | \$0.69 | \$0.59 |
| 2301183 | Jameco Valuepro | DC470/1K-N750 | 0.00047 | 470 | 470 pF | 1000 | 10 | 12 | 26 | 7 | \$0.59 | \$0.49 |
| 2302079 | Jameco Valuepro | DC470/2000-Y5F | 0.00047 | 470 | 470 pF | 2000 | 10 | 8 | 40 | 8 | \$0.69 | \$0.59 |
| 2301319 | Jameco Valuepro | DC470/2500 | 0.00047 | 470 | 470 pF | 2500 | 10 | 19 | 32 | 11 | \$0.69 | \$0.59 |
| 2301607 | Jameco Valuepro | DC470/2500-N3300 | 0.00047 | 470 | 470 pF | 2500 | 10 | 23 | 36 | 10 | \$0.69 | \$0.59 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 2301991 | Jameco Valuepro | DC470/50 | 0.00047 | 470 | 470 pF | 50 | 10 | 5 | 30 | 3 | \$0.25 | \$0.19 |
| 15528 | Jameco Valuepro | DC470 | 0.00047 | 470 | 470 pF | 50 | 20 | 4 | 12 | 3 | \$0.25 | \$0.19 |
| 2301999 | Jameco Valuepro | DC500-25 | 0.0005 | 500 | 500 pF | 25 | 10 | 6 | 23 | 5 | \$0.59 | \$0.49 |
| 2302007 | Jameco Valuepro | DC500-50 | 0.0005 | 500 | 500 pF | 50 | 10 | 6 | 28 | 6 | \$0.29 | \$0.19 |
| 2302015 | Jameco Valuepro | DC560 | 0.00056 | 560 | 560 pF | 50 | 10 | 10 | 28 | 6 | \$0.29 | \$0.19 |
| 2301199 | Jameco Valuepro | DC560/50-Y5E | 0.00056 | 560 | 560 pF | 50 | 20 | 5 | 22 | 5 | \$0.25 | \$0.16 |
| 2302023 | Jameco Valuepro | DC680/1K | 0.00068 | 680 | 680 pF | 1000 | 10 | 6 | 25 | 6 | \$0.69 | \$0.59 |
| 2301335 | Jameco Valuepro | DC680/1500-N1500 | 0.00068 | 680 | 680 pF | 1500 | 5 | 20 | 7 | 7 | \$0.79 | \$0.69 |
| 2300871 | Jameco Valuepro | DC680/50 | 0.00068 | 680 | 680 pF | 50 | 10 | 4 | 30 | 3 | \$0.29 | \$0.19 |
| 2301343 | Jameco Valuepro | DC700/2000-N2200 | 0.0007 | 700 | 700 pF | 2000 | 10 | 22 | 37 | 10 | \$0.69 | \$0.59 |
| 2162759 | Arndt | DC820 | 0.00082 | 820 | 820 pF | 1000 | 20 | 7 | 34 | 7 | \$0.69 | \$0.59 |
| 2300791 | Jameco Valuepro | DC820/6000-Y5P | 0.00082 | 820 | 820 pF | 6000 | 10 | 17 | 36 | 14 | \$1.19 | \$1.09 |
| 2301087 | Jameco Valuepro | DC910 | 0.00091 | 910 | 910 pF | 1000 | 20 | 7 | 40 | 6 | \$0.49 | \$0.45 |
| 1947343 | Arndt | DC.001TR | 0.001 | 1000 | 0.001 µF | 100 | +80/-20 | 4 | 14 | 5 | \$0.29 | \$0.22 |
| 2301119 | Jameco Valuepro | DC.001/100-Y5U | 0.001 | 1000 | 0.001 µF | 100 | 20 | 7 | 40 | 6 | \$0.29 | \$0.19 |
| 2301103 | Jameco Valuepro | DC.001/1K-Y5P | 0.001 | 1000 | 0.001 µF | 1000 | 10 | 7 | 28 | 6 | \$0.29 | \$0.25 |
| 332436 | Jameco Valuepro | DC.001/1K | 0.001 | 1000 | 0.001 µF | 1000 | 20 | 5 | 26 | 5 | \$0.69 | \$0.59 |
| 2301095 | Jameco Valuepro | DC.001/1K-Z5U | 0.001 | 1000 | 0.001 µF | 1000 | 20 | 6 | 13 | 6 | \$0.59 | \$0.49 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 2302095 | Jameco Valuepro | DC.001/2000-5 | 0.001 | 1000 | 0.001 µF | 2000 | +50/-20 | 5 | 38 | 8 | \$0.55 | \$0.45 |
| 2301351 | Jameco Valuepro | DC.001/2000-Y5U | 0.001 | 1000 | 0.001 µF | 2000 | 20 | 8 | 14 | 5 | \$0.65 | \$0.55 |
| 2301615 | Jameco Valuepro | DC.001/3000-Y5U | 0.001 | 1000 | 0.001 µF | 3000 | 20 | 8 | 28 | 7 | \$0.59 | \$0.49 |
| 2300999 | Jameco Valuepro | DC.001/3K-Z5U | 0.001 | 1000 | 0.001 µF | 3000 | 20 | 11 | 40 | 5 | \$0.69 | \$0.59 |
| 2301207 | Jameco Valuepro | DC.001/50 | 0.001 | 1000 | 0.001 µF | 50 | +80/-20 | 5 | 25 | 3 | \$0.25 | \$0.16 |
| 2302031 | Jameco Valuepro | DC.001/50-10 | 0.001 | 1000 | 0.001 µF | 50 | 10 | 5 | 32 | 7 | \$0.35 | \$0.25 |
| 15190 | Jameco Valuepro | DC.001 | 0.001 | 1000 | 0.001 µF | 50 | 20 | 5 | 25 | 5 | \$0.25 | \$0.16 |
| 1947415 | Jameco Valuepro | DC.001/500 | 0.001 | 1000 | 0.001 µF | 500 | 10 | 7 | 4 | 5 | \$0.25 | \$0.19 |
| 2301359 | Jameco Valuepro | DC.0012/3000-Y5U | 0.0012 | 1200 | 0.0012 µF | 3000 | +50/-20 | 7 | 38 | 8 | \$0.69 | \$0.59 |
| 2301215 | Jameco Valuepro | DC.0012/50 | 0.0012 | 1200 | 0.0012 µF | 50 | +80/-20 | 5 | 28 | 3 | \$0.25 | \$0.16 |
| 2301135 | Jameco Valuepro | DC.0015/1K | 0.0015 | 1500 | 0.0015 µF | 1000 | 10 | 7 | 40 | 6 | \$1.95 | \$1.75 |
| 2301367 | Jameco Valuepro | DC.0015/2000 | 0.0015 | 1500 | 0.0015 µF | 2000 | 10 | 8 | 28 | 5 | \$0.65 | \$0.55 |
| 2301623 | Jameco Valuepro | DC.0015/3000-Y5F | 0.0015 | 1500 | 0.0015 µF | 3000 | 10 | 13 | 37 | 10 | \$0.79 | \$0.69 |
| 2301279 | Jameco Valuepro | DC.0015/50 | 0.0015 | 1500 | 0.0015 µF | 50 | 10 | 5 | 5 | 5 | \$0.25 | \$0.16 |
| 2301239 | Jameco Valuepro | DC.0018/50-Y5P | 0.0018 | 1800 | 0.0018 µF | 50 | 10 | 7 | 30 | 5 | \$0.25 | \$0.16 |
| 1947327 | Jameco Valuepro | DC.0022TR | 0.0022 | 2200 | 0.0022 µF | 25 | 20 | 4 | 26 | 5 | \$0.49 | \$0.39 |
| 2301503 | Jameco Valuepro | DC.0022/50-Z5U | 0.0022 | 2200 | 0.0022 µF | 50 | +80/-20 | 5 | 24 | 5 | \$0.25 | \$0.16 |
| 2301231 | Jameco Valuepro | DC.0022/50 | 0.0022 | 2200 | 0.0022 µF | 50 | 20 | 5 | 30 | 5 | \$0.29 | \$0.19 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|----------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 2159883 | Arndt | DC.0033/1K | 0.0033 | 3300 | 0.0033 µF | 1000 | 20 | 7 | 28 | 7 | \$1.95 | \$1.75 |
| 2280775 | Jameco Valuepro | DC.0033/3K | 0.0033 | 3300 | 0.0033 µF | 3000 | 10 | 15 | 30 | 9 | \$0.79 | \$0.69 |
| 1947407 | Jameco Valuepro | DC.0033 | 0.0033 | 3300 | 0.0033 µF | 500 | 20 | 9 | 40 | 6 | \$0.29 | \$0.25 |
| 1947335 | Jameco Valuepro | DC.0047TR | 0.0047 | 4700 | 0.0047 µF | 100 | +80/-20 | 5 | 20 | 6 | \$0.29 | \$0.19 |
| 15211 | Jameco Valuepro | DC.0047 | 0.0047 | 4700 | 0.0047 µF | 50 | 20 | 8 | 29 | 6 | \$0.25 | \$0.16 |
| 2301383 | Jameco Valuepro | DC.005/3000-5ZU | 0.005 | 5000 | 0.005 µF | 3000 | 20 | 14 | 6 | 10 | \$0.99 | \$0.89 |
| 2301223 | Jameco Valuepro | DC.005/50-Z5V | 0.005 | 5000 | 0.005 µF | 50 | +80/-20 | 6 | 25 | 6 | \$0.25 | \$0.16 |
| 2301247 | Jameco Valuepro | DC.0068 | 0.0068 | 6800 | 0.0068 µF | 50 | +80/-20 | 4 | 22 | 6 | \$0.25 | \$0.16 |
| 2301255 | Jameco Valuepro | DC.0068/50 | 0.0068 | 6800 | 0.0068 µF | 50 | 10 | 9 | 5 | 6 | \$0.29 | \$0.19 |
| 2301391 | Jameco Valuepro | DC.0082/1500-Z5U | 0.0082 | 8200 | 0.0082 µF | 1500 | 20 | 16 | 40 | 9 | \$1.95 | \$1.75 |
| 2301631 | Jameco Valuepro | DC.0082/3000-Z5U | 0.0082 | 8200 | 0.0082 µF | 3000 | 20 | 22 | 35 | 10 | \$1.95 | \$1.75 |
| 97375 | Jameco Valuepro | DC.01/1K | 0.01 | 10000 | 0.01 µF | 1000 | 20 | 11 | 32 | 7 | \$0.69 | \$0.59 |
| 2302071 | Jameco Valuepro | DC.01/2000-Y5U | 0.01 | 10000 | 0.01 µF | 2000 | +50/-20 | 15 | 6 | 8 | \$0.89 | \$0.79 |
| 2302063 | Jameco Valuepro | DC.01/2000-Y5U | 0.01 | 10000 | 0.01 µF | 2000 | 20 | 15 | 37 | 8 | \$0.89 | \$0.79 |
| 2302103 | Jameco Valuepro | DC.01/2000 | 0.01 | 10000 | 0.01 µF | 2000 | 20 | 18 | 40 | 10 | \$0.99 | \$0.89 |
| 2301271 | Jameco Valuepro | DC.01/50 | 0.01 | 10000 | 0.01 µF | 50 | +80/-20 | 6 | 21 | 6 | \$0.25 | \$0.19 |
| 15229 | Jameco Valuepro | DC.01 | 0.01 | 10000 | 0.01 µF | 50 | 20 | 5 | 26 | 6 | \$0.25 | \$0.16 |
| 2283463 | Vishay | 594-D103M43Z5UL63L6R | 0.01 | 10000 | 0.01 µF | 500 | 20 | 11 | 20 | 6.4 | \$0.85 | \$0.75 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 2302039 | Jameco Valuepro | DC.015/25-Y5P | 0.015 | 15000 | 0.015 µF | 25 | 20 | 5 | 28 | 5 | \$0.39 | \$0.29 |
| 2302047 | Jameco Valuepro | DC.015/50-Z5V | 0.015 | 15000 | 0.015 µF | 50 | +80/-20 | 7 | 28 | 6 | \$0.25 | \$0.16 |
| 332487 | Jameco Valuepro | DC.02/1K | 0.02 | 20000 | 0.02 µF | 1000 | 20 | 17 | 32 | 9 | \$0.79 | \$0.69 |
| 2302055 | Jameco Valuepro | DC.02/50-5ZU | 0.02 | 20000 | 0.02 µF | 50 | +80/-20 | 6 | 25 | 5 | \$0.25 | \$0.17 |
| 15245 | Jameco Valuepro | DC.022 | 0.022 | 22000 | 0.022 µF | 50 | 20 | 4 | 14 | 2 | \$0.25 | \$0.16 |
| 1947351 | Jameco Valuepro | DC.047/25 | 0.047 | 47000 | 0.047 µF | 25 | +80/-20 | 7 | 40 | 5 | \$0.35 | \$0.25 |
| 15253 | Jameco Valuepro | DC.047 | 0.047 | 47000 | 0.047 µF | 50 | 20 | 5 | 28 | 4 | \$0.25 | \$0.16 |
| 2289847 | Jameco Valuepro | DC.047/50 | 0.047 | 47000 | 0.047 µF | 50 | 20 | 8 | 34 | 6 | \$0.25 | \$0.16 |
| 332507 | Jameco Valuepro | DC.05/1K | 0.05 | 50000 | 0.05 µF | 1000 | 20 | 19 | 26 | 9 | \$1.85 | \$1.75 |
| 332516 | Jameco Valuepro | DC.1/1K | 0.1 | 100000 | 0.1 µF | 1000 | 20 | 22 | 28 | 9 | \$1.29 | \$1.09 |
| 2289855 | Jameco Valuepro | DC.1/16 | 0.1 | 100000 | 0.1 µF | 16 | 20 | 7 | 30 | 6 | \$0.29 | \$0.25 |
| 2300983 | Jameco Valuepro | DC.1/25-Y5V | 0.1 | 100000 | 0.1 µF | 25 | +80/-20 | 6 | 26 | 6 | \$0.25 | \$0.16 |
| 2301071 | Jameco Valuepro | DC.1/25-Y5V-8 | 0.1 | 100000 | 0.1 µF | 25 | +80/-20 | 8 | 16 | 6 | \$0.25 | \$0.16 |
| 151116 | Jameco Valuepro | DC.1/25 | 0.1 | 100000 | 0.1 µF | 25 | 20 | 5 | 12 | 2 | \$0.25 | \$0.15 |
| 2300975 | Jameco Valuepro | DC.1/25-Y5T | 0.1 | 100000 | 0.1 µF | 25 | 20 | 8 | 6 | 25 | \$0.25 | \$0.16 |
| 2300967 | Jameco Valuepro | DC.1/25-Y5F | 0.1 | 100000 | 0.1 µF | 25 | 20 | 14 | 7 | 10 | \$0.25 | \$0.16 |
| 2300991 | Jameco Valuepro | DC.1/25-Y5V | 0.1 | 100000 | 0.1 µF | 50 | +80/-20 | 7 | 6 | 5 | \$0.25 | \$0.16 |
| 2146302 | Jameco Valuepro | DC.1/50-6 | 0.1 | 100000 | 0.1 µF | 50 | 20 | 6 | 28 | 5 | \$0.25 | \$0.16 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Capacitance (uF) | Capacitance (pF) | Capacitance Value | Voltage | Tolerance (%) | Body Width or Diameter (mm) | Lead Length (mm) | Lead Spacing (mm) | Price 1 | Price 10 |
|-------------------------|-----------------|---------------------|------------------|------------------|-------------------|---------|---------------|-----------------------------|------------------|-------------------|---------|----------|
| 15270 | Jameco Valuepro | DC.1/50-7 | 0.1 | 100000 | 0.1 µF | 50 | 20 | 7 | 28 | 4 | \$0.25 | \$0.15 |
| 2146311 | Jameco Valuepro | DC.1/50-11 | 0.1 | 100000 | 0.1 µF | 50 | 20 | 11 | 26 | 6 | \$0.25 | \$0.14 |
| 2289863 | Jameco Valuepro | DC.1/50-13 | 0.1 | 100000 | 0.1 µF | 50 | 20 | 13 | 32 | 7 | \$0.25 | \$0.19 |
| 2301935 | Jameco Valuepro | DC.02/50-Z5V | 0.2 | 200000 | 0.2 µF | 1000 | +80/-20 | 7 | 24 | 4 | \$0.25 | \$0.16 |