



[Click Here to Request a Large Quantity Quote](#)

[15 to 24 Volt DC to DC Enclosed Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage Range (VDC)	Input Voltage (VDC)	Maximum Input Current (A)	Output Connector Type	Pin_Count	Number of Outputs	Price 1
175813	MEAN WELL	SD-25A-24	24	1.1	26.4	SD-25	9.2 to 18	12	3.2	Screw Terminal Block	5	1	\$21.90
2254987	MEAN WELL	RSD-30L-24	24	1.25	30	RSD-30	18 to 72	48	0.8			1	\$27.60
2254944	MEAN WELL	RSD-30G-24	24	1.25	30	RSD-30	9 to 36	24	1.5			1	\$27.60
2107266	MEAN WELL	SD-50A-24	24	2.1	50.4	SD-50	9.2 to 18	12	7	Screw Terminal Block	5	1	\$27.20
2254709	MEAN WELL	RSD-60G-24	24	2.5	60	RSD-60	9 to 36	24	3			1	\$35.20
2107039	MEAN WELL	SD-100C-24	24	4.2	100.8	SD-100	36 to 72	48	2.4		7	1	\$34.20
2107098	MEAN WELL	SD-150C-24	24	6.3	151.2	SD-150	36 to 72				7	1	\$45.20
2304407	MEAN WELL	ERDN20-24		20	1.5	ERDN20	19 to 29	24	20	Screw Terminal Block		1	\$24.10