



[Click Here to Request a Large Quantity Quote](#)

Inductors

| Jameco Part # | Manufacturer | Manufacturer Part # | Description | Inductance (uH) | Rated Current (mA) | Price 1 |
|-------------------------|-----------------|---------------------|---|-----------------|--------------------|---------|
| 2295975 | Major Brands | 0805CS-270XJBC | Chip Inductor 0805CS SMD 0.027uH 500mA 5% 250MHz | 0.027 | 500 | \$0.49 |
| 372285 | Jameco Valuepro | 9230-94-VP | Choke Axial Molded RF 0.1uH 1.1A 10% | 0.1 | 1100 | \$0.79 |
| 372293 | Jameco Valuepro | 9230-00-VP | Choke Axial Molded RF 0.15uH 1.1A 10% | 0.15 | 1100 | \$0.79 |
| 372306 | Jameco Valuepro | 9230-04-VP | Choke Axial Molded RF 0.22uH 935mA 10% | 0.22 | 935 | \$0.79 |
| 372314 | Jameco Valuepro | 9230-10-VP | Choke Axial Molded RF 0.39uH 640mA 10% | 0.39 | 640 | \$0.79 |
| 372322 | Jameco Valuepro | 9230-12-VP | Choke Axial Molded RF 0.47uH 590mA 10% | 0.47 | 590 | \$0.79 |
| 372331 | Jameco Valuepro | 9230-14-VP | Choke Axial Molded RF 0.56uH 495mA 10% | 0.56 | 495 | \$0.79 |
| 372349 | Jameco Valuepro | 9230-16-VP | Choke Axial Molded RF 0.68uH 450mA 10% | 0.68 | 450 | \$0.79 |
| 372373 | Jameco Valuepro | 9230-34-VP | Choke Axial Molded RF 3.9uH 350mA 10% | 3.9 | 350 | \$0.99 |
| 2296615 | Jameco Valuepro | LHL10NB822J | Fixed Inductor 8.2mH 150 mA 5% 12 Ohm 11mm Radial Vertical Cylinder | 8.2 | 150 | \$0.59 |
| 372171 | Jameco Valuepro | 78F100K-VP | Choke Axial Conformal 10uH 370mA 10% | 10 | 370 | \$0.45 |
| 2296135 | Major Brands | DO3316P-103 | Power Inductor SMD 10uH 3900mA 20% 0.038 Ohms | 10 | 3900 | \$1.49 |
| 2296199 | Major Brands | DC5022P103 | Power Inductor SMD 10uH 4300mA 20% 0.031 Ohms | 10 | 4300 | \$1.95 |
| 2296463 | Major Brands | DHC-7342-100R | Power Inductor SMD High Current 10uH 7100mA 10% 0.0157 Ohms | 10 | 7100 | \$2.95 |
| 2296207 | Major Brands | CO3321P-153 | Power Inductor SMD 15uH 3100mA 20% 0.046 Ohms | 15 | 3100 | \$1.59 |
| 372402 | Jameco Valuepro | 9230-52-VP | Choke Axial Molded RF 22uH 190mA 10% | 22 | 190 | \$0.79 |
| 372411 | Jameco Valuepro | 9230-56-VP | Choke Axial Molded RF 33uH 187mA 10% | 33 | 187 | \$0.99 |
| 371581 | Jameco Valuepro | 2109-H-VP | Inductor Toroid Horizontal 47uH 3.6A 15% | 47 | 3600 | \$1.79 |
| 372429 | Jameco Valuepro | 9230-64-VP | Choke Axial Molded RF 68uH 135mA 10% | 68 | 135 | \$0.99 |
| 2296359 | Major Brands | PVC-0-823-03 | Power Choke 82uH 2800mA 10% 0.11 Ohms Vertical Mount | 82 | 2800 | \$1.95 |
| 208194 | Jameco Valuepro | CEC-101J | Choke Axial Conformal 100uH 240mA 5% | 100 | 240 | \$0.99 |
| 371856 | Jameco Valuepro | 2112-V-VP | Inductor Toroid Vertical 100uH 240mA 15% | 100 | 240 | \$1.95 |
| 2295887 | Jameco Valuepro | CT67F-101K | High Power Toroid Inductor 100uH 2.5A(DC) 10% Vertical 1.0kHz | 100 | 2500 | \$1.95 |
| 372445 | Jameco Valuepro | 9230-70-VP | Choke Axial Molded RF120uH 97mA 10% | 120 | 97 | \$0.99 |
| 372269 | Jameco Valuepro | 78F221J-VP | Choke Axial Conformal 220uH 130mA 5% | 220 | 130 | \$0.39 |
| 387268 | Jameco Valuepro | 2316-V-VP | Inductor Toroid Vertical 220uH 5.8A 15% | 220 | 5800 | \$2.49 |
| 208240 | Jameco Valuepro | CEC-102J | Choke Axial Conformal 1000uH 160mA 5% | 1000 | 160 | \$0.39 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Description | Inductance (uH) | Rated Current (mA) | Price 1 |
|-------------------------|-------------------|---------------------|--|-----------------|--------------------|---------|
| 371979 | Jameco Valuepro | 2124-V-VP | Inductor Toroid Vertical 1000uH 250mA 15% | 1000 | 250 | \$2.29 |
| 2287095 | Yageo Corporation | SL0608T-472K-B-N | Choke Radial Molded 4700uH 52mA 10% | 4700 | 52 | \$0.59 |
| 372453 | Jameco Valuepro | MCGSB-1501-1R0K | Choke Axial Molded RF 10000uH 24mA 10% | 10000 | 24 | \$1.95 |
| 2233959 | Jameco Valuepro | VC1019-104K-UL-CID | Choke Axial High Current RF 100,000uH 65mA 10% | 10000 | 65 | \$1.29 |
| 642741 | Jameco Valuepro | VC0513-103K-UL | Choke Axial High Current RF 10,000uH 125mA 10% | 10000 | 125 | \$0.89 |
| 2279935 | Jameco Valuepro | VC1019-103K-UL-1KV | Choke Axial High Current RF 10,000uH 266mA 10% | 10000 | 266 | \$0.99 |
| 642927 | Jameco Valuepro | GSPCU1020-103K08 | Choke Axial High Current RF 10,000uH 350mA 10% | 10000 | 350 | \$1.29 |
| 2233967 | Jameco Valuepro | VC1019-503K-UL | Choke Axial High Current RF 50,000uH 100mA 10% | 50000 | 100 | \$1.29 |