



[Click Here to Request a Large Quantity Quote](#)

[Electrolytic Capacitors \(Radial & SMD\)](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">2151970</a>	Jameco Valuepro	R0.1/50	0.1	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">609545</a>	Jameco Valuepro	UVZ1H0R1MDD	0.1	50	20	5 x 11 x 2	Radial	105	Through Hole	\$0.25	\$0.19
<a href="#">330465</a>	Jameco Valuepro	RA0.47/50-R	0.47	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.21	\$0.15
<a href="#">330431</a>	Jameco Valuepro	RA1/25-R	1	25	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.16
<a href="#">94161</a>	Jameco Valuepro	ECE-A1HKS010	1	50	20	4 x 5	Radial	85	Through Hole	\$0.21	\$0.15
<a href="#">29831</a>	Jameco Valuepro	R1/50	1	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.16
<a href="#">330772</a>	Jameco Valuepro	RB1/50-R	1	50	20	5 x 11 x 2	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">2283471</a>	Nichicon	647-UES1H010MDM	1	50	20	5 x 12.5 x 2	Radial	85	Through Hole	\$0.99	\$0.89
<a href="#">115423</a>	Arndt	R1/63	1	63	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.15
<a href="#">158491</a>	Jameco Valuepro	R1B100-R	1	100	20	5 x 11 x 2	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">93731</a>	Jameco Valuepro	R2.2/50-VP-R	2.2	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.21	\$0.12
<a href="#">93729</a>	Jameco Valuepro	R2.2/50	2.2	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">609561</a>	Jameco Valuepro	UVZ1H2R2MDD	2.2	50	20	5 x 11 x 2	Radial	105	Through Hole	\$0.21	\$0.15
<a href="#">135184</a>	Jameco Valuepro	R3.3/50-VP	3.3	50	20	5 x 12 x 2	Radial	85	Through Hole	\$0.25	\$0.15
<a href="#">2143460</a>	Jameco Valuepro	R4.7/25	4.7	25	20	4 x 7 x 2.5	Radial	85	Through Hole	\$0.21	\$0.12

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">2230109</a>	Xicon	R4.7/35	4.7	35	20	5 x 11 x 2	Radial	85	Though Hole	\$0.21	\$0.12
<a href="#">2290623</a>	Jameco Valuepro	RB4.7/50-4X8	4.7	50	20	4 x 8 x 1.5	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">31000</a>	Jameco Valuepro	R4.7/50	4.7	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.21	\$0.16
<a href="#">330781</a>	Jameco Valuepro	RB4.7/50-R	4.7	50	20	6 x 11 x 2	Radial	105	Through Hole	\$0.21	\$0.15
<a href="#">2279983</a>	Nippon Chemi Con	ESMG401ELL4R7MJ16S	4.7	400	20	10 x 16 x 5	Radial	85	Through Hole	\$0.39	\$0.29
<a href="#">198839</a>	Jameco Valuepro	EC1016H511-R	10	16	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">330692</a>	Jameco Valuepro	RB10/16-R	10	16	20	5 x 11 x 2	Radial	105	Through Hole	\$0.21	\$0.15
<a href="#">94212</a>	Jameco Valuepro	10UF/25V 4X5-R	10	25	20	4 x 5	Radial	85	Through Hole	\$0.25	\$0.15
<a href="#">1946367</a>	Jameco Valuepro	R10/25A	10	25	20	5 x 11 x 5	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">94221</a>	Jameco Valuepro	E00035SR0505	10	35	20	5 x 5 x 2	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">29891</a>	Jameco Valuepro	R10/50	10	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">29893</a>	Jameco Valuepro	R10/50-VP-R	10	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.21	\$0.12
<a href="#">330799</a>	Jameco Valuepro	RB10/50-R	10	50	20	5 x 11 x 2	Radial	105	Through Hole	\$0.25	\$0.19
<a href="#">609641</a>	Jameco Valuepro	UVZ1J100MDD	10	63	20	5 x 11 x 2	Radial	105	Through Hole	\$0.19	\$0.13
<a href="#">610036</a>	Jameco Valuepro	UVZ2W100MHD	10	450	20	13 x 21 x 6	Radial	105	Through Hole	\$0.59	\$0.49
<a href="#">2286335</a>	Panasonic	EEVFCOJ22OR	22	6.3	20	4 x 6.3	SMD	105	SMD	\$0.19	\$0.13
<a href="#">1946295</a>	Jameco Valuepro	R22/16	22	16	20	5 x 12 x 2	Radial	85	Through Hole	\$0.21	\$0.12
<a href="#">158327</a>	Jameco Valuepro	LHK220M35V511	22	35	20	5 x 11 x 2	Radial	105	Through Hole	\$0.19	\$0.13

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">93739</a>	Jameco Valuepro	R22/50-VP-R	22	50	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">2286135</a>	Panasonic	EEVFK1K220P	22	80	20	8 x 10	SMD	105	SMD	\$0.25	\$0.15
<a href="#">2279967</a>	Panasonic	ECA-2EM220	22	250	20	10 x 20 x 5	Radial	85	Through Hole	\$0.49	\$0.39
<a href="#">2230281</a>	Arndt	RB22/350	22	350	20	13 x 25 x 6	Radial	105	Through Hole	\$0.69	\$0.59
<a href="#">609721</a>	Jameco Valuepro	UVZ1V331MPD	33	35	20	10 x 16 x 5	Radial	105	Through Hole	\$0.39	\$0.29
<a href="#">93747</a>	Jameco Valuepro	R33/50-VP-R	33	50	20	6.3 x 11 x 2.5	Radial	85	Through Hole	\$0.21	\$0.15
<a href="#">2279975</a>	Nichicon	UHE1V102MHT6	35	35	20	18 x 16 x 8	Radial	105	Through Hole	\$0.59	\$0.49
<a href="#">2290799</a>	Nichicon	PCF1A470MCL1GS	47	10	20	6.3 x 6	SMD	105	SMD	\$0.99	\$0.85
<a href="#">609502</a>	Jameco Valuepro	UVZ1C470MDD	47	16	20	5 x 11 x 2	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">1946244</a>	Jameco Valuepro	R47/16TR	47	16	20	5 x 12 x 5	Radial	85	Through Hole	\$0.21	\$0.12
<a href="#">198952</a>	Jameco Valuepro	EC4735H511-R	47	35	20	5 x 11 x 2	Radial	85	Through Hole	\$0.21	\$0.13
<a href="#">31114</a>	Nichicon	UVR1H470MEA1TD	47	50	20	6 x 11 x 2.5	Radial	85	Through Hole	\$0.21	\$0.14
<a href="#">330820</a>	Jameco Valuepro	RB47/50-R	47	50	20	6.3 x 11 x 2.5	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">2280543</a>	Nichicon	UFWA470MPD	47	100	20	10 x 12.5 x 2	Radial	105	Through Hole	\$0.35	\$0.25
<a href="#">610010</a>	Jameco Valuepro	UVZ2E470MHD	47	250	20	13 x 25 x 6	Radial	105	Through Hole	\$0.89	\$0.75
<a href="#">330676</a>	Jameco Valuepro	RA47/450-R	47	450	20	18 x 30	Radial	85	Through Hole	\$1.59	\$1.29
<a href="#">1946261</a>	Jameco Valuepro	R68/16TR	68	16	20	5 x 11 x 5	Radial	85	Through Hole	\$0.21	\$0.12
<a href="#">2286127</a>	NIC Components	NACZ102M6.3V8X10.5TR13	100	6.3	20	8 x 10.5	SMD	105	SMD	\$0.29	\$0.19
<a href="#">1946228</a>	Jameco Valuepro	RB100/10	100	10	20	5 x 11 x 3.5	Radial	105	Through Hole	\$0.23	\$0.15

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">2230539</a>	Jameco Valuepro	R100/10	100	10	20	6 x 11 x 2	Radial	85	Through Hole	\$0.21	\$0.12
<a href="#">330422</a>	Jameco Valuepro	RA100/16-R	100	16	20	5 x 11 x 2	Radial	85	Through Hole	\$0.25	\$0.12
<a href="#">94289</a>	Nichicon	USR1C101MDA1TP	100	16	20	6 x 5 x 2.5	Radial	85	Through Hole	\$0.21	\$0.12
<a href="#">93761</a>	Jameco Valuepro	R100/25	100	25	20	6 x 11 x 5	Radial	85	Through Hole	\$0.25	\$0.17
<a href="#">330740</a>	Jameco Valuepro	RB100/25-R	100	25	20	6.3 x 11 x 2.5	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">198970</a>	Jameco Valuepro	EC10035H611-R	100	35	20	6.3 x 11 x 2.5	Radial	85	Through Hole	\$0.23	\$0.15
<a href="#">158394</a>	Jameco Valuepro	R100B50-R	100	50	20	13 x 21 x 5	Radial	105	Through Hole	\$0.29	\$0.19
<a href="#">29962</a>	Jameco Valuepro	R100/50	100	50	20	8 x 11 x 3.5	Radial	85	Through Hole	\$0.25	\$0.16
<a href="#">608032</a>	Jameco Valuepro	UPL1J101MHH6	100	63	20	12.5 x 15	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">330529</a>	Jameco Valuepro	RA100/100-R	100	100	20	10 x 17	Radial	85	Through Hole	\$0.49	\$0.35
<a href="#">330580</a>	Jameco Valuepro	RA100/160S-R	100	160	20	16 x 25 x 7.5	Radial	85	Through Hole	\$0.79	\$0.65
<a href="#">2279959</a>	Nippon Chemi Con	EKXG201ELL101ML20S	100	200	20	16 x 21 x 8	Radial	105	Through Hole	\$1.09	\$0.89
<a href="#">2279951</a>	Panasonic	EEUED2D101	100	200	20	16 x 26 x 8	Radial	105	Through Hole	\$1.19	\$0.99
<a href="#">609967</a>	Jameco Valuepro	UVZ2E101MHD	100	250	20	16 x 32 x 8	Radial	105	Through Hole	\$1.49	\$1.19
<a href="#">330684</a>	Jameco Valuepro	RA100/450-R	100	450	20	22 x 47 x 10	Radial	85	Through Hole	\$2.75	\$2.25
<a href="#">2286383</a>	NIC Components	NSP121M63D3TRF	120	6.3	20	7.3 x 4.3 x 2.8	SMD	105	SMD	\$0.99	\$0.89
<a href="#">2158426</a>	Arndt	RC120/400	120	400	20	16 x 35	Radial	105	Through Hole	\$1.09	\$0.99
<a href="#">608340</a>	Jameco Valuepro	ECA1JFQ151L	150	63	20	10 x 20 x 5	Radial	105	Through Hole	\$0.25	\$0.15

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">606934</a>	Jameco Valuepro	UHE1J181MPD	180	63	20	10 x 21 x 5	Radial	105	Through Hole	\$0.25	\$0.15
<a href="#">198872</a>	Jameco Valuepro	EC22016H611-R	220	16	20	6.3 x 11 x 2.5	Radial	85	Through Hole	\$0.22	\$0.15
<a href="#">158263</a>	Jameco Valuepro	R220B25-R	220	25	20	8 x 11	Radial	105	Through Hole	\$0.29	\$0.19
<a href="#">30496</a>	Jameco Valuepro	R220/25	220	25	20	8 x 11 x 3.5	Radial	85	Through Hole	\$0.25	\$0.19
<a href="#">93770</a>	Jameco Valuepro	R220/35	220	35	20	10 x 12 x 5	Radial	105	Through Hole	\$0.35	\$0.25
<a href="#">93772</a>	Jameco Valuepro	R220/35-R	220	35	20	8 x 12 x 3.5	Radial	85	Through Hole	\$0.29	\$0.19
<a href="#">606820</a>	Jameco Valuepro	UHE1H221MPD	220	50	20	10 x 16 x 5	Radial	105	Through Hole	\$0.21	\$0.15
<a href="#">93778</a>	Jameco Valuepro	R220/50	220	50	20	10 x 17 x 5	Radial	85	Through Hole	\$0.39	\$0.29
<a href="#">2279943</a>	Nichicon	UVZ2D221MDH	220	200	20	18 x 36 x 7	Radial	105	Through Hole	\$1.75	\$1.49
<a href="#">93796</a>	Jameco Valuepro	R330/25	330	25	20	10 x 12 x 5	Radial	85	Through Hole	\$0.29	\$0.19
<a href="#">2285951</a>	NIC Components	NACZ331M35V10X10.5TR13	330	35	20	10 x 10.5	SMD	105	SMD	\$0.39	\$0.29
<a href="#">198978</a>	Jameco Valuepro	EC33035H1017-R	330	35	20	8 x 12 x 3.5	Radial	85	Through Hole	\$0.35	\$0.29
<a href="#">330473</a>	Jameco Valuepro	RA330/50-R	330	50	20	10 x 16 x 5	Radial	85	Through Hole	\$0.39	\$0.29
<a href="#">607136</a>	Nichicon	UPF2A331MHH	330	100	20	12.5 x 40	Radial	105	Through Hole	\$0.59	\$0.49
<a href="#">93809</a>	Jameco Valuepro	R470/16	470	16	20	8 x 11 x 3.5	Radial	85	Through Hole	\$0.25	\$0.18
<a href="#">158203</a>	Jameco Valuepro	R470B16	470	16	20	8 x 11 x 3.5	Radial	105	Through Hole	\$0.35	\$0.25
<a href="#">31181</a>	Jameco Valuepro	R470/25	470	25	20	10 x 12 x 5	Radial	85	Through Hole	\$0.29	\$0.19
<a href="#">606740</a>	Jameco Valuepro	R470/35/105	470	25	20	10 x 16	Radial	105	Through Hole	\$0.35	\$0.29

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">158289</a>	Jameco Valuepro	R470B25	470	25	20	10 x 16 x 5	Radial	105	Through Hole	\$0.39	\$0.29
<a href="#">2280023</a>	Nippon Chemi Con	ELXV250ETD471MJ20	470	25	20	10 x 20 x 5	Radial	105	Through Hole	\$0.35	\$0.25
<a href="#">93817</a>	Jameco Valuepro	R470/35	470	35	20	10 x 16 x 5	Radial	85	Through Hole	\$0.39	\$0.29
<a href="#">93827</a>	Jameco Valuepro	R470/50-VP-R	470	50	20	10 x 20	Radial	85	Through Hole	\$0.59	\$0.45
<a href="#">606854</a>	Jameco Valuepro	UHE1H471MPD	470	50	20	13 x 25 x 5	Radial	105	Through Hole	\$0.59	\$0.45
<a href="#">2287791</a>	Nichicon	UPM1J471MHH67N	470	63	20	10 x 26 x 7	Radial	105	Through Hole	\$0.25	\$0.19
<a href="#">158465</a>	Jameco Valuepro	R470B63	470	63	20	13 x 20 x 5	Radial	85	Through Hole	\$0.65	\$0.49
<a href="#">2133430</a>	Panasonic	EEU-FM1C681L	680	16	20	8 x 21 x 2.5	Radial	105	Through Hole	\$0.29	\$0.25
<a href="#">2229554</a>	Nichicon	R680UF-25V	680	25	20	16 x 25 x 7	Radial	85	Through Hole	\$0.49	\$0.39
<a href="#">330456</a>	Jameco Valuepro	RA680/25S	680	25	20	8 x 16 x 3.5	Radial	85	Through Hole	\$0.49	\$0.39
<a href="#">2129781</a>	Jameco Valuepro	E681035SR1321	680	35	20	13 x 21 x 4	Radial	105	Through Hole	\$0.59	\$0.49
<a href="#">607355</a>	Jameco Valuepro	UPW0J821MPD	820	6.3	20	8 x 11 x 4	Radial	105	Through Hole	\$0.39	\$0.29
<a href="#">606432</a>	Jameco Valuepro	UHE0J102MPD	1000	6.3	20	8 x 14 x 3.5	Radial	105	Through Hole	\$0.35	\$0.25
<a href="#">607363</a>	Jameco Valuepro	UPW1A102MPD6	1000	10	20	8 x 14 x 4	Radial	105	Through Hole	\$0.39	\$0.29
<a href="#">30015</a>	Jameco Valuepro	R1000/16	1000	16	20	10 x 16 x 5	Radial	85	Through Hole	\$0.39	\$0.29
<a href="#">330722</a>	Jameco Valuepro	RB1000/16-R	1000	16	20	10 x 20 x 5	Radial	105	Through Hole	\$0.49	\$0.35
<a href="#">2234302</a>	Arndt	RB1000/16-12	1000	16	20	12 x 14 x 5	Radial	85	Through Hole	\$0.45	\$0.35
<a href="#">158298</a>	Jameco Valuepro	R1000B25-R	1000	25	20	10 x 17 x 5	Radial	105	Through Hole	\$0.49	\$0.39

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">93833</a>	Jameco Valuepro	R1000/25	1000	25	20	13 x 20 x 5	Radial	85	Through Hole	\$0.45	\$0.32
<a href="#">1984494</a>	Panasonic	EEU-EB1V102	1000	35	20	12.5 x 25	Radial	105	Through Hole	\$0.59	\$0.49
<a href="#">158378</a>	Jameco Valuepro	R1000B35-R	1000	35	20	13 x 21 x 5	Radial	105	Through Hole	\$0.59	\$0.49
<a href="#">609553</a>	Jameco Valuepro	UVZ1H102MHD	1000	50	20	13 x 25 x 5	Radial	105	Through Hole	\$0.89	\$0.69
<a href="#">93841</a>	Jameco Valuepro	R1000/50	1000	50	20	13 x 26	Radial	85	Through Hole	\$0.75	\$0.65
<a href="#">199111</a>	Jameco Valuepro	EC1000100H1840-R	1000	100	20	18 x 41 x 7.5	Radial	85	Through Hole	\$1.75	\$1.39
<a href="#">606627</a>	Jameco Valuepro	UHE1C122MPD	1200	16	20	10 x 24 x 5	Radial	105	Through Hole	\$0.69	\$0.55
<a href="#">2285543</a>	Panasonic	EEV-FK1C152Q	1500	16	20	12.5 x 14	SMD	105	SMD	\$0.99	\$0.79
<a href="#">2287655</a>	Jameco Valuepro	ECA1CFG152S	1500	16	20	16 x 16 x 8	Radial	105	Through Hole	\$0.79	\$0.59
<a href="#">607742</a>	Jameco Valuepro	UPW1E152MHD6	1500	25	20	13 x 25 x 5	Radial	105	Through Hole	\$0.95	\$0.75
<a href="#">606467</a>	Jameco Valuepro	UHE0J182MHD	1800	6.3	20	10 x 20 x 5	Radial	105	Through Hole	\$0.59	\$0.49
<a href="#">2296711</a>	Panasonic	ECA-1VFQ182S	1800	35	20	18 x 26 x 7.5	Radial	105	Through Hole	\$1.39	\$1.09
<a href="#">609342</a>	Jameco Valuepro	UVZ0J222MPD	2200	6.3	20	10 x 20 x 5	Radial	105	Through Hole	\$0.49	\$0.39
<a href="#">606563</a>	Jameco Valuepro	UHE1A222MPD	2200	10	20	13 x 21 x 6	Radial	105	Through Hole	\$0.69	\$0.55
<a href="#">133148</a>	Nichicon	R2200/16-R	2200	16	20	18 x 16 x 8	Radial	85	Through Hole	\$0.49	\$0.39
<a href="#">30533</a>	Jameco Valuepro	R2200/25	2200	25	20	12 x 25 x 5	Radial	85	Through Hole	\$0.79	\$0.65
<a href="#">30535</a>	Jameco Valuepro	R2200/25-VP-R	2200	25	20	13 x 21 x 5	Radial	85	Through Hole	\$0.65	\$0.45
<a href="#">2229562</a>	Arndt	CEVSM1E222(V)-J2	2200	25	20	16 x 38 x 7	Radial	105	Through Hole	\$0.79	\$0.69

Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">2229546</a>	Arndt	R2200UF-25V	2200	25	20	22 x 40 x 12	Radial	85	Through Hole	\$0.79	\$0.65
<a href="#">198986</a>	Jameco Valuepro	EC220035H1626-R	2200	35	20	16 x 25 x 7.5	Radial	85	Through Hole	\$0.89	\$0.75
<a href="#">609705</a>	Jameco Valuepro	UVZ1V222MHD	2200	35	20	16 x 26 x 8	Radial	105	Through Hole	\$1.25	\$0.99
<a href="#">2290615</a>	Nichicon	UVZ1V222MHD1AA	2200	35	20	16 x 26 x 8(4.5 Lds)	Radial	105	Through Hole	\$1.09	\$0.85
<a href="#">158431</a>	Illinois Capacitor	R2200B35	2200	35	20	18 x 36 x 8	Radial	105	Through Hole	\$1.25	\$0.99
<a href="#">158432</a>	Jameco Valuepro	R2200B50-R	2200	50	20	16 x 32 x 8	Radial	105	Through Hole	\$1.39	\$1.19
<a href="#">2286359</a>	Jameco Valuepro	UFW1H222MHD	2200	50	20	16 x 36 x 8	Radial	85	Through Hole	\$1.59	\$1.29
<a href="#">2234978</a>	Vishay	67D102	2900	40	20	26 x 74 x 11	Radial	85	Through Hole	\$1.95	\$1.75
<a href="#">198898</a>	Jameco Valuepro	EC330016H1321-R	3300	16	20	13 x 21 x 5	Radial	85	Through Hole	\$0.99	\$0.79
<a href="#">30893</a>	Jameco Valuepro	R3300/25-VP-R	3300	25	20	13 x 29 x 5	Radial	85	Through Hole	\$0.89	\$0.75
<a href="#">2033551</a>	Nichicon	UVR1V332MHD	3300	35	20	16 x 36 x 7	Radial	85	Through Hole	\$1.25	\$0.99
<a href="#">608278</a>	Jameco Valuepro	E332035HR	3300	35	20	18 x 31 x 8	Radial	105	Through Hole	\$1.29	\$0.99
<a href="#">609588</a>	Jameco Valuepro	UVZ1H332MHD	3300	50	20	18 x 36 x 8	Radial	105	Through Hole	\$1.95	\$1.59
<a href="#">198901</a>	Jameco Valuepro	EC470016H1626-R	4700	16	20	16 x 25 x 7.5	Radial	85	Through Hole	\$0.99	\$0.79
<a href="#">93850</a>	Jameco Valuepro	R4700/25	4700	25	20	18 x 26 x 7	Radial	85	Through Hole	\$1.25	\$0.99
<a href="#">607814</a>	Jameco Valuepro	UPW1E472MHD	4700	25	20	18 x 35 x 8	Radial	105	Through Hole	\$1.95	\$1.69
<a href="#">199006</a>	Jameco Valuepro	EC470035H1836-R	4700	35	20	18 x 34 x 8	Radial	85	Through Hole	\$1.59	\$1.29
<a href="#">163301</a>	Jameco Valuepro	R4700/50	4700	50	20	22 x 36 x 10	Radial	105	Through Hole	\$2.49	\$2.25



Jameco Part #	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (VDC)	Tolerance (%)	Size (mm)(Dia. x H x LS)	Construction	Max. Operating Temp. (&deg;C)	Mounting	Price 1	Price 10
<a href="#">2203098</a>	Arndt	R5600B6.3	5600	6.3	20	13 x 40 x 5	Radial	105	Through Hole	\$0.95	\$0.79
<a href="#">2125641</a>	Nichicon	R5600B16	5600	16	20	16 x 40 x 7.5	Radial	105	Through Hole	\$1.49	\$1.25
<a href="#">198935</a>	Jameco Valuepro	EC680025H1836-R	6800	25	20	18 x 36 x 8	Radial	85	Through Hole	\$1.75	\$1.39
<a href="#">609473</a>	Jameco Valuepro	UVZ1C103MHD	10000	16	20	18 x 40.5 x 8	Radial	105	Through Hole	\$1.75	\$1.39