



[Click Here to Request a Large Quantity Quote](#)

[Standard Output 10mm LEDs](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Luminous Intensity	Lens Type	Viewing Angle	Typical Forward Voltage	Typical Forward Current	Peak Wavelength	Height	Lead Pitch	Price 1	Price 10
2152104	Jameco Valuepro	MCDL-10003SGD	10mm, T-3 1/4	Green	50 mcd	Diffused	60°	2.2 V	30 mA	570 nm	13.2mm	0.1"	\$0.59	\$0.55
2152139	Jameco Valuepro	MCDL-10003ED-E	10mm, T-3 1/4	Orange	25 mcd	Diffused	60°	2 V	30 mA	610 nm	13.2mm	0.1"	\$0.45	\$0.39
2152112	Jameco Valuepro	MCDL-10003SED	10mm, T-3 1/4	Red	35 mcd	Diffused	60°	2 V	30 mA	635 nm	13.2mm	0.1"	\$0.49	\$0.35
2152121	Jameco Valuepro	MCDL-10003SYD	10mm, T-3 1/4	Yellow	35 mcd	Diffused	60°	2 V	30 mA	590 nm	13.2mm	0.1"	\$0.55	\$0.49