



[Click Here to Request a Large Quantity Quote](#)

[Open Frame Medical Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Number of Outputs	Price 1
2265983	MEAN WELL	MFM-05-5	5	1	5	MFM-05		80 to 264	47 to 440	0.2	4 Pins	1	\$7.40
2266023	MEAN WELL	MFM-10-5	5	2	10	MFM-10		80 to 264	47 to 440	0.3	4 Pins	1	\$8.70
695092	MEAN WELL	NFM-10-5	5	2	10	NFM-10		85 to 264	47 to 440	0.25	Pin Terminal Block	1	\$8.95
695130	MEAN WELL	NFM-15-5	5	3	15	NFM-15		85 to 264	47 to 440	0.35	Pin Terminal Block	1	\$10.49
2106247	MEAN WELL	RPD-60B	5	3.85	53.5	RPD-60B	24	90 to 264	47 to 63	1.1	JST RCY Male	2	\$13.95
695199	MEAN WELL	NFM-20-5	5	4.4	22	NFM-20		85 to 264	47 to 440	0.6	Pin Terminal Block	1	\$12.95
2248413	MEAN WELL	RPS-30-5	5	6	30	RPS-30		80 to 264	47 to 63	1	JST B2P-VH (2-Pin)	1	\$12.00
2104014	MEAN WELL	MPD-65B	5	6	65.5	MPD-65	24	90 to 264	47 to 440	1.6	Pin Terminal Block	2	\$23.95
2129676	Elpac Power Supplies	MSM40D	5.1		40	MSM40D	24, -12	85 to 264	47 to 63			3	\$4.25
2265991	MEAN WELL	MFM-05-12	12	0.42	5	MFM-05		80 to 264	47 to 440	0.2	4 Pins	1	\$7.40
694989	MEAN WELL	NFM-05-12	12	0.42	5.04	NFM-05		85 to 264	47 to 440	0.12	Pin Terminal Block	1	\$7.95
695105	MEAN WELL	NFM-10-12	12	0.85	10.2	NFM-10		85 to 264	47 to 440	0.25	Pin Terminal Block	1	\$8.99
695201	MEAN WELL	NFM-20-12	12	1.8	21.6	NFM-20		85 to 264	47 to 440	0.6	Pin Terminal Block	1	\$12.95
2266175	MEAN WELL	MFM-30-12	12	2.5	30	MFM-30		80 to 264	47 to 63	0.75	4 Pins	1	\$15.60
2248430	MEAN WELL	RPS-30-12	12	2.5	30	RPS-30		80 to 264	47 to 63	1	JST B2P-VH (2-Pin)	1	\$12.00
2293487	MEAN WELL	RPS-500-12	12	26.7	320.4	RPS-500		80 to 264	47 to 63	5.8	Screw Terminal	1	\$90.30

