



[Click Here to Request a Large Quantity Quote](#)

[Audio Components-Buzzers Piezo](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Tone Mode	Operating Voltage (Vp-p/mA)	Voltage Range (Vp-p)	Sound (dB)	Frequency (Hz)	Size (H" x Dia.)	Price 1
2151216	Projects Unlimited	EAT-17	Continuous	1-20/1	1-20	80	3800	.27 x .54	\$0.45
336314	Jameco Valuepro	KWT2340F12L-2E	Continuous	12-30/3	12-30	80	4000	.22 x 1.40	\$1.55
2231849	Jameco Valuepro	LD-72	Continuous	12/110	6-15	108	4000	1.87 x .90	\$5.95
2202925	Jameco Valuepro	PKM33EP-1001	Continuous	12/7	3-30	70	4000	.29 x 1.25	\$0.59
2232817	Mallory Products	PK-12N40P	Continuous	3/10	3-15	83	4100	.29 x .55	\$1.95
2172906	Mallory Products	SCM616N-1	Continuous	6/16 / 6-22	6-16	90	2900	1.06 x 1.7	\$1.75
2236092	Kobitone Audio Company	254-353	Continuous	6/6	3-30	90	2800	.63 x 1.63	\$1.25
2236105	Kobitone Audio Company	254-PB517	Continuous	9/7	3-15	90	3400	.46 x .96	\$1.25
2302423	Mallory Products	PK-20A35EW	Continuous/Fast Pulse	12/10	3-24	95	3500	0.99 x 1.10	\$3.95
249498	Jameco Valuepro	11D3120-LF-TA	Dual/Continuous	12/25	4-16	95	2900	1.35 x 1.72	\$3.59
123538	Jameco Valuepro	11D3240-R	Dual/Continuous	24/20	4-28	80	2900	1.4 x 1.7	\$3.55
2244076	Jameco Valuepro	GKWT1470J05B	External Drive	5/3	5-25	80	4000	.27 x .55	\$1.25
2117430	Jameco Valuepro	7P3120LF-LA	Pulse	12/10	3-15	90	3200	.98 x 1.1	\$2.75
336989	Jameco Valuepro	11S3120LF-TA	Single	1-16/30	6-16	100	2900	1.35 x 1.71	\$3.25
2234337	Jameco Valuepro	SL12ADF3120LF-EA	Single	12/20	6-28	90	2900	1.3 x 1.7	\$2.75
2261298	Velleman	SVM12N	Single	12/25	8-15	85	500	.92 x .58	\$4.95
2290431	Jameco Valuepro	PS1205	Single	12/5	12	100	3500	.26 x .91	\$1.49
2271031	Jameco Valuepro	32S4120	Single	12/7	3-16	80	4000	.55 x .30	\$1.59
138713	Jameco Valuepro	32S4120-LFPN	Single	12/7	3-16	80	4000	30 x 54	\$1.99
2120452	Jameco Valuepro	23S3120ANLF-PN	Single	12/8	3-20	85	2900	.63 x .93	\$1.75
32602	Jameco Valuepro	11S3240LF-TA	Single	24/15	1-27	95	2900	1.4 x 1.7	\$2.75
76021	Jameco Valuepro	7S3240LFLA	Single	24/20	1.5-28	95	3200	1.0 x 1.1	\$3.95
335557	Jameco Valuepro	116S3120XLF-PN	Single	3-20/3-16	3-20	90	3400	.39 x .91	\$2.19
2173861	Jameco Valuepro	20S1060LF - LA	Single	6/25	4-8	75	400	.91 x .61	\$1.75
2131223	Velleman	SV/PS1	Siren	12/200	6-15	107	3500	2.2 x 1.7	\$7.49
207993	Jameco Valuepro	SL15R3120LA-R	Siren	12/250	6-16	105	3500	2.3 x 1.6	\$4.75
2203063	Jameco Valuepro	BPS8432L-12-C	Siren	12/85	6-15	105	2800	3.3 x 1.3	\$4.49

Jameco Part #	Manufacturer	Manufacturer Part #	Tone Mode	Operating Voltage (Vp-p/mA)	Voltage Range (Vp-p)	Sound (dB)	Frequency (Hz)	Size (H" x Dia.)	Price 1
2207081	Jameco Valuepro	AZ-3040E-W-LF	Speaker	3/5	3-30	85	4000	.22 x 1.18	\$1.09
673900	Jameco Valuepro	SEP-1172	Transducer	12/7	3-28	81	3300	0.63 x 1.25	\$0.35
2287511	Murata	PKLCS1212E4001-R1	Transducer	25/1.5	25	84	4000	.48 x .11	\$1.59