



[Click Here to Request a Large Quantity Quote](#)

[Rectangular Connectors-.200" \(5.08mm\) Series](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Contact Gender	Number of Rows	Number of Contacts	Mounting	Length	Depth	Minimum Operating Temperature	Maximum Operating Temperature	Body Orientation	Price 1
527056	TE Connectivity	1-480318-0	Female Socket	1	2	Cable	13.46 mm	21.84 mm	-25°C	85°C	Straight	\$0.15
42068	Jameco Valuepro	JS-1114-04H-R	Female Socket	1	4	Cable	26.1 mm	21.9 mm	-25°C	120°C	Straight	\$0.15
42076	Jameco Valuepro	CH398-04	Male Pin	1	4	Through Hole	23.4 mm	23.8 mm	-25°C	105°C	Straight	\$0.29
117568	Jameco Valuepro	CW390R-04	Male Pin	1	4	Through Hole	23.8 mm	10.1 mm	-25°C	105°C	Right Angle	\$0.75
109146	Jameco Valuepro	JS-1114-04WS-R	Male Pin	1	4	Through Hole	3.5 mm	23.8 mm	-25°C	105°C	Straight	\$0.55