



[Click Here to Request a Large Quantity Quote](#)

12 Volt DC Brushless Fan

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2134299	ADDA Corporation	AD2012LB-K70	12	20	20	6	0.6	Ball	60	CE	19.5	5.5"	\$7.95
2095269	ADDA Corporation	AD2012LX-G70	12	20	20	10	0.6	Hypro	70	UL/CUL/CE	20	5.5"	\$4.95
2227655	ADDA Corporation	AD0212MX-K50	12	25	25	6	2.4	Hypro	60	UL/CUL	29	5.5"	\$10.95
2232198	ADDA Corporation	AD0212MX-K53	12	25	25	6	2.4	Hypro	90	UL/CUL/TUV/CE	29	(3) 5.5"	\$7.95
1951641	ADDA Corporation	AD0212MB-G50GL	12	25	25	10	2	Ball	80	UL/CUL/TUV/CE	25	5.5" w/ connector	\$5.95
2179454	Jamicon Corporation	KF0210S1H	12	25	25	10	2.57	Sleeve	125	UL/TUV/CE	27	12"	\$3.95
2224198	ADDA Corporation	AD0312LX-K73	12	30	30	6	2.6	Hypro	60	UL/CUL/TUV	20	5.3"	\$9.95
2133860	ADDA Corporation	AD0312MB-G50	12	30	30	10	3.3	Hypro	60	UL/CE/TUV	20.3	5.5"	\$9.95
2131901	ADDA Corporation	AD0312HB-G53	12	30	30	10	4.5	Ball	70	UL/CUL/TUV/CE	34	(3) 5.5" (tach)	\$10.95
2276391	NMB/MAT	1404KL-04W-B59	12	35	35	10	5.6	Ball	80	UL/CUL/VDE	27	(3) 11"	\$8.95
2179411	Sunon	MF35101V1-10000-A99	12	35	35	10	7	Vapo	60	UL/CSA/TUV/CE	28	6"	\$10.95
2186224	Delta Electronics	FFB03812VHN-F00	12	38	38	28	20.2	Ball	65	UL/CE/CSA	58.5	(3) 13"	\$3.95
2215435	ADDA Corporation	AD0412HX-K96(X)	12	40	40	6	5.4	Hypro	72	UL/CUL/TUC/CE	30.5	(3) 5.5", speed sensor	\$7.65
2095314	ADDA Corporation	AD0412LX-G70	12	40	40	10	4.7	Ball	70	UL/CUL/TUV/CE	14	11"	\$5.95
2292607	ADDA Corporation	AD0412LX-G76(XT1)	12	40	40	10	4.7	Hypro	50	UL/CUL/TUV/CE	21	(3) 12", speed sensor	\$7.95
2224180	ADDA Corporation	AD0412LX-G76	12	40	40	10	4.7	Hypro	70	UL/CUL/TUV	14	(3) 12", speed sensor	\$5.95
2132162	ADDA Corporation	AD0412LS-G70(T)	12	40	40	10	4.7	Sleeve	70	UL/CUL/TUV/CE/CSA	14	12"	\$3.95
2232307	ADDA Corporation	AD0412LB-G71	12	40	40	10	5	Ball	70	UL/CUL/TUV/CE	34.5	12"	\$5.49
2167630	Sunon	HA40101V4-0000-999	12	40	40	10	5.3	Vapo	65	UL/TUV/CE	18.2	12"	\$7.95
2288943	Akasa	DFS401012M	12	40	40	10	5.62	Sleeve	66	UL/TUV/CE	24.8	(3) 13" w/ conn.	\$7.95
2290279	Common Wealth	FP-108HX/DC(S-2)12SW	12	40	40	10	6.5	Sleeve	90	UL/CUL/TUV/CE	27	12"	\$8.95
2231777	ADDA Corporation	AD0412HB-G70	12	40	40	10	6.7	Ball	100	UL/CE	25	6" w/ conn.	\$8.95
2205384	ADDA Corporation	AD0412HB-G70(T)	12	40	40	10	6.7	Ball	100	UL/CUL/TUV	25	12"	\$11.95
2167234	Sunon	ME40101V1-0000-A99	12	40	40	10	8	Vapo	100	UL/CUL/TUV	32	12"	\$9.95
1708473	Sunon	KDE1204PFVX11.MS.A	12	40	40	10	9.5	Vapo	150	UL/CUL/TUV	39	12"	\$6.95
2231793	ADDA Corporation	AD0412LB-D50	12	40	40	15	6.8	Ball	80	UL/TUV/CE	30.3	11"	\$4.95
2231769	ADDA Corporation	AD0412HB-D50	12	40	40	15	9.2	Ball	120	UL/CUL/CE	39.3	12"	\$4.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2228181	Delta Electronics	AFB0412LD	12	40	40	20	3.88	Ball	20	UL/TUV/CE/CSA	25	13"	\$2.95
2289295	Sanyo Denki	109P0412F602	12	40	40	20	6.5	Ball	90	UL/CSA/TUV	28	12"	\$8.95
195899	Sunon	KDE1204PKS2	12	40	40	20	6.5	Sleeve	70	UL/TUV/CSA	25.5	12"	\$3.95
2289263	Jameco Valuepro	280DH1LP11000	12	40	40	20	6.9	Ball	120	UL/CSA	33	2" w/ conn.	\$3.95
2134176	ADDA Corporation	AD0412LB-C50	12	40	40	20	7	Ball	70	UL/TUV/CSA	30	12"	\$8.95
2289279	INNOVATIVE	SP402012M	12	40	40	20	7.2	Sleeve	100	UL	28.4	7"	\$6.95
2289287	Sunon	KD1204PKS3	12	40	40	20	7.7	Sleeve	50	UL/CSA/TUV	19	6" w/ conn.	\$6.95
2233166	ADDA Corporation	AD0412MB-C71GP	12	40	40	20	8	Ball	120	UL/CUL/TUV/CE	26	11"	\$6.49
2289271	Delta Electronics	DFB0412H	12	40	40	20	8.1	Ball	80	UL/CSA	29	2" w/ conn.	\$5.95
1928118	ADDA Corporation	AD0412HB-C50-LF	12	40	40	20	8.8	Ball	100	UL/CUL/TUV/CE	32	12"	\$9.95
2220218	ADDA Corporation	AD0412HB-C50(G)	12	40	40	20	8.8	Ball	100	UL/CUL/TUV/CE	36	10"	\$5.95
2230969	Delta Electronics	EFB0412HHD	12	40	40	20	9.5	Ball	100	UL/CUL/CE/CSA	30.5	13"	\$9.95
2231785	ADDA Corporation	AD0412HX-C56	12	40	40	20	9.6	Hypro	110	UL	31	(3) 11", speed sensor	\$6.49
2135380	ADDA Corporation	AD0412UB-C72GP(P)	12	40	40	20	10.6	Ball	170	UL/CUL/TUV/CE	34	(3) 12", lock rotor	\$8.45
2233924	Sunon	MF40201VX-10000-G99	12	40	40	20	10.8	Vapo	80	UL/CUL/TUV	27.5	(3) 12", speed sensor	\$8.95
2292415	Gulf Electrics	GD124020UB-H	12	40	40	20	12	Ball	250	UL/CUL/CE	37.5	12"	\$8.95
2186232	Delta Electronics	FFB0412HN-5T20	12	40	40	28	10.6	Ball	70	UL/CE	36	(3) 3.5", speed sensor	\$4.95
2082089	Sanyo Denki	109P0412H302	12	40	40	28	11.3	Ball	210	UL/TUV/CSA	37	3.75"	\$3.95
2099518	ADDA Corporation	AD0412UB-B33	12	40	40	28	16.6	Ball	230	UL/CUL/TUV	36.1	(3) 12", speed sensor	\$6.95
2235348	ADDA Corporation	AD04012UB285300(LAP)	12	40	40	28	20.7	Ball	750	UL/CUL/TUV/CE	50.8	(3) 12" w/ conn., speed sensor	\$7.95
2099500	ADDA Corporation	AD0412VB-B53GP(P)	12	40	40	28	21	Ball	80	UL/CUL/TUV/CE	31	(3) 5.5", speed sensor	\$7.95
2288983	Sunon	PMD1204WQB1-A	12	40	40	28	24	Ball	330	UL/CUL/TUV	45	(3) 12" w/ conn., lock rotor	\$14.95
2277823	Sanyo Denki	9CRB0412P5K001	12	40	40	56	26.8	Ball	880	UL, CUL, TUV, CSA	62	(8) 12", speed sensor + PWM	\$22.95
2277671	Sanyo Denki	9CRD0412P5J03	12	40	40	56	30.7	Ball	1150	UL, CUL, TUV, CSA	61	(8) 12", speed sensor + PWM	\$19.95
2228800	Delta Electronics	GFB0412EHS-C	12	40	40	56	32.2	Ball	1.3	UL/CUL/TUV/CE	64.5	(8) 3" w/ conn., speed sensor + PWM	\$4.95
2233588	ADDA Corporation	AD4512DB-G70	12	45	45	10	5.8	Ball	50	UL/CUL/TUV/CE	30	11"	\$5.95
2095322	ADDA Corporation	AD4512MX-G76	12	45	45	10	6.7	Hypro	70	UL/CUL/TUV/CE	22	(3) 11", speed sensor	\$7.95
2232219	ADDA Corporation	AD4512HX-G70(T)	12	45	45	10	9.1	Hypro	90	UL/CUL/TUV/CE	27.4	11"	\$7.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2299199	Jameco Valuepro	MW510M12C	12	50	50	10	9	Ball	110	UL/TUV/CE	27	10" w/ conn.	\$4.95
2299047	Delta Electronics	EFB0512HA	12	50	50	10	11.4	Ball	150	UL/CSA/CE/VDE	30	6" w/ conn.	\$6.95
2099534	ADDA Corporation	AD5012HB-D70	12	50	50	15	12.6	Hypro	100	UL/CUL/TUV/CE	29	5.5"	\$5.95
2258451	Sunon	KDE1205PHV1.MS.AF.GN	12	50	50	15	17	Vapo	83	UL/CUL	33	(3) 12", speed sensor	\$5.95
2228261	NMB Technologies	2106KL-04W-B39	12	52	52	15	9.9	Ball	70	UL/CUL/CE	21	(3) 12", speed sensor	\$5.95
2233609	ADDA Corporation	AD0612LS-G70	12	60	60	10	9.8	Sleeve	110	UL/CUL/TUV/CE	23	11"	\$6.95
2121332	ADDA Corporation	AD0612LX-G76(T)	12	60	60	10	10	Hypro	110	UL/CUL/TUV/CE	23	(3) 11", speed sensor	\$5.95
144160	ADDA Corporation	AD0612LB-G76	12	60	60	10	11.7	Ball	80	UL/CUL/TUV	22.7	(3) 12", speed sensor	\$9.95
2205499	ADDA Corporation	AD0612HB-G90	12	60	60	10	14.06	Ball	140	UL/TUV	32.8	4.5"	\$3.95
2095357	ADDA Corporation	AD0612HB-G70	12	60	60	10	14.5	Ball	150	UL/CUL/TUV/CE	32	11"	\$7.95
1946025	Evercool Thermal	EC6010M12CA	12	60	60	10	15.5	Ball	160	UL/CE/TUV	30	(3) 9", speed sensor	\$8.95
1928126	ADDA Corporation	AD0612HX-G76(T)	12	60	60	10	16.3	Ball	160	UL/CE/TUV/CSA	31	(3) 12", speed sensor	\$7.95
2210909	Delta Electronics	AFB0612LB-TXNS	12	60	60	15	11.55	Ball	0.07	UL/TUV	24	6"	\$4.49
2295207	Gulf Electrics	GD126015LB (2N3	12	60	60	15	15.2	Dual Ball	140	UL/CUL/CE		12"	\$6.95
2270935	Sunon	MF60151V1-10000-A99	12	60	60	15	26.4	Vapo	147	UL/CUL/TUV/CE	34.2	12"	\$7.95
2272671	Delta Electronics	DFD0612L	12	60	60	20	12.4	Ball	120	UL/CUL/TUV/CE	27	11"	\$5.05
2133982	ADDA Corporation	AD0612LX-C70GL(T)	12	60	60	20	13.3	Sleeve	80	UL/CSA/TUV/CE	21.6	12"	\$5.49
2302247	ADDA Corporation	AD0612HS-C70GL	12	60	60	20	16.3	Sleeve	160	UL/CUL/TUV/CE	25	12"	\$6.95
2289303	Matsushita Electronic Comp.	FBP-06A12L	12	60	60	25	14.1	Hypro	120	-	24	12" w/ conn.	\$5.95
2288903	Delta Electronics	AUB0612LD	12	60	60	25	14.13	Ball	70	UL/CUL/VDE	24	3.5" w/ conn.	\$4.95
2288911	Delta Electronics	AFB0612L	12	60	60	25	14.13	Dual Ball	80	UL/CUL/VDE	26.5	20"	\$6.95
2289111	Max-Flow	MFD6025AD1	12	60	60	25	15.7	Ball	100	UL/CUL/TUV/CE	27	9" w/ conn.	\$5.95
2227276	YS Tech Usa	NYWO60250125BL	12	60	60	25	15.8	Ball	80	UL/CUL/TUV	23.5	7" w/ conn.	\$3.95
2288975	Jamicon Corporation	JF06025S	12	60	60	25	17.6	Sleeve	200	UL	31.5	7"	\$4.95
2288919	Sanyo Denki	109R0612H401	12	60	60	25	18.7	Ball	110	UL/CSA/VDE	28	(3) 4" w/ conn., speed sensor	\$6.95
2205149	Sunon	MB60251V2-000U-G99	12	60	60	25	19.3	Vapo	74	UL/CUL	29	(3) 12", speed sensor	\$9.95
2230766	Thermactive Electronics	RDH6025B-PWM	12	60	60	25	20.3	Ball	140	UL/CUL/TUV/CE	29	(4) 12", speed sensor + PWM	\$6.49
2228818	Mitsubishi Electric and Electronics USA	MMF-06D12DL	12	60	60	25	21.6	Ball	70	UL/CSA	23	8.5"	\$4.95
2286215	Coolmax Technology	F126025BU	12	60	60	25	24.5	Ball	340	UL/TUV/CE	32.1	(3) 7.25", PWM	\$7.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2292911	ADDA Corporation	AG06012HB257203(0L5)	12	60	60	25	24.8	Ball	230	UL/CUL/TUV	32.3	(3) 12", alarm	\$10.95
2279183	ADDA Corporation	AG06012HB257003(0L5)	12	60	60	25	24.8	Ball	230	UL/CUL/TUV	32.3	12"	\$10.95
2133974	ADDA Corporation	AD0612XB-A72GL(P)	12	60	60	25	31.7	Hypro	230	UL/CSA/TUV/CE	32.3	(3) 12", alarm	\$10.95
2289103	EVERFLOW	F1260025BU	12	60	60	25	34	Dual Ball	260	UL/TUV/CE	33.1	5" w/ conn.	\$7.95
2289215	INNOVATIVE	BP602512HH-03	12	60	60	25	38.4	Ball	390	UL/CUL/CE	46.7	(3) 12" w/ conn., speed sensor	\$9.95
2289231	Nidec Corporation	A97578-001	12	60	60	38	27	Ball	1600	UL	31	(3) 11", speed sensor	\$10.95
2288927	Delta Electronics	FFB0612SHE-FOO	12	60	60	38	43.4	Ball	550	UL/CSA/VDE/CE	50.5	(3) 12", speed sensor	\$10.95
2232930	ADDA Corporation	AD0712HS-D73	12	70	70	15	32	Sleeve	250	UL/CUL/TUV/CE	40.3	(3) 12"	\$5.95
2233203	ADDA Corporation	AD0712HS-D71	12	70	70	15	34	Sleeve	250	UL/CUL/TUV/CE	40.3	12"	\$6.49
2125561	AVC America	DE07015R12U	12	70	70	15	43	Hydraulic	700	UL/CE/TUV	46	8" w/ conn.	\$6.95
2227647	JMC Products	7025-12LS	12	70	70	25	22	Sleeve	100	UL/CUL/TUV	24.3	6" w/ conn.	\$5.95
2192561	ADDA Corporation	AD0812LB-D70(T)	12	80	80	15	20	Ball	90	UL/CSA/TUV/CE	19.6	12"	\$6.75
2232948	ADDA Corporation	AD0812MX-D71	12	80	80	15	22.4	Hypro	150	UL/CUL/TUV/CE	26	12"	\$6.95
2132007	ADDA Corporation	AD0812HS-D70-LF	12	80	80	15	38.6	Sleeve	250	UL/CUL/TUV/CE	33	12"	\$3.95
141921	ADDA Corporation	AD0812HB-C70-R	12	80	80	20	27.3	Ball	240	UL/CSA/CE	34	12"	\$9.35
2228121	NMB Technologies	3110GL-B4W-B14	12	80	80	25	24.7	Ball	10	UL/CUL	22	10"	\$5.95
2228113	Nidec Corporation	D08A-12TL	12	80	80	25	24.7	Ball	60	-	19	8" w/ conn.	\$5.95
2288935	NMB Technologies	3110KL-04W-B20	12	80	80	25	28.2	Ball	110	UL/CUL/CE/TUV	25	12" w/ conn.	\$8.95
2289255	Arndt	DF1208SL	12	80	80	25	29.9	Sleeve	200	UL/CUL/TUV/CE	34	20"	\$5.95
2271511	ADDA Corporation	AD08012MX257304	12	80	80	25	30.9	Ball	150	UL/VDE/CE	26	(3) 11", lock rotor	\$9.95
2288951	Delta Electronics	AFB0812M	12	80	80	25	31.4	Ball	120	UL/CSA/VDE/CE	28	(3) 3" w/ conn., speed sensor	\$4.95
2234450	Sunon	EE80251B3-0000-G99	12	80	80	25	33	Ball	88	UL/CUL/TUV/CE	28	(3) 12", speed sensor	\$7.95
234895	ADDA Corporation	AD0812HB-A73GL	12	80	80	25	38.6	Ball	160	UL/CUL/TUV/CE	33.4	(3) 12", speed sensor	\$7.95
2135697	NMB Technologies	FBM-08A12H	12	80	80	25	39.6	Sleeve	220	UL/CSA	32	12" w/ conn.	\$3.29
2078194	ADDA Corporation	AD0812UB-A71GP	12	80	80	25	40.2	Sleeve	250	UL/CSA/TUV/CE	34	12"	\$6.49
2210984	Sunon	EE80251B1-0000-A99	12	80	80	25	41	Ball	145	UL/TUV/CE	33	12"	\$7.95
2295487	Sunon	ME80251V1-000U-A99	12	80	80	25	41	Vapo	140	UL/CUL/TUV/CE	33	6" w/ conn.	\$4.95
2233238	ADDA Corporation	AD0812UX-A73GL	12	80	80	25	48.8	Hypro	300	UL/CUL/TUV/CE	40.8	(3) 12", speed sensor	\$8.95
2081078	Jamicon Corporation	JF0825B1UR-R	12	80	80	25	52	Dual Ball	370	UL/CUL/TUV/CE	40	12"	\$9.95
2288967	Delta Electronics	QFR0812SH-FOO	12	80	80	25	54.6	Ball	330	UL/CUL/TUV/CE	41.2	(3) 12", speed sensor	\$14.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2228164	EBM Papst	8312	12	80	80	32	31.8	Ball	216	UL/CSA/TUV	36	12"	\$10.95
107406	EBM Papst	8312GHL	12	80	80	32	39.4	Sleeve	330	UL/CSA/CE/VDE	43	12"	\$4.95
2134213	ADDA Corporation	AD0812MB-Y51	12	80	80	32	44.6	Ball	20	UL/CUL/TUV/CE	37	12"	\$11.95
2230758	Thermactive Electronics	RGM8038B1	12	80	80	38	83.4	Ball	850	UL/CUL/TUV/CE	57	12"	\$8.95
1928100	ADDA Corporation	AD0812XB-F71DS(M)	12	80	80	38	99	Ball	1500	UL/CE/TUV	57	12"	\$9.95
2233650	ADDA Corporation	AD0912HX-C70	12	92	92	20	32.8	Hypro	250	UL/CUL/TUV/CE	33	11"	\$4.95
1928097	ADDA Corporation	AD0912LX-A76GL(T)	12	92	92	25	32.4	Hypro	120	UL/CSA/TUV/CE	26.5	(3) 12", speed sensor	\$7.95
1952783	Nidec Corporation	TA350DC-M34138-34	12	92	92	25	35	Ball	160	UL/CSA	26.4	(4) 10", PWM	\$3.49
2232981	ADDA Corporation	AD0912LB-A72GL	12	92	92	25	37.7	Ball	130	UL/CUL/TUV/CE	42	(3) 12", alarm	\$7.95
1818605	NMB Technologies	3610KL-04W-B30	12	92	92	25	40.6	Ball	160	UL	34	24"	\$8.95
1928003	ADDA Corporation	AD0912MS-A70GL	12	92	92	25	43	Sleeve	170	UL/CUL/TUV/CE	31	12"	\$10.95
154641	Nidec Corporation	TA350DC-M33422-16	12	92	92	25	48	Ball	290	UL/CSA	34.8	12"	\$8.95
2193942	Orion Fans	DPF92B012	12	92	92	25	50	Ball	290	UL/CUL	33	12"	\$6.49
1928089	ADDA Corporation	AD0912HS-A76GL(T)	12	92	92	25	50	Sleeve	130	UL/CUL/TUV/CE	23.5	(3) 12", speed sensor	\$7.95
2228201	Mechatronics	E9225H12B2	12	92	92	25	51	Ball	360	UL/CUL/TUV	36	(3) 14", speed sensor	\$7.95
2234871	Sunon	PMD1209PTB3-A(2).F.GN	12	92	92	25	65	Ball	300	UL/CUL/TUV/CE	43	(3) 12", speed sensor	\$10.15
2302839	JAPAN SERVO	KLDC12B4	12	92	92	32	53	Ball	280	UL/CSA/TUV	39	12"	\$14.95
174140	Common Wealth	FP-108M/DC(S-3)12SW	12	120	120	25	54	Sleeve	140	UL/TUV/CE/CSA	25	12"	\$8.95
2233019	ADDA Corporation	AD1212LX-A71GL	12	120	120	25	72	Hypro	240	UL/CE	34.4	12"	\$7.95
2228172	AVC America	F1225B12L	12	120	120	25	75.2	Ball	270	UL/TUV/CE/CSA	39.5	8"	\$8.95
2134053	ADDA Corporation	AD1212HB-A72GL(N)	12	120	120	25	85.2	Ball	330	UL/TUV/CE/CE	38	(3) 12", alarm	\$8.95
2270855	ADDA Corporation	AD1212HB-A71GL	12	120	120	25	87.8	Ball	370	UL/CUL	39.1	12"	\$13.95
2233060	ADDA Corporation	AQ1212HB-A71GL	12	120	120	25	87.9	Ball	290	UL/CUL/CE	39.1	12"	\$14.95
2271335	ADDA Corporation	AD1212HB-A73GL(N)	12	120	120	25	88.7	Ball	336	UL/CUL/TUV	39.1	(3) 11", speed sensor	\$10.95
2170927	ADDA Corporation	AD1212US-A71GL-LF	12	120	120	25	99.12	Sleeve	500	UL/CUL/TUV/CE	43.3	11"	\$8.95
1928020	ADDA Corporation	AD1212MB-Y51	12	120	120	32	99	Ball	370	UL/CUL/TUV/CE	41.1	11"	\$8.95
2290303	Common Wealth	FP-108-32/DC(S-1)12BW	12	120	120	32	110	Ball	420	UL/TUV/CE	43	(3) 12" w/ conn., speed sensor	\$11.95
2134264	ADDA Corporation	AD1212HX-A71GL(N)	12	120	120	38	85.2	Ball	500	UL/CUL/TUV	46.7	12"	\$9.95
2231697	Nidec Corporation	TA450DC-A31276-10A	12	120	120	38	104	Ball	440	UL/CSA	51.9	Terminals	\$9.95
2290335	Common Wealth	FP-108/DC(S-1)12SW*	12	120	120	38	105	Sleeve	600	UL/CSA	45	4" w/ 2.1mm male jack	\$12.95
2173079	Sunon	EEC0381B2-0000-A99	12	120	120	38	108	Ball	421	UL/CUL/TUV/CE	44	12"	\$14.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2231478	ADDA Corporation	AD1212UB-F52	12	120	120	38	120	Ball	620	UL/CUL/TUV/CE	48	(3) 11", lock rotor	\$10.95
2270871	ADDA Corporation	AD17212LB5151MD(0CW)	12	172	151	51	295	Ball	2300	UL/TUV/CSA/CE	60.6	12"	\$49.95
2288991	Panasonic	FBM06F18H	18	60	60	20	16.6	Hypro	130	UL/CSA	32	1.5" w/ conn.	\$4.95