



[Click Here to Request a Large Quantity Quote](#)

[48 to 216 Volt LED Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2274711	MEAN WELL	UHP-500-5	5	80		90 to 264		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4.85	Terminal Block	400	\$91.20
2274719	MEAN WELL	UHP-500-12	12	41.7		90 to 264		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4.85	Terminal Block	500.4	\$91.20
2274735	MEAN WELL	UHP-500-24	24	20.9		90 to 264		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4.85	Terminal Block	501.6	\$91.20
2165722	MEAN WELL	LPF-16D-48	48	0.34		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Stripped and Tinned	16.32	\$20.90
2122466	MEAN WELL	PLN-20-48	48	0.42		90 to 277		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.4	Stripped and Tinned	20.2	\$19.00
2148762	MEAN WELL	HLG-40H-48B	48	0.84		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.43	Stripped and Tinned	40.32	\$30.40
2140630	MEAN WELL	LPF-40D-48	48	0.84		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.6	Stripped and Tinned	40.32	\$23.95
2140541	MEAN WELL	LPF-40-48	48	0.84		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.6	Stripped and Tinned	40.32	\$24.70
2102633	MEAN WELL	LPV-60-48	48	1.25		90 to 264		No	UL/CB/CE/EN/EAC	1.2	Stripped and Tinned	60	\$14.80
2140728	MEAN WELL	LPF-60-48	48	1.25		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.8	Stripped and Tinned	60	\$22.95
2140816	MEAN WELL	LPF-60D-48	48	1.25		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.8	Stripped and Tinned	60	\$28.70
2254291	MEAN WELL	LPFH-60-48	48	1.25		200 to 400		Yes	UL/CUL/FCC/EN/EAC	0.4	Stripped and Tinned	60	\$30.60
2220980	MEAN WELL	PWM-60-48	48	1.25		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.8	Stripped and Tinned	60	\$27.90
2148391	MEAN WELL	HLG-60H-48A	48	1.3		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.64	Stripped and Tinned	62.4	\$30.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2104858	MEAN WELL	PLP-60-48	48	1.3		90 to 264		Yes	UL/TUV/CB/CE/EN/EAC/CCC	0.8	Screw Terminal Block	62.5	\$16.00
2121949	MEAN WELL	CEN-60-48	48	1.3		90 to 295		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.8	Stripped and Tinned	62.4	\$33.95
2142248	MEAN WELL	HLG-80H-48A	48	1.7		90 to 305		Yes	UL/TUV/CB/CE/EN/EAC/CCC	0.85	Stripped and Tinned	81.6	\$36.10
2142336	MEAN WELL	HLG-80H-48B	48	1.7		90 to 305		Yes	UL/TUV/CB/CE/EN/EAC/CCC	0.85	Stripped and Tinned	81.6	\$37.20
2215072	MEAN WELL	NPF-90-48	48	1.88		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.95	Stripped and Tinned	90.24	\$37.10
2214985	MEAN WELL	NPF-90D-48	48	1.88		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.95	Stripped and Tinned	90.24	\$39.00
1918892	MEAN WELL	PLN-100-48	48	2	40.8 to 48	90 to 264		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.1	Stripped and Tinned	96	\$42.20
2103880	MEAN WELL	PLC-100-48	48	2	40.8 to 48	90 to 264		Yes	UL/TUV/CB/CE/EN/EAC/CCC	1.1	Screw Terminal Block	96	\$42.20
2142774	MEAN WELL	HLG-100H-48B	48	2		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.2	Stripped and Tinned	96	\$45.00
2156527	MEAN WELL	HVG-100-48A	48	2		180 to 528		Yes	UL/CUL/FCC/EN/EAC	0.32	Stripped and Tinned	96	\$66.50
2141237	MEAN WELL	LPV-100-48	48	2.1		90 to 264		No	UL/CUL/CE/EN/EAC	2.2	Stripped and Tinned	100.8	\$24.30
2137588	MEAN WELL	HLG-120H-48A	48	2.5	43 to 53	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.4	Stripped and Tinned	120	\$45.20
2221801	MEAN WELL	NPF-120D-48	48	2.5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.3	Stripped and Tinned	120	\$44.70
2221894	MEAN WELL	OWA-120U-48	48	2.5		90 to 264		Yes	UL/CUL/FCC	1.3	4-pin DIN female	120	\$52.30
2221712	MEAN WELL	NPF-120-48	48	2.5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.3	Stripped and Tinned	120	\$42.80
2174223	MEAN WELL	HVG-150-48A	48	3.13		180 to 528		Yes	UL/CUL/FCC/EN/EAC	0.5	Stripped and Tinned	150.24	\$70.30

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2249707	MEAN WELL	ELG-150-48	48	3.13		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.7	Stripped and Tinned	150.2	\$35.20
2137668	MEAN WELL	HLG-150H-48A	48	3.2	43 to 53	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.7	Stripped and Tinned	153.6	\$45.80
2215291	MEAN WELL	LPV-150-48	48	3.2		180 to 305		No	UL/CUL/CE/EN/EAC	1.7	Stripped and Tinned	153.6	\$33.30
2136711	MEAN WELL	HLG-185H-48A	48	3.9	43 to 53	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	2.1	Stripped and Tinned	187.2	\$49.20
2252050	MEAN WELL	ELG-200-48A	48	4.16		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.8	Stripped and Tinned	199.68	\$43.70
2109042	MEAN WELL	HLG-240H-48A	48	5	44.8 to 51.2	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4	Stripped and Tinned	240	\$61.00
2115160	MEAN WELL	HLG-240H-48B	48	5	44.8 to 51.2	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4	Stripped and Tinned	240	\$62.70
2252586	MEAN WELL	ELG-240-48A	48	5		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.2	Stripped and Tinned	240	\$45.60
2141763	MEAN WELL	HLG-320H-48	48	6.7	43 to 52	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	3.5	Stripped and Tinned	321.6	\$81.70
2141851	MEAN WELL	HLG-320H-48A	48	6.7	43 to 52	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	3.5	Stripped and Tinned	321.6	\$81.70
2256131	MEAN WELL	HLG-480H-48A	48	10		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	5	Stripped and Tinned	480	\$124.00
2256190	MEAN WELL	HLG-480H-48B	48	10		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	5	Stripped and Tinned	480	\$134.00
2274751	MEAN WELL	UHP-500-48	48	10.45		90 to 264		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	4.85	Terminal Block	501.6	\$91.20
2218450	MEAN WELL	HLG-600H-48A	48	12.5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	7	Stripped and Tinned	600	\$179.00
2218468	MEAN WELL	HLG-600H-48B	48	12.5		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	7	Stripped and Tinned	600	\$182.00
2172181	MEAN WELL	HLG-60H-C700A	50	0.7	51 to 100	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.69	Stripped and Tinned	70	\$30.80
2165731	MEAN WELL	LPF-16D-54	54	0.3		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Stripped and Tinned	16.2	\$20.90

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2165917	MEAN WELL	LPF-25D-54	54	0.47		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Stripped and Tinned	25.38	\$23.20
2140648	MEAN WELL	LPF-40D-54	54	0.76		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.6	Stripped and Tinned	41.04	\$26.60
2221991	MEAN WELL	OWA-60U-54	54	1.12		90 to 264		No	UL/FCC	1.2	Female Barrel Plug	60.48	\$27.70
2189214	MEAN WELL	HLG-120H-C1400A	54	1.4	55 to 108	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.6	Stripped and Tinned	151	\$45.20
2189265	MEAN WELL	HLG-120H-C1400B	54	1.4	55 to 108	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.6	Stripped and Tinned	151	\$46.60
2140904	MEAN WELL	LPF-90-54	54	1.67		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	0.95	Stripped and Tinned	90.18	\$38.20
2142715	MEAN WELL	HLG-100H-54A	54	1.77		90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	1.2	Stripped and Tinned	95.58	\$43.90
2137596	MEAN WELL	HLG-120H-54A	54	2.3	49 to 58	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.4	Stripped and Tinned	124.2	\$45.20
2249475	MEAN WELL	ELG-150-54B	54	2.8		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.7	Stripped and Tinned	151.2	\$37.10
2141624	MEAN WELL	HLG-185H-54A	54	3.45	49 to 58	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	2.1	Stripped and Tinned	186.3	\$49.20
2196220	MEAN WELL	HBG-100-60A	60	1.6		90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.1	Stripped and Tinned	96	\$41.00
2188115	MEAN WELL	HLG-80H-C700A	64	0.7	65 to 130	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.88	Stripped and Tinned	90.3	\$36.10
2189345	MEAN WELL	HLG-185H-C1400B	71	1.4	72 to 143	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	2	Stripped and Tinned	200	\$50.50
2189302	MEAN WELL	HLG-185H-C1400A	71	1.4	72 to 143	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	2	Stripped and Tinned	200	\$49.20
2189257	MEAN WELL	HLG-120H-C1050B	74	1.05	75 to 148	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.6	Stripped and Tinned	155	\$46.60
2189290	MEAN WELL	HLG-185H-C1050A	95	1.05	96 to 190	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	2	Stripped and Tinned	200	\$49.20
2172199	MEAN WELL	HLG-60H-C350B	100	0.35	101 to 200	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.69	Stripped and Tinned	70	\$31.50

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2189193	MEAN WELL	HLG-120H-C700A	107	0.7	108 to 215	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.6	Stripped and Tinned	151	\$45.20
2189281	MEAN WELL	HLG-185H-C700A	143	0.7	144 to 286	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	2	Stripped and Tinned	200	\$49.20
2189231	MEAN WELL	HLG-120H-C500B	150	0.5	151 to 300	90 to 305		Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	1.6	Stripped and Tinned	150	\$46.60
2234433	EPtronics	LG120W-171-C0700-RD	171	0.7	57 to 171	120 to 277			UL/CUL/FCC/CE	1.2	Stripped and Tinned	120	\$13.95
2260640	MEAN WELL	HLG-240H-C2100A		2.1	59 to 119	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.5	Stripped and Tinned	249.9	\$61.00
2253028	MEAN WELL	HLG-240H-C1050B		1.05	119 to 238	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.5	Stripped and Tinned	249.9	\$62.70
2248958	MEAN WELL	HVGC-240-1050B		1.05	114.3 to 228.6	180 to 528		Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	0.76	Stripped and Tinned	240	\$81.70
2141114	MEAN WELL	PCD-25-350B		0.35	40 to 58	180 to 295		Yes	UL/CB/CE/EN/ENEC/EAC	0.6	Stripped and Tinned	20.3	\$16.00
2236885	MEAN WELL	HLG-240H-C1400B		1.4	89 to 179	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.5	Stripped and Tinned	250.6	\$62.70
2249061	MEAN WELL	HLG-320H-C2800A		2.8	57 to 114	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	3.5	Stripped and Tinned	319.2	\$81.70
2249125	MEAN WELL	HLG-320H-C2100B		2.1	76 to 152	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	3.5	Stripped and Tinned	319.2	\$84.60
2253010	MEAN WELL	HLG-240H-C700B		0.7	178 to 357	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.5	Stripped and Tinned	249.9	\$62.70
2204963	MEAN WELL	HBG-240-60B		4	36 to 60	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.5	Stripped and Tinned	240	\$73.70
2221561	MEAN WELL	LPC-100-700		0.7	72 to 143	90 to 264		No	EN/EAC/CE	2.2	Stripped and Tinned	100.1	\$24.30
2255584	MEAN WELL	IDLC-25-350		0.35	49 to 70	90 to 295		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Terminal Block	24.5	\$15.80
2204921	MEAN WELL	HBG-240-60A		4	36 to 60	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.5	Stripped and Tinned	240	\$71.60
2271559	MEAN WELL	XLG-50-A		1	22 to 54	100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.57	Stripped and Tinned	50	\$20.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2145967	MEAN WELL	LDD-1000H		1	2 to 52		9 to 56		FCC/CE	0.9	PC Pins		\$4.95
2284143	MEAN WELL	XLG-25-AB		0.7	22 to 54	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.29	Stripped and Tinned	25	\$21.90
2259681	MEAN WELL	ELG-150-C700B		0.7		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.9	Stripped and Tinned	149.8	\$37.10
2259631	MEAN WELL	ELG-150-C1050A		1.05		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.9	Stripped and Tinned	150.15	\$35.20
2256288	MEAN WELL	HLG-480H-C2100B		2.1	114 to 229	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	5	Stripped and Tinned	481	\$134.00
2252842	MEAN WELL	ELG-240-C2100A		2.1	57 to 115	100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	2.2	Stripped and Tinned	241.5	\$45.60
2252316	MEAN WELL	ELG-200-C1050A		1.05	95 to 190	100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.8	Stripped and Tinned	199.5	\$43.70
2252279	MEAN WELL	ELG-200-C1400		1.4	71 to 142	100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.8	Stripped and Tinned	198.8	\$43.70
2255621	MEAN WELL	IDLC-25A-350		0.35	12, 49 to 70	90 to 295		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Terminal Block	24.5	\$16.30
2248114	MEAN WELL	HVGC-320-1050A		1.05	152.4 to 304.8	180 to 528		Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	1.1	Stripped and Tinned	320	\$101.00
2248122	MEAN WELL	HVGC-320-1400A		1.4	114.3 to 228.6	180 to 528		Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	1.1	Stripped and Tinned	320	\$101.00
2271567	MEAN WELL	XLG-50-AB		1	22 to 54	100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.57	Stripped and Tinned	50	\$22.80
2259649	MEAN WELL	ELG-150-C1400A		1.4		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.9	Stripped and Tinned	149.8	\$35.20
2253440	MEAN WELL	IDLC-45-700		0.7	38 to 64	90 to 295		Yes	UL/CUL/CB/CE/EN/EAC/CCC	0.6	Terminal Block	44.8	\$18.10
2263663	MEAN WELL	IDLC-65-1050		1.05	46 to 62	180 to 295		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.4	Terminal Block	65.1	\$20.00
2259585	MEAN WELL	ELG-150-C1400		1.4		100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	0.9	Stripped and Tinned	149.8	\$35.20
2252308	MEAN WELL	ELG-200-C700A		0.7	142 to 286	100 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	1.8	Stripped and Tinned	200.2	\$43.70

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Voltage Range (VDC)	PFC Function	Agency Approvals	Maximum Input Current (A)	Output Connector Type	Maximum Output Power (W)	Price 1
2256237	MEAN WELL	HLG-480H-C2100A		2.1	114 to 229	90 to 305		Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	5	Stripped and Tinned	481	\$124.00
2253423	MEAN WELL	IDLC-45-350		0.35	57 to 95	90 to 295		Yes	UL/CUL/CB/CE/EN/EAC/CCC	0.6	Terminal Block	33.25	\$18.10
2274167	MEAN WELL	HVGC-480-M-AB		2.1	92 to 228.5	180 to 528		Yes	UL/CUL/CB/CE/FCC/EN/ENEC/EAC	1.52	Stripped and Tinned	480	\$167.00
2248886	MEAN WELL	HVGC-240-1050A		1.05	114.3 to 228.6	180 to 528		Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	0.76	Stripped and Tinned	240	\$79.80