



[Click Here to Request a Large Quantity Quote](#)

[LED Enclosed Power Supplies with PFC](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2142053</a>	MEAN WELL	APV-12-5	5	2		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.10
<a href="#">2141190</a>	MEAN WELL	LPV-100-5	5	12		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
<a href="#">2274711</a>	MEAN WELL	UHP-500-5	5	80		90 to 264	Terminal Block	9.13	3.19	1.22	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$91.20
<a href="#">2226290</a>	MEAN WELL	APV-8-12	12	0.67		90 to 264	Stripped and Tinned	2.36	1.18	0.87	No	UL/CUL/CE/EN/EAC	\$4.90
<a href="#">2142061</a>	MEAN WELL	APV-12-12	12	1		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.10
<a href="#">2142109</a>	MEAN WELL	APV-16-12	12	1.25		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.30
<a href="#">2165562</a>	MEAN WELL	LPF-16-12	12	1.34		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$19.00
<a href="#">2101059</a>	MEAN WELL	LPL-18-12	12	1.5		90 to 132	Stripped and Tinned	5.51	1.18	0.86	No	CE/FCC/EN/EAC	\$8.60
<a href="#">2122423</a>	MEAN WELL	PLN-20-12	12	1.6		90 to 277	Stripped and Tinned	5.84	1.51	1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$19.00
<a href="#">2102596</a>	MEAN WELL	LPV-20-12	12	1.67		90 to 264	Stripped and Tinned	4.64	1.37	1.02	No	UL/CUL/TUV/CE/EN/EAC	\$9.30
<a href="#">2164076</a>	MEAN WELL	APV-25-12	12	2.1		90 to 264	Stripped and Tinned	3.31	2.24	1.16	No	UL/CUL/CE/EN/EAC	\$10.60
<a href="#">2165749</a>	MEAN WELL	LPF-25-12	12	2.1		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$21.30
<a href="#">2103142</a>	MEAN WELL	LPV-35-12	12	3		90 to 264	Stripped and Tinned	5.82	1.57	1.18	No	UL/CUL/CE/EN/EAC	\$13.30
<a href="#">2164121</a>	MEAN WELL	APV-35-12	12	3		90 to 264	Stripped and Tinned	3.31	2.24	1.16	No	UL/CUL/CE/EN/EAC	\$11.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2234783	EPtronics	LD40W-12-C3330	12	3.33	4 to 12	90 to 305	Stripped and Tinned	3.7	2.7	1.2		UL/CUL/FCC/CE	\$11.95
2148623	MEAN WELL	HLG-40H-12B	12	3.33		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.40
2148957	MEAN WELL	HLN-40H-12A	12	3.33		90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$31.00
2148615	MEAN WELL	HLG-40H-12A	12	3.33		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$29.60
2140568	MEAN WELL	LPF-40D-12	12	3.34		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.60
2220998	MEAN WELL	NPF-40-12	12	3.34		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.90
2263815	MEAN WELL	IDLV-65A-12	12	4.2	12	180 to 295	Terminal Block	5.12	2.95	0.98	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.90
1918833	MEAN WELL	PLN-100-12	12	5	10.2 to 12	90 to 264	Stripped and Tinned	7.87	2.77	1.37	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
2196975	MEAN WELL	HVG-65-12A	12	5	10.8 to 13.5	180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/FCC/EN/EAC	\$52.30
2103901	MEAN WELL	PLC-60-12	12	5	11.5 to 13	90 to 264	Screw Terminal Block	7.14	2.44	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$33.30
1918913	MEAN WELL	PLN-60-12	12	5	11.5 to 13	90 to 295	Stripped and Tinned	7.12	2.42	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$33.30
2249723	MEAN WELL	ELG-75-12	12	5	6 to 12	100 to 305	Stripped and Tinned	7.09	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$29.50
2103169	MEAN WELL	LPV-60-12	12	5		90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	CUL/CB/CE/EN/EAC	\$14.80
2221915	MEAN WELL	OWA-60U-12	12	5		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	CUL/FCC	\$27.70
2140656	MEAN WELL	LPF-60-12	12	5		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.80
2220955	MEAN WELL	PWM-60-12	12	5		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.90

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2224972</a>	MEAN WELL	OWA-60E-12	12	5		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	CB/CE/EN/EAC	\$27.70
<a href="#">2293815</a>	MEAN WELL	XLG-75-12-A	12	5		100 to 305	Stripped and Tinned	5.51	2.48	1.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$24.70
<a href="#">2142176</a>	MEAN WELL	HLG-80H-12A	12	5		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$36.10
<a href="#">2254311</a>	MEAN WELL	LPFH-60D-12	12	5		200 to 400	Stripped and Tinned	6.4	1.69	1.26	Yes	UL/CUL/FCC/EN/EAC	\$32.50
<a href="#">2104954</a>	MEAN WELL	PLP-60-12	12	5		90 to 264	Screw Terminal Block	4	2	1.16	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$16.00
<a href="#">2197062</a>	MEAN WELL	HVG-65-12B	12	5		180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/FCC/EN/EAC	\$53.80
<a href="#">2254240</a>	MEAN WELL	LPFH-60-12	12	5		200 to 400	Stripped and Tinned	6.4	1.69	1.26	Yes	UL/CUL/FCC/EN/EAC	\$30.60
<a href="#">2215099</a>	MEAN WELL	PWM-90-12	12	7.5		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$39.00
<a href="#">2215005</a>	MEAN WELL	NPF-90-12	12	7.5		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
<a href="#">2215136</a>	MEAN WELL	OWA-90U-12	12	7.5		90 to 264	4-pin DIN female	6.73	2.48	1.48	Yes	CUL/FCC	\$40.90
<a href="#">2214918</a>	MEAN WELL	NPF-90D-12	12	7.5		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$39.00
<a href="#">2293863</a>	MEAN WELL	XLG-100-12-A	12	8		100 to 305	Stripped and Tinned	5.51	2.48	1.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.60
<a href="#">2133131</a>	MEAN WELL	LPV-100-12	12	8.5		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
<a href="#">2148105</a>	MEAN WELL	HLG-120H-12B	12	10	10.8 to 13.5	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$46.60
<a href="#">2137529</a>	MEAN WELL	HLG-120H-12A	12	10	10.8 to 13.5	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
<a href="#">2215259</a>	MEAN WELL	LPV-150-12	12	10		180 to 305	Stripped and Tinned	7.52	2.48	1.48	No	UL/CUL/CE/EN/EAC	\$33.30

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2221827</a>	MEAN WELL	OWA-120U-12	12	10		90 to 264	4-pin DIN female	7.52	2.48	1.48	Yes	UL/CUL/FCC	\$52.30
<a href="#">2222002</a>	MEAN WELL	PWM-120-12	12	10		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$44.70
<a href="#">2221641</a>	MEAN WELL	NPF-120-12	12	10		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$42.80
<a href="#">2249660</a>	MEAN WELL	ELG-150-12	12	10		100 to 305	Stripped and Tinned	8.62	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.20
<a href="#">1954877</a>	MEAN WELL	CLG-150-12A	12	11		90 to 295	Stripped and Tinned	8.74	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$47.95
<a href="#">2108699</a>	MEAN WELL	CLG-150-12	12	11		90 to 295	Stripped and Tinned	9.61	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$42.95
<a href="#">2137609</a>	MEAN WELL	HLG-150H-12A	12	12.5	10.8 to 13.5	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
<a href="#">2147911</a>	MEAN WELL	HLG-150H-12	12	12.5		90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.95
<a href="#">2147920</a>	MEAN WELL	HLG-150H-12B	12	12.5		90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.10
<a href="#">2294191</a>	MEAN WELL	XLG-150-12-A	12	12.5		100 to 305	Stripped and Tinned	7.09	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$30.40
<a href="#">2136690</a>	MEAN WELL	HLG-185H-12A	12	13	10.8 to 13.5	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$49.20
<a href="#">2102158</a>	MEAN WELL	HLG-240H-12A	12	16	11.2 to 12.8	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
<a href="#">2115004</a>	MEAN WELL	HLG-240H-12	12	16	11.2 to 12.8	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$64.95
<a href="#">2251954</a>	MEAN WELL	ELG-200-12	12	16		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2252017</a>	MEAN WELL	ELG-200-12A	12	16		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2141780</a>	MEAN WELL	HLG-320H-12A	12	22	10.8 to 13.5	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70
<a href="#">2141691</a>	MEAN WELL	HLG-320H-12	12	22	10.8 to 13.5	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2141878	MEAN WELL	HLG-320H-12B	12	22	10.8 to 13.5	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$84.60
2218311	MEAN WELL	HLG-600H-12A	12	40		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$179.00
2218329	MEAN WELL	HLG-600H-12B	12	40		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$182.00
2274719	MEAN WELL	UHP-500-12	12	41.7		90 to 264	Terminal Block	9.13	3.19	1.22	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$91.20
2165669	MEAN WELL	LPF-16D-15	15	1.07		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.90
2102781	MEAN WELL	LPV-35-15	15	2.4		90 to 264	Stripped and Tinned	5.82	1.57	1.18	No	UL/CUL/CE/EN/EAC	\$13.30
2148631	MEAN WELL	HLG-40H-15A	15	2.67		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$29.60
2196983	MEAN WELL	HVG-65-15A	15	4.3	13.5 to 17	180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/FCC/EN/EAC	\$52.30
2141202	MEAN WELL	LPV-100-15	15	6.7		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
2137502	MEAN WELL	HLG-150H-15A	15	10	13.5 to 17	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
2122431	MEAN WELL	PLN-20-18	18	1.1		90 to 277	Stripped and Tinned	5.84	1.51	1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$19.00
2142651	MEAN WELL	HLG-100H-20A	20	4.8		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
2142088	MEAN WELL	APV-12-24	24	0.5		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.10
2142125	MEAN WELL	APV-16-24	24	0.67		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.30
2270951	EPtronics	LD20W-24	24	0.83		90 to 305	Stripped and Tinned	3.7	1.5	1		UL/CUL/FCC/CE	\$9.95
2102617	MEAN WELL	LPV-20-24	24	0.84		90 to 264	Stripped and Tinned	4.64	1.37	1.02	No	UL/CUL/TUV/CE/EN/EAC	\$9.30
2164092	MEAN WELL	APV-25-24	24	1.05		90 to 264	Stripped and Tinned	3.31	2.24	1.16	No	UL/CUL/CE/EN/EAC	\$10.60



Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2165861	MEAN WELL	LPF-25D-24	24	1.05		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.20
2103505	MEAN WELL	PLC-30-24	24	1.25	22.8 to 26.4	90 to 264	Screw Terminal Block	6.29	1.81	1.18	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$21.30
2220921	MEAN WELL	PWM-40-24	24	1.67		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$25.80
2148674	MEAN WELL	HLG-40H-24A	24	1.67		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$29.60
2148682	MEAN WELL	HLG-40H-24B	24	1.67		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.40
2221114	MEAN WELL	NPF-40D-24	24	1.67		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$25.80
2221026	MEAN WELL	NPF-40-24	24	1.67		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.90
2123004	MEAN WELL	PLN-45-24	24	1.9	24 to 26	90 to 295	Stripped and Tinned	7.12	2.42	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$31.40
2104831	MEAN WELL	PLP-45-24	24	1.9		90 to 264	Screw Terminal Block	4	2	1.16	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$15.00
2263823	MEAN WELL	IDLV-65-24	24	2.4		180 to 295	Terminal Block	5.12	2.95	0.98	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.00
2102801	MEAN WELL	LPV-60-24	24	2.5		90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	CUL/CB/CE/EN/EAC	\$14.80
2221940	MEAN WELL	OWA-60U-24	24	2.5		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	CUL/FCC	\$27.70
2165378	MEAN WELL	HLG-60H-24	24	2.5		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
2140681	MEAN WELL	LPF-60-24	24	2.5		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.80
2148316	MEAN WELL	HLG-60H-24A	24	2.5		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
2121906	MEAN WELL	CEN-60-24	24	2.5		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$32.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2220963</a>	MEAN WELL	PWM-60-24	24	2.5		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.90
<a href="#">2221296</a>	MEAN WELL	NPF-60D-24	24	2.5		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.90
<a href="#">2104840</a>	MEAN WELL	PLP-60-24	24	2.5		90 to 264	Screw Terminal Block	4	2	1.16	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$16.00
<a href="#">2254338</a>	MEAN WELL	LPFH-60D-24	24	2.5		200 to 400	Stripped and Tinned	6.4	1.69	1.26	Yes	UL/CUL/FCC/EN/EAC	\$32.50
<a href="#">2254266</a>	MEAN WELL	LPFH-60-24	24	2.5		200 to 400	Stripped and Tinned	6.4	1.69	1.26	Yes	UL/CUL/FCC/EN/EAC	\$30.60
<a href="#">2225001</a>	MEAN WELL	OWA-60E-24	24	2.5		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	CB/CE/EN/EAC	\$27.70
<a href="#">2197097</a>	MEAN WELL	HVG-65-24B	24	2.71		180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/FCC/EN/EAC	\$53.80
<a href="#">2293823</a>	MEAN WELL	XLG-75-24-A	24	3.1		100 to 305	Stripped and Tinned	5.51	2.48	1.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$24.70
<a href="#">2142205</a>	MEAN WELL	HLG-80H-24A	24	3.4		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$36.10
<a href="#">2142387</a>	MEAN WELL	HLG-80H-24	24	3.4		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$32.10
<a href="#">2142299</a>	MEAN WELL	HLG-80H-24B	24	3.4		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$37.20
<a href="#">2148498</a>	MEAN WELL	HLN-80H-24A	24	3.4		90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$41.20
<a href="#">2140859</a>	MEAN WELL	LPF-90-24	24	3.75		90 to 305	Stripped and Tinned	6.33	2.4	1.41	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$38.20
<a href="#">2215101</a>	MEAN WELL	PWM-90-24	24	3.75		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$39.00
<a href="#">2215030</a>	MEAN WELL	NPF-90-24	24	3.75		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
<a href="#">2214942</a>	MEAN WELL	NPF-90D-24	24	3.75		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2103871</a>	MEAN WELL	PLC-100-24	24	4	20.4 to 24	90 to 264	Screw Terminal Block	7.89	2.73	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
<a href="#">1918868</a>	MEAN WELL	PLN-100-24	24	4	20.4 to 24	90 to 264	Stripped and Tinned	7.87	2.77	1.37	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
<a href="#">2142731</a>	MEAN WELL	HLG-100H-24B	24	4		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$45.00
<a href="#">2142660</a>	MEAN WELL	HLG-100H-24A	24	4		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
<a href="#">2121818</a>	MEAN WELL	CEN-100-24	24	4		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$42.95
<a href="#">2293871</a>	MEAN WELL	XLG-100-24-A	24	4		100 to 305	Stripped and Tinned	5.51	2.48	1.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.60
<a href="#">2156412</a>	MEAN WELL	HVG-100-24B	24	4		180 to 528	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/FCC/EN/EAC	\$68.40
<a href="#">2156404</a>	MEAN WELL	HVG-100-24A	24	4		180 to 528	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/FCC/EN/EAC	\$66.50
<a href="#">2234767</a>	EPtronics	LD100W-24-C4200	24	4.2	8 to 24	90 to 305	Stripped and Tinned	6.5	2.8	1.8		UL/CUL/FCC/CE	\$22.95
<a href="#">2141211</a>	MEAN WELL	LPV-100-24	24	4.2		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
<a href="#">2137545</a>	MEAN WELL	HLG-120H-24A	24	5	22 to 27	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
<a href="#">2148164</a>	MEAN WELL	HLG-120H-24B	24	5	22 to 27	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$46.60
<a href="#">2222011</a>	MEAN WELL	PWM-120-24	24	5		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$44.70
<a href="#">2221675</a>	MEAN WELL	NPF-120-24	24	5		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$42.80
<a href="#">2221851</a>	MEAN WELL	OWA-120U-24	24	5		90 to 264	4-pin DIN female	7.52	2.48	1.48	Yes	UL/CUL/FCC	\$52.30
<a href="#">2174186</a>	MEAN WELL	HVG-150-24A	24	6.25		180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/FCC/EN/EAC	\$70.30



Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2249432</a>	MEAN WELL	ELG-150-24B	24	6.25		100 to 305	Stripped and Tinned	8.62	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
<a href="#">2174274</a>	MEAN WELL	HVG-150-24B	24	6.25		180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/FCC/EN/EAC	\$72.20
<a href="#">2137625</a>	MEAN WELL	HLG-150H-24A	24	6.3	22 to 27	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.95
<a href="#">2147971</a>	MEAN WELL	HLG-150H-24	24	6.3		90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.95
<a href="#">2147989</a>	MEAN WELL	HLG-150H-24B	24	6.3		90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.95
<a href="#">2260543</a>	MEAN WELL	LPVL-150-24	24	6.3		90 to 132	Stripped and Tinned	7.52	2.48	1.46	No	UL/CUL/CE/FCC/EN/EAC	\$33.30
<a href="#">2189433</a>	MEAN WELL	HBG-160-24B	24	6.5	14.5 to 24.0	90 to 305	Stripped and Tinned	6	6	2.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$54.20
<a href="#">2189396</a>	MEAN WELL	HBG-160-24A	24	6.5	14.5 to 24.0	90 to 305	Stripped and Tinned	6	6	2.7	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$52.60
<a href="#">2136737</a>	MEAN WELL	HLG-185H-24B	24	7.8	22 to 27	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$50.50
<a href="#">2251962</a>	MEAN WELL	ELG-200-24	24	8.4		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2252025</a>	MEAN WELL	ELG-200-24A	24	8.4		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2102174</a>	MEAN WELL	HLG-240H-24A	24	10	22.4 to 25.6	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
<a href="#">2115127</a>	MEAN WELL	HLG-240H-24B	24	10	22.4 to 25.6	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$62.70
<a href="#">2115039</a>	MEAN WELL	HLG-240H-24	24	10	22.4 to 25.6	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
<a href="#">2252551</a>	MEAN WELL	ELG-240-24A	24	10		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$45.60
<a href="#">2248309</a>	MEAN WELL	HVG-240-24B	24	10		180 to 528	Stripped and Tinned	10.01	2.68	1.53	Yes	UL/CUL/FCC/EN/EAC	\$81.70
<a href="#">2141819</a>	MEAN WELL	HLG-320H-24A	24	13.3	21 to 26	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2147903</a>	MEAN WELL	HLG-320H-24	24	13.34	21 to 26	90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70
<a href="#">2141907</a>	MEAN WELL	HLG-320H-24B	24	13.34	21 to 26	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$84.60
<a href="#">2248018</a>	MEAN WELL	HVG-320-24B	24	13.4		180 to 528	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/FCC/EN/EAC	\$110.00
<a href="#">2255859</a>	MEAN WELL	HVG-480-24A	24	20	20.4 to 25.2	180 to 528	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/FCC/EN/EAC	\$154.00
<a href="#">2256093</a>	MEAN WELL	HLG-480H-24A	24	20		90 to 305	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$124.00
<a href="#">2255912</a>	MEAN WELL	HVG-480-24B	24	20		180 to 528	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/FCC/EN/EAC	\$158.00
<a href="#">2274735</a>	MEAN WELL	UHP-500-24	24	20.9		90 to 264	Terminal Block	9.13	3.19	1.22	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$91.20
<a href="#">2218388</a>	MEAN WELL	HLG-600H-24B	24	25		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$182.00
<a href="#">2218370</a>	MEAN WELL	HLG-600H-24A	24	25		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$179.00
<a href="#">2100574</a>	MEAN WELL	PLN-60-27	27	2.3	25 to 30	90 to 295	Stripped and Tinned	7.12	2.42	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$33.30
<a href="#">2140699</a>	MEAN WELL	LPF-60-30	30	2		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.80
<a href="#">2140947</a>	MEAN WELL	LPF-90D-30	30	3		90 to 305	Stripped and Tinned	6.33	2.4	1.41	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$40.10
<a href="#">2142811</a>	MEAN WELL	HLG-100H-30	30	3.2		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
<a href="#">2121826</a>	MEAN WELL	CEN-100-30	30	3.2		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$42.95
<a href="#">2137553</a>	MEAN WELL	HLG-120H-30A	30	4	27 to 33	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
<a href="#">2137633</a>	MEAN WELL	HLG-150H-30A	30	5	27 to 33	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
<a href="#">2141659</a>	MEAN WELL	HLG-185H-30B	30	6.2	27 to 33	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$50.50

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2102297	MEAN WELL	HLG-240H-30A	30	8	28 to 32	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
2100540	MEAN WELL	LPC-60-1750	34	1.75	9 to 34	90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	CUL/CB/CE/EN/EAC	\$14.80
2103151	MEAN WELL	LPV-35-36	36	1		90 to 264	Stripped and Tinned	5.82	1.57	1.18	No	UL/CUL/CE/EN/EAC	\$13.30
2140613	MEAN WELL	LPF-40D-36	36	1.12		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.60
2140525	MEAN WELL	LPF-40-36	36	1.12		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$24.70
2220939	MEAN WELL	PWM-40-36	36	1.12		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$25.80
2140701	MEAN WELL	LPF-60-36	36	1.67		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.80
2221966	MEAN WELL	OWA-60U-36	36	1.67		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	CUL/FCC	\$27.70
2148367	MEAN WELL	HLG-60H-36B	36	1.7		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$31.50
2121922	MEAN WELL	CEN-60-36	36	1.7		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$0.00
2142221	MEAN WELL	HLG-80H-36A	36	2.3		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$36.10
2214969	MEAN WELL	NPF-90D-36	36	2.5		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$39.00
2142686	MEAN WELL	HLG-100H-36A	36	2.65		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
2196246	MEAN WELL	HBG-100-36B	36	2.7		90 to 305	Stripped and Tinned	4.45	2.56	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$41.00
2196203	MEAN WELL	HBG-100-36A	36	2.7		90 to 305	Stripped and Tinned	4.45	2.56	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$41.00
2141229	MEAN WELL	LPV-100-36	36	2.8		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
2137561	MEAN WELL	HLG-120H-36A	36	3.4	33 to 40	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2137641	MEAN WELL	HLG-150H-36A	36	4.2	33 to 40	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
2148025	MEAN WELL	HLG-150H-36B	36	4.2		90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.10
2141667	MEAN WELL	HLG-185H-36B	36	5.2	33 to 40	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$50.50
2248261	MEAN WELL	HVG-240-36A	36	6.7	18 to 36	180 to 528	Stripped and Tinned	10.01	2.68	1.53	Yes	UL/CUL/FCC/EN/EAC	\$79.80
2141835	MEAN WELL	HLG-320H-36A	36	8.9	32 to 39	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70
2255875	MEAN WELL	HVG-480-36A	36	13.3	30.6 to 37.8	180 to 528	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/FCC/EN/EAC	\$154.00
2255939	MEAN WELL	HVG-480-36B	36	13.3		180 to 528	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/FCC/EN/EAC	\$158.00
2165714	MEAN WELL	LPF-16D-42	42	0.39		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.90
2165802	MEAN WELL	LPF-25-42	42	0.6		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$21.30
2165896	MEAN WELL	LPF-25D-42	42	0.6		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.20
2140621	MEAN WELL	LPF-40D-42	42	0.96		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.60
2221974	MEAN WELL	OWA-60U-42	42	1.5		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	UL/FCC	\$27.70
2142230	MEAN WELL	HLG-80H-42A	42	1.95		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$36.10
2142328	MEAN WELL	HLG-80H-42B	42	1.95		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$37.20
2142766	MEAN WELL	HLG-100H-42B	42	2.28		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$45.00
2148210	MEAN WELL	HLG-120H-42B	42	2.9	38 to 46	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$46.60
2137570	MEAN WELL	HLG-120H-42A	42	2.9	38 to 46	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2249395</a>	MEAN WELL	ELG-150-42A	42	3.57		100 to 305	Stripped and Tinned	8.62	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.20
<a href="#">2137650</a>	MEAN WELL	HLG-150H-42A	42	3.6	38 to 46	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
<a href="#">2101737</a>	MEAN WELL	HLG-240H-42A	42	5.72	39 to 45	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
<a href="#">2247980</a>	MEAN WELL	HVG-320-42A	42	7.6	21 to 42	180 to 528	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/FCC/EN/EAC	\$106.00
<a href="#">2141931</a>	MEAN WELL	HLG-320H-42B	42	7.65	38 to 45	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$84.60
<a href="#">2122466</a>	MEAN WELL	PLN-20-48	48	0.42		90 to 277	Stripped and Tinned	5.84	1.51	1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$19.00
<a href="#">2148762</a>	MEAN WELL	HLG-40H-48B	48	0.84		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.40
<a href="#">2140630</a>	MEAN WELL	LPF-40D-48	48	0.84		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$23.95
<a href="#">2102633</a>	MEAN WELL	LPV-60-48	48	1.25		90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	UL/CB/CE/EN/EAC	\$14.80
<a href="#">2140728</a>	MEAN WELL	LPF-60-48	48	1.25		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$22.95
<a href="#">2140816</a>	MEAN WELL	LPF-60D-48	48	1.25		90 to 305	Stripped and Tinned	6.39	1.71	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$28.70
<a href="#">2254291</a>	MEAN WELL	LPFH-60-48	48	1.25		200 to 400	Stripped and Tinned	6.4	1.69	1.26	Yes	UL/CUL/FCC/EN/EAC	\$30.60
<a href="#">2220980</a>	MEAN WELL	PWM-60-48	48	1.25		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.90
<a href="#">2148391</a>	MEAN WELL	HLG-60H-48A	48	1.3		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
<a href="#">2104858</a>	MEAN WELL	PLP-60-48	48	1.3		90 to 264	Screw Terminal Block	4	2	1.16	Yes	UL/TUV/CB/CE/EN/EAC/CCC	\$16.00
<a href="#">2121949</a>	MEAN WELL	CEN-60-48	48	1.3		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$33.95



Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2142248</a>	MEAN WELL	HLG-80H-48A	48	1.7		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	UL/TUV/CB/CE/EN/EAC/CCC	\$36.10
<a href="#">2142336</a>	MEAN WELL	HLG-80H-48B	48	1.7		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	UL/TUV/CB/CE/EN/EAC/CCC	\$37.20
<a href="#">2215072</a>	MEAN WELL	NPF-90-48	48	1.88		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
<a href="#">2214985</a>	MEAN WELL	NPF-90D-48	48	1.88		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$39.00
<a href="#">2103880</a>	MEAN WELL	PLC-100-48	48	2	40.8 to 48	90 to 264	Screw Terminal Block	7.89	2.73	1.37	Yes	UL/TUV/CB/CE/EN/EAC/CCC	\$42.20
<a href="#">1918892</a>	MEAN WELL	PLN-100-48	48	2	40.8 to 48	90 to 264	Stripped and Tinned	7.87	2.77	1.37	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
<a href="#">2142774</a>	MEAN WELL	HLG-100H-48B	48	2		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$45.00
<a href="#">2156527</a>	MEAN WELL	HVG-100-48A	48	2		180 to 528	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/FCC/EN/EAC	\$66.50
<a href="#">2141237</a>	MEAN WELL	LPV-100-48	48	2.1		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
<a href="#">2137588</a>	MEAN WELL	HLG-120H-48A	48	2.5	43 to 53	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
<a href="#">2221801</a>	MEAN WELL	NPF-120D-48	48	2.5		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$44.70
<a href="#">2221894</a>	MEAN WELL	OWA-120U-48	48	2.5		90 to 264	4-pin DIN female	7.52	2.48	1.48	Yes	UL/CUL/FCC	\$52.30
<a href="#">2221712</a>	MEAN WELL	NPF-120-48	48	2.5		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$42.80
<a href="#">2249707</a>	MEAN WELL	ELG-150-48	48	3.13		100 to 305	Stripped and Tinned	8.62	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.20
<a href="#">2137668</a>	MEAN WELL	HLG-150H-48A	48	3.2	43 to 53	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
<a href="#">2136711</a>	MEAN WELL	HLG-185H-48A	48	3.9	43 to 53	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$49.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2252050</a>	MEAN WELL	ELG-200-48A	48	4.16		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2109042</a>	MEAN WELL	HLG-240H-48A	48	5	44.8 to 51.2	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
<a href="#">2115160</a>	MEAN WELL	HLG-240H-48B	48	5	44.8 to 51.2	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$62.70
<a href="#">2252586</a>	MEAN WELL	ELG-240-48A	48	5		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$45.60
<a href="#">2141763</a>	MEAN WELL	HLG-320H-48	48	6.7	43 to 52	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70
<a href="#">2256131</a>	MEAN WELL	HLG-480H-48A	48	10		90 to 305	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$124.00
<a href="#">2256190</a>	MEAN WELL	HLG-480H-48B	48	10		90 to 305	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$134.00
<a href="#">2274751</a>	MEAN WELL	UHP-500-48	48	10.45		90 to 264	Terminal Block	9.13	3.19	1.22	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$91.20
<a href="#">2218450</a>	MEAN WELL	HLG-600H-48A	48	12.5		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$179.00
<a href="#">2218468</a>	MEAN WELL	HLG-600H-48B	48	12.5		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$182.00
<a href="#">2172181</a>	MEAN WELL	HLG-60H-C700A	50	0.7	51 to 100	90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
<a href="#">2165731</a>	MEAN WELL	LPF-16D-54	54	0.3		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.90
<a href="#">2165917</a>	MEAN WELL	LPF-25D-54	54	0.47		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.20
<a href="#">2140648</a>	MEAN WELL	LPF-40D-54	54	0.76		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.60
<a href="#">2221991</a>	MEAN WELL	OWA-60U-54	54	1.12		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	UL/FCC	\$27.70
<a href="#">2189214</a>	MEAN WELL	HLG-120H-C1400A	54	1.4	55 to 108	90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
<a href="#">2189265</a>	MEAN WELL	HLG-120H-C1400B	54	1.4	55 to 108	90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$46.60

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2140904	MEAN WELL	LPF-90-54	54	1.67		90 to 305	Stripped and Tinned	6.33	2.4	1.41	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$38.20
2140980	MEAN WELL	LPF-90D-54	54	1.67		90 to 305	Stripped and Tinned	6.33	2.4	1.41	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$40.10
2142715	MEAN WELL	HLG-100H-54A	54	1.77		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
2137596	MEAN WELL	HLG-120H-54A	54	2.3	49 to 58	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
2249475	MEAN WELL	ELG-150-54B	54	2.8		100 to 305	Stripped and Tinned	8.62	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
2141624	MEAN WELL	HLG-185H-54A	54	3.45	49 to 58	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$49.20
2196220	MEAN WELL	HBG-100-60A	60	1.6		90 to 305	Stripped and Tinned	4.45	2.56	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$41.00
2188115	MEAN WELL	HLG-80H-C700A	64	0.7	65 to 130	90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$36.10
2189345	MEAN WELL	HLG-185H-C1400B	71	1.4	72 to 143	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$50.50
2189302	MEAN WELL	HLG-185H-C1400A	71	1.4	72 to 143	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$49.20
2189257	MEAN WELL	HLG-120H-C1050B	74	1.05	75 to 148	90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$46.60
2189290	MEAN WELL	HLG-185H-C1050A	95	1.05	96 to 190	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$49.20
2172199	MEAN WELL	HLG-60H-C350B	100	0.35	101 to 200	90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$31.50
2189193	MEAN WELL	HLG-120H-C700A	107	0.7	108 to 215	90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
2234425	EPtronics	LG75W-108-C0700-RD	108	0.7	36 to 108	120 to 277	Stripped and Tinned	9.4	1.8	1.3		UL/CUL/FCC/CE	\$11.95
2189281	MEAN WELL	HLG-185H-C700A	143	0.7	144 to 286	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$49.20
2189231	MEAN WELL	HLG-120H-C500B	150	0.5	151 to 300	90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$46.60

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2234433	EPtronics	LG120W-171-C0700-RD	171	0.7	57 to 171	120 to 277	Stripped and Tinned	9.4	1.8	1.3		UL/CUL/FCC/CE	\$13.95
2101315	MEAN WELL	LPC-60-1400		1.4	9 to 42	90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	UL/CUL/CB/CE/EN/EAC	\$14.80
2101121	MEAN WELL	LPC-20-350		0.35	9 to 48	90 to 264	Stripped and Tinned	4.65	1.38	1.02	No	UL/TUV/CE/EN/EAC	\$9.30
2101307	MEAN WELL	LPC-35-700		0.7	9 to 48	90 to 264	Stripped and Tinned	5.82	1.57	1.18	No	UL/CE/EN/EAC	\$13.30
2260640	MEAN WELL	HLG-240H-C2100A		2.1	59 to 119	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$61.00
2101147	MEAN WELL	LPC-60-1050		1.05	9 to 48	90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	UL/CUL/CB/CE/EN/EAC	\$14.80
2141000	MEAN WELL	PCD-16-700A		0.7	16 to 24	90 to 135	Stripped and Tinned	3.3	2.24	1.16	Yes	CUL/FCC/EN/EAC	\$14.80
2260623	MEAN WELL	HLG-240H-C1400A		1.4	89 to 179	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$61.00
2253028	MEAN WELL	HLG-240H-C1050B		1.05	119 to 238	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$62.70
2164041	MEAN WELL	APC-35-700		0.7	15 to 50	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	UL/CE/EN/EAC	\$11.80
2163997	MEAN WELL	APC-25-500		0.5	15 to 50	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	UL/CE/EN/EAC	\$10.60
2164050	MEAN WELL	APC-35-1050		1.05	11 to 33	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	CUL/CE/EN/EAC	\$11.80
2141093	MEAN WELL	PCD-25-1050A		1.05	16 to 24	90 to 135	Stripped and Tinned	3.3	2.24	1.16	Yes	CUL/FCC/EN/EAC	\$16.00
2248958	MEAN WELL	HVGC-240-1050B		1.05	114.3 to 228.6	180 to 528	Stripped and Tinned	10.01	2.68	1.53	Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	\$81.70
2253458	MEAN WELL	IDLC-45-1050		1.05	26 to 43	90 to 295	Terminal Block	4.72	2.95	0.98	Yes	UL/CUL/CB/CE/EN/EAC/CCC	\$18.10
2141114	MEAN WELL	PCD-25-350B		0.35	40 to 58	180 to 295	Stripped and Tinned	3.3	2.24	1.16	Yes	UL/CB/CE/EN/ENEC/EAC	\$16.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2193096	MEAN WELL	PLM-40-1050		1.05	19 to 38	110 to 295	Screw Terminal Block	6.89	1.65	0.94	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$15.20
2236885	MEAN WELL	HLG-240H-C1400B		1.4	89 to 179	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$62.70
2249061	MEAN WELL	HLG-320H-C2800A		2.8	57 to 114	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$81.70
2164017	MEAN WELL	APC-25-1050		1.05	9 to 24	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	CUL/CE/EN/EAC	\$10.60
2249125	MEAN WELL	HLG-320H-C2100B		2.1	76 to 152	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$84.60
2221499	MEAN WELL	HBG-60-1400		1.4	28 to 43	90 to 295	Stripped and Tinned		3.86	2.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$21.50
2253010	MEAN WELL	HLG-240H-C700B		0.7	178 to 357	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$62.70
2204963	MEAN WELL	HBG-240-60B		4	36 to 60	90 to 305	Stripped and Tinned				Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$73.70
2221561	MEAN WELL	LPC-100-700		0.7	72 to 143	90 to 264	Stripped and Tinned	7.48	2.05	1.46	No	EN/EAC/CE	\$24.30
2255584	MEAN WELL	IDLC-25-350		0.35	49 to 70	90 to 295	Terminal Block	4.33	2.95	0.87	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$15.80
2204921	MEAN WELL	HBG-240-60A		4	36 to 60	90 to 305	Stripped and Tinned				Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$71.60
2271559	MEAN WELL	XLG-50-A		1	22 to 54	100 to 305	Stripped and Tinned	4.13	2.48	1.18	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.00
2226329	MEAN WELL	APC-8-350		0.35	11 to 23	90 to 264	Stripped and Tinned	2.36	1.18	0.87	No	UL/CUL/CE/EN/EAC	\$4.90
2141018	MEAN WELL	PCD-16-1050A		1.05	12 to 16	90 to 135	Stripped and Tinned	3.3	2.24	1.16	Yes	CUL/FCC/EN/EAC	\$14.80
2284143	MEAN WELL	XLG-25-AB		0.7	22 to 54	90 to 305	Stripped and Tinned	4.13	2.48	1.18	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$21.90
2294263	MEAN WELL	XLG-200-24-A		8.3		100 to 305	Stripped and Tinned	7.83	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10



Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2101294</a>	MEAN WELL	LPC-35-1400		1.4	9 to 24	90 to 264	Stripped and Tinned	5.82	1.57	1.18	No	UL/CUL/CE/EN/EAC	\$13.30
<a href="#">2259681</a>	MEAN WELL	ELG-150-C700B		0.7		100 to 305	Stripped and Tinned	8.62	2.48	1.41	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
<a href="#">2253491</a>	MEAN WELL	IDLC-45A-700		0.7	38 to 64	90 to 295	Terminal Block	4.72	2.95	0.98	Yes	UL/CUL/CB/CE/EN/EAC/CCC	\$19.00
<a href="#">2259631</a>	MEAN WELL	ELG-150-C1050A		1.05		100 to 305	Stripped and Tinned	8.62	2.48	1.41	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.20
<a href="#">2256288</a>	MEAN WELL	HLG-480H-C2100B		2.1	114 to 229	90 to 305	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$134.00
<a href="#">2204824</a>	MEAN WELL	PLM-25-500		0.5	30 to 50	110 to 295	Screw Terminal	5.7	1.49	0.86	Yes	UL/CUL/CB/CE/EN/ENEC/EAC	\$12.50
<a href="#">2216711</a>	MEAN WELL	LCM-25DA		1.05	6 to 54	180 to 277	JST B2B-PH-KL	4.13	2.68	0.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$29.10
<a href="#">2252842</a>	MEAN WELL	ELG-240-C2100A		2.1	57 to 115	100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$45.60
<a href="#">2174573</a>	MEAN WELL	LCM-40		1.05	2 to 100	180 to 295	JST B2B-XH	4.9	3.2	0.9	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$28.50
<a href="#">2193002</a>	MEAN WELL	PCD-60-1050B		1.05	34 to 57	180 to 295	Stripped and Tinned	5.04	2.36	1.24	Yes	CB/CE/EN/ENEC/EAC	\$22.00
<a href="#">2174581</a>	MEAN WELL	LCM-40DA		1.05	2 to 100	180 to 295	JST B2B-XH	4.9	3.2	0.9	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$34.20
<a href="#">2174469</a>	MEAN WELL	HVGC-150-1400A		1.4	12 to 107	180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$70.30
<a href="#">2197257</a>	MEAN WELL	HVGC-65-700B		0.7	9 to 93	180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/CB/CE/FCC/EN/ENEC/EAC	\$53.80
<a href="#">2141157</a>	MEAN WELL	PLD-25-350		0.35	40 to 58	90 to 295	Stripped and Tinned	3.3	2.24	1.16	Yes	UL/CB/CE/FCC/EN/ENEC/EAC	\$15.60
<a href="#">2252316</a>	MEAN WELL	ELG-200-C1050A		1.05	95 to 190	100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2216702</a>	MEAN WELL	LCM-25		1.05	6 to 54	180 to 277	JST B2B-PH-KL	4.13	2.68	0.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.40
<a href="#">2252279</a>	MEAN WELL	ELG-200-C1400		1.4	71 to 142	100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2253466</a>	MEAN WELL	IDLC-45-1400		1.4	19 to 32	90 to 295	Terminal Block	4.72	2.95	0.98	Yes	UL/CUL/CB/CE/EN/EAC/CCC	\$18.10

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2255605</a>	MEAN WELL	IDLC-25-700		0.7	25.2 to 36	90 to 295	Terminal Block	4.33	2.95	0.87	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$15.80
<a href="#">2255621</a>	MEAN WELL	IDLC-25A-350		0.35	12, 49 to 70	90 to 295	Terminal Block	4.33	2.95	0.87	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$16.30
<a href="#">2248114</a>	MEAN WELL	HVGC-320-1050A		1.05	152.4 to 304.8	180 to 528	Stripped and Tinned	10.32	3.54	1.72	Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	\$101.00
<a href="#">2248122</a>	MEAN WELL	HVGC-320-1400A		1.4	114.3 to 228.6	180 to 528	Stripped and Tinned	10.32	3.54	1.72	Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	\$101.00
<a href="#">2271567</a>	MEAN WELL	XLG-50-AB		1	22 to 54	100 to 305	Stripped and Tinned	4.13	2.48	1.18	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$22.80
<a href="#">2221587</a>	MEAN WELL	LPC-100-1400		1.4	36 to 72	90 to 264	Stripped and Tinned	7.48	2.05	1.46	No	EN/EAC/CE	\$24.30
<a href="#">2174426</a>	MEAN WELL	HVGC-150-350A		0.35	42 to 428	180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$70.30
<a href="#">2255648</a>	MEAN WELL	IDLC-25A-700		0.7	12, 25.2 to 36	90 to 295	Terminal Block	4.33	2.95	0.87	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$16.30
<a href="#">2259649</a>	MEAN WELL	ELG-150-C1400A		1.4		100 to 305	Stripped and Tinned	8.62	2.48	1.41	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.20
<a href="#">2253440</a>	MEAN WELL	IDLC-45-700		0.7	38 to 64	90 to 295	Terminal Block	4.72	2.95	0.98	Yes	UL/CUL/CB/CE/EN/EAC/CCC	\$18.10
<a href="#">2222352</a>	MEAN WELL	PLM-25E-500		0.5	30 to 50	180 to 295	Screw Terminal	5.7	1.49	0.86	Yes	CB/CE/EN/ENEC/EAC/CCC	\$10.60
<a href="#">2263663</a>	MEAN WELL	IDLC-65-1050		1.05	46 to 62	180 to 295	Terminal Block	5.12	2.95	0.98	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.00
<a href="#">2259585</a>	MEAN WELL	ELG-150-C1400		1.4		100 to 305	Stripped and Tinned	8.62	2.48	1.41	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.20
<a href="#">2252308</a>	MEAN WELL	ELG-200-C700A		0.7	142 to 286	100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
<a href="#">2259593</a>	MEAN WELL	ELG-150-C1750		1.75		100 to 305	Stripped and Tinned	8.62	2.48	1.41	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.20
<a href="#">2264079</a>	MEAN WELL	IDPC-65A-1050		1.05	12, 46 to 62	180 to 295	Terminal Block	5.12	2.66	0.81	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$19.20
<a href="#">2264127</a>	MEAN WELL	IDPC-65A-1750		1.75	12, 27 to 36	180 to 295	Terminal Block	5.12	2.66	0.81	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$19.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2256237</a>	MEAN WELL	HLG-480H-C2100A		2.1	114 to 229	90 to 305	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$124.00
<a href="#">2253423</a>	MEAN WELL	IDLC-45-350		0.35	57 to 95	90 to 295	Terminal Block	4.72	2.95	0.98	Yes	UL/CUL/CB/CE/EN/EAC/CCC	\$18.10
<a href="#">2174451</a>	MEAN WELL	HVGC-150-1050A		1.05	15 to 143	180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$70.30
<a href="#">2197231</a>	MEAN WELL	HVGC-65-350B		0.35	18 to 186	180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/CB/CE/FCC/EN/ENEC/EAC	\$53.80
<a href="#">2264055</a>	MEAN WELL	IDPC-65A-700		0.7	12, 69 to 93	180 to 295	Terminal Block	5.12	2.66	0.81	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$19.20
<a href="#">2274167</a>	MEAN WELL	HVGC-480-M-AB		2.1	92 to 228.5	180 to 528	Stripped and Tinned	10.315	4.92	1.72	Yes	UL/CUL/CB/CE/FCC/EN/ENEC/EAC	\$167.00
<a href="#">2174590</a>	MEAN WELL	LCM-60		1.4	2 to 90	180 to 295	JST B2B-XH	4.9	3.2	0.9	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$31.40
<a href="#">2264103</a>	MEAN WELL	IDPC-65A-1400		1.4	12, 34 to 46	180 to 295	Terminal Block	5.12	2.66	0.81	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$19.20
<a href="#">2248886</a>	MEAN WELL	HVGC-240-1050A		1.05	114.3 to 228.6	180 to 528	Stripped and Tinned	10.01	2.68	1.53	Yes	UL/CUL/CE/FCC/EN/ENEC/EAC	\$79.80