



[Click Here to Request a Large Quantity Quote](#)

[15 to 23 Volt LED Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2142070</a>	MEAN WELL	APV-12-15	15	0.8		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.10
<a href="#">2142117</a>	MEAN WELL	APV-16-15	15	1		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.30
<a href="#">2165669</a>	MEAN WELL	LPF-16D-15	15	1.07		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.90
<a href="#">2102781</a>	MEAN WELL	LPV-35-15	15	2.4		90 to 264	Stripped and Tinned	5.82	1.57	1.18	No	UL/CUL/CE/EN/EAC	\$13.30
<a href="#">2148631</a>	MEAN WELL	HLG-40H-15A	15	2.67		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$29.60
<a href="#">2103177</a>	MEAN WELL	LPV-60-15	15	4		90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	CUL/CB/CE/EN/EAC	\$14.80
<a href="#">2141202</a>	MEAN WELL	LPV-100-15	15	6.7		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
<a href="#">2215267</a>	MEAN WELL	LPV-150-15	15	8		180 to 305	Stripped and Tinned	7.52	2.48	1.48	No	UL/CUL/CE/EN/EAC	\$33.30
<a href="#">2137502</a>	MEAN WELL	HLG-150H-15A	15	10	13.5 to 17	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
<a href="#">2122431</a>	MEAN WELL	PLN-20-18	18	1.1		90 to 277	Stripped and Tinned	5.84	1.51	1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$19.00
<a href="#">2142651</a>	MEAN WELL	HLG-100H-20A	20	4.8		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
<a href="#">2197003</a>	MEAN WELL	HVG-65-24A	24	2.71	22 to 27	180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/FCC/EN/EAC	\$52.30
<a href="#">2141000</a>	MEAN WELL	PCD-16-700A		0.7	16 to 24	90 to 135	Stripped and Tinned	3.3	2.24	1.16	Yes	CUL/FCC/EN/EAC	\$14.80
<a href="#">2164041</a>	MEAN WELL	APC-35-700		0.7	15 to 50	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	UL/CE/EN/EAC	\$11.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
<a href="#">2163997</a>	MEAN WELL	APC-25-500		0.5	15 to 50	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	UL/CE/EN/EAC	\$10.60
<a href="#">2141093</a>	MEAN WELL	PCD-25-1050A		1.05	16 to 24	90 to 135	Stripped and Tinned	3.3	2.24	1.16	Yes	CUL/FCC/EN/EAC	\$16.00
<a href="#">2193096</a>	MEAN WELL	PLM-40-1050		1.05	19 to 38	110 to 295	Screw Terminal Block	6.89	1.65	0.94	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$15.20
<a href="#">2207540</a>	MEAN WELL	PLM-12-350		0.35	22 to 36	110 to 295	Screw Terminal	5.7	1.49	0.86	Yes	UL/CUL/CB/CE/EN/ENEC/EAC	\$12.20
<a href="#">2141173</a>	MEAN WELL	PLD-25-1050		1.05	16 to 24	90 to 295	Stripped and Tinned	3.3	2.24	1.16	Yes	CUL/CB/CE/FCC/EN/ENEC/EAC	\$15.60
<a href="#">2174451</a>	MEAN WELL	HVGC-150-1050A		1.05	15 to 143	180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$70.30
<a href="#">2197231</a>	MEAN WELL	HVGC-65-350B		0.35	18 to 186	180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/CB/CE/FCC/EN/ENEC/EAC	\$53.80