



[Click Here to Request a Large Quantity Quote](#)

[24 to 35 Volt LED Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2294191	MEAN WELL	XLG-150-12-A	12	12.5		100 to 305	Stripped and Tinned	7.09	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$30.40
2226302	MEAN WELL	APV-8-24	24	0.34		90 to 264	Stripped and Tinned	2.36	1.18	0.87	No	UL/CUL/CE/EN/EAC	\$4.90
2142088	MEAN WELL	APV-12-24	24	0.5		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.10
2142125	MEAN WELL	APV-16-24	24	0.67		90 to 264	Stripped and Tinned	3.03	1.57	1.14	No	UL/CUL/CB/CE/EN/ENEC/EAC	\$6.30
2165597	MEAN WELL	LPF-16-24	24	0.67		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$19.00
2165685	MEAN WELL	LPF-16D-24	24	0.67		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.90
2122491	MEAN WELL	PLP-20-24	24	0.8		90 to 277	Stripped and Tinned	5.51	1.25	0.86	Yes	UL/CUL/TUV/CE	\$14.00
2270951	EPtronics	LD20W-24	24	0.83		90 to 305	Stripped and Tinned	3.7	1.5	1		UL/CUL/FCC/CE	\$9.95
2102617	MEAN WELL	LPV-20-24	24	0.84		90 to 264	Stripped and Tinned	4.64	1.37	1.02	No	UL/CUL/TUV/CE/EN/EAC	\$9.30
2164092	MEAN WELL	APV-25-24	24	1.05		90 to 264	Stripped and Tinned	3.31	2.24	1.16	No	UL/CUL/CE/EN/EAC	\$10.60
2165861	MEAN WELL	LPF-25D-24	24	1.05		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.20
2165773	MEAN WELL	LPF-25-24	24	1.05		90 to 305	Stripped and Tinned	5.8	1.6	1.3	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$21.30
2103505	MEAN WELL	PLC-30-24	24	1.25	22.8 to 26.4	90 to 264	Screw Terminal Block	6.29	1.81	1.18	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$21.30
2102799	MEAN WELL	LPV-35-24	24	1.5		90 to 264	Stripped and Tinned	5.82	1.57	1.18	No	UL/CUL/CE/EN/EAC	\$13.30

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2164148	MEAN WELL	APV-35-24	24	1.5		90 to 264	Stripped and Tinned	3.31	2.24	1.16	No	UL/CUL/CE/EN/EAC	\$11.80
2140509	MEAN WELL	LPF-40-24	24	1.67		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$24.70
2140592	MEAN WELL	LPF-40D-24	24	1.67		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.60
2220921	MEAN WELL	PWM-40-24	24	1.67		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$25.80
2148674	MEAN WELL	HLG-40H-24A	24	1.67		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$29.60
2148682	MEAN WELL	HLG-40H-24B	24	1.67		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.40
2221114	MEAN WELL	NPF-40D-24	24	1.67		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$25.80
2221026	MEAN WELL	NPF-40-24	24	1.67		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$23.90
2123004	MEAN WELL	PLN-45-24	24	1.9	24 to 26	90 to 295	Stripped and Tinned	7.12	2.42	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$31.40
2104831	MEAN WELL	PLP-45-24	24	1.9		90 to 264	Screw Terminal Block	4	2	1.16	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$15.00
2263823	MEAN WELL	IDLV-65-24	24	2.4		180 to 295	Terminal Block	5.12	2.95	0.98	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$20.00
2103636	MEAN WELL	PLC-60-24	24	2.5	24 to 26	90 to 264	Screw Terminal Block	7.14	2.44	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$33.30
2102801	MEAN WELL	LPV-60-24	24	2.5		90 to 264	Stripped and Tinned	6.39	1.67	1.25	No	CUL/CB/CE/EN/EAC	\$14.80
2140779	MEAN WELL	LPF-60D-24	24	2.5		90 to 305	Stripped and Tinned	6.39	1.71	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$28.70
2221940	MEAN WELL	OWA-60U-24	24	2.5		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	CUL/FCC	\$27.70
2165378	MEAN WELL	HLG-60H-24	24	2.5		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
2140681	MEAN WELL	LPF-60-24	24	2.5		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2148324	MEAN WELL	HLG-60H-24B	24	2.5		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$31.50
2148316	MEAN WELL	HLG-60H-24A	24	2.5		90 to 305	Stripped and Tinned	6.73	2.42	1.45	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$30.80
2121906	MEAN WELL	CEN-60-24	24	2.5		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$32.95
2220963	MEAN WELL	PWM-60-24	24	2.5		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.90
2221202	MEAN WELL	NPF-60-24	24	2.5		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$26.00
2221296	MEAN WELL	NPF-60D-24	24	2.5		90 to 305	Stripped and Tinned	5.91	2.09	1.38	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.90
2104840	MEAN WELL	PLP-60-24	24	2.5		90 to 264	Screw Terminal Block	4	2	1.16	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$16.00
2254338	MEAN WELL	LPFH-60D-24	24	2.5		200 to 400	Stripped and Tinned	6.4	1.69	1.26	Yes	UL/CUL/FCC/EN/EAC	\$32.50
2254266	MEAN WELL	LPFH-60-24	24	2.5		200 to 400	Stripped and Tinned	6.4	1.69	1.26	Yes	UL/CUL/FCC/EN/EAC	\$30.60
2225001	MEAN WELL	OWA-60E-24	24	2.5		90 to 264	Female Barrel Plug	5.12	2.09	1.38	No	CB/CE/EN/EAC	\$27.70
2197097	MEAN WELL	HVG-65-24B	24	2.71		180 to 528	Stripped and Tinned	7.44	2.42	1.45	Yes	UL/CUL/FCC/EN/EAC	\$53.80
2293823	MEAN WELL	XLG-75-24-A	24	3.1		100 to 305	Stripped and Tinned	5.51	2.48	1.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$24.70
2121981	MEAN WELL	CEN-75-24	24	3.15		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$34.95
2304623	MEAN WELL	SLD-80-24	24	3.3		110 to 305	Screw Terminal Block	12.6	1.18	0.66	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$24.70
2142205	MEAN WELL	HLG-80H-24A	24	3.4		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$36.10
2142387	MEAN WELL	HLG-80H-24	24	3.4		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$32.10
2142299	MEAN WELL	HLG-80H-24B	24	3.4		90 to 305	Stripped and Tinned	7.7	2.42	1.53	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$37.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2148498	MEAN WELL	HLN-80H-24A	24	3.4		90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$41.20
2140859	MEAN WELL	LPF-90-24	24	3.75		90 to 305	Stripped and Tinned	6.33	2.4	1.41	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$38.20
2215101	MEAN WELL	PWM-90-24	24	3.75		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$39.00
2215030	MEAN WELL	NPF-90-24	24	3.75		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
2215161	MEAN WELL	OWA-90U-24	24	3.75		90 to 264	4-pin DIN female	6.73	2.48	1.48	Yes	CUL/FCC	\$40.90
2214942	MEAN WELL	NPF-90D-24	24	3.75		90 to 305	Stripped and Tinned	6.73	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$35.00
2103871	MEAN WELL	PLC-100-24	24	4	20.4 to 24	90 to 264	Screw Terminal Block	7.89	2.73	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
1918868	MEAN WELL	PLN-100-24	24	4	20.4 to 24	90 to 264	Stripped and Tinned	7.87	2.77	1.37	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$42.20
2142731	MEAN WELL	HLG-100H-24B	24	4		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$45.00
2142660	MEAN WELL	HLG-100H-24A	24	4		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
2121818	MEAN WELL	CEN-100-24	24	4		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$42.95
2293871	MEAN WELL	XLG-100-24-A	24	4		100 to 305	Stripped and Tinned	5.51	2.48	1.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$27.60
2156412	MEAN WELL	HVG-100-24B	24	4		180 to 528	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/FCC/EN/EAC	\$68.40
2156404	MEAN WELL	HVG-100-24A	24	4		180 to 528	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/FCC/EN/EAC	\$66.50
2234767	EPtronics	LD100W-24-C4200	24	4.2	8 to 24	90 to 305	Stripped and Tinned	6.5	2.8	1.8		UL/CUL/FCC/CE	\$22.95
2141211	MEAN WELL	LPV-100-24	24	4.2		90 to 264	Stripped and Tinned	7.48	2.04	1.45	No	UL/CUL/CE/EN/EAC	\$24.30
2137545	MEAN WELL	HLG-120H-24A	24	5	22 to 27	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2148164	MEAN WELL	HLG-120H-24B	24	5	22 to 27	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$46.60
2148156	MEAN WELL	HLG-120H-24	24	5	22 to 27	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
2222011	MEAN WELL	PWM-120-24	24	5		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$44.70
2221675	MEAN WELL	NPF-120-24	24	5		90 to 305	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$42.80
2221851	MEAN WELL	OWA-120U-24	24	5		90 to 264	4-pin DIN female	7.52	2.48	1.48	Yes	UL/CUL/FCC	\$52.30
2174186	MEAN WELL	HVG-150-24A	24	6.25		180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/FCC/EN/EAC	\$70.30
2249432	MEAN WELL	ELG-150-24B	24	6.25		100 to 305	Stripped and Tinned	8.62	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
2174274	MEAN WELL	HVG-150-24B	24	6.25		180 to 528	Stripped and Tinned	9.6	2.7	1.5	Yes	UL/CUL/FCC/EN/EAC	\$72.20
2137625	MEAN WELL	HLG-150H-24A	24	6.3	22 to 27	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.95
2147971	MEAN WELL	HLG-150H-24	24	6.3		90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.95
2147989	MEAN WELL	HLG-150H-24B	24	6.3		90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$47.95
2215275	MEAN WELL	LPV-150-24	24	6.3		180 to 305	Stripped and Tinned	7.52	2.48	1.48	No	UL/CUL/CE/EN/EAC	\$33.30
2260543	MEAN WELL	LPVL-150-24	24	6.3		90 to 132	Stripped and Tinned	7.52	2.48	1.46	No	UL/CUL/CE/FCC/EN/EAC	\$33.30
2136737	MEAN WELL	HLG-185H-24B	24	7.8	22 to 27	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$50.50
2136702	MEAN WELL	HLG-185H-24A	24	7.8	22 to 27	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$49.20
2251962	MEAN WELL	ELG-200-24	24	8.4		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70
2252025	MEAN WELL	ELG-200-24A	24	8.4		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$43.70

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2248245	MEAN WELL	HVG-240-24A	24	10	12 to 24	180 to 528	Stripped and Tinned	10.01	2.68	1.53	Yes	UL/CUL/FCC/EN/EAC	\$79.80
2102174	MEAN WELL	HLG-240H-24A	24	10	22.4 to 25.6	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
2115127	MEAN WELL	HLG-240H-24B	24	10	22.4 to 25.6	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$62.70
2115039	MEAN WELL	HLG-240H-24	24	10	22.4 to 25.6	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
2252551	MEAN WELL	ELG-240-24A	24	10		100 to 305	Stripped and Tinned	9.6	2.8	1.48	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$45.60
2248309	MEAN WELL	HVG-240-24B	24	10		180 to 528	Stripped and Tinned	10.01	2.68	1.53	Yes	UL/CUL/FCC/EN/EAC	\$81.70
2141819	MEAN WELL	HLG-320H-24A	24	13.3	21 to 26	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70
2147903	MEAN WELL	HLG-320H-24	24	13.34	21 to 26	90 to 305	Stripped and Tinned	8.66	2.67	1.52	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$81.70
2141907	MEAN WELL	HLG-320H-24B	24	13.34	21 to 26	90 to 305	Stripped and Tinned	9.92	3.54	1.72	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$84.60
2248018	MEAN WELL	HVG-320-24B	24	13.4		180 to 528	Stripped and Tinned	7.52	2.48	1.48	Yes	UL/CUL/FCC/EN/EAC	\$110.00
2255859	MEAN WELL	HVG-480-24A	24	20	20.4 to 25.2	180 to 528	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/FCC/EN/EAC	\$154.00
2256093	MEAN WELL	HLG-480H-24A	24	20		90 to 305	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$124.00
2255912	MEAN WELL	HVG-480-24B	24	20		180 to 528	Stripped and Tinned	10.31	4.92	1.72	Yes	UL/CUL/FCC/EN/EAC	\$158.00
2218388	MEAN WELL	HLG-600H-24B	24	25		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$182.00
2218370	MEAN WELL	HLG-600H-24A	24	25		90 to 305	Stripped and Tinned	11.02	5.67	1.91	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$179.00
2100574	MEAN WELL	PLN-60-27	27	2.3	25 to 30	90 to 295	Stripped and Tinned	7.12	2.42	1.37	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$33.30
2140699	MEAN WELL	LPF-60-30	30	2		90 to 305	Stripped and Tinned	6.39	1.69	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$26.80

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2140787	MEAN WELL	LPF-60D-30	30	2		90 to 305	Stripped and Tinned	6.39	1.71	1.25	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$28.70
2140947	MEAN WELL	LPF-90D-30	30	3		90 to 305	Stripped and Tinned	6.33	2.4	1.41	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$40.10
2142811	MEAN WELL	HLG-100H-30	30	3.2		90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$43.90
2121826	MEAN WELL	CEN-100-30	30	3.2		90 to 295	Stripped and Tinned	7.2	2.46	1.59	Yes	CUL/TUV/CB/CE/EN/EAC/CCC	\$42.95
2137553	MEAN WELL	HLG-120H-30A	30	4	27 to 33	90 to 305	Stripped and Tinned	8.66	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.20
2137633	MEAN WELL	HLG-150H-30A	30	5	27 to 33	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC	\$45.80
2141659	MEAN WELL	HLG-185H-30B	30	6.2	27 to 33	90 to 305	Stripped and Tinned	8.98	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$50.50
2102297	MEAN WELL	HLG-240H-30A	30	8	28 to 32	90 to 305	Stripped and Tinned	9.61	2.68	1.53	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$61.00
2141085	MEAN WELL	PCD-25-700A		0.7	24 to 36	90 to 135	Stripped and Tinned	3.3	2.24	1.16	Yes	UL/FCC/EN/EAC	\$16.00
2253458	MEAN WELL	IDLC-45-1050		1.05	26 to 43	90 to 295	Terminal Block	4.72	2.95	0.98	Yes	UL/CUL/CB/CE/EN/EAC/CCC	\$18.10
2164025	MEAN WELL	APC-35-350		0.35	28 to 100	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	CE/EN/EAC	\$11.80
2140998	MEAN WELL	PCD-16-350A		0.35	24 to 48	90 to 135	Stripped and Tinned	3.3	2.24	1.16	Yes	UL/FCC/EN/EAC	\$14.80
2221499	MEAN WELL	HBG-60-1400		1.4	28 to 43	90 to 295	Stripped and Tinned		3.86	2.26	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$21.50
2164033	MEAN WELL	APC-35-500		0.5	25 to 70	90 to 264	Stripped and Tinned	8.66	2.67	1.52	No	CE/EN/EAC	\$11.80
2294263	MEAN WELL	XLG-200-24-A		8.3		100 to 305	Stripped and Tinned	7.83	2.48	1.4	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$37.10
2204824	MEAN WELL	PLM-25-500		0.5	30 to 50	110 to 295	Screw Terminal	5.7	1.49	0.86	Yes	UL/CUL/CB/CE/EN/ENEC/EAC	\$12.50
2193002	MEAN WELL	PCD-60-1050B		1.05	34 to 57	180 to 295	Stripped and Tinned	5.04	2.36	1.24	Yes	CB/CE/EN/ENEC/EAC	\$22.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2193011	MEAN WELL	PCD-60-1400B		1.4	25 to 43	180 to 295	Stripped and Tinned	5.04	2.36	1.24	Yes	CB/CE/EN/ENEC/EAC	\$22.00
2255605	MEAN WELL	IDLC-25-700		0.7	25.2 to 36	90 to 295	Terminal Block	4.33	2.95	0.87	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$15.80
2255648	MEAN WELL	IDLC-25A-700		0.7	12, 25.2 to 36	90 to 295	Terminal Block	4.33	2.95	0.87	Yes	UL/CUL/CB/CE/EN/ENEC/EAC/CCC	\$16.30
2222352	MEAN WELL	PLM-25E-500		0.5	30 to 50	180 to 295	Screw Terminal	5.7	1.49	0.86	Yes	CB/CE/EN/ENEC/EAC/CCC	\$10.60