



[Click Here to Request a Large Quantity Quote](#)

[36 to 45.6 Volt LED Switching Power Supplies](#)

| Jameco Part #           | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Additional Output Voltages (VDC) | Input Voltage (VAC) | Output Connector Type | Length (inch) | Width (inch) | Height (inch) | PFC Function | Agency Approvals                 | Price 1 |
|-------------------------|--------------|---------------------|------------------------------|--------------------|----------------------------------|---------------------|-----------------------|---------------|--------------|---------------|--------------|----------------------------------|---------|
| <a href="#">2165790</a> | MEAN WELL    | LPF-25-36           | 36                           | 0.7                |                                  | 90 to 305           | Stripped and Tinned   | 5.8           | 1.6          | 1.3           | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$21.30 |
| <a href="#">2103151</a> | MEAN WELL    | LPV-35-36           | 36                           | 1                  |                                  | 90 to 264           | Stripped and Tinned   | 5.82          | 1.57         | 1.18          | No           | UL/CUL/CE/EN/EAC                 | \$13.30 |
| <a href="#">2140613</a> | MEAN WELL    | LPF-40D-36          | 36                           | 1.12               |                                  | 90 to 305           | Stripped and Tinned   | 6.39          | 1.69         | 1.25          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$26.60 |
| <a href="#">2140525</a> | MEAN WELL    | LPF-40-36           | 36                           | 1.12               |                                  | 90 to 305           | Stripped and Tinned   | 6.39          | 1.69         | 1.25          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$24.70 |
| <a href="#">2220939</a> | MEAN WELL    | PWM-40-36           | 36                           | 1.12               |                                  | 90 to 305           | Stripped and Tinned   | 5.91          | 2.09         | 1.38          | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$25.80 |
| <a href="#">2140701</a> | MEAN WELL    | LPF-60-36           | 36                           | 1.67               |                                  | 90 to 305           | Stripped and Tinned   | 6.39          | 1.69         | 1.25          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$26.80 |
| <a href="#">2221966</a> | MEAN WELL    | OWA-60U-36          | 36                           | 1.67               |                                  | 90 to 264           | Female Barrel Plug    | 5.12          | 2.09         | 1.38          | No           | CUL/FCC                          | \$27.70 |
| <a href="#">2148367</a> | MEAN WELL    | HLG-60H-36B         | 36                           | 1.7                |                                  | 90 to 305           | Stripped and Tinned   | 6.73          | 2.42         | 1.45          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$31.50 |
| <a href="#">2148359</a> | MEAN WELL    | HLG-60H-36A         | 36                           | 1.7                |                                  | 90 to 305           | Stripped and Tinned   | 6.73          | 2.42         | 1.45          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$30.80 |
| <a href="#">2121922</a> | MEAN WELL    | CEN-60-36           | 36                           | 1.7                |                                  | 90 to 295           | Stripped and Tinned   | 7.2           | 2.46         | 1.59          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$0.00  |
| <a href="#">2142221</a> | MEAN WELL    | HLG-80H-36A         | 36                           | 2.3                |                                  | 90 to 305           | Stripped and Tinned   | 7.7           | 2.42         | 1.53          | Yes          | CUL/TUV/CB/CE/EN/EAC/CCC         | \$36.10 |
| <a href="#">2214969</a> | MEAN WELL    | NPF-90D-36          | 36                           | 2.5                |                                  | 90 to 305           | Stripped and Tinned   | 6.73          | 2.48         | 1.48          | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$39.00 |
| <a href="#">2142686</a> | MEAN WELL    | HLG-100H-36A        | 36                           | 2.65               |                                  | 90 to 305           | Stripped and Tinned   | 8.66          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$43.90 |
| <a href="#">2196246</a> | MEAN WELL    | HBG-100-36B         | 36                           | 2.7                |                                  | 90 to 305           | Stripped and Tinned   | 4.45          | 2.56         | 1.53          | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$41.00 |

| Jameco Part #           | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Additional Output Voltages (VDC) | Input Voltage (VAC) | Output Connector Type | Length (inch) | Width (inch) | Height (inch) | PFC Function | Agency Approvals                 | Price 1  |
|-------------------------|--------------|---------------------|------------------------------|--------------------|----------------------------------|---------------------|-----------------------|---------------|--------------|---------------|--------------|----------------------------------|----------|
| <a href="#">2196203</a> | MEAN WELL    | HBG-100-36A         | 36                           | 2.7                |                                  | 90 to 305           | Stripped and Tinned   | 4.45          | 2.56         | 1.53          | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$41.00  |
| <a href="#">2141229</a> | MEAN WELL    | LPV-100-36          | 36                           | 2.8                |                                  | 90 to 264           | Stripped and Tinned   | 7.48          | 2.04         | 1.45          | No           | UL/CUL/CE/EN/EAC                 | \$24.30  |
| <a href="#">2137561</a> | MEAN WELL    | HLG-120H-36A        | 36                           | 3.4                | 33 to 40                         | 90 to 305           | Stripped and Tinned   | 8.66          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$45.20  |
| <a href="#">2174207</a> | MEAN WELL    | HVG-150-36A         | 36                           | 4.17               |                                  | 180 to 528          | Stripped and Tinned   | 9.6           | 2.7          | 1.5           | Yes          | UL/CUL/FCC/EN/EAC                | \$70.30  |
| <a href="#">2137641</a> | MEAN WELL    | HLG-150H-36A        | 36                           | 4.2                | 33 to 40                         | 90 to 305           | Stripped and Tinned   | 8.98          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$45.80  |
| <a href="#">2148025</a> | MEAN WELL    | HLG-150H-36B        | 36                           | 4.2                |                                  | 90 to 305           | Stripped and Tinned   | 8.98          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$47.10  |
| <a href="#">2141667</a> | MEAN WELL    | HLG-185H-36B        | 36                           | 5.2                | 33 to 40                         | 90 to 305           | Stripped and Tinned   | 8.98          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$50.50  |
| <a href="#">2248261</a> | MEAN WELL    | HVG-240-36A         | 36                           | 6.7                | 18 to 36                         | 180 to 528          | Stripped and Tinned   | 10.01         | 2.68         | 1.53          | Yes          | UL/CUL/FCC/EN/EAC                | \$79.80  |
| <a href="#">2141835</a> | MEAN WELL    | HLG-320H-36A        | 36                           | 8.9                | 32 to 39                         | 90 to 305           | Stripped and Tinned   | 9.92          | 3.54         | 1.72          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$81.70  |
| <a href="#">2255875</a> | MEAN WELL    | HVG-480-36A         | 36                           | 13.3               | 30.6 to 37.8                     | 180 to 528          | Stripped and Tinned   | 10.31         | 4.92         | 1.72          | Yes          | UL/CUL/FCC/EN/EAC                | \$154.00 |
| <a href="#">2255939</a> | MEAN WELL    | HVG-480-36B         | 36                           | 13.3               |                                  | 180 to 528          | Stripped and Tinned   | 10.31         | 4.92         | 1.72          | Yes          | UL/CUL/FCC/EN/EAC                | \$158.00 |
| <a href="#">2165714</a> | MEAN WELL    | LPF-16D-42          | 42                           | 0.39               |                                  | 90 to 305           | Stripped and Tinned   | 5.8           | 1.6          | 1.3           | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$20.90  |
| <a href="#">2165802</a> | MEAN WELL    | LPF-25-42           | 42                           | 0.6                |                                  | 90 to 305           | Stripped and Tinned   | 5.8           | 1.6          | 1.3           | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$21.30  |
| <a href="#">2165896</a> | MEAN WELL    | LPF-25D-42          | 42                           | 0.6                |                                  | 90 to 305           | Stripped and Tinned   | 5.8           | 1.6          | 1.3           | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$23.20  |
| <a href="#">2140621</a> | MEAN WELL    | LPF-40D-42          | 42                           | 0.96               |                                  | 90 to 305           | Stripped and Tinned   | 6.39          | 1.69         | 1.25          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$26.60  |
| <a href="#">2140808</a> | MEAN WELL    | LPF-60D-42          | 42                           | 1.43               |                                  | 90 to 305           | Stripped and Tinned   | 6.39          | 1.71         | 1.25          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$28.70  |
| <a href="#">2221974</a> | MEAN WELL    | OWA-60U-42          | 42                           | 1.5                |                                  | 90 to 264           | Female Barrel Plug    | 5.12          | 2.09         | 1.38          | No           | UL/FCC                           | \$27.70  |

| Jameco Part #           | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Additional Output Voltages (VDC) | Input Voltage (VAC) | Output Connector Type | Length (inch) | Width (inch) | Height (inch) | PFC Function | Agency Approvals                 | Price 1  |
|-------------------------|--------------|---------------------|------------------------------|--------------------|----------------------------------|---------------------|-----------------------|---------------|--------------|---------------|--------------|----------------------------------|----------|
| <a href="#">2142230</a> | MEAN WELL    | HLG-80H-42A         | 42                           | 1.95               |                                  | 90 to 305           | Stripped and Tinned   | 7.7           | 2.42         | 1.53          | Yes          | CUL/TUV/CB/CE/EN/EAC/CCC         | \$36.10  |
| <a href="#">2142328</a> | MEAN WELL    | HLG-80H-42B         | 42                           | 1.95               |                                  | 90 to 305           | Stripped and Tinned   | 7.7           | 2.42         | 1.53          | Yes          | CUL/TUV/CB/CE/EN/EAC/CCC         | \$37.20  |
| <a href="#">2142766</a> | MEAN WELL    | HLG-100H-42B        | 42                           | 2.28               |                                  | 90 to 305           | Stripped and Tinned   | 8.66          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$45.00  |
| <a href="#">2148210</a> | MEAN WELL    | HLG-120H-42B        | 42                           | 2.9                | 38 to 46                         | 90 to 305           | Stripped and Tinned   | 8.66          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$46.60  |
| <a href="#">2137570</a> | MEAN WELL    | HLG-120H-42A        | 42                           | 2.9                | 38 to 46                         | 90 to 305           | Stripped and Tinned   | 8.66          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$45.20  |
| <a href="#">2249395</a> | MEAN WELL    | ELG-150-42A         | 42                           | 3.57               |                                  | 100 to 305          | Stripped and Tinned   | 8.62          | 2.48         | 1.4           | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC     | \$35.20  |
| <a href="#">2137650</a> | MEAN WELL    | HLG-150H-42A        | 42                           | 3.6                | 38 to 46                         | 90 to 305           | Stripped and Tinned   | 8.98          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$45.80  |
| <a href="#">2148041</a> | MEAN WELL    | HLG-150H-42B        | 42                           | 3.6                |                                  | 90 to 305           | Stripped and Tinned   | 8.98          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$47.10  |
| <a href="#">2101737</a> | MEAN WELL    | HLG-240H-42A        | 42                           | 5.72               | 39 to 45                         | 90 to 305           | Stripped and Tinned   | 9.61          | 2.68         | 1.53          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$61.00  |
| <a href="#">2247980</a> | MEAN WELL    | HVG-320-42A         | 42                           | 7.6                | 21 to 42                         | 180 to 528          | Stripped and Tinned   | 7.52          | 2.48         | 1.48          | Yes          | UL/CUL/FCC/EN/EAC                | \$106.00 |
| <a href="#">2141931</a> | MEAN WELL    | HLG-320H-42B        | 42                           | 7.65               | 38 to 45                         | 90 to 305           | Stripped and Tinned   | 9.92          | 3.54         | 1.72          | Yes          | UL/CUL/TUV/CB/CE/EN/EAC/CCC      | \$84.60  |
| <a href="#">2140980</a> | MEAN WELL    | LPF-90D-54          | 54                           | 1.67               |                                  | 90 to 305           | Stripped and Tinned   | 6.33          | 2.4          | 1.41          | Yes          | UL/CUL/TUV/CB/CE/EN/ENEC/EAC/CCC | \$40.10  |
| <a href="#">2234425</a> | EPtronics    | LG75W-108-C0700-RD  | 108                          | 0.7                | 36 to 108                        | 120 to 277          | Stripped and Tinned   | 9.4           | 1.8          | 1.3           |              | UL/CUL/FCC/CE                    | \$11.95  |
| <a href="#">2141077</a> | MEAN WELL    | PCD-25-350A         |                              | 0.35               | 40 to 58                         | 90 to 135           | Stripped and Tinned   | 3.3           | 2.24         | 1.16          | Yes          | UL/FCC/EN/EAC                    | \$16.00  |
| <a href="#">2253491</a> | MEAN WELL    | IDLC-45A-700        |                              | 0.7                | 38 to 64                         | 90 to 295           | Terminal Block        | 4.72          | 2.95         | 0.98          | Yes          | UL/CUL/CB/CE/EN/EAC/CCC          | \$19.00  |
| <a href="#">2141157</a> | MEAN WELL    | PLD-25-350          |                              | 0.35               | 40 to 58                         | 90 to 295           | Stripped and Tinned   | 3.3           | 2.24         | 1.16          | Yes          | UL/CB/CE/FCC/EN/ENEC/EAC         | \$15.60  |
| <a href="#">2221587</a> | MEAN WELL    | LPC-100-1400        |                              | 1.4                | 36 to 72                         | 90 to 264           | Stripped and Tinned   | 7.48          | 2.05         | 1.46          | No           | EN/EAC/CE                        | \$24.30  |

| Jameco Part #           | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Additional Output Voltages (VDC) | Input Voltage (VAC) | Output Connector Type | Length (inch) | Width (inch) | Height (inch) | PFC Function | Agency Approvals             | Price 1 |
|-------------------------|--------------|---------------------|------------------------------|--------------------|----------------------------------|---------------------|-----------------------|---------------|--------------|---------------|--------------|------------------------------|---------|
| <a href="#">2174426</a> | MEAN WELL    | HVGC-150-350A       |                              | 0.35               | 42 to 428                        | 180 to 528          | Stripped and Tinned   | 9.6           | 2.7          | 1.5           | Yes          | UL/CUL/TUV/CB/CE/FCC/EN/EAC  | \$70.30 |
| <a href="#">2259593</a> | MEAN WELL    | ELG-150-C1750       |                              | 1.75               |                                  | 100 to 305          | Stripped and Tinned   | 8.62          | 2.48         | 1.41          | Yes          | UL/CUL/CB/CE/EN/ENEC/EAC/CCC | \$35.20 |