



[Click Here to Request a Large Quantity Quote](#)

[Rectangular Connectors-Shunts & Shorting Blocks](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Contacts	Number of Rows	Product Type	Current Rating	Maximum Contact Resistance	Contact Plating	Contact Material	Housing Material	Color	Pitch	Price 1
152671	Jameco Valuepro	2012JH-R	2	1	Top Closed	1 A	30 mOhm	Gold	Brass	Polyamide66	Black Tab	0.100 in., 2.54 mm	\$0.13
19141	Jameco Valuepro	7600A-R	2	1	Top Closed	3 A	20 mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Black	0.100 in., 2.54 mm	\$0.13
112442	Jameco Valuepro	GJWCL-B-R	2	1	Top Closed	3 A	20 mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Blue	0.100 in., 2.54 mm	\$0.15
112432	Jameco Valuepro	2012J-CR	2	1	Top Closed	3 A	20 mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Red	0.100 in., 2.54 mm	\$0.15
112425	Jameco Valuepro	JOPENB-R	2	1	Top Open	3 A	20 mOhm	Gold	Phosphor Bronze	Polybutylene Terephthalate	Blue	0.100 in., 2.54 mm	\$0.15
112417	Jameco Valuepro	2012J-OR-R	2	1	Top Open	3 A	20 mOhm	Gold	Phosphor Bronze	Polybutylene Terephthalate	Red	0.100 in., 2.54 mm	\$0.15
22024	Jameco Valuepro	7600-B-R	2	1	Top Open	3 A	20 mOhm	Gold Over Nickel	Phosphor Bronze	Polybutylene Terephthalate	Black	0.100 in., 2.54 mm	\$0.15
2314167	TE Connectivity	881545-1	2	1	Top Open	3A	n/a	Gold		Thermoplastic	Black	0.100 in., 2.54 mm	\$0.14