



[Click Here to Request a Large Quantity Quote](#)

[Medical Enclosed Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Length (inch)	Width (inch)	Height (inch)	PFC Function	Agency Approvals	Price 1
2251090	MEAN WELL	MPM-20-12	12	1.8	80 to 264	47 to 440	PCB Pin	2.06	1.07	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
2172244	MEAN WELL	MSP-100-12	12	8.5	85 to 264	47 to 63	Screw Terminal Block	6.3	3.8	1.5	Yes	UL/CUL/CB/CE/EN/EAC	\$48.50
2166039	MEAN WELL	MSP-300-12	12	27	85 to 264	47 to 440	Screw Terminal Block	7.8	4.1	1.6	Yes	UL/CUL/CB/CE/EN/EAC	\$110.00
2251111	MEAN WELL	MPM-20-24	24	0.9	80 to 264	47 to 440	PCB Pin	2.06	1.07	0.94	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.30
2172341	MEAN WELL	MSP-200-24	24	8.4	85 to 264	47 to 63	Screw Terminal Block	7.8	3.9	1.5	Yes	UL/CUL/CB/CE/EN/EAC	\$80.00
2279599	MEAN WELL	MSP-1000-24	24	42	90 to 264	47 to 63	Screw Terminal Block	8.58	4.13	2.5	Yes	UL/CUL/CB/CE/EN/EAC	\$209.00
2166063	MEAN WELL	MSP-300-36	36	9	85 to 264	47 to 440	Screw Terminal Block	7.8	4.1	1.6	Yes	UL/CUL/CB/CE/EN/EAC	\$110.00
2166071	MEAN WELL	MSP-300-48	48	7	85 to 264	47 to 440	Screw Terminal Block	7.8	4.1	1.6	Yes	UL/CUL/CB/CE/EN/EAC	\$110.00
2279607	MEAN WELL	MSP-1000-48	48	21	90 to 264	47 to 63	Screw Terminal Block	8.58	4.13	2.5	Yes	UL/CUL/CB/CE/EN/EAC	\$209.00