



[Click Here to Request a Large Quantity Quote](#)

[Medical Wall Adapter Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	Input Connector	Price 1
2283567	MEAN WELL	GSM12U12-P1J	12	1	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.45 x 1.08 x 1.8	UL/CUL/FCC/EAC	NEMA1-15P	\$12.90
2225465	MEAN WELL	GSM18U12-P1J	12	1.5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	3.11 x 2.13 x 1.3	UL/CUL//TUV/CB/FCC/EAC	NEMA1-15P	\$10.95
2271047	MEAN WELL	GSM25U12-E13-MOD-2.1	12	2.08	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	3.11 x 2.13 x 1.31	UL/CUL//TUV/CB/FCC/EAC	NEMA1-15P	\$6.49
2271055	MEAN WELL	GSM36U12-E13-MOD-2.1	12	3	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	3.11 x 2.13 x 1.3	UL/CUL//TUV/CB/FCC/EAC	NEMA1-15P	\$6.95
2283087	MEAN WELL	GSM60U12-P1J	12	4.5	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.26 x 1.87	UL/CB/FCC	NEMA1-15P	\$26.60
2196369	MEAN WELL	GSM06U15-P1J	15	0.4	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	1.3 x 2.6 x 1.7	UL/CUL/FCC/EAC	NEMA1-15P	\$9.95
2283591	MEAN WELL	GSM12U24-P1J	24	0.5	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.45 x 1.08 x 1.8	UL/CUL/FCC/EAC	NEMA1-15P	\$12.90