



[Click Here to Request a Large Quantity Quote](#)

[Interchangeable Plug Wall Adapters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	AC Power Cord	Price 1
2202829	Phihong	PSA08R-050-1.3	5	1	100 to 240	47 to 63	Cylindrical Female	1.3mm x 3.5mm	Center Positive	2.8 x 1.8 x 1.0	UL/CUL/CE		\$4.49
2270967	Globtek	GTM41076-0605	5	1.2	100 to 240	50 to 60	USB micro-B	N/A	N/A	2.9 x 1.7 x 1.4	UL/CUL		\$7.95
2197812	Cincon Electronics Company	TR10R050	5	1.6	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm right angle	Center Positive	3.1 x 2.3 x 1.6	UL/CUL/TUV/FCC/EN		\$3.25
2226353	MEAN WELL	GEM18I05-P1J	5	3	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.54 x 2.21	UL/CUL/TUV/CB/CE/FCC/EN/EAC		\$14.10
2230045	Phihong	PSC12R-090	9	1.11	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.7 x 1.7 x 1.1	UL/CUL/CE		\$9.95
2202896	Phihong	PSA21R-090	9	1.67	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.9 x 2.3 x 1.2	UL/CUL/TUV/CE		\$7.95
2226361	MEAN WELL	GEM18I09-P1J	9	2	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.54 x 2.21	UL/CUL/TUV/CB/CE/FCC/EN/EAC		\$14.10
2082311	MEAN WELL	GE18I09-P1J	9	2	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$14.10
2295255	Jameco Reliapro	DCT12W120100ZZ-00	12	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	1.36 x 1.75 x 2.22	UL/CUL/CE/FCC/CEC	AC Plug clips included	\$9.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	AC Power Cord	Price 1
2227831	Phihong	PLA12R-120	12	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.7 x 2 x 1.2	UL/CUL/CE		\$8.95
2253095	MEAN WELL	GEM12I12-P1J	12	1	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.91 x 1.54 x 1.91	UL/CUL/TUV/CE/FCC/EN/EAC		\$12.20
2102385	MEAN WELL	GE12I12-P1J	12	1	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.8 x 1.6 x 1.5	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$10.30
2258689	Phihong	PSAC12R-120-R	12	1	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.82 x 1.9 x 1.2	UL/CUL/TUV/CE		\$12.95
2154986	Arndt	FW75550/12	12	1.25	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.4 x 2 x 1.3	UL/CUL/CE/ENEC		\$9.95
2226370	MEAN WELL	GEM18I12-P1J	12	1.5	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.54 x 2.21	UL/CUL/TUV/CB/CE/FCC/EN/EAC		\$14.10
2101673	MEAN WELL	GE18I12-P1J	12	1.5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$14.10
2261061	Phihong	PSAA20R-120L6-R	12	1.67	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.82 x 2 x 1.2	UL/CUL/CE		\$18.95
228849	Phihong	PSA21R-120	12	1.67	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.9 x 2.5 x 1.4	UL/CUL/TUV/CE		\$8.95
2102094	MEAN WELL	GE24I12-P1J	12	2	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$14.60
2227532	Dee Van Enterprise Usa	DSA-24CA-12	12	2	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	3 x 1.9 x 1.6	CECV		\$10.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	AC Power Cord	Price 1
2246899	MEAN WELL	GE30I12-P1J	12	2.5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$16.00
2292919	Phihong	PSAA30R-120R	12	2.5	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.3 x 2.2 x 1.5	UL/CUL/CE		\$13.49
2299535	MEAN WELL	GE40I12-P1J	12	3.3	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.7 x 1.9 x 1.5	UL/CUL/TUV/CE/FCC/EN/EAC/CCC	AC Plug clips not included	\$19.00
2282959	MEAN WELL	GEM60I12-P1J	12	4.5	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.54 x 2.21	UL/CUL/TUV/CB/CE/FCC/EN/EAC		\$26.60
2226388	MEAN WELL	GEM18I15-P1J	15	1.2	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.54 x 2.21	UL/CUL/TUV/CB/CE/FCC/EN/EAC		\$14.10
2082345	MEAN WELL	GE12I24-P1J	24	0.63	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	2.8 x 1.5 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$10.30
2226409	MEAN WELL	GEM18I24-P1J	24	0.75	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.54 x 2.21	UL/CUL/TUV/CB/CE/FCC/EN/EAC		\$14.10
2102086	MEAN WELL	GE18I24-P1J	24	0.75	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$14.10
2271159	Arndt	CPS024240100	24	1	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.55 x 2 x 1.4	UL/TUV/CE		\$9.95
2102115	MEAN WELL	GE24I24-P1J	24	1	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$14.60

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Size (L" x W" x H")	Agency Approvals	AC Power Cord	Price 1
2246928	MEAN WELL	GE30I24-P1J	24	1.25	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.2 x 1.7 x 1.6	UL/CUL/TUV/CE/FCC/EN/CCC	AC Plug clips not included, see p/n: 2082396	\$16.00
2299559	MEAN WELL	GE40I24-P1J	24	1.67	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	3.7 x 1.9 x 1.5	UL/CUL/TUV/CE/FCC/EN/EAC/CCC	AC Plug clips not included	\$19.00
2282983	MEAN WELL	GEM60I24-P1J	24	2.5	80 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center positive	2.97 x 1.54 x 2.21	UL/CUL/TUV/CB/CE/FCC/EN/EAC		\$26.60