



[Click Here to Request a Large Quantity Quote](#)

[Open-Frame Switching AC-to-DC Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Size (L" x W" x H")	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
2265983	MEAN WELL	MFM-05-5	1	5	1		80 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.2	\$7.40
2105586	MEAN WELL	PS-05-5	1	5	1.2		85 to 264	47 to 63	3 x 1.6 x 0.8	No	CB/CE/EN/EAC	0.15	\$5.70
695092	MEAN WELL	NFM-10-5	1	5	2		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.25	\$8.95
2266023	MEAN WELL	MFM-10-5	1	5	2		80 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.3	\$8.70
695130	MEAN WELL	NFM-15-5	1	5	3		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.35	\$10.49
2174071	MEAN WELL	EPS-15-5	1	5	3.3	4.75 to 5.5	85 to 264	47 to 63	2.5 x 1.8 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.4	\$7.20
695199	MEAN WELL	NFM-20-5	1	5	4.4		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.6	\$12.95
2164316	MEAN WELL	EPS-25-5	1	5	5.5	4.75 to 5.5	85 to 264	47 to 63	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	0.6	\$11.20
2164404	MEAN WELL	EPS-35-5	1	5	6.6	4.75 to 5.5	85 to 264	47 to 63	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	0.75	\$11.60
2164498	MEAN WELL	EPS-45-5	1	5	9	4.75 to 5.5	90 to 264	47 to 63	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$12.40
2164501	MEAN WELL	EPS-45-7.5	1	7.5	6	7.13 to 8.25	90 to 264	47 to 63	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$12.40
2188772	Umec USA	UP0401S-09	1	9	4.4		90 to 264	47 to 63	3.58 x 2.48 x 1.13	No	UL/CSA/TUV/CB/CE		\$4.95
2099981	Arndt	SBU60-105	1	11	4.84	12 , 13	90 to 264	47 to 63	5 x 3 x 1.1	No	UL/CUL/CE	5.25	\$7.95
2265991	MEAN WELL	MFM-05-12	1	12	0.42		80 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.2	\$7.40
694989	MEAN WELL	NFM-05-12	1	12	0.42		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.12	\$7.95
2105543	MEAN WELL	PS-05-12	1	12	0.5		85 to 264	47 to 63	3 x 1.6 x 0.8	No	CB/CE/EN/EAC	0.15	\$5.70

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Size (L" x W" x H")	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
695105	MEAN WELL	NFM-10-12	1	12	0.85		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.25	\$8.99
2174098	MEAN WELL	EPS-15-12	1	12	1.38	10.8 to 13.5	85 to 264	47 to 63	2.5 x 1.8 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.4	\$7.20
695201	MEAN WELL	NFM-20-12	1	12	1.8		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.6	\$12.95
2164332	MEAN WELL	EPS-25-12	1	12	2.34	10.8 to 13.5	85 to 264	47 to 63	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	0.6	\$11.20
2266175	MEAN WELL	MFM-30-12	1	12	2.5		80 to 264	47 to 63			UL/CUL/TUV/CB/CE/EN/EAC	0.75	\$15.60
2164421	MEAN WELL	EPS-35-12	1	12	3.3	10.8 to 13.5	85 to 264	47 to 63	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	0.75	\$11.60
2164519	MEAN WELL	EPS-45-12	1	12	4.2	10.8 to 13.5	90 to 264	47 to 63	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$12.40
2205413	Astrodyne	ASM60-1380	1	12	5		100 to 240	50 to 60			UL/CUL/CB/CE	1.5	\$4.95
2164674	MEAN WELL	EPS-65-12	1	12	6	10.8 to 13.5	90 to 264	47 to 63	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$13.10
173472	MEAN WELL	LPS-100-12	1	12	8.4		88 to 132, 176 to 264	47 to 63	8.7 x 2.4 x 1.3	No	UL/CUL/TUV/CB/CE/EN/EAC	2.3	\$27.60
2239429	MEAN WELL	EPS-120-12	1	12	10		80 to 264	47 to 63	4 x 2 x 1.14	No	UL/CUL/TUV/CB/CE/EN/EAC	2.1	\$20.30
213681	MEAN WELL	LPP-150-12	1	12	12.5		85 to 264	47 to 63	8.7 x 3 x 1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	2.5	\$33.30
2172447	MEAN WELL	EPP-150-12	1	12	12.5		90 to 264	47 to 63	4 x 2 x 1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$39.00
668713	MEAN WELL	PPS-200-12	1	12	16.6	10.8 to 13.2	90 to 264	47 to 63	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN	2.2	\$61.95
2164252	MEAN WELL	EPP-300-12	1	12	25		90 to 264	47 to 63	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN/EAC	3.5	\$57.00
2210731	Phihong	PSA-25-115	1	15	1.6		100 to 240	47 to 63	4 x 3 x 1.3	No	UL/CUL/CSA/CE	0.8	\$3.49
2164682	MEAN WELL	EPS-65-15	1	15	4.8	13.5 to 16.5	90 to 264	47 to 63	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$13.10

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Size (L" x W" x H")	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
216751	MEAN WELL	PS-65-15	1	15	4.8		90 to 264	47 to 440	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN	1.2	\$15.95
221170	MEAN WELL	MPS-65-15	1	15	4.8		90 to 264	47 to 63			UL/CUL/TUV/CB/CE/EN	1.6	\$22.99
216670	MEAN WELL	LPP-100-15	1	15	6.7		85 to 264	47 to 63	8.7 x 2.4 x 1.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	1.7	\$31.20
2239728	MEAN WELL	EPS-120-15	1	15	8		80 to 264	47 to 63	4 x 2 x 1.14	No	UL/CUL/TUV/CB/CE/EN/EAC	2.1	\$20.30
375065	MEAN WELL	LPP-150-15	1	15	10		85 to 264	47 to 63	8.7 x 3 x 1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	2.5	\$33.30
694997	MEAN WELL	NFM-05-24	1	24	0.23		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.12	\$7.49
2266007	MEAN WELL	MFM-05-24	1	24	0.23		80 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.2	\$7.40
2105560	MEAN WELL	PS-05-24	1	24	0.25		85 to 264	47 to 63	3 x 1.6 x 0.8	No	CB/CE/EN/EAC	0.15	\$5.70
695228	MEAN WELL	NFM-20-24	1	24	0.92		85 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN/EAC	0.6	\$12.95
2164359	MEAN WELL	EPS-25-24	1	24	1.17	21.6 to 27	85 to 264	47 to 63	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	0.6	\$11.20
2164535	MEAN WELL	EPS-45-24	1	24	2.1	21.6 to 27	90 to 264	47 to 63	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$12.40
2164691	MEAN WELL	EPS-65-24	1	24	3	21.6 to 27	90 to 264	47 to 63	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$13.10
148647	MEAN WELL	PS-65-24	1	24	3		90 to 264	47 to 440	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN	1.2	\$15.95
1773591	Artesyn Embedded Power	LPS65	1	24	3.3		85 to 264	47 to 440	5 x 3 x 1.7	No	CB/CE/CSA/EN/IEC/LVD/NEMKO/UL/VDE	1.5	\$111.09
244727	MEAN WELL	LPS-75-24	1	24	3.5	22 to 27	90 to 264	47 to 63	8.7 x 2.2 x 1.2	No	UL/CUL/TUV/CB/CE/EN/EAC	1.9	\$17.50
173463	MEAN WELL	LPS-100-24	1	24	4.2		88 to 132, 176 to 264	47 to 63	8.7 x 2.4 x 1.3	No	UL/CUL/TUV/CB/CE/EN/EAC	2.3	\$27.60
2172463	MEAN WELL	EPP-150-24	1	24	6.25		90 to 264	47 to 63	4 x 2 x 1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$39.00

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Size (L" x W" x H")	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
213672	MEAN WELL	LPP-150-24	1	24	6.3		85 to 264	47 to 63	8.7 x 3 x 1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	2.5	\$33.30
668730	MEAN WELL	PPS-200-24	1	24	8.3	21.6 to 26.4	90 to 264	47 to 63	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN	2.2	\$61.95
2164279	MEAN WELL	EPP-300-24	1	24	12.5		90 to 264	47 to 63	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN/EAC	3.7	\$57.00
2174143	MEAN WELL	EPS-15-48	1	48	0.344	43.2 to 52.8	85 to 264	47 to 63	2.5 x 1.8 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.4	\$7.20
2106378	MEAN WELL	RPS-60-48	1	48	1.375		90 to 264	47 to 63			UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$9.95
2172480	MEAN WELL	EPP-150-48	1	48	3.125		90 to 264	47 to 63	4 x 2 x 1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC	1.8	\$39.00
668756	MEAN WELL	USP-350-48	1	48	7.3	43.2 to 52.8	90 to 264	47 to 63	9.3 x 4 x 1.5	Yes	UL/CUL/TUV/CB/CE/EN/EAC	4	\$92.95
2197741	Skynet	SNP-N563	2	3.3	6	5	85 to 264	47 to 63	5 x 3 x 1.38	No	UL/CUL/TUV/VDE		\$5.95
212338	MEAN WELL	PD-25A	2	5	2.1	12	85 to 264	47 to 63	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	0.65	\$11.95
212312	MEAN WELL	PD-2505	2	5	2.5	-5	85 to 264	47 to 63	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CE/EN	0.65	\$10.95
194862	MEAN WELL	PD-45A	2	5	3.2	12	90 to 264	47 to 440	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1	\$12.49
194871	MEAN WELL	PD-45B	2	5	3.2	24	90 to 264	47 to 440	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1	\$12.75
194897	MEAN WELL	PD-65B	2	5	3.5	24	90 to 264	47 to 440	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.5	\$15.49
2106247	MEAN WELL	RPD-60B	2	5	3.85	24	90 to 264	47 to 63			UL/CUL/TUV/CB/CE/EN/EAC	1.1	\$13.95
194889	MEAN WELL	PD-65A	2	5	5.5	12	90 to 264	47 to 440	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1.5	\$15.49
2104014	MEAN WELL	MPD-65B	2	5	6	24	90 to 264	47 to 440			UL/CUL/TUV/CB/CE/EN	1.6	\$23.95

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Size (L" x W" x H")	PFC Function	Agency Approvals	Maximum Input Current (A)	Price 1
148690	MEAN WELL	PD-2512	2	12	1	-12	85 to 264	47 to 63	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CE/EN	0.65	\$11.95
2100857	MEAN WELL	PD-2515	2	15	1	-15	85 to 264	47 to 63	4.2 x 2.4 x 1.1	No	UL/CUL/TUV/CE/EN	0.65	\$11.95
88402	MEAN WELL	PT-45B	3	5	3	12 , -12	90 to 264	47 to 440	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1	\$13.49
215707	MEAN WELL	PT-65D	3	5	4	12 , 24	90 to 264	47 to 440	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN/EAC	1.5	\$15.95
375030	MEAN WELL	PT-45C	3	5	5	15 , -15	90 to 264	47 to 440	5 x 3 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	1	\$13.49
216734	MEAN WELL	PT-65B	3	5	5.5	12 , -12	90 to 264	47 to 440	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN/EAC	1.5	\$13.95
216726	MEAN WELL	PT-65C	3	5	5.5	15 , -15	90 to 264	47 to 440	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN/EAC	1.5	\$15.95
2129676	Elpac Power Supplies	MSM40D	3	5.1		24, -12	85 to 264	47 to 63			UL/CUL/CS/CB/CE		\$4.25