



[Click Here to Request a Large Quantity Quote](#)

[Prototyping Systems-Proto Boards](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Plating	Centers (in.)	No. Of Holes	Size L x W (ins.)	Hole Diameter (ins.)	Thickness (in.)	No. of Mounting Holes x Dia. (in.)	Sides	Circuit Pattern	Price 1
105100	Jameco Valuepro	(PCB228)	Protoboard	Epoxy Glass	0.1	288	2.7 x 1.6	0.035	0.0625	2 x 0.115	Single	Pad Per Hole	\$3.95
105102	Jameco Valuepro	PCB-365-R	Protoboard	Epoxy Glass	0.1	365	3.5 x 1.5	0.038	0.0625	2 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$3.95
645677	Jameco Valuepro	PB-456	Protoboard	Epoxy Glass	0.1	555	3.5 x 2.5	0.036	0.0625	4 x 0.140	Double		\$7.95
2191445	Busboard Prototype Systems	PAD1	Protoboard	Epoxy Glass	0.1	589	3.2 x 2	0.037	0.0625	4 x 0.125	Double		\$3.75
105111	Jameco Valuepro	PCB-102-R	Protoboard	Epoxy Glass	0.1	637	3.4 x 2.4	0.038	0.0625	2 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$8.95
263215	Jameco Valuepro	PCB-858-R	Protoboard	Epoxy Glass	0.1	640	4.3 x 2.5	0.042	0.0625	4 x 0.120	Double	10 Hole Solder Pad and Bus	\$4.95
105129	Jameco Valuepro	2853PCB-R	Protoboard	Epoxy Glass	0.1	669	4.4 x 2	0.038	0.0625	4 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$6.59
263207	Jameco Valuepro	PCB-463-R	Protoboard	Epoxy Glass	0.1	674	4.1 x 2.4	0.032	0.0625	4 x 0.130	Double	Pad Per Hole	\$6.95
105137	Jameco Valuepro	PCB-1266-R	Protoboard	Epoxy Glass	0.1	1266	4.5 x 3.3	0.035	0.0625	4 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$4.95
262511	Jameco Valuepro	PB-1135	Protoboard	Epoxy Glass	0.1	1324	5 x 3.7	0.036	0.0625	4 x 0.140	Double		\$9.95
105153	Jameco Valuepro	2851PCB-R	Protoboard	Epoxy Glass	0.1	1450	5.5 x 3.1	0.035	0.0625	4 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$5.49
206579	Jameco Valuepro	PCB-578-R	Protoboard	Epoxy Glass	0.1	1684	4.3 x 4.6	0.042	0.0625	4 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$3.95
2127232	Busboard Prototype Systems	PR2H3U	Protoboard	Epoxy Glass	0.1	2356	6.3 x 3.9	0.037	0.0625	0	Single		\$8.95
2127241	Busboard Prototype Systems	PR3U	Protoboard	Epoxy Glass	0.1	2356	6.3 x 3.9	0.037	0.0625	2 x 0.100	Single		\$9.95

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Plating	Centers (in.)	No. Of Holes	Size L x W (ins.)	Hole Diameter (ins.)	Thickness (in.)	No. of Mounting Holes x Dia. (in.)	Sides	Circuit Pattern	Price 1
21435	Jameco Valuepro	JE401-R	Protoboard	Epoxy Glass	0.1	2360	6.5 x 4.5	0.042	0.0625	0	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$7.95
52943	Vector Electronics	#84P44WE	Protoboard	Epoxy Glass	0.1	2430	8.5 x 4.5	0.042	0.0625	0	Single		\$12.49
206587	Jameco Valuepro	PCB-586-R	Protoboard	Epoxy Glass	0.1	2550	6.8 x 4.3	0.042	0.0625	4 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$7.95
105180	Jameco Valuepro	PCB-135-R	Protoboard	Epoxy Glass	0.1	2829	6.5 x 5	0.035	0.0625	8 x 0.120	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$7.95
43140	Vector Electronics	64P44XXXP	Protoboard	Epoxy Glass	0.1	2860	6.5 x 4.5	0.042	0.0625	0	Single		\$8.59
206594	Jameco Valuepro	PCB-594	Protoboard	Epoxy Glass	0.1	3906	8 x 5.5	0.042	0.0625	4 x 0.140	Single	Power/Ground Perimeter Bus w/ Pad Per Hole	\$9.95
37612	Vector Electronics	169P44XXXP	Protoboard	Epoxy Glass	0.1	7524	17 x 4.5	0.042	0.0625	0	Single		\$16.95
37621	Vector Electronics	169P84WE	Protoboard	Epoxy Glass	0.1	14448	17 x 8.5	0.042	0.0625	0	Single		\$29.95
2213421	DFRobot	FIT0099	Protoboard	Phenolic	0.1	572	2.3 x 3.1	0.038	0.0625	4 x 0.140	Single		\$1.49
262537	Jameco Valuepro	PB-1931	Protoboard	Phenolic	0.1	2192	6 x 4.9	0.036	0.0625	4 x 0.140	Double		\$10.95
616673	GC Electronics	22-512	Protoboard	Phenolic	0.15	800	6.8 x 3.4	0.03	0.0625	0	Single		\$5.19
616649	GC Electronics	22-508	Protoboard	Phenolic	0.3	684	6 x 2	0.03	0.0625	4 x 0.120	Single		\$10.95
616518	GC Electronics	22-264	Protoboard Blank	Copper Plated	0	0	10 x 8	0	0.0625	0	Single		\$7.59
169325	Jameco Valuepro	CIC 21-222-R	Protoboard Blank	Copper Plated	0	0	12 x 2	0	0.0625	0	Double		\$15.95
169296	Jameco Valuepro	21-227-R	Protoboard Blank	Copper Plated	0	0	12 x 2	0	0.0625	0	Single		\$10.95
169279	Jameco Valuepro	21-225	Protoboard Blank	Copper Plated	0	0	3 x 6	0	0.0625	0	Single		\$3.59
169288	Jameco Valuepro	21-226-R	Protoboard Blank	Copper Plated	0	0	5.9 x 5.9	0	0.0625	0	Single		\$3.95
616489	GC Electronics	22-260	Protoboard Blank	Copper Plated	0	0	6 x 4	0	0.0625	0	Single		\$2.45
169317	Jameco Valuepro	21-221-R	Protoboard Blank	Copper Plated	0	0	6 x 6	0	0.0625	0	Double		\$5.95

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Plating	Centers (in.)	No. Of Holes	Size L x W (ins.)	Hole Diameter (ins.)	Thickness (in.)	No. of Mounting Holes x Dia. (in.)	Sides	Circuit Pattern	Price 1
616500	GC Electronics	22-263	Protoboard Blank	Copper Plated	0	0	9 x 6	0	0.0625	0	Single		\$3.95
616690	GC Electronics	22-516	Protoboard Perforated	Phenolic	0.1	2565	6 x 4.5	0.042	0.0625	0	Single		\$4.19
2125042	Busboard Prototype Systems	SB300	Solderable Breadboard	Copper Plated	0.1	300	3 x 1.2	0.042	0.0625	0	Single		\$3.95
2191402	Busboard Prototype Systems	SB404	Solderable Breadboard	Epoxy Glass	0.1	628	3.8 x 1.9	0.042	0.0625	4 x 0.125	Single		\$4.95
2125034	Busboard Prototype Systems	BR1	Solderable Breadboard	Epoxy Glass	0.1	1226	7.1 x 1.9	0.042	0.0625		Single		\$6.49
2191411	Busboard Prototype Systems	SB830	Solderable Breadboard	Epoxy Glass	0.1	1258	7.3 x 1.9	0.042	0.0625	4 x 0.125	Single		\$6.49
2191429	Busboard Prototype Systems	SB1660	Solderable Breadboard	Epoxy Glass	0.1	2528	7.3 x 3.7	0.042	0.0625	6 x 0.125	Single		\$11.95
2125051	Busboard Prototype Systems	SB400	Solderable Breadboard	Phenolic	0.1	400	3 x 1.9	0.042	0.0625	0	Single		\$4.95
2191461	Busboard Prototype Systems	PR2H1	Stripboard	Copper Plated	0.1	589	3.2 x 2	0.037	0.0625	4 x 0.125	Single		\$3.15
2191470	Busboard Prototype Systems	PR2H2	Stripboard	Epoxy Glass	0.1	1209	4 x 3.2	0.03	0.0625	4 x 0.125	Single		\$5.69
2127267	Busboard Prototype Systems	ST3U	Stripboard	Epoxy Glass	0.1	2356	6.3 x 3.9	0.037	0.0625	0	Single		\$9.95
2191488	Busboard Prototype Systems	ST1	Stripboard	Phenolic	0.1	589	2 x 3.2	0.037	0.0625	4 x 0.125	Single		\$3.15
2191496	Busboard Prototype Systems	ST2	Stripboard	Phenolic	0.1	899	4 x 3.2	0.037	0.0625	4 x 0.125	Single		\$5.69