



[Click Here to Request a Large Quantity Quote](#)

Power Transformers

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Side Voltage	Primary Frequency	Secondary Side Voltage	Power Rating	Current Rating	Termination Style	Length (mm)	Width (mm)	Height (mm)	Mounting Style	Price 1
112513	Jameco Reliapro	112512.-R	115 VAC	50Hz to 60Hz	24 V	48 VA	2 A	Wires	58.42	81.28	58.42	Chassis	\$13.95
2297783	Hammond Manufacturing	187C24	115 VAC	50Hz to 60Hz	24 V CT	12 VA	0.5 A	0.187 Tab	71.37	43.82	41.15	Chassis	\$9.89
29226	Jameco Reliapro	29225-R	115 VAC, 230 VAC	50Hz to 60Hz	12.6 V CT	25.2 VA	2 A	Wires	60.96	71.12	50.8	Chassis	\$12.95
102593	Jameco Reliapro	SPW2304	115 VAC, 230 VAC	50Hz to 60Hz	Parallel 12 V, Series 24 V CT	12 VA	Parallel 1 A, Series 0.5 A	PC Tails	40.64	48.26	38.1	Through Hole	\$6.95
2231152	Tamura Corporation	3FL12-475	115 VAC, 230 VAC	50Hz to 60Hz	Parallel 6.3 V, Series 12.6 V	6 VA	Parallel 0.95 A, Series 0.475 A	PC Tails	39.62	47.63	21.59	Through Hole	\$6.95
221400	Jameco Reliapro	P-8657-R	117 VAC	50Hz to 60Hz	12 V	18 VA	1.5 A	Wires	48.26	71.12	50.8	Chassis	\$11.95
221356	Jameco Reliapro	P-8658	117 VAC	50Hz to 60Hz	12 V	48 VA	4 A	Wires	101.6	60.96	68.58	Chassis	\$12.95
221365	Jameco Reliapro	GTR-22404	117 VAC	50Hz to 60Hz	12 V, 24 V	96 VA	4 A	Solder Tab	116.84	76.2	0	Chassis	\$29.95
221373	Jameco Reliapro	P-8662-R	117 VAC	50Hz to 60Hz	24 V CT	48 VA	2 A	Wires	60.96	91.44	58.42	Chassis	\$13.95
2265671	Jameco Reliapro	67-1121	117 VAC	60 Hz	12 V CT	12 VA	1 A	Solder Tab/Push-on	34.79	42.93	35.81	Chassis	\$10.95
2188502	Arndt	53260	120 VAC	50Hz to 60Hz	11 V	12 VA	2 A	Wires	83.82	58.42	49.53	Chassis	\$5.95
102121	Jameco Reliapro	PT-50466-R	120 VAC	50Hz to 60Hz	12.6 V CT	50.4 VA	4 A	Wires	63.5	81.28	58.42	Chassis	\$12.95
149771	Jameco Reliapro	PT12666-R	120 VAC	50Hz to 60Hz	12.6 V CT	50.4 VA	4 A	Wires	63.5	81.28	58.42	Chassis	\$12.95
105532	Jameco Reliapro	AC518-1-R	120 VAC	50Hz to 60Hz	18 V CT	18 VA	1 A	Wires	55.88	71.12	50.8	Chassis	\$10.95
149957	Jameco Reliapro	PT-1848-R	120 VAC	50Hz to 60Hz	18 V CT	36 VA	2 A	Wires	58.42	81.28	68.58	Chassis	\$12.95
618556	Triad Magnetics	F-261U	120 VAC	50Hz to 60Hz	24	192 VA	8 A	Wires	104.77	87.3	88.9	Chassis	\$51.39
102112	Jameco Reliapro	102111-R	120 VAC	50Hz to 60Hz	24 V CT	24 VA	1 A	Wires	60.96	71.12	50.8	Chassis	\$11.95
2230491	Jameco Reliapro	67-1242	120 VAC	50Hz to 60Hz	24 V CT	48 VA	2 A	Solder Tab	49.53	58.93	50.8	Chassis	\$15.95
101864	Jameco Reliapro	ACT-2457	120 VAC	50Hz to 60Hz	24 V CT	57.6 VA	2.4 A	Solder Tab	53.34	68.58	58.42	Chassis	\$15.95
149797	Jameco Reliapro	PT-2866-R	120 VAC	50Hz to 60Hz	28 V CT	56 VA	2 A	Wires	63.5	81.28	58.42	Chassis	\$13.95
102163	Jameco Reliapro	AC463-1.2-R	120 VAC	50Hz to 60Hz	6.3 V CT	7.6 VA	1.2 A	Wires	45.72	60.96	43.18	Chassis	\$10.95
105524	Jameco Reliapro	TR4820-91-R	120 VAC	50Hz to 60Hz	9 V CT	9 VA	1 A	Wires	45.72	60.96	43.18	Chassis	\$10.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Side Voltage	Primary Frequency	Secondary Side Voltage	Power Rating	Current Rating	Termination Style	Length (mm)	Width (mm)	Height (mm)	Mounting Style	Price 1
2292983	Hammond Manufacturing	172A	230 VAC	50Hz to 60Hz	115 VAC	100 VA	1 A	NEMA 6-15P, NEMA 5-15R	129	97	119	Chassis	\$119.95