



[Click Here to Request a Large Quantity Quote](#)

[Diodes & Rectifiers-TVS](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Package	DC Breakover Voltage (Nominal)	Maximum Peak Pulse Current	Peak Pulse Power Dissipation	Direction Type	Price 1
2286311	STMicroelectronics	1.5KE150	128V Transient Voltage Suppression Diode DO-201	DO-201	128 V	7.3 A	1500 W	Uni-Directional	\$0.35
1542961	Vishay	1.5KE16CA	TVS Diode 22.5V Clamp 66.7A Ipp Through Hole 1500W 1.5KE	DO-201	15.2 V	66.7 A	1500 W	Bi-Directional	\$0.55
2286319	STMicroelectronics	1.5KE250CA	213V Transient Voltage Suppression Diode DO-201	DO-201	250 V	4.4 A	1500 W	Uni-Directional	\$0.39
1961137	STMicroelectronics	1.5KE6V8A	Diode Transient Voltage Suppressor Single Uni Directional 5.8 Volt 1.5KW 2-Pin DO-201 Ammo	DO-201	5.8 V	746 A	1500 W	Uni-Directional	\$0.45
2286303	STMicroelectronics	1.5KE75CP	64.1V Transient Voltage Suppression Diode DO-201	DO-201	64.1 V	14.8 A	1500 W	Bi-Directional	\$0.59
2303247	Major Brands	1.5KE8.2C	TVS Diode 12.1V Clamp 125.6A Ipp DO-201	DO-201	7.02 V	125.6 A	1500 W	Bi-Directional	\$0.59
618118	Major Brands	1N5908	TVS Diode Unidirectional 6V Breakdown 8.5V Clamp 120A Ipp 1500W DO-201AD	DO-201	6 V	120 A	1500 W	Uni-Directional	\$1.25
2245917	New Jersey Semiconductor	1N6072A	Diode 1N6072A BiDirectional Transient Absorption 185V 1.5K watts	DO-13	185 V	4.6 A	1500 W	Bi-Directional	\$8.95
1944821	Major Brands	P1803AC	IC P1803AC Balanced Three-chip SIDACTor Device 150 Volt 5 amp TO-220	TO-220	150 V	400 A	330 W		\$2.95
289035	Major Brands	P6KE12A	TVS Diode 16.7V Clamp 36.5A Ipp DO-15	DO-15	11.4 V	36 A	600 W	Uni-Directional	\$0.29
256663	Major Brands	P6KE6.8A	TVS DIODE 600W 5.8-171V ESD Class 3 DO-15	DO-15	6.8 V	58.1 A	600 W	Bi-Directional	\$0.35
2302895	Major Brands	P6KE8V2A	Transient Voltage Suppressor (TVS) Diode 12.1V Clamp 50A Ipp DO-15	DO-15	7.79 V	50 A	600 W	Uni-Directional	\$0.59
1542371	Diodes Incorporated	SMBJ24A-13-F	TVS Diode 38.9V Clamp 15.4A Ipp Surface Mount SMB	SMB	24 V	15.4 A	600 W		\$0.25
2277479	Bourns	TISP4300H3LM	Bidirectional Thyristor with Overvoltage Protectors 230V TO-92	DO-92	300 V	300 A	1500 W	Bi-Directional	\$0.69
2277495	Bourns	TISP4350M3LM	Bidirectional Thyristor with Overvoltage Protectors 275V 50A TO-92	DO-92	350 V	220 A	1500 W	Bi-Directional	\$0.69

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Package	DC Breakover Voltage (Nominal)	Maximum Peak Pulse Current	Peak Pulse Power Dissipation	Direction Type	Price 1
2277447	Bourns	TISP4395M3LMFR	3-pin TRIAC Logic Sensitive Gate 600V 1A	DO-92	395 V	220 A	1500 W	Bi-Directional	\$0.59