



[Click Here to Request a Large Quantity Quote](#)

[24 Volt DC Brushless Fan](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
<a href="#">2304959</a>	Gulf Electrics	GD244010LB (2N3)	24	40	40	10	4.5	Dual Ball	50	UL/CUL/CE	21.5	12"	\$8.49
<a href="#">2304175</a>	ADDA Corporation	AD0424HB-G76(BT1)	24	40	40	10	6	Dual Ball	90	UL/TUV/CE	25	(3) 12", speed sensor	\$10.95
<a href="#">2167605</a>	ADDA Corporation	AD0424HB-G70-LF	24	40	40	10	6.7	Ball	90	UL/CUL/TUV/CE	25	12"	\$10.95
<a href="#">2231806</a>	ADDA Corporation	AD0424LB-C50	24	40	40	20	7.7	Ball	60	UL/TUV/CE	25	12"	\$10.95
<a href="#">2158514</a>	Sunon	MF40202V2-10000-A99	24	40	40	20	7.7	Vapo	33	UL/TUV/CE/CSA	21	12"	\$10.95
<a href="#">2307719</a>	ADDA Corporation	1608KL-05W-B50-L00	24	40	40	20	9.5	Ball	80	UL/CSA/VDE/CE	33	12"	\$10.95
<a href="#">2235268</a>	ADDA Corporation	AD0524HS-G70	24	50	50	10	11.2	Sleeve	90	UL/CUL/TUV/CE	26	12"	\$10.95
<a href="#">1708422</a>	Sunon	KDE2406PHS3	24	60	60	15	15	Sleeve	50	UL/CUL/TUV/CE	31	12"	\$8.95
<a href="#">2188588</a>	Sunon	MF60152V2-10000-A99	24	60	60	15	21.9	Vapo	85	UL/CUL/TUV/CE	32.5	12"	\$8.95
<a href="#">2304967</a>	Gulf Electrics	GD246015EB (2I9)	24	60	60	15	26	Dual Ball	180	UL/CUL/CE	40	12"	\$9.95
<a href="#">2271135</a>	ADDA Corporation	AG06024DB207000	24	60	60	20	15.1	Dual Ball	30	UL/CUL/CE	30.9	12"	\$9.95
<a href="#">2233191</a>	ADDA Corporation	AD0624HX-C70GL	24	60	60	20	16.3	Hypro	90	UL/CUL/TUV/CE	29.7	12"	\$9.95
<a href="#">2231831</a>	ADDA Corporation	AD0624LB-A70GL	24	60	60	25	13.2	Ball	80	UL/TUV/CE	16.1	12"	\$6.95
<a href="#">2295543</a>	NMB Technologies	FBA06A-24L1A	24	60	60	25	14.1	Ball	100	UL/CSA	24	12"	\$6.95
<a href="#">2132111</a>	ADDA Corporation	AD0624HB-D71GL	24	60	60	25	17	Ball	80	UL/CSA/TUV/CUL/CE	28.3	12"	\$7.95
<a href="#">2121391</a>	ADDA Corporation	AD06024MB257100	24	60	60	25	17.3	Ball	80	UL/CUL/TUV/CE	26.9	12"	\$7.95
<a href="#">189861</a>	Jamicon Corporation	JF0625B2M-005-065R	24	60	60	25	18	Ball	130	UL/CSA/TUV/CE	31.3	10"	\$8.95
<a href="#">2271295</a>	NMB Technologies	2410NL-05W-B30	24	60	60	25	19	Ball	60	CSA	31	4" w/ conn.	\$6.95
<a href="#">2306695</a>	NMB Technologies	2410ML-05W-B50	24	60	60	25	23.3	Ball	100	UL/CUL/TUV/CE	35	12"	\$8.95
<a href="#">2234492</a>	ADDA Corporation	AG06024HB257002	24	60	60	25	23.3	Ball	120	UL/CUL/TUV/CE	33	12"	\$8.95
<a href="#">2228244</a>	Frilec	2406PTB1	24	60	60	25	23.5	Ball	110	UL/CSA/CE	33	12"	\$6.95
<a href="#">2235313</a>	ADDA Corporation	AQ0624HB-70GL(T)	24	60	60	25	24.5	Ball	120	UL/CUL/CE	35.2	12"	\$6.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
<a href="#">2306567</a>	Sanyo Denki	109R0624D4011	24	60	60	25	25.4	Ball	120	UL/CSA/TUV	58	(3) 12", speed sensor	\$9.95
<a href="#">212628</a>	ADDA Corporation	AD0624UB-A71GL-LF	24	60	60	25	27.8	Sleeve	150	UL/CSA/TUV/CE	32.3	12"	\$7.95
<a href="#">2304975</a>	Gulf Electrics	GD246025EB (2I9)	24	60	60	25	29.3	Dual Ball	110	UL/CUL/CE	40.5	12"	\$9.95
<a href="#">2306671</a>	Sunon	ME80252V3-000U-A99	24	80	80	25	33	Vapo	49	UL/CUL/TUV/CSA	28	12"	\$8.95
<a href="#">2302255</a>	ADDA Corporation	AD0824HB-A74GL	24	80	80	25	39	Ball	160	UL/CUL/CE	34.4	12"	\$14.95
<a href="#">136161</a>	Jamicon Corporation	JF0825B2H-005-065R	24	80	80	25	39.2	Ball	150	UL/CSA/TUV	31	12"	\$9.95
<a href="#">2158565</a>	Sunon	EE80252B1-0000-A99	24	80	80	25	41	Ball	73	UL/CUL/TUV	33	12"	\$11.95
<a href="#">2271039</a>	Thermactive Electronics	RDH8025B2	24	80	80	25	41	Ball	150	UL/CUL/TUV/CE	35	12"	\$10.95
<a href="#">2306679</a>	Sunon	PE80252B1-000U-A99	24	80	80	25	41	Ball	200	UL/CSA/TUV/CE	47.5	12"	\$9.95
<a href="#">2292639</a>	ADDA Corporation	AD08024UB257104(05H3)	24	80	80	25	47.31	Ball	160	UL/CUL/TUV/CE	41	11"	\$9.95
<a href="#">2304983</a>	Gulf Electrics	GD248025EB-N (2I9)	24	80	80	25	49.7	Dual Ball	140	UL/CUL/CE	39.5	12"	\$9.95
<a href="#">2234847</a>	ADDA Corporation	AD0824UB-A73GL(LN)	24	80	80	25	52.4	Ball	150	UL/CUL/TUV/CE	40.8	(3) 12", speed sensor	\$11.95
<a href="#">2211160</a>	NMB Technologies	3113PL05WB30	24	80	80	32	28	Ball	130	UL/CUL	31	12"	\$3.95
<a href="#">2271287</a>	EBM Papst	8314/19H	24	80	80	32	47.1	Ball	245	UL/CSA	48	(3) 11", speed sensor	\$39.95
<a href="#">2220171</a>	ADDA Corporation	AD0824UB-Y51	24	80	80	32	55.3	Ball	150	UL/CUL/TUV/CE	43.8	12"	\$12.95
<a href="#">2232964</a>	ADDA Corporation	AD0824UB-F73DS	24	80	80	38	88	Ball	440	UL/VDE/CE	55	(3) 12", speed sensor	\$12.95
<a href="#">2232075</a>	ADDA Corporation	AD0924HB-C70-LF	24	92	92	20	33	Ball	140	UL/CUL/TUV/CE/CSA	32.8	11"	\$14.95
<a href="#">2289223</a>	Canon	CF92-H201N1D	24	92	92	25	35	Ball	85	UL/CSA	27	11"	\$6.95
<a href="#">2203071</a>	NMB Technologies	3610PL-05W-B30	24	92	92	25	41	Ball	150	UL	47.2	12"	\$7.95
<a href="#">2232999</a>	ADDA Corporation	AD0924LB-A71GL	24	92	92	25	41.6	Ball	80	UL/CUL/TUV/CE	30	12"	\$8.95
<a href="#">2203080</a>	Nidec Corporation	A31394-55	24	92	92	25	42	Ball	140	UL/CSA	48	3" w/ conn.	\$4.95
<a href="#">2215751</a>	NMB Technologies	3610PL-05W-B20-100	24	92	92	25	43	Ball	150	UL/CUL	39	12"	\$6.95
<a href="#">2233001</a>	ADDA Corporation	AD0924MX-A70GL	24	92	92	25	47.2	Hypro	120	UL/CUL/TUV/CE	31.3	12"	\$7.95
<a href="#">2306599</a>	Sanyo Denki	9WS0924H402	24	92	92	25	48.7	Ball	100	UL/CSA/TUV	33	12"	\$29.95
<a href="#">2132082</a>	ADDA Corporation	AD0924HX-A72GL	24	92	92	25	50	Ball	150	UL/CSA/TUV/CUL/CE	33.7	(3) 12", alarm	\$8.95
<a href="#">2155065</a>	Delta Electronics	AFB0924H-R00	24	92	92	25	51.2	Ball	100	UL/CSA/CE	34	(3) 12", lock rotor	\$10.95

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
<a href="#">2158303</a>	Sunon	EE92252B1-0000-A99	24	92	92	25	51.5	Ball	87	UL/CE/TUV	34	12"	\$11.95
<a href="#">2121527</a>	ADDA Corporation	AD1224MB-A71GL	24	120	120	25	80.5	Ball	170	UL/CUL/TUV/CE	38	11"	\$12.95
<a href="#">2218046</a>	ADDA Corporation	AD1224UB-A70GL	24	120	120	25	99	Ball	250	UL/CUL/TUV/CE	43.3	12"	\$13.95
<a href="#">2289015</a>	EBM Papst	TYP4484F	24	120	120	25	100	Ball	208	UL/CSA/VDE	43	12"	\$29.95
<a href="#">2235330</a>	ADDA Corporation	AS12024LB25A100	24	120	120	25	126	Ball	280	UL/CUL/TUV/CE	51	12"	\$24.95
<a href="#">2306559</a>	Sanyo Denki	9GV1224G402	24	120	120	25	171	Ball	840	UL	55.5	12"	\$29.95
<a href="#">2232104</a>	ADDA Corporation	AD1224UB-Y5B	24	120	120	32	133	Ball	320	UL/CUL/TUV/CE	48.4	(3) 12", PWM + FG	\$13.95
<a href="#">153411</a>	Sunon	KD2412PMBX-6A	24	120	120	38	98	Ball	230	UL/TUV/CSA	36.5	12" w/ terminals	\$7.95
<a href="#">694524</a>	Jamicon Corporation	JF1238B2MR-R	24	120	120	38	101.3	Ball	220	UL/TUV/CE/CSA	39.1	9"	\$15.95
<a href="#">2304991</a>	Gulf Electrics	GD241238MB (2I5)	24	120	120	38	107	Ball	450	UL/CUL/CE	43	12"	\$12.95
<a href="#">2271167</a>	ADDA Corporation	AD1224US-F51(FN)	24	120	120	38	120	Sleeve	400	UL/CUL/TUV/CE	48	12"	\$12.95
<a href="#">2236404</a>	Sunon	MEC0382V1-0000-A99	24	120	120	38	138	Vapo	383	UL/CUL/TUV/CE	48	12"	\$12.95
<a href="#">2299191</a>	Delta Electronics	AFB1224EHE-EP	24	120	120	38	212	Dual Ball	850	UL/CSA/CE/VDE	58.5	(4) 12", speed & PWM	\$19.95
<a href="#">2306591</a>	Sanyo Denki	9SG1224P1G03	24	120	120	38	260	Ball	2000	UL/CSA/TUV	64	(3) 12", locked rotor	\$29.95
<a href="#">2234919</a>	ADDA Corporation	AD1324VB-F51	24	127	127	38	242.15	Ball	1100	UL/CUL/TUV/CE	64.5	12"	\$27.95
<a href="#">2270879</a>	ADDA Corporation	AD17224MB5151M0(0CW)	24	172	151	51	327	Ball	1450	UL/TUV/CSA/CE	64	12"	\$49.95
<a href="#">2306551</a>	Sanyo Denki	109E5724C505	24	172	151	51	350	Ball	2300	UL/CUL/TUV	66	12"	\$19.95