



[Click Here to Request a Large Quantity Quote](#)

[Female Header Receptacles](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Number of Rows	Number of Contacts	Maximum Current Rating	Maximum Voltage Rating	Maximum Contact Resistance	Contact Material	Contact Plating	Housing Color	Housing Material	Price 1
2172560	Jameco Valuepro	7400-1X10SG-R	Female	1	10	1	250 VAC	20 mOhm	Phosphor Bronze/Brass	Gold	Black	Thermoplastic	\$0.59
2160753	Jameco Valuepro	F301-SGP-D024-01	Female	1	10	2	250 VAC	20 mOhm	Phosphor Bronze	Gold	Black	Polyester	\$0.59
2177627	Adam Technologies	RS1-10-G-.561-A11596	Female	1	10	3	250 VAC	20 mOhm	Phosphor Bronze	Gold	Black	Polybutylene Terephthalate	\$0.59
200783	Jameco Valuepro	B06-1X12BG-R	Female	1	12	1	250 VAC	30 mOhm	Phosphor Bronze/Brass	Gold	Black	Polybutylene Terephthalate	\$0.59
2213641	Adam Technologies	RS1-12-G-.561-A11596	Female	1	12	3	250 VAC	20 mOhm	Phosphor Bronze	Gold	Black	Polybutylene Terephthalate	\$0.49
308592	Jameco Valuepro	TDH16SG-VP-R	Female	1	16	1	250 VAC	30 mOhm	Phosphor Bronze/Brass	Gold	Black	Polybutylene Terephthalate	\$0.79
2213659	Adam Technologies	RS1-16-G-.561-A11596	Female	1	16	3	250 VAC	20 mOhm	Phosphor Bronze	Gold	Black	Polybutylene Terephthalate	\$0.49
308567	Jameco Valuepro	G85-20-R	Female	1	20	1	250 VAC	30 mOhm	Brass	Gold	Black	Polybutylene Terephthalate	\$0.89
2213667	Adam Technologies	RS1-20-G-.561-A11596	Female	1	20	3	250 VAC	20 mOhm	Phosphor Bronze	Gold	Black	Polybutylene Terephthalate	\$0.69
2169758	Adam Technologies	RS1-04-G	Female	1	4	3	250 VAC	20 mOhm	Phosphor Bronze	Gold Over Nickel	Black	Polybutylene Terephthalate	\$0.31
2168173	Adam Technologies	RS1-40-T	Female	1	40	3	250 VAC	20 mOhm	Phosphor Bronze	Tin Over Copper	Black	Polybutylene Terephthalate	\$1.19
2144614	Adam Technologies	RS1-06-G-.561-A11596	Female	1	6	3	250 VAC	20 mOhm	Phosphor Bronze	Gold	Black	Polybutylene Terephthalate	\$0.49
70755	Jameco Valuepro	7400-1X8SG-R	Female	1	8	1	250 VAC	20 mOhm	Phosphor Bronze/Brass	Gold Over Nickel	Black	Thermoplastic	\$0.55
2144631	Adam Technologies	RS1-08-G-.561-A11596	Female	1	8	3	250 VAC	20 mOhm	Phosphor Bronze	Gold	Black	Polybutylene Terephthalate	\$0.59
70721	Jameco Valuepro	TDH16SG-R	Female	2	16	3	250 VAC	20 mOhm	Brass	Gold	Black	Thermoplastic	\$0.79

Jameco Part #	Manufacturer	Manufacturer Part #	Gender	Number of Rows	Number of Contacts	Maximum Current Rating	Maximum Voltage Rating	Maximum Contact Resistance	Contact Material	Contact Plating	Housing Color	Housing Material	Price 1
163862	Jameco Valuepro	2017-254-34SG	Female	2	17	1	250 VAC	20 mOhm	Phosphor Bronze/Brass	Gold	Black	Polybutylene Terephthalate	\$0.89
70827	Jameco Valuepro	GOLDSUN G85-20-R	Female	2	20	3	250 VAC	20 mOhm	Brass	Gold	Black	Thermoplastic	\$0.95
105057	Jameco Valuepro	7400-2X15SG-R	Female	2	30	1	250 VAC	20 mOhm	Phosphor Bronze/Brass	Gold Over Nickel	Black	Thermoplastic	\$0.99
111705	Jameco Valuepro	2221-40-S-02-3.2	Female	2	40	1	250 VAC	20 mOhm	Phosphor Bronze/Brass	Gold Over Nickel	Black	Thermoplastic	\$1.25
2290847	HARWIN INTERCONNECT	M20-6103245	Female	2	64	3	12 VDC	30 mOhm	Phosphor Bronze	Gold	Black	Thermoplastic	\$5.95