



[Click Here to Request a Large Quantity Quote](#)

[Circuit Protection-Thermistors](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Resistance (Ohms) @ 25C	Tolerance	B Parameter	Power Rating	Package / Case	Body Diameter (mm)	Price 1
2312191	EPCOS	B57235S509M	NTC	5	±20%	2800 K	1800 mW	Radial	9.5	\$0.69
2280383	Ametherm	SL105R004-B	NTC	5	±20%	2967 K	11 mW	Radial	10	\$0.39
2285279	General Electric	CL150	NTC	5	±25%	n/a	15 mW	Radial	14	\$0.49
2312183	EPCOS	B57153S809M	NTC	8	±20%	n/a	1400 mW	Radial	8.5	\$0.69
2312575	EPCOS	B57164K100K	NTC	10	±10%	2900 K	450 mW	Radial	5.5	\$0.75
2312599	EPCOS	B57153S100M	NTC	10	±20%	2800 K	1400 mW	Radial	8.5	\$0.55
1842736	EPCOS	B57153S100M51	NTC	10	±20%	n/a	1400 mW	Radial	8.5	\$0.75
2312199	EPCOS	B57238S220M51	NTC	22	±20%	n/a	3900 mW	Radial	16	\$1.29
207483	Jameco Valuepro	NTC-102-R	NTC	1000	±10%	3636 K	550 mW	Radial	4.5	\$0.39
2312583	Vishay	NTCLE100E3472HB0	NTC	4700	±3%	3977 K	500 mW	Radial	3	\$0.69
207441	Jameco Valuepro	NTC-502-R	NTC	5000	±10%	3935 K	550 mW	Radial	4.5	\$0.39
2312647	EPCOS	B57863S502F0	NTC	5000	±5%	3988 K	60 mW	Bead w/ wires	6.5	\$2.95
2312639	EPCOS	B57862S103F	NTC	10000	±1%	3988 K	60 mW	Bead w/ wires	7.5	\$4.95
2312631	EPCOS	B57861S102J40	NTC	10000	±1%	3988 K	60 mW	Radial	7.5	\$1.79
2234126	Jameco Valuepro	AP03201	NTC	10000	±1%	4965 K	550 mW	Radial	5	\$0.79
207037	Jameco Valuepro	NTC-103-R	NTC	10000	±10%	4038 K	550 mW	Radial	4.5	\$0.39
2312591	Vishay	NTCLE203E3103HB0	NTC	10000	±3%	3977 K	100 mW	Radial	3	\$0.79
2312623	EPCOS	B57500M103A	NTC	10000	±3%	3988 K	60 mW	Cylindrical Probe	15	\$3.59
2312655	EPCOS	B57891S203F8	NTC	20000	±1%	4300 K	200 mW	Radial	4.5	\$1.95
207002	Jameco Valuepro	NTC-503-R	NTC	50000	±10%	4204 K	550 mW	Radial	4.5	\$0.39
2277103	Honeywell	597-32BM07-104	NTC	100000	±2%	4261 K	20 mW	8 Stud Ring Tongue	8.7	\$2.95