



[Click Here to Request a Large Quantity Quote](#)

[Interface-MPU Supervisory Circuits](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Description	Package	Price 1
2291399	Dallas Semiconductor	DS1231-20	Supervisor Open Drain or Open Collector 1 Channel PDIP-8	DIP-8	\$6.95
114331	Dallas Semiconductor	DS1232LP	IC DS1232LP Low Power MicroMonitor Chip 4.5-to-5.5V 200uA	DIP-8	\$3.95
2291407	Dallas Semiconductor	DS1232S	Supervisor Open Drain Push-Pull 1 Channel SOIC-16	SOIC-16	\$2.95
2291415	Dallas Semiconductor	DS1233-10	Supervisor Open Drain or Open Collector 1 Channel TO-92-3	TO-92	\$1.39
1193730	Maxim Semiconductor	DS1233D-10+	Supervisor Open Drain or Open Collector Channel 4.375 Volt 50uA TO-92-3	TO-92	\$1.29
2290743	Maxim Semiconductor	DS1833Z-5+	EconoReset Monitor 5V NPU Supervisor SOT-223-4	SOT-223-4	\$2.95
2321135	Linear Technology	LTC1326CS8-2.5	Voltage Supervisor Open Drain or Open Collector 3 Channel 8-SOIC	SOIC-8	\$3.95
2296263	Maxim Semiconductor	MAX6316LUK29CU T	Supervisor Push-Pull Totem Pole Single Channel SOT-23-5	SOT-23-5	\$2.95
820439	Maxim Semiconductor	MAX704CPA	IC MAX704CPA Low-Cost Microprocessor Supervisory Circuit with Battery Backup	DIP-8	\$4.95
33460	National Semiconductor	TL7702ACP	TL7702ACP Supply-Voltage Supervisor	DIP-8	\$0.69
2320463	TI	TL7705ACP	Supply-Voltage Supervisor 20V 4.55V Threshold 1us 70C Input Current 16mA DIP-8	DIP-8	\$0.65
760860	TI	TL7705BCP	Supply-Voltage Supervisor 18V Supply 4.55V Threshold 270ns 125C Input Current 20mA DIP-8	DIP-8	\$0.69