



[Click Here to Request a Large Quantity Quote](#)

[Circuit Protection-Fuses 5mm x 20mm](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Blow characteristic	Rated Breaking Capacity (A)	Rated AC Voltage (URac) (V)	Fuse Material	Body Diameter (inch)	Body Length (inch)	Price 1
<a href="#">2287479</a>	Littelfuse	020200H5	202	Fast Acting	5	250	Thermo Plastic	0.37	0.16	\$1.25
<a href="#">1709960</a>	Littelfuse	0225003.H	225	Fast Acting	3	250	Glass	0.25	1.25	\$0.59
<a href="#">1710451</a>	Littelfuse	0251.125MXL	251	Very Fast	0.125	125	Epoxy Coated	0.25	1.25	\$0.49
<a href="#">1710661</a>	Littelfuse	0273.250H	273	Very Fast	0.25	125	Glass	0.25	0.35	\$5.75
<a href="#">652949</a>	Littelfuse	0312001.HXP	312	Fast Acting	1	250	Glass	0.25	1.25	\$0.39
<a href="#">653319</a>	Littelfuse	0313.125HXP	313	Slow Blow	0.125	250	Glass	0.25	1.25	\$1.09
<a href="#">653589</a>	Littelfuse	0313008.HXP	313	Slow Blow	8	250	Glass	0.25	1.25	\$1.49
<a href="#">656974</a>	Littelfuse	0314015.HXP	314	Fast Acting	15	250	Ceramic	0.25	1.25	\$0.49
<a href="#">1711656</a>	Littelfuse	0326020.HXP	326	Slow Blow	20	250	Ceramic	0.25	1.25	\$0.99
<a href="#">1711445</a>	Littelfuse	0324015P	3AB	Fast Acting	15	250	Ceramic	0.25	1.25	\$0.29
<a href="#">2296639</a>	Littelfuse	311015	3AG	Fast Acting	15	32	Glass	0.25	1.25	\$0.35
<a href="#">2294455</a>	Littelfuse	0KLN001.T	5AG	Fast Acting	1	600	Ceramic	0.41	1.5	\$13.95
<a href="#">2291135</a>	Eaton	AGX30	8AG	Fast Acting	30	32	Glass	0.25	1	\$0.75
<a href="#">69404</a>	Jameco Valuepro	AGC-1/4-R-VP	AGC	Fast Acting	0.25	250	Glass	0.25	1.25	\$0.49
<a href="#">10410</a>	Jameco Valuepro	AGC-1/2-VP	AGC	Fast Acting	0.5	250	Glass	0.25	1.25	\$0.35
<a href="#">2296887</a>	Littelfuse	312.75	AGC	Fast Acting	0.75	250	Glass	0.25	1.25	\$0.35
<a href="#">10373</a>	Jameco Valuepro	AGC-1-R-VP	AGC	Fast Acting	1	250	Glass	0.25	1.25	\$0.35
<a href="#">2205472</a>	Littelfuse	31301.2	AGC	Fast Acting	1.25	250	Glass	0.25	1.25	\$0.35
<a href="#">10382</a>	Jameco Valuepro	AGC-2-R-VP	AGC	Fast Acting	2	250	Glass	0.25	1.25	\$0.39
<a href="#">69439</a>	Jameco Valuepro	FUSE 3A-R	AGC	Fast Acting	3	250	Glass	0.25	1.25	\$0.39

Jameco Part #	Manufacturer	Manufacturer Part #	Family	Blow characteristic	Rated Breaking Capacity (A)	Rated AC Voltage (URac) (V)	Fuse Material	Body Diameter (inch)	Body Length (inch)	Price 1
<a href="#">10402</a>	Jameco Valuepro	FUSE 5A-R	AGC	Fast Acting	5	250	Glass	0.25	1.25	\$0.39
<a href="#">2258427</a>	Schurter	F6.3A/125V	AGC	Fast Acting	6.3	125	Glass	0.25	1.25	\$0.29
<a href="#">2280535</a>	Littelfuse	312008.MPX	AGC	Fast Acting	8	250	Glass	0.25	1.25	\$0.25
<a href="#">69462</a>	Jameco Valuepro	FUSE 10A	AGC	Fast Acting	10	250	Glass	0.25	1.25	\$0.49
<a href="#">2296815</a>	Eaton	AGC-12	AGC	Fast Acting	12	32	Glass	0.25	1.25	\$0.35
<a href="#">2296943</a>	Eaton	323002	AGC	Slow Blow	2	250	Ceramic	0.25	1.25	\$0.39
<a href="#">2296919</a>	Eaton	GMC-V-10A	GMC	Medium Delay	10	125	Glass	0.2	0.83	\$0.39
<a href="#">2297223</a>	Eaton	GMQ-1	GMQ	Slow Blow	1.6	300	Ceramic	0.25	2.25	\$4.95
<a href="#">69535</a>	Jameco Valuepro	TSA-3A	MDL	Fast Acting	3	250	Glass	0.25	1.25	\$0.79
<a href="#">186301</a>	Jameco Valuepro	FUSE 16A	MDL	Fast Acting	16	250	Glass	0.25	1.25	\$0.29
<a href="#">25655</a>	Jameco Valuepro	GFSL250MA-R	MDL	Slow Blow	0.25	250	Glass	0.25	1.25	\$0.79
<a href="#">25639</a>	Jameco Valuepro	G1SA1A-R	MDL	Slow Blow	1	250	Glass	0.25	1.25	\$0.79
<a href="#">25646</a>	Jameco Valuepro	TSA-2A	MDL	Slow Blow	2	250	Glass	0.25	1.25	\$0.59
<a href="#">25672</a>	Jameco Valuepro	MDL-5A-R	MDL	Slow Blow	5	250	Glass	0.25	1.25	\$0.79
<a href="#">69570</a>	Jameco Valuepro	G1SF10A-R	MDL	Slow Blow	10	250	Glass	0.25	1.25	\$0.79
<a href="#">197544</a>	Jameco Valuepro	MFA1-4	MFA	Fast Acting	4	250	Glass	0.25	1.25	\$0.35
<a href="#">2297215</a>	Eaton	SFE-20	SFE-20	Fast Acting	20	32	Glass	0.25	1.25	\$0.79