

[Click Here to Request a Large Quantity Quote](#)

[Breakaway Headers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	Number of Rows	Number of Contacts	Body Orientation	Contact Material	Contact Plating	Gender	Housing Color	Housing Material	Price 1
2302231	AVX	11-5016-2016-10-001	1.27	2	16	Straight	Brass	Gold Flash	Male	Black	Polybutylene Terephthalate	\$0.43
2295895	GS Magic Inc/GS Magicstor	2PH1-06S-G-F1	2.00	1	6	Straight	Brass	Gold Flash	Male	Black	Polybutylene Terephthalate	\$0.25
2076797	Jameco Valuepro	SMH01	2.54	1	1	Straight	Brass	Gold	Male	Black	Polybutylene Terephthalate	\$0.03
2294615	Jameco Valuepro	7000-1X10RG-A	2.54	1	10	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.35
103393	Jameco Valuepro	7000-1X10SG-R	2.54	1	10	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.29
2294623	Jameco Valuepro	7000-1X11RG-A	2.54	1	11	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.39
2294671	Jameco Valuepro	7000-1X11SG-R	2.54	1	11	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.29
2294631	Jameco Valuepro	7000-1X12RG-A	2.54	1	12	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.41
686680	Jameco Valuepro	7000-1X12SG-R	2.54	1	12	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.32
2294679	Jameco Valuepro	7000-1X13SG-R	2.54	1	13	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.32
2294639	Jameco Valuepro	7000-1X14RG-A	2.54	1	14	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.43
2294687	Jameco Valuepro	7000-1X14SG-R	2.54	1	14	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.34
2294695	Jameco Valuepro	7000-1X15SG-R	2.54	1	15	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.34
2294647	Jameco Valuepro	7000-1X16RG-A	2.54	1	16	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.49
2294703	Jameco Valuepro	7000-1X16G-R	2.54	1	16	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.35

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	Number of Rows	Number of Contacts	Body Orientation	Contact Material	Contact Plating	Gender	Housing Color	Housing Material	Price 1
103377	Jameco Valuepro	7000-1X17SG-R	2.54	1	17	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.35
2228826	Arndt	SMH18	2.54	1	18	Straight	Phosphor Bronze	Tin	Male	Black	Polybutylene Terephthalate	\$0.29
2294655	Jameco Valuepro	7000-1X19RG-A	2.54	1	19	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.59
2294575	Jameco Valuepro	7000-1X2RG-A	2.54	1	2	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.09
108338	Jameco Valuepro	7000-1X2SG-R	2.54	1	2	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.07
2144884	Jameco Valuepro	SMH02T	2.54	1	2	Straight	Brass	Tin	Male	Black	Polybutylene Terephthalate	\$0.06
103369	Jameco Valuepro	7000-1X20SG-R	2.54	1	20	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.39
2229036	Jameco Valuepro	2012-254-20	2.54	1	20	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.35
2236797	Jameco Valuepro	PH-14.3-120S	2.54	1	20	Straight	Phosphor Bronze	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.39
202825	Jameco Valuepro	2012-254-1X22SG	2.54	1	22	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.43
2294711	Jameco Valuepro	7000-1X23SG-R	2.54	1	23	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.45
2294719	Jameco Valuepro	7000-1X24SG-R	2.54	1	24	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.45
103351	Jameco Valuepro	7000-1X25SG-R	2.54	1	25	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.29
2076869	Jameco Valuepro	RMH26	2.54	1	26	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.69
2294583	Jameco Valuepro	7000-1X3RG-A	2.54	1	3	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.13
109576	Jameco Valuepro	7000-1X3SG-R	2.54	1	3	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.10
103342	Jameco Valuepro	7000-1X30SG-R	2.54	1	30	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.47
2207849	Jameco Valuepro	2012-254-1X32SG	2.54	1	32	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.49

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	Number of Rows	Number of Contacts	Body Orientation	Contact Material	Contact Plating	Gender	Housing Color	Housing Material	Price 1
2076826	Jameco Valuepro	2012-254-1X34SG	2.54	1	34	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.49
103271	Jameco Valuepro	7000-1X36RG-R (B TYPE)	2.54	1	36	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.99
68339	Jameco Valuepro	1X36SG	2.54	1	36	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.55
2288607	Adam Technologies	PH1-36-U	2.54	1	36	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.45
2294591	Jameco Valuepro	7000-1X4RG-A	2.54	1	4	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.17
2120276	On Shore Technology	PH1-787/120-041	2.54	1	4	Straight	Brass	Gold	Male	Black	Polybutylene Terephthalate	\$0.15
117560	Jameco Valuepro	JS-1109-4-R	2.54	1	4	Straight	Phosphor bronse	Gold	Male	Black	Polybutylene Terephthalate	\$0.14
2294663	Jameco Valuepro	7000-1X40RG-A	2.54	1	40	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.99
2236800	Jameco Valuepro	PH-14.3-140S	2.54	1	40	Straight	Brass	Gold	Male	Black	Polybutylene Terephthalate	\$0.75
160882	Jameco Valuepro	7000-1X40SG-R	2.54	1	40	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.75
2168211	Adam Technologies	PH1-40-UA	2.54	1	40	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.59
2229044	Jameco Valuepro	2012-254-40	2.54	1	40	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.69
2076789	Jameco Valuepro	SMH05	2.54	1	5	Straight	Brass	Gold	Male	Black	Polybutylene Terephthalate	\$0.17
153700	Jameco Valuepro	JS1109-6-R	2.54	1	6	Straight	Brass	Gold	Male	Black	Polybutylene Terephthalate	\$0.18
2229327	Arndt	255-0004	2.54	1	6	Straight	Brass	Gold /Tin	Male	Black	Polybutylene Terephthalate	\$0.15
2294599	Jameco Valuepro	7000-1X7RG-A	2.54	1	7	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.25
2076800	Jameco Valuepro	7000-1X7SG-R	2.54	1	7	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.23
153728	Jameco Valuepro	7000-1X8RG-B	2.54	1	8	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.29

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	Number of Rows	Number of Contacts	Body Orientation	Contact Material	Contact Plating	Gender	Housing Color	Housing Material	Price 1
153702	Jameco Valuepro	7000-1X8SG-R	2.54	1	8	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.25
2120284	Adam Technologies	PH2-80-TA	2.54	1	80	Straight	Brass	Gold	Male	Black	Polybutylene Terephthalate	\$0.85
2294607	Jameco Valuepro	7000-1X9RG-A	2.54	1	9	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.32
2076818	Jameco Valuepro	7000-1X9SG-R	2.54	1	9	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.27
203932	Jameco Valuepro	2012-254-2X5RG	2.54	2	10	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.35
2302287	Molex	10-89-1103	2.54	2	10	Straight	Brass	Gold Flash	Male	Black	Polybutylene Terephthalate	\$0.89
67821	Jameco Valuepro	7000-2X5SG-R	2.54	2	10	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.29
1946041	Jameco Valuepro	7000-1X36RG-R(A TYPE)	2.54	2	10	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.99
2280319	Samtec	TSW105-07-T-D	2.54	2	10	Straight	Phosphor Bronze	Tin	Male	Black	Polyester	\$0.39
203941	Jameco Valuepro	7000-2X6RG-R	2.54	2	12	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.39
203810	Jameco Valuepro	2012-254-2X6SG	2.54	2	12	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.25
53495	Jameco Valuepro	7000-2X13SG	2.54	2	13	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.35
203959	Jameco Valuepro	2012-254-2X7RG	2.54	2	14	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.49
118456	Jameco Valuepro	7000-2X7SG-R	2.54	2	14	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.39
203967	Jameco Valuepro	2012-254-2X8RG	2.54	2	16	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.55
109568	Jameco Valuepro	7000-2X8SG-R	2.54	2	16	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.43
2302223	Jameco Valuepro	7000-2X9SG-LL-R	2.54	2	18	Straight	Brass	Gold Flash	Male	Black	Polybutylene Terephthalate	\$0.46
2076877	Jameco Valuepro	7000-2X9SG-R	2.54	2	18	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.45

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	Number of Rows	Number of Contacts	Body Orientation	Contact Material	Contact Plating	Gender	Housing Color	Housing Material	Price 1
53576	Jameco Valuepro	7000-2X01RG-R	2.54	2	20	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.65
2286087	Jameco Valuepro	923820DT	2.54	2	20	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.59
53480	Jameco Valuepro	7000-2X10SG-R	2.54	2	20	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.49
2205528	Mill Max	460-10-220-00-001000	2.54	2	20	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$2.25
203836	Jameco Valuepro	7000-2X11SG-R	2.54	2	22	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.55
203991	Jameco Valuepro	7000-2X12RG-R	2.54	2	24	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.69
203844	Jameco Valuepro	2012-254-2X12SG	2.54	2	24	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.59
53583	Jameco Valuepro	7000-2X13RG	2.54	2	26	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.75
204003	Jameco Valuepro	7000-2X14RG-R	2.54	2	28	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.79
203852	Jameco Valuepro	7000-2X14SG-R	2.54	2	28	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.69
204011	Jameco Valuepro	7000-2X15RG-R	2.54	2	30	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.85
203879	Jameco Valuepro	7000-2X15SG-R	2.54	2	30	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.75
203861	Jameco Valuepro	7000-2X16SG-R	2.54	2	32	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.79
204038	Jameco Valuepro	7000-2X17RG-R	2.54	2	34	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.89
53517	Jameco Valuepro	7000-2X17SG-R	2.54	2	34	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.39
203888	Jameco Valuepro	7000-2X18SG-R	2.54	2	36	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.85
204054	Jameco Valuepro	7000-2X19RG-R	2.54	2	38	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.95
203895	Jameco Valuepro	7000-2X19SG-R	2.54	2	38	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.85

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	Number of Rows	Number of Contacts	Body Orientation	Contact Material	Contact Plating	Gender	Housing Color	Housing Material	Price 1
203908	Jameco Valuepro	7000-2X2RG-R	2.54	2	4	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.25
115027	Jameco Valuepro	C2X2SG	2.54	2	4	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.14
109517	Jameco Valuepro	7000-2X4SG-R	2.54	2	4	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.25
53605	Jameco Valuepro	7000-2X20RG-R	2.54	2	40	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.99
53532	Jameco Valuepro	7000-2X20SG	2.54	2	40	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.85
53612	Jameco Valuepro	7000-2X25RG	2.54	2	50	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.89
53560	Jameco Valuepro	7000-2X25SG-R	2.54	2	50	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.89
203916	Jameco Valuepro	7000-2X3RG-R	2.54	2	6	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.29
115035	Jameco Valuepro	7000-2X3SG	2.54	2	6	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.17
68574	Jameco Valuepro	7000-2X30SG	2.54	2	60	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.95
103406	Jameco Valuepro	70002X36SG-R	2.54	2	72	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.99
2200701	Berg Electronics	67997-472	2.54	2	72	Straight	Phosphor Bronze	Tin	Male	Black	High Temperature Plastic	\$0.59
203924	Jameco Valuepro	7000-2X4RG-R	2.54	2	8	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.33
2135312	Fujitsu	724P008AU	2.54	2	8	Straight	Phosphor Bronze	Gold	Male	Black	Thermoplastic	\$0.25
2280303	Samtec	ZW-04-10-T-D-590-120	2.54	2	8	Straight	Phosphor Bronze	Tin Over Nickel	Male	Black	Polyester	\$0.99
139564	Jameco Valuepro	7000-2X40RG-R	2.54	2	80	Right Angle	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$1.29
117197	Jameco Valuepro	7000-2X40SG-R	2.54	2	80	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$1.29
2076893	Jameco Valuepro	933824TS	2.54	3	24	Straight	Brass	Gold Over Nickel	Male	Black	Polybutylene Terephthalate	\$0.15

Jameco Part #	Manufacturer	Manufacturer Part #	Pitch (mm)	Number of Rows	Number of Contacts	Body Orientation	Contact Material	Contact Plating	Gender	Housing Color	Housing Material	Price 1
164815	On Shore Technology	OSTOP240000	5.00	1	24	Straight	Brass	Tin	Male	Black	Thermoplastic	\$1.29