



[Click Here to Request a Large Quantity Quote](#)

[Round Ferrite Speakers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Impedance (Ohms)	Size (Diameter x Depth) (inch)	Nominal Input Power (W)	Input Power (max) (W)	Ouput SPL (dB)	Frequency Range (Hz)	Magnet Size (Diameter x H) (inches)	Termination Method	Price 1
2224041	Jameco Valuepro	110153-01	4	2.4 x 1.4	10	10	85	1000 - 12000	2.20 x 0.50	Solderable Lug	\$1.95
2205561	Panasonic	45P30S	8	1.8 x 0.7	0.1	0.1	93	530 - 3000	0.69 x 0.45	Solderable Lug	\$0.75
2302999	Jameco Valuepro	FR-504LT	8	2.0 x 0.65	0.2	0.25	86	900 - 9000	1.25 x 0.40	Wires with conn.	\$2.49
2239146	MG Electronics	MSC299SWC	8	2.0 x 0.7	0.7	2	83	500 - 8000	1.30 x 0.40	Wires with conn.	\$1.95
135589	Regal Electronics	8PROC5	8	2.0 x 0.70	0.2	0.4	83	420 - 5000	1.30 x 0.40	Solderable Lug	\$2.25
320362	Jameco Valuepro	TR-050F	8	2.0 x 0.70	0.2	0.4	86	900 - 9000	1.30 x 0.70	Solderable Lug	\$2.55
2208825	Jameco Valuepro	EAS-6P60SD	8	2.2 x 1.3	0.4	0.8	85	100 - 5000	2.20 x 1.30	Solderable Lug	\$0.99
2265895	Jameco Valuepro	BLS86-2-08H30.5-05LF	8	3.4 x 3.4 x 1.21	6	12	87	800 - 10000	2.30 x 0.40	Solderable Lug	\$2.95
2303023	Jameco Valuepro	SS2-16FWSS	16	2.0 x 0.65	0.2	0.4	96	240 - 360	1.26 x 0.40	Wires with conn.	\$2.75
2303615	Jameco Valuepro	5322-240-34014	25	2.0 x 0.67	0.25	0.5	86	288 - 432	0.67 x 0.45	Solderable Lug	\$3.95
2303623	Jameco Valuepro	MSC298M32	32	1.6 x 0.26	0.1	0.2	97	480 - 6000	0.69 x 0.10	Solderable Lug	\$2.75
2188916	Sharp Electronic Components	80P-G3YB	32	3.0 x 0.7	0.5	2	92	200 - 3000	0.80 x 0.50	Solderable Lug	\$0.89
2303031	Jameco Valuepro	SWC-50R12.8	45	2.0 x 0.45	0.05	1	88	400 - 9000	0.70 x 0.22	Wires with conn.	\$1.75