



[Click Here to Request a Large Quantity Quote](#)

[Switches-Rotary](#)

| Jameco Part # | Manufacturer | Manufacturer Part # | Number of Poles | Number of Positions | Max Current (mA) | Voltage Rating | Index Angle (Deg) | Size (Length x Diameter) (inch) | Shaft Diameter (inch) | Shaft Length (inch) | Shaft Type | Terminal Type | Price 1 |
|-------------------------|--------------------|---------------------|-----------------|---------------------|------------------|----------------|-------------------|---------------------------------|-----------------------|---------------------|---------------|-----------------|---------|
| 2281535 | Grayhill | 50D90-01-1-AJN | 1 | 4 | 150 | 115VAC | 90 | 1.28 x 0.50 | 0.125 | 0.375 | D Flat Side | Solder | \$18.59 |
| 2184464 | Jameco Valuepro | RSL25-1-1-7-19R | 1 | 7 | 300 | 125VAC | 30 | 1.46 x 1.22 | 0.285 | 0.5 | Round | Solder | \$3.49 |
| 2236181 | Taiwan Alpha | SR2513-110NS | 1 | 10 | 300 | 125VAC | 30 | 1.36 x 1.22 | 0.235 | 0.437 | D Flat Side | PCB | \$1.75 |
| 576501 | C&K | A11215RNZQ | 1 | 12 | 2.5/350 | 125VAC/250VAC | 30 | 2.63 x 1.12 | 0.245 | 1.5 | D Flat Side | Solder | \$6.95 |
| 2236201 | Taiwan Alpha | SR2513-112NS | 1 | 12 | 300 | 125VAC | 30 | 1.36 x 1.22 | 0.235 | 0.437 | D Flat Side | PCB | \$1.75 |
| 101532 | Jameco Valuepro | G3SR026-R | 1 | 12 | 300/300 | 125VAC/30VDC | 30 | 1.57 x 1.19 | 0.235 | 0.5 | Slotted Knurl | Solder | \$1.95 |
| 2167322 | Jameco Valuepro | KC52A13.00NPS | 1 | 12 | 350/150 | 125VAC/250VAC | 30 | 1.53 x 1.10 | 0.235 | 0.45 | D Flat Side | PCB | \$1.95 |
| 2276455 | NKK Switches | MRB24H | 2 | 3 | 400 | 28VDC | 45 | 0.62 x 0.64 | 0.09 | 0.393 | D Flat Side | PCB/Right Angle | \$7.95 |
| 2236199 | Taiwan Alpha | SR2513-24NS | 2 | 4 | 300 | 125VAC | 30 | 1.36 x 1.22 | 0.235 | 0.437 | D Flat Side | PCB | \$1.75 |
| 2281543 | Grayhill | 71BD36-01-2-AJN | 2 | 5 | 250 | 115VAC | 36 | 1.45 x 0.69 | 0.25 | 0.375 | D Flat Side | Solder | \$18.95 |
| 2170353 | Jameco Valuepro | SR2511F-25FN | 2 | 5 | 300 | 125VAC | 30 | 1.56 x 1.22 | 0.245 | 0.75 | D Flat Side | Solder | \$2.95 |
| 2236236 | Lorlin Electronics | CK2407 | 2 | 6 | 1/150 | 24VDC/250VAC | 30 | 1.54 x 1.08 | 0.245 | 0.375 | D Flat Side | Solder | \$1.95 |
| 576421 | C&K | A20615RNZQ | 2 | 6 | 2500 | 125VAC | 30 | 1.50 x .874 | 0.3 | 1.5 | D Flat Side | Solder | \$6.95 |
| 101574 | Jameco Valuepro | G3SR022-R | 2 | 6 | 300/300 | 125VAC/30VDC | 45 | 1.57 x 1.19 | 0.235 | 0.5 | Slotted Knurl | Solder | \$1.95 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Number of Poles | Number of Positions | Max Current (mA) | Voltage Rating | Index Angle (Deg) | Size (Length x Diameter) (inch) | Shaft Diameter (inch) | Shaft Length (inch) | Shaft Type | Terminal Type | Price 1 |
|-------------------------|--------------------|---------------------|-----------------|---------------------|------------------|----------------|-------------------|---------------------------------|-----------------------|---------------------|---------------|---------------|---------|
| 2236228 | Lorlin Electronics | CK1026 | 3 | 4 | 1/150 | 24VDC/250VAC | 30 | 2.30 x 1.08 | 0.245 | 1.15 | D Flat Side | Solder | \$2.95 |
| 2267695 | Mountain Switch | 105SR251334NS | 3 | 4 | 300 | 125VAC | 30 | 1.36 x 1.22 | 0.235 | 0.437 | D Flat Side | PCB | \$1.75 |
| 101566 | Jameco Valuepro | G3SR023-R | 3 | 4 | 300/300 | 125VAC/30VDC | 45 | 1.57 x 1.19 | 0.235 | 0.5 | Slotted Knurl | Solder | \$1.95 |
| 2236244 | Taiwan Alpha | SR2513-43NS | 4 | 3 | 300 | 125VAC | 30 | 1.36 x 1.22 | 0.235 | 0.437 | D Flat Side | PCB | \$1.59 |
| 101558 | Jameco Valuepro | G3SR024-R | 4 | 3 | 300/300 | 125VAC/30VDC | 30 | 1.51 x 1.19 | 0.235 | 0.5 | Slotted Knurl | Solder | \$1.95 |