



[Click Here to Request a Large Quantity Quote](#)

Terminals-Terminals

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Product Depth (inch)	Product Length (inch)	Wire Gauge (AWG)	Gender	Insulation	Color	Stud Size	Plating	Body Material	Price 1
303247	TE Connectivity	640923-1	Quick Connect	0.11	0.8	22-18	Female	Nylon	Red	N/A	Tin	Brass	\$0.25
106922	Jameco Valuepro	FDV1-187(8)-R	Quick Connect	0.187	0.748	22-16	Female	Vinyl	Red	N/A	Tin	Brass	\$0.12
459188	Molex	19003-0107	Quick Connect	0.187	0.78	22-18	Female	Nylon	Red	N/A	Tin	Brass	\$0.25
2276991	Molex	19007-0001	Quick Connect	0.236	0.585	22-18	Female	Nylon	Red	N/A	Tin	Brass	\$0.39
103668	Jameco Valuepro	FDV1-250-R	Quick Connect	0.25	0.787	22-16	Female	Vinyl	Red	N/A	Tin	Brass	\$0.15
2284943	TYCO Power Systems	42100-2	Quick Connect	0.25	0.84	18-14	Female	Non-Insulated	Natural	N/A	Tin	Brass	\$0.25
109112	Jameco Valuepro	GFF1250-R	Quick Connect	0.295	0.866	22-16	Female	Vinyl	Red	N/A	Tin	Brass	\$0.12
303327	TE Connectivity	640905-1	Quick Connect	0.3	0.92	16-14	Female	Nylon	Blue	N/A	Tin	Brass	\$0.25
489694	Molex	19003-0050	Quick Connect	0.316	0.78	16-14	Female	Nylon 6/6	Blue	N/A	Tin	Brass	\$0.29
489643	Molex	19003-0017	Quick Connect	0.316	0.78	22-18	Female	Nylon 6/6	Red	N/A	Tin	Brass	\$0.29
489635	Molex	19003-0011	Quick Connect	0.316	0.78	22-18	Female	Nylon 6/6	Salmon	N/A	Tin	Brass	\$0.19
460040	Molex	19002-0024	Quick Connect	0.32	0.8	16-14	Female	Nylon	Blue	N/A	Tin	Brass	\$0.25
524197	TE Connectivity	2-520182-2	Quick Connect	0.336	0.865	22-18	Female	Nylon	Red	N/A	Tin	Brass	\$0.19
489678	Molex	19003-0040	Quick Connect	0.38	0.86	16-14	Female	Nylon 6/6	Blue	N/A	Tin	Brass	\$0.19
489627	Molex	19003-0001	Quick Connect	0.38	0.86	22-18	Female	Nylon 6/6	Red	N/A	Tin	Brass	\$0.19
489766	Molex	19005-0005	Quick Connect	0.38	0.89	16-14	Female	Nylon	Blue/Natural	N/A	Tin	Brass	\$0.25
489774	Molex	19005-0010	Quick Connect	0.38	1.04	12-10	Female	Nylon	Yellow	N/A	Tin	Brass	\$0.39
489731	Molex	19004-0005	Quick Connect	0.45	0.97	16-14	Male	Nylon	Blue	N/A	Zinc Chromate	Copper	\$0.35
489723	Molex	19004-0001	Quick Connect	0.45	0.97	22-18	Male	Nylon	Red	N/A	Zinc Chromate	Copper	\$0.25
2284951	TE Connectivity	63860-1	Quick Connect PCB	0.247	0.512	N/A	Male	Non-Insulated	Natural	N/A	Tin	Brass	\$0.25
752464	TE Connectivity	42822-2	Quick Connect PCB	0.295	0.402	N/A	Male	Non-Insulated	Natural	8-6	Tin	Steel	\$0.15
2150897	Keystone Electronics	1287	Quick Connect PCB	0.312	0.622	N/A	Male	Non-Insulated	Natural	N/A	Tin	Brass	\$0.25

Jameco Part #	Manufacturer	Manufacturer Part #	Product Type	Product Depth (inch)	Product Length (inch)	Wire Gauge (AWG)	Gender	Insulation	Color	Stud Size	Plating	Body Material	Price 1
103684	Jameco Valuepro	RVS1-3.7-R	Ring Tongue	0.217	0.689	22-16	N/A	Vinyl	Red	6	Tin	Copper	\$0.21
844254	TE Connectivity	34105	Ring Tongue	0.218	0.449	22-16	N/A	Non-Insulated	Natural	6	Tin	Copper	\$0.15
302720	TE Connectivity	320619	Ring Tongue	0.25	0.703	16-14	N/A	Nylon	Blue	6	Tin	Copper	\$0.25
844289	TE Connectivity	34107	Ring Tongue	0.281	0.574	22-16	N/A	Non-Insulated	Natural	6	Tin	Copper	\$0.25
302666	TE Connectivity	36152	Ring Tongue	0.281	0.797	22-16	N/A	Nylon	Red	6	Tin	Copper	\$0.29
2144681	Panduit Corporation	PV10-8R-D	Ring Tongue	0.311	1.051	12-10	N/A	Non-Insulated	Yellow	8	Tin	Copper	\$0.25
302674	TE Connectivity	31890	Ring Tongue	0.312	0.844	22-16	N/A	Nylon	Red	8	Tin	Copper	\$0.25
302738	TE Connectivity	320565	Ring Tongue	0.343	0.859	16-14	N/A	Nylon	Blue	8	Tin	Copper	\$0.25
2285527	Panduit Corporation	PN10-10R-D	Ring Tongue	0.382	1.059	12-10	N/A	Nylon	Yellow	10	Tin	Copper	\$0.29
103588	Jameco Valuepro	SVS1-3.7-R	Spade Tongue	0.224	0.827	22-16	Male	Vinyl	Red	6	Tin	Copper	\$0.15
2129764	ETCO	PS55-130-THB	Spade Tongue	0.245	0.52	26-22	Male	Non-Insulated	Natural	6	Tin	Brass	\$0.25
2160577	Jameco Valuepro	SNYDL1-3.7/34541	Spade Tongue	0.248	0.888	22-16	Male	Nylon	Red	6	Tin	Copper	\$0.15
2160631	Jameco Valuepro	SNBL1-3.7/323127	Spade Tongue	0.25	0.628	22-16	Male	Non-Insulated	Natural	6	Tin	Copper	\$0.12
302877	TE Connectivity	34541	Spade Tongue	0.25	0.846	22-16	Male	Nylon	Red	6	Tin	Copper	\$0.25
2160585	Jameco Valuepro	SNYDLL2-3.7/35559	Spade Tongue	0.285	0.899	16-14	Male	Nylon	Blue	8	Tin	Copper	\$0.15
303010	TE Connectivity	320862	Spade Tongue	0.294	0.737	16-14	Male	Nylon	Blue	8	Tin	Copper	\$0.15
302906	TE Connectivity	35559	Spade Tongue	0.297	0.753	16-14	Male	Nylon	Blue	6	Tin	Copper	\$0.22
502879	Molex	19144-0001	Spade Tongue	0.316	0.915	22-18	Male	Polyvinyl Chloride	Red	6	Tin	Copper	\$0.25
2234151	Arndt	4FRJ6	Spade Tongue	0.32	0.86	16-14	Male	Vinyl	Blue	10	Tin	Copper	\$0.25
2231881	Panduit Corporation	PV10-10LFB-2K	Spade Tongue	0.34	1.04	12-10	Male	Vinyl	Yellow	10	Tin	Copper	\$0.25
303183	TE Connectivity	320562	Splice	0.14	1.265	16-14	Female	Nylon	Blue	N/A	Tin	Copper	\$0.59
303175	TE Connectivity	320559	Splice	0.207	1.265	22-16	Female	Nylon	Red	N/A	Tin	Copper	\$0.49
844107	TE Connectivity	34070	Splice	0.21	1.076	22-16	Female	Nylon	Red	N/A	Tin	Copper	\$0.25
169747	Excel Cell Electronics	ECT UYZ	Splice	0.34	0.486	26-22	Female	Polypropylene	Yellow	N/A	Tin	Plastic	\$0.25
2239154	Jameco Valuepro	878101	Splice	0.373	0.78	18-14	Female	Polypropylene	Blue	N/A	Tin	Brass	\$0.15